




L1-BS




L2-GND




L3-GND




L4-L2









Through Holes						
Symbol	Diameter	Tolerance	Plated	Type	HoleName	Quantity
A	Ø.0079		Yes	Drill	Rnd 200	305
B	Ø.0276		Yes	Drill	Rnd 700	40
H	Ø.0315		Yes	Drill	Rnd 800	63
Δ	Ø.1299		Yes	Drill	Rnd 3.300	3

