




\* SURFACE - AIR 0 MM

L1: TOP CONDUCTOR - COPPER 0.035 MM

\* DIELECTRIC - FR-4 0.73 MM

L2: BOTTOM CONDUCTOR - COPPER 0.035 MM

\* SURFACE - AIR 0 MM



DRILL CHART: TOP to BOTTOM			
ALL UNITS ARE IN MILLIMETERS			
FIGURE	SIZE	PLATED	QTY
⊙	0.3	PLATED	52
■	0.9	NON-PLATED	2