

TAPE AND REEL INFORMATION

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE


*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|------------------|------------------|-----------------|------|-----|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TL2575-05IKTTR | DDPAK/ TO-263 | KTT | 5 | 500 | 330.0 | 24.4 | 10.75 | 14.85 | 5.0 | 16.0 | 24.0 | Q2 |
| TL2575-12IKTTR | DDPAK/ TO-263 | KTT | 5 | 500 | 330.0 | 24.4 | 10.75 | 14.85 | 5.0 | 16.0 | 24.0 | Q2 |
| TL2575-15IKTTR | DDPAK/ TO-263 | KTT | 5 | 500 | 330.0 | 24.4 | 10.8 | 16.3 | 5.11 | 16.0 | 24.0 | Q2 |
| TL2575-33IKTTR | DDPAK/ TO-263 | KTT | 5 | 500 | 330.0 | 24.4 | 10.75 | 14.85 | 5.0 | 16.0 | 24.0 | Q2 |
| TL2575-ADJIKTTR | DDPAK/ TO-263 | KTT | 5 | 500 | 330.0 | 24.4 | 10.75 | 14.85 | 5.0 | 16.0 | 24.0 | Q2 |
| TL2575HV-05IKTTR | DDPAK/ TO-263 | KTT | 5 | 500 | 330.0 | 24.4 | 10.75 | 14.85 | 5.0 | 16.0 | 24.0 | Q2 |
| TL2575HV-12IKTTR | DDPAK/ TO-263 | KTT | 5 | 500 | 330.0 | 24.4 | 10.75 | 14.85 | 5.0 | 16.0 | 24.0 | Q2 |
| TL2575HV-15IKTTR | DDPAK/ TO-263 | KTT | 5 | 500 | 330.0 | 24.4 | 10.8 | 16.3 | 5.11 | 16.0 | 24.0 | Q2 |
| TL2575HV-15IKTTR | DDPAK/ TO-263 | KTT | 5 | 500 | 330.0 | 24.4 | 10.75 | 14.85 | 5.0 | 16.0 | 24.0 | Q2 |

| Device | Package Type | Package Drawing | Pins | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------------|------------------|-----------------|------|-----|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| TL2575HV-33IKTTR | DDPAK/ TO-263 | KTT | 5 | 500 | 330.0 | 24.4 | 10.8 | 16.3 | 5.11 | 16.0 | 24.0 | Q2 |
| TL2575HV-33IKTTR | DDPAK/ TO-263 | KTT | 5 | 500 | 330.0 | 24.4 | 10.8 | 16.1 | 4.9 | 16.0 | 24.0 | Q2 |
| TL2575HV-ADJIKTTR | DDPAK/ TO-263 | KTT | 5 | 500 | 330.0 | 24.4 | 10.75 | 14.85 | 5.0 | 16.0 | 24.0 | Q2 |

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|-------------------|--------------|-----------------|------|-----|-------------|------------|-------------|
| TL2575-05IKTTR | DDPAK/TO-263 | KTT | 5 | 500 | 356.0 | 356.0 | 45.0 |
| TL2575-12IKTTR | DDPAK/TO-263 | KTT | 5 | 500 | 356.0 | 356.0 | 45.0 |
| TL2575-15IKTTR | DDPAK/TO-263 | KTT | 5 | 500 | 340.0 | 340.0 | 38.0 |
| TL2575-33IKTTR | DDPAK/TO-263 | KTT | 5 | 500 | 356.0 | 356.0 | 45.0 |
| TL2575-ADJIKTTR | DDPAK/TO-263 | KTT | 5 | 500 | 356.0 | 356.0 | 45.0 |
| TL2575HV-05IKTTR | DDPAK/TO-263 | KTT | 5 | 500 | 356.0 | 356.0 | 45.0 |
| TL2575HV-12IKTTR | DDPAK/TO-263 | KTT | 5 | 500 | 356.0 | 356.0 | 45.0 |
| TL2575HV-15IKTTR | DDPAK/TO-263 | KTT | 5 | 500 | 340.0 | 340.0 | 38.0 |
| TL2575HV-15IKTTR | DDPAK/TO-263 | KTT | 5 | 500 | 356.0 | 356.0 | 45.0 |
| TL2575HV-33IKTTR | DDPAK/TO-263 | KTT | 5 | 500 | 340.0 | 340.0 | 38.0 |
| TL2575HV-33IKTTR | DDPAK/TO-263 | KTT | 5 | 500 | 350.0 | 334.0 | 47.0 |
| TL2575HV-ADJIKTTR | DDPAK/TO-263 | KTT | 5 | 500 | 356.0 | 356.0 | 45.0 |

TUBE


*All dimensions are nominal

| Device | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (µm) | B (mm) |
|-----------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| TL2575-05IKV | KV | TO-220 | 5 | 50 | 534 | 32.7 | 700 | 15.6 |
| TL2575-05IN | N | PDIP | 16 | 25 | 506 | 13.97 | 11230 | 4.32 |
| TL2575-12IKV | KV | TO-220 | 5 | 50 | 534 | 32.7 | 700 | 15.6 |
| TL2575-12IN | N | PDIP | 16 | 25 | 506 | 13.97 | 11230 | 4.32 |
| TL2575-15IKV | KV | TO-220 | 5 | 50 | 534 | 32.7 | 700 | 15.6 |
| TL2575-15IN | N | PDIP | 16 | 25 | 506 | 13.97 | 11230 | 4.32 |
| TL2575-33IKV | KV | TO-220 | 5 | 50 | 534 | 32.7 | 700 | 15.6 |
| TL2575-33IN | N | PDIP | 16 | 25 | 506 | 13.97 | 11230 | 4.32 |
| TL2575-ADJIKV | KV | TO-220 | 5 | 50 | 534 | 32.7 | 700 | 15.6 |
| TL2575-ADJIN | N | PDIP | 16 | 25 | 506 | 13.97 | 11230 | 4.32 |
| TL2575HV-05IKV | KV | TO-220 | 5 | 50 | 534 | 32.7 | 700 | 15.6 |
| TL2575HV-05IN | N | PDIP | 16 | 25 | 506 | 13.97 | 11230 | 4.32 |
| TL2575HV-12IKV | KV | TO-220 | 5 | 50 | 534 | 32.7 | 700 | 15.6 |
| TL2575HV-12IN | N | PDIP | 16 | 25 | 506 | 13.97 | 11230 | 4.32 |
| TL2575HV-15IKV | KV | TO-220 | 5 | 50 | 534 | 32.7 | 700 | 15.6 |
| TL2575HV-15IN | N | PDIP | 16 | 25 | 506 | 13.97 | 11230 | 4.32 |
| TL2575HV-33IKV | KV | TO-220 | 5 | 50 | 534 | 32.7 | 700 | 15.6 |
| TL2575HV-33IN | N | PDIP | 16 | 25 | 506 | 13.97 | 11230 | 4.32 |
| TL2575HV-ADJIKV | KV | TO-220 | 5 | 50 | 534 | 32.7 | 700 | 15.6 |
| TL2575HV-ADJIN | N | PDIP | 16 | 25 | 506 | 13.97 | 11230 | 4.32 |