

## TAPE AND REEL INFORMATION



### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



\*All dimensions are nominal

| Device            | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| CDC6CE025000ADLER | VSON         | DLE             | 4    | 3000 | 330.0              | 12.4               | 2.8     | 3.5     | 1.2     | 4.0     | 12.0   | Q1            |
| CDC6CE025000ADLET | VSON         | DLE             | 4    | 250  | 180.0              | 12.4               | 2.8     | 3.5     | 1.2     | 4.0     | 12.0   | Q1            |
| CDC6CE025000ADLFR | VSON         | DLF             | 4    | 3000 | 180.0              | 8.4                | 2.25    | 2.8     | 1.1     | 4.0     | 8.0    | Q1            |
| CDC6CE025000ADLFT | VSON         | DLF             | 4    | 250  | 180.0              | 8.4                | 2.25    | 2.8     | 1.1     | 4.0     | 8.0    | Q1            |
| CDC6CE025000ADLYR | VSON         | DLY             | 4    | 3000 | 180.0              | 8.4                | 1.45    | 1.9     | 1.07    | 4.0     | 8.0    | Q1            |

**TAPE AND REEL BOX DIMENSIONS**


\*All dimensions are nominal

| Device            | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-------------------|--------------|-----------------|------|------|-------------|------------|-------------|
| CDC6CE025000ADLER | VSON         | DLE             | 4    | 3000 | 367.0       | 367.0      | 35.0        |
| CDC6CE025000ADLET | VSON         | DLE             | 4    | 250  | 182.0       | 182.0      | 20.0        |
| CDC6CE025000ADLFR | VSON         | DLF             | 4    | 3000 | 182.0       | 182.0      | 20.0        |
| CDC6CE025000ADLFT | VSON         | DLF             | 4    | 250  | 182.0       | 182.0      | 20.0        |
| CDC6CE025000ADLYR | VSON         | DLY             | 4    | 3000 | 182.0       | 182.0      | 20.0        |