

**TAPE AND REEL INFORMATION**

**QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE**


\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
TPS922052DMTR	VSON	DMT	14	3000	330.0	12.4	3.3	4.8	1.2	8.0	12.0	Q1
TPS922052DRRR	WSON	DRR	12	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2
TPS922052DYR	SOT-23-THIN	DYY	14	3000	330.0	12.4	4.8	3.6	1.6	8.0	12.0	Q3
TPS922053DMTR	VSON	DMT	14	3000	330.0	12.4	3.3	4.8	1.2	8.0	12.0	Q1
TPS922053DRRR	WSON	DRR	12	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2
TPS922053DYR	SOT-23-THIN	DYY	14	3000	330.0	12.4	4.8	3.6	1.6	8.0	12.0	Q3
TPS922054DMTR	VSON	DMT	14	3000	330.0	12.4	3.3	4.8	1.2	8.0	12.0	Q1
TPS922054DRRR	WSON	DRR	12	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2
TPS922054MDMTR	VSON	DMT	14	3000	330.0	12.4	3.3	4.8	1.2	8.0	12.0	Q1
TPS922055DMTR	VSON	DMT	14	3000	330.0	12.4	3.3	4.8	1.2	8.0	12.0	Q1
TPS922055DRRR	WSON	DRR	12	3000	330.0	12.4	3.3	3.3	1.1	8.0	12.0	Q2
TPS922055MDMTR	VSON	DMT	14	3000	330.0	12.4	3.3	4.8	1.2	8.0	12.0	Q1

**TAPE AND REEL BOX DIMENSIONS**


\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
TPS922052DMTR	VSON	DMT	14	3000	367.0	367.0	35.0
TPS922052DRRR	WSON	DRR	12	3000	367.0	367.0	35.0
TPS922052DYR	SOT-23-THIN	DYY	14	3000	336.6	336.6	31.8
TPS922053DMTR	VSON	DMT	14	3000	367.0	367.0	35.0
TPS922053DRRR	WSON	DRR	12	3000	367.0	367.0	35.0
TPS922053DYR	SOT-23-THIN	DYY	14	3000	336.6	336.6	31.8
TPS922054DMTR	VSON	DMT	14	3000	367.0	367.0	35.0
TPS922054DRRR	WSON	DRR	12	3000	367.0	367.0	35.0
TPS922054MDMTR	VSON	DMT	14	3000	367.0	367.0	35.0
TPS922055DMTR	VSON	DMT	14	3000	367.0	367.0	35.0
TPS922055DRRR	WSON	DRR	12	3000	367.0	367.0	35.0
TPS922055MDMTR	VSON	DMT	14	3000	367.0	367.0	35.0