


- * SURFACE - AIR 0 MM
- L1: TOP CONDUCTOR - COPPER 0.035 MM
- * DIELECTRIC - FR-4 0.175 MM
- L2: L2 PLANE - COPPER 0.018 MM
- * DIELECTRIC - FR-4 1.14 MM
- L3: L3 PLANE - COPPER 0.018 MM
- * DIELECTRIC - FR-4 0.175 MM
- L4: BOTTOM CONDUCTOR - COPPER 0.035 MM
- * SURFACE - AIR 0 MM

DESIGN CROSS SECTION CHART
TOTAL THICKNESS 1.596 MM



DRILL CHART: TOP to BOTTOM			
ALL UNITS ARE IN MILLIMETERS			
FIGURE	SIZE	PLATED	QTY
◉	0.2	PLATED	261
⊙	0.2	PLATED	25
·	0.4	PLATED	21
△	1.501	NON-PLATED	4