

TMS320C5535 eZdsp™ USB Development Kit



Key features and benefits

- Small form factor DSP development kit for the C5535 processor
- TMS320C5535 fixed-point ultra-low-power DSP
- Embedded XDS100 emulator
- 8-MB serial Flash memory
- TLV320AIC3204 programmable low-power stereo audio codec
- USB 2.0 high speed
- Micro SD card slot with 2-GB micro SD card
- Line in/Mic in, headphone out audio jacks
- Earphone with mic
- 60-pin expansion connector
- 96 × 16-pixel OLED display
- Two push buttons
- Includes Code Composer Studio™ IDE 4.0
- Software framework for USB audio class and HID applications
- Out-of-the-box demo software
- Full documentation with source code on CD-ROM

The TMDX5535eZdsp is a small form factor, very-low-cost USB-powered DSP development kit which includes hardware and software needed to evaluate the C553x generation, which is the industry's lowest-cost and lowest-power 16-bit DSP. This ultra-low-cost kit allows quick and easy evaluation of the advanced capabilities of the C5532, C5533, C5534 and C5535 processors. The kit has an on-board XDS100 emulator for full source-level debug capability and supports Code Composer Studio™ (CCStudio) Integrated

Development Environment (IDE) version 4.0 and eXpressDSP™ software which includes the DSP/BIOS™ kernel. The full contents of the Development Kit include C5535 eZdsp board, CCStudio IDE Rev. 4.0, a headphone with mic, a 2-GB micro SD card, a free software framework for USB audio class and human interface device (HID) applications and an out-of-the-box comprehensive demo for USB audio class applications.

Technical details

The C5535 eZdsp USB kit simplifies development by providing integrated features including:

- Complete Code Composer Studio v4 IDE for fast code development
- On-board XDS100 v2 emulator provides complete debugging capabilities and visibility inside the processor for algorithm optimization and benchmarking
- On-board audio codec and connectors allow developers to evaluate the C5535 processor and quickly optimize complex DSP algorithms in terms of performance and power consumption across a variety of design scenarios
- Energy-efficient C5535 DSP allows the entire development tool to be powered by the USB port – no other components or cables are needed
- Rich set of features including LCD 96 × 16 monochrome OLED display screen, MicroSD card slot, USB 2.0 port for applications, *Bluetooth*®/Chipcon expansion connector

Software


Designers can readily target the TMS320C5532/33/34/35 DSP through TI's robust and comprehensive Code Composer Studio IDE, including:



- A complete Integrated Development Environment, an efficient optimizing C/C++ compiler assembler, linker, debugger, integrated CodeWright editor with CodeSense technology for faster code creation, data visualization, a profiler and a flexible project manager
- DSP/BIOS™ real-time kernel
- Chip Support Library
- Free, integrated software framework for USB audio class and HID applications, including an out-of-the-box demo

Community support

The eZdsp USB kit is supported by TI's online community e2e.ti.com. Complete collateral, CCStudio IDE drivers, Chip Support Library (CSL) and all the required production-quality



documentation for the DSP is available today. Complete schematics and layout files are available for the tool at <http://support.spectrumdigital.com/boards/ezdsp5535/revb/>, so customers can use this as a reference for their own system development.

Various examples in audio/musical special effects, digital filter design, USB audio class with HID and many others will also be available in the community. Special pricing incentives are available for educators, university students

and developers that actively participate in the community. e2e.ti.com/code.google.com/p/c5535-ezdsp/

Get started today

The feature-rich C5535 eZdsp™ USB Development Kit (part number: TMDX5535eZdsp) is available now for the low cost of U.S. \$99. Pricing includes the full XDS100 v2 emulator and the industry-leading CCStudio v.4 IDE as well as pre-loaded

demo software. To celebrate this momentous achievement, a one-time promotional price of just U.S. \$55 is offered for 55 days starting August 30, 2011. To order, please visit www.ti.com/c5535ezdsp.

The TMS320C553x DSP generation is supported by TI's extensive Developer Network, as well as a complete Chip Support Library, comprehensive application notes, reference designs, application guides, videos and online communities.

TI Worldwide Technical Support

Internet

TI Semiconductor Product Information Center Home Page
support.ti.com

TI E2E™ Community Home Page
e2e.ti.com

Product Information Centers

Americas	Phone	+1(972) 644-5580
Brazil	Phone	0800-891-2616
Mexico	Phone	0800-670-7544
	Fax	+1(972) 927-6377
	Internet/Email	support.ti.com/sc/pic/americas.htm

Europe, Middle East, and Africa

Phone	
European Free Call	00800-ASK-TEXAS (00800 275 83927)
International	+49 (0) 8161 80 2121
Russian Support	+7 (4) 95 98 10 701

Note: The European Free Call (Toll Free) number is not active in all countries. If you have technical difficulty calling the free call number, please use the international number above.

Fax	+ (49) (0) 8161 80 2045
Internet	support.ti.com/sc/pic/euro.htm
Direct Email	asktexas@ti.com

Japan

Phone	Domestic	0120-92-3326
Fax	International	+81-3-3344-5317
	Domestic	0120-81-0036
Internet/Email	International	support.ti.com/sc/pic/japan.htm
	Domestic	www.tij.co.jp/pic

Asia

Phone	
International	+91-80-41381665
Domestic	Toll-Free Number
Note: Toll-free numbers do not support mobile and IP phones.	
Australia	1-800-999-084
China	800-820-8682
Hong Kong	800-96-5941
India	1-800-425-7888
Indonesia	001-803-8861-1006
Korea	080-551-2804
Malaysia	1-800-80-3973
New Zealand	0800-446-934
Philippines	1-800-765-7404
Singapore	800-886-1028
Taiwan	0800-006800
Thailand	001-800-886-0010
Fax	+8621-23073686
Email	tiasia@ti.com or ti-china@ti.com
Internet	support.ti.com/sc/pic/asia.htm

Important Notice: The products and services of Texas Instruments Incorporated and its subsidiaries described herein are sold subject to TI's standard terms and conditions of sale. Customers are advised to obtain the most current and complete information about TI products and services before placing orders. TI assumes no liability for applications assistance, customer's applications or product designs, software performance, or infringement of patents. The publication of information regarding any other company's products or services does not constitute TI's approval, warranty or endorsement thereof.

B122010

The platform bar, C55x, Code Composer Studio, DSP/BIOS, E2E and eXpressDSP are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Mobile Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated