

Parts List

515500-0002R

ASSY,DRV8302-HC-C2 MOTOR BOARD

SUBA

Type	PL	PCB Package
Revision	D	ION Footprint
Status	U	Package Qty 1
Date	10/7/2011	Bin Loc.
By		SUBA

Item	Qty Unit	Part Number	Type Rev	Title Detail	Reference
		ION Footprint		Mfr P/N	Mfr Name

1	1 each	515501-0001R	DWG D	PWB,DRV830X-HC-C2 MOTOR BOARD CSTM	
---	-----------	--------------	----------	---------------------------------------	--

2	1 each	515502-0001	DOC D	LOGIC,DRV830X-HC-C2 MOTOR BOARD SCH	
---	-----------	-------------	----------	--	--

4	1 each	103742-0001R	PS	IC,TSSOP16,TRANSLATOR,6-BIT MATL	U7 TXB0106PWR Texas Instruments
		pw16-14x70			

5	1 each	103808-0002R	PS	IC,TSSOP56,THREE PHASE PRE-DRIVER MATL	U1 DRV8302DCA Texas Instruments
---	-----------	--------------	----	---	---------------------------------------

7	2 each	103805-0001R	PS	IC,SOT23-5,OP AMP MATL	U13, U9 OPA365AIDBVR Texas Instruments
		dbv-20x60-5			

8	1 each	103806-0001R	PS	IC,SOIC,HIGH SPEED QUAD DIGITAL MATL	U5 ISO7241ADW Texas Instruments
		dw16-25x75-375			

9	1 each	103518-0001R	PS	IC,SMT8,ISOLATED CAN TRANSCEIVER MATL	U4 ISO1050DUBR Texas Instruments
		dub8-35x90			

10	1 each	103743-0001R	PS	IC,DBV6,DUAL SCHMITT-TRIGGER BUFFER MATL	U6 SN74LVC2G17DBVR Texas Instruments
		dbv6-27x39-6			

11	2 each	103807-0033R	PS	IC,DBV5,LDO REGULATOR,3.3V,400mA MATL	U3, U8 TPS73633MDBVREP Texas Instruments
		dbv-20x60-5			

Parts List

ASSY,DRV8302-HC-C2 MOTOR BOARD
SUBA

515500-0002R

Rev D

Printed 2/15/2012

Item	Qty Unit	Part Number	Type Rev	Title Detail	Reference
ION Footprint				Mfr P/N	Mfr Name
12	1 each	103739-0005R	PS	POWER MODULE,5V,1W,ADJUSTABLE MATL DCH010505SN7	U2 Texas Instruments
15	2 each	103825-0001R	PS	TRANSISTOR,SOT23,MOSFET,150V,530mA MATL SI2325DS-T1-E3	Q1, Q2 Vishay Intertechnology
16	1 each	103824-0001R	PS	TRANSISTOR,SOT23,MOSFET,N CHANNEL MATL 2N7002E,215	Q3 NXP Semiconductors
17	6 each	103810-0001R	PS	TRANSISTOR,TO263,MOSFET,60V,110A MATL SUM110N06-3M9H-E3	Q4, Q5, Q6, Q7, Q8, Q9 Vishay Intertechnology
18	3 each	103952-0001R	PS	IC,SO5,OP AMP,1.8V MATL TLV2781IDBVR	U10, U11, U12 Texas Instruments
20	1 each	103820-0001R	PS	DIODE,SMT,SCHOTTKY,2A,100V MATL CDBB2100-G	D1 Comchip Technology
25	5 each	103827-0002R	PS	LED,SMT 0805,GREEN MATL LTST-C170KGKT	LED1, LED10, LED11, LED12, LED3 LITEON
26	1 each	103827-0001R	PS	LED,SMT 0805,SUPER RED MATL LTST-C170KRKT	LED6 LITEON
27	1 each	103330-0003R	PS	LED,SMT 0805,YELLOW MATL LTST-C171YKT	LED5 LITEON
30	1 each	103135-0331R	PS	INDUCTOR,SMT,33uH MATL DR74-330-R	L1 Coiltronics Incorporated

Parts List

ASSY,DRV8302-HC-C2 MOTOR BOARD
SUBA

515500-0002R

Rev D

Printed 2/15/2012

Item	Qty Unit	Part Number	Type Rev	Title Detail	Reference
ION Footprint				Mfr P/N	Mfr Name
40	1 each	103818-0222R	PS	CAP,ELEC,SMT,220uF,10V MATL EEE-1AA221XP	C57 Panasonic
45	2 each	103819-0332R	PS	CAP,ELEC,RADIAL,330uF,100V,20% MATL UVZ2A331MHD	C93, C94 Nichicon Corporation
46	1 each	103817-0103R	PS	CAP,ELEC,RADIAL,1000uF,100V,20% MATL ECA-2AHG102	C50 Panasonic
50	1 each	103815-0471R c1210-70x102	PS	CAP,CER,SMT 1210,47uF,16V,X5R,+/-20% MATL EMK325BJ476MM-T	C11 Taiyo Yuden
51	5 each	103814-0220R c1210-70x102	PS	CAP,CER,SMT 1210,2.2uF,100V,X7R,+/-10% MATL C3225X7R2A225K	C6, C7, C81, C82, C83 TDK Corporation
55	1 each	101415-0220R c805-35x60	PS	CAP,CER,SMT 0805,2.2uF,25V,X7R,10% MATL 08053C225KAT2A	C14 AVX Corporation
56	3 each	103813-1100R c805-35x60	PS	CAP,CER,SMT 0805,.1uF,100V,+10/-10%,X7R MATL C0805C104K1RACTU	C5, C51, C8 Kemet Electronics Corporation
58	1 each	100993-1682R c603-35x45	PS	CAP,CER,SMT 0603,6800pF,50V,+/-10%,X7R MATL ECJ-1VB1H682K	C1 Panasonic
59	1 each	101002-1394R c603-35x45	PS	CAP,CER,SMT 0603,39pF,50V,+/-5%,NPO MATL ECJ-1VC1H390J	C2 Panasonic
60	5 each	102965-0220R c603-35x45	PS	CAP,CER,SMT 0603,2.2uF,10V,+/-10%,X7R MATL GRM188R71A225KE15D	C20, C22, C44, C46, C48 Murata Electronics

Parts List

ASSY,DRV8302-HC-C2 MOTOR BOARD
SUBA

515500-0002R

Rev D

Printed 2/15/2012

Item	Qty Unit	Part Number	Type Rev	Title Detail	Reference
ION Footprint				Mfr P/N	Mfr Name
61	5 each	103594-0100R c603-35x45	PS	CAP,CER,SMT 0603,1uF,25V,+/-10%,X5R MATL GRM188R61E105KA12D	C10, C12, C15, C19, C23 Murata Electronics
62	4 each	103816-1470R c603-35x45	PS	CAP,CER,SMT 0603,.47uF,25V,+/-10%,X7R MATL GRM188R71E474KA12D	C29, C30, C31, C33 Murata Electronics
63	28 each	100993-1100R c603-35x45	PS	CAP,CER,SMT 0603,.1uF,50V,+/-10%,X7R MATL 06035C104KAT2A	C13, C16, C17, C18, C21, C24, C25, C26, C27, C28, C32, C34, C35, C42, C43, C45, C47, C58, C59, C67, C68, C69, C72, C74, C76, C77, C85, C9 AVX Corporation
64	1 each	100993-1221R c603-35x45	PS	CAP,CER,SMT 0603,.022uF,50V,+/-10%,X7R MATL GRM188R71H223KA01D	C3 Murata Electronics
65	1 each	102482-1101R c603-35x45	PS	CAP,CER,SMT 0603,.01uF,100V,+/-10%,X7R MATL C1608X7R2A103K	C53 TDK Corporation
66	1 each	100993-1151R c603-35x45	PS	CAP,CER,SMT 0603,.015uF,50V,+/-10%,X7R MATL ECJ-1VB1H153K	C4 Panasonic
67	12 each	100993-1102R c603-35x45	PS	CAP,CER,SMT 0603,.001uF,50V,+/-10%,X7R MATL 06035C102KAT2A	C36, C37, C38, C39, C40, C41, C75, C78, C79, C80, C84, C98 AVX Corporation
75	1 each	103811-1003R	PS	POT,12mm SQ,10K,1/8 WATT,SINGLE TURN MATL 296UD103B1N	R28 CTS Electronics Corporation
80	14 each	100687-0001R r603-35X45	PS	RES,SMT 0603,0 OHM,1/16 WATT MATL ERJ-3GEY0R00V	R109, R110, R111, R112, R117, R130, R133, R134, R135, R5, R50, R91, R97, R98 Panasonic

Parts List

ASSY,DRV8302-HC-C2 MOTOR BOARD
SUBA

515500-0002R

Rev D

Printed 2/15/2012

Item	Qty Unit	Part Number	Type Rev	Title Detail	Reference
		ION Footprint		Mfr P/N	Mfr Name
81	7 each	100687-0100R r603-35X45	PS	RES,SMT 0603,1 OHM,5%,1/16 WATT MATL ERJ-3RQJ1R0V	R66, R67, R68, R69, R70, R71, R8 Panasonic
82	1 each	100642-1000R r603-35x45	PS	RES,SMT 0603,10 OHM,1%,1/16 WATT MATL ERJ-3EKF10R0V	R87 Panasonic
84	1 each	100687-1201R r603-35X45	PS	RES,SMT 0603,120 OHM,5%,1/16 WATT MATL ERJ-3GEYJ121V	R17 Panasonic
85	11 each	100687-1002R r603-35X45	PS	RES,SMT 0603,1K OHM,5%,1/16 WATT MATL RC0603JR-071KL	R12, R13, R21, R29, R30, R31, R32, R33, R34, R43, R47 Yageo
86	1 each	100687-8201R r603-35X45	PS	RES,SMT 0603,820 OHM,5%,1/16 WATT MATL ERJ-3GEYJ821V	R49 Panasonic
87	4 each	100687-4701R r603-35X45	PS	RES,SMT 0603,470 OHM,5%,1/16 WATT MATL ERJ-3GEYJ471V	R20, R22, R23, R26 Panasonic
88	5 each	100687-3301R r603-35X45	PS	RES,SMT 0603,330 OHM,5%,1/16 WATT MATL ERJ-3GEYJ331V	R14, R15, R18, R24, R27 Panasonic
91	1 each	100642-1004R r603-35x45	PS	RES,SMT 0603,100K OHM,1%,1/16 WATT MATL RC0603FR-07100KL	R40 Yageo
92	1 each	100642-1963R r603-35x45	PS	RES,SMT 0603,19.6K OHM,1%,1/16 WATT MATL ERJ-3EKF1962V	R41 Panasonic
93	5 each	100642-1003R r603-35x45	PS	RES,SMT 0603,10K OHM,1%,1/16 WATT MATL ERJ-3EKF1002V	R10, R11, R7, R9, R44 Panasonic

Parts List

ASSY,DRV8302-HC-C2 MOTOR BOARD
SUBA

515500-0002R

Rev D

Printed 2/15/2012

Item	Qty Unit	Part Number	Type Rev	Title Detail	Reference
		ION Footprint		Mfr P/N	Mfr Name
94	1 each	100642-2054R r603-35x45	PS	RES,SMT 0603,205K OHM,1%,1/16 WATT MATL ERJ-3EKF2053V	R1 Panasonic
95	1 each	100642-2803R r603-35x45	PS	RES,SMT 0603,28K OHM,1%,1/16 WATT MATL ERJ-3EKF2802V	R4 Panasonic
96	13 each	100642-4992R r603-35x45	PS	RES,SMT 0603,4.99K OHM,1%,1/16 WATT MATL ERJ-3EKF4991V	R122, R123, R124, R125, R126, R127, R19, R25, R36, R48, R62, R64, R65 Panasonic
97	2 each	100642-4993R r603-35x45	PS	RES,SMT 0603,49.9K OHM,1%,1/16 WATT MATL ERJ-3EKF4992V	R128, R129 Panasonic
98	1 each	100642-5363R r603-35x45	PS	RES,SMT 0603,53.6K OHM,1%,1/16 WATT MATL ERJ-3EKF5362V	R6 Panasonic
99	4 each	100642-9533R r603-35x45	PS	RES,SMT 0603,95.3K OHM,1%,1/16 WATT MATL ERJ-3EKF9532V	R35, R60, R61, R63 Panasonic
101	6 each	103951-2003R r603-35x45	PS	RES,SMT 0603,20K OHM, .1%,1/10 WATT MATL ERA-3AEB203V	R103, R105, R107, R108, R113, R95 Panasonic
102	2 each	103951-1003R r603-35x45	PS	RES,SMT 0603,10K OHM, .1%,1/10 WATT MATL ERA-3AEB103V	R37, R38 Panasonic
103	6 each	103951-1002R r603-35x45	PS	RES,SMT 0603,1K OHM, .1%,1/10 WATT MATL ERA-3AEB102V	R99, R101, R104, R92, R94, R102 Panasonic
106	1 each	100155-0100R r1206-40x70	PS	RES,SMT 1206,1 OHM,5%,1/4 WATT MATL ERJ-8GEYJ1R0V	R16 Panasonic

Parts List

ASSY,DRV8302-HC-C2 MOTOR BOARD
SUBA

515500-0002R

Rev D

Printed 2/15/2012

Item	Qty Unit	Part Number	Type Rev	Title Detail	Reference
		ION Footprint		Mfr P/N	Mfr Name
108	1 each	100155-0330R	PS	RES,SMT 1206,3.3 OHM,5%,1/4 WATT MATL ERJ-8GEYJ3R3V	R39 Panasonic
		r1206-40x70			
110	3 each	103809-0002R	PS	RES,SMT 4527,.002 OHM,1%,5W MATL WSR52L000FEA	R80, R81, R82 Vishay Intertechnology
115	2 each	102984-0001R	PS	SWITCH,SMT,PUSHBUTTON,MOMENTARY,4mm MATL 7914J-1-000E	SW1, SW2 Bourns
		sw4-50x70-7914J			
120	2 each	103823-0002R	PS	TERMINAL BLOCK,2 POS.,VERT.,15mm SPC.,90A MATL 39920-0502	J25, J26 Molex
121	1 each	103821-0002R	PS	TERMINAL BLOCK,2 POS.,VERT.,5mm SPC. MATL ED500/2DS	J2 On-Shore Technology, Inc.
122	1 each	103823-0004R	PS	TERMINAL BLOCK,4 POS.,VERT.,15mm SPC.,90A MATL 39920-0504	J11 Molex
125	1 each	102232-0100R	PS	CONN,100 PIN,DIMM SOCKET,W/EXTRACTORS MATL 87630-1001	J1 Molex
		molex100-71251-5101			
129	6 each	100115-0002R	PL	HEADER,2 X 1,VERTICAL,PIN SUBA	J12, J13, J23, J24, JP2, JP4
		JUMP1X2-6040			
130	1 each	100115-0003R	PL	HEADER,3 X 1,VERTICAL,PIN SUBA	J7
		JUMP1X3-6040			
133	4 each	100115-0005R	PL	HEADER,5 X 1,VERTICAL,PIN SUBA	J10, J4, J6, J8
		JUMP1X5-6040			

Parts List

ASSY,DRV8302-HC-C2 MOTOR BOARD
SUBA

515500-0002R

Rev D

Printed 2/15/2012

Item	Qty Unit	Part Number	Type Rev	Title Detail	Reference
		ION Footprint		Mfr P/N	Mfr Name
134	1 each	100116-0005R JUMP2X5-6040	PL	HEADER,5 X 2,VERTICAL,PIN SUBA 2011-2X05G00SB/SN	J20 Oupiin
135	1 each	100116-0007R JUMP2X7-6040	PL	HEADER,7 X 2,VERTICAL,PIN SUBA 2011-2X07G00SB/SN	J21 Oupiin
136	1 each	100116-0020R conn40-5638	PL	HEADER,20 X 2,VERTICAL,PIN SUBA	J5
145	10 each	103020-5003R	PS	TEST POINT,ORANGE MATL 5003	TP12, TP13, TP14, TP16, TP17, TP19, TP23, TP24, TP25, TP3 Keystone Electronics Corp.
146	4 each	103020-5000R	PS	TEST POINT,RED MATL 5000	TP11, TP4, TP5, TP6 Keystone Electronics Corp.
147	5 each	103020-5001R	PS	TEST POINT,BLACK MATL 5001	TP10, TP20, TP7, TP8, TP9 Keystone Electronics Corp.
150	2 each	100123-0001R	PS	JUMPER,SHUNT,2 POS MATL SPC02SYAN	JP2, JP4 Sullins Electronics, Corp.
151	8 each	100329-0250R	PS	SCREW,PHILLIPS,PAN,SS,4-40 X .250 MATL 0440X0250PNPHSSPS	XXMH1, XXMH2, XXMH3, XXMH4, XXMH5, XXMH6, XXMH7, XXMH8 Above Board Electronics,Inc.
152	8 each	103812-0875R	PS	SPACER,ROUND,ALUM,4-40,.187 O.D. X .875L MATL 2030	XXMH1, XXMH2, XXMH3, XXMH4, XXMH5, XXMH6, XXMH7, XXMH8 Keystone Electronics Corp.
155	8 each	C0603-NOPOP c603-35x45	PS	NP	C52, C86, C87, C88, C95, C96, C97, C73

Parts List

ASSY,DRV8302-HC-C2 MOTOR BOARD
SUBA

515500-0002R

Rev D

Printed 2/15/2012

Item	Qty Unit	Part Number	Type Rev	Title Detail	Reference
		ION Footprint		Mfr P/N	Mfr Name
160	7 each	R0603-NOPOP	PS	NP	R2, R3, R42, R45, R46, R119, R132
		r603-35X45			
170	1 each	NO-POP	PS	NP	D2
200	6 each	TP-27SQ15-NO-POP	PS	NP	TP1, TP15, TP18, TP2, TP21, TP22