

Data sheet acquired from Harris Semiconductor SCHS171D

# CD54HC257, CD74HC257, CD54HCT257, CD74HCT257

## High-Speed CMOS Logic Quad 2-Input Multiplexer with Three-State Non-Inverting Outputs

November 1997 - Revised October 2003

## Features

- Buffered Inputs
- Typical Propagation Delay ( In to Output ) = 12ns at  $V_{CC}$  = 5V, C<sub>L</sub> = 15pF, T<sub>A</sub> = 25<sup>o</sup>C
- Fanout (Over Temperature Range)
  - Standard Outputs......10 LSTTL Loads
- Bus Driver Outputs ...... 15 LSTTL Loads
- Wide Operating Temperature Range ... -55°C to 125°C
- Balanced Propagation Delay and Transition Times
- Significant Power Reduction Compared to LSTTL Logic ICs
- HC Types
  - 2V to 6V Operation
  - High Noise Immunity: NIL = 30%, NIH = 30% of V<sub>CC</sub> at V<sub>CC</sub> = 5V
- HCT Types
  - 4.5V to 5.5V Operation
  - Direct LSTTL Input Logic Compatibility, V<sub>IL</sub>= 0.8V (Max), V<sub>IH</sub> = 2V (Min)
  - CMOS Input Compatibility, II  $\leq$  1µA at VOL, VOH

## Description

The 'HC257 and 'HCT257 are quad 2-input multiplexers which select four bits of data from two sources under the control of a common Select Input (S). The Output Enable input ( $\overline{OE}$ ) is active LOW. When  $\overline{OE}$  is HIGH, all of the outputs (1Y-4Y) are in the high impedance state regardless of

all other input conditions.


Moving data from two groups of registers to four common output buses is a common use of the 257. The state of the Select input determines the particular register from which the data comes. It can also be used as a function generator.

## **Ordering Information**

PART NUMBER	TEMP. RANGE ( <sup>o</sup> C)	PACKAGE
CD54HC257F3A	-55 to 125	16 Ld CERDIP
CD54HCT257F3A	-55 to 125	16 Ld CERDIP
CD74HC257E	-55 to 125	16 Ld PDIP
CD74HC257M	-55 to 125	16 Ld SOIC
CD74HC257MT	-55 to 125	16 Ld SOIC
CD74HC257M96	-55 to 125	16 Ld SOIC
CD74HCT257E	-55 to 125	16 Ld PDIP
CD74HCT257M	-55 to 125	16 Ld SOIC
CD74HCT257MT	-55 to 125	16 Ld SOIC
CD74HCT257M96	-55 to 125	16 Ld SOIC

NOTE: When ordering, use the entire part number. The suffix 96 denotes tape and reel. The suffix T denotes a small-quantity reel of 250.

## Pinout



"이 드	
11 <sub>1</sub> 3	14 4I <sub>0</sub>
1Y 4	13 4I <sub>1</sub>
2l <sub>0</sub> 5	12 4Y
2l <sub>1</sub> 6	11 3I <sub>0</sub>
2Y 7	10 3I <sub>1</sub>
GND 8	9 3Y

CAUTION: These devices are sensitive to electrostatic discharge. Users should follow proper IC Handling Procedures.

Copyright © 2003, Texas Instruments Incorporated

#### Functional Diagram 0E 0<sup>15</sup> s 0 41<sub>1</sub> o<u>13</u> . 12 **-0** 4Y <u>م14</u> Ν 4I<sub>0</sub> I 10 9 3l<sub>1</sub> **-0** 3Y 0 11 3I<sub>0</sub> 0 6 2I<sub>1</sub> **3 CIRCUITS IDENTICAL TO CIRCUIT** 0 7 -0 2Y 5 IN ABOVE DASHED ENCLOSURE 2l<sub>0</sub> o 3 1I<sub>1</sub> • 2 4 **-0** 1Y 1I<sub>0</sub> •

### TRUTH TABLE

OUTPUT ENABLE	SELECT INPUT	DATA I	NPUTS	OUTPUT
ŌĒ	S	I <sub>0</sub>	Y	
н	Х	Х	Х	Z
L	L	L	Х	L
L	L	Н	Х	Н
L	Н	Х	L	L
L	Н	Х	Н	Н

H= High Voltage Level

L= Low Voltage Level

X= Don't Care

Z= High Impedance, OFF State

### **Absolute Maximum Ratings**

DC Supply Voltage, V <sub>CC</sub>
For $V_1 < -0.5V$ or $V_1 > V_{CC} + 0.5V$
DC Output Diode Current, I <sub>OK</sub>
For $V_0 < -0.5V$ or $V_0 > V_{CC} + 0.5V$
DC Drain Current, per Output, I <sub>O</sub>
For -0.5V < V <sub>O</sub> < V <sub>CC</sub> + 0.5V±35mA
DC Output Source or Sink Current per Output Pin, IO
For $V_0 > -0.5V$ or $V_0 < V_{CC} + 0.5V$ ±25mA
DC V <sub>CC</sub> or Ground Current, I <sub>CC</sub> ±70mA

### **Operating Conditions**

Temperature Range, $T_A$
Supply Voltage Range, V <sub>CC</sub>
HC Types
HCT Types4.5V to 5.5V
DC Input or Output Voltage, VI, VO 0V to VCC
Input Rise and Fall Time
2V
4.5V 500ns (Max)
6V

### **Thermal Information**

Thermal Resistance (Typical, Note 1)	θ <sub>JA</sub> ( <sup>o</sup> C/W)
E (PDIP) Package	67
M (SOIC) Package	73
Maximum Junction Temperature	150 <sup>0</sup> C
Maximum Storage Temperature Range	65 <sup>0</sup> C to 150 <sup>0</sup> C
Maximum Lead Temperature (Soldering 10s)	
(SOIC - Lead Tips Only)	

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

#### NOTE:

1. The package thermal impedance is calculated in accordance with JESD 51-7.

## **DC Electrical Specifications**

			ST ITIONS		25 <sup>0</sup> C			-40°C TO 85°C		-55°C TO 125°C		
PARAMETER	SYMBOL	V <sub>I</sub> (V)	I <sub>O</sub> (mA)	V <sub>CC</sub> (V)	MIN	TYP	MAX	MIN	MAX	MIN	MAX	UNITS
HC TYPES			-						-	_	-	-
High Level Input	V <sub>IH</sub>	-	-	2	1.5	-	-	1.5	-	1.5	-	V
Voltage				4.5	3.15	-	-	3.15	-	3.15	-	V
				6	4.2	-	-	4.2	-	4.2	-	V
Low Level Input	V <sub>IL</sub>	-	-	2	-	-	0.5	-	0.5	-	0.5	V
Voltage				4.5	-	-	1.35	-	1.35	-	1.35	V
				6	-	-	1.8	-	1.8	-	1.8	V
High Level Output	V <sub>OH</sub>	V <sub>IH</sub> or V <sub>IL</sub>	-0.02	2	1.9	-	-	1.9	-	1.9	-	V
Voltage CMOS Loads			-0.02	4.5	4.4	-	-	4.4	-	4.4	-	V
			-0.02	6	5.9	-	-	5.9	-	5.9	-	V
High Level Output			-6	4.5	3.98	-	-	3.84	-	3.7	-	V
Voltage TTL Loads			-7.8	6	5.48	-	-	5.34	-	5.2	-	V
Low Level Output	V <sub>OL</sub>	V <sub>IH</sub> or	0.02	2	-	-	0.1	-	0.1	-	0.1	V
Voltage CMOS Loads		VIL	0.02	4.5	-	-	0.1	-	0.1	-	0.1	V
			0.02	6	-	-	0.1	-	0.1	-	0.1	V
Low Level Output			6	4.5	-	-	0.26	-	0.33	-	0.4	V
Voltage TTL Loads			7.8	6	-	-	0.26	-	0.33	-	0.4	V
Input Leakage Current	Ц	V <sub>CC</sub> or GND	-	6	-	-	±0.1	-	±1	-	±1	μA

## CD54HC257, CD74HC257, CD54HCT257, CD74HCT257

PARAMETER		TEST CONDITIONS				25 <sup>0</sup> C			ГО 85 <sup>0</sup> С	-55 <sup>о</sup> С Т		
	SYMBOL	V <sub>I</sub> (V)	I <sub>O</sub> (mA)	V <sub>CC</sub> (V)	MIN	ТҮР	MAX	MIN	MAX	MIN	MAX	UNITS
Quiescent Device Current	ICC	V <sub>CC</sub> or GND	0	6	-	-	8	-	80	-	160	μA
Three-State Leakage Current	I <sub>OZ</sub>	V <sub>IL</sub> or V <sub>IH</sub>	-	6	-	-	±0.5	-	±5	-	±10	μA
HCT TYPES												
High Level Input Voltage	VIH	-	-	4.5 to 5.5	2	-	-	2	-	2	-	V
Low Level Input Voltage	VIL	-	-	4.5 to 5.5	-	-	0.8	-	0.8	-	0.8	V
High Level Output Voltage CMOS Loads	V <sub>OH</sub>	V <sub>IH</sub> or V <sub>IL</sub>	-0.02	4.5	4.4	-	-	4.4	-	4.4	-	V
High Level Output Voltage TTL Loads			-6	4.5	3.98	-	-	3.84	-	3.7	-	V
Low Level Output Voltage CMOS Loads	V <sub>OL</sub>	V <sub>IH</sub> or V <sub>IL</sub>	0.02	4.5	-	-	0.1	-	0.1	-	0.1	V
Low Level Output Voltage TTL Loads			6	4.5	-	-	0.26	-	0.33	-	0.4	V
Input Leakage Current	lı	V <sub>CC</sub> to GND	0	5.5	-	-	±0.1	-	±1	-	±1	μA
Quiescent Device Current	I <sub>CC</sub>	V <sub>CC</sub> or GND	0	5.5	-	-	8	-	80	-	160	μA
Additional Quiescent Device Current Per Input Pin: 1 Unit Load	ΔI <sub>CC</sub> (Note 2)	V <sub>CC</sub> -2.1	-	4.5 to 5.5	-	100	360	-	450	-	490	μA
Three-State Leakage Current	I <sub>OZ</sub>	V <sub>IL</sub> or V <sub>IH</sub>	-	5.5	-	-	±0.5	-	±5	-	±10	μΑ

NOTE:

2. For dual-supply systems theoretical worst case (VI = 2.4V, V<sub>CC</sub> = 5.5V) specification is 1.8mA.

## **HCT Input Loading Table**

INPUT	UNIT LOADS
Data	0.95
S	3
ŌĒ	0.6

NOTE: Unit Load is  $\Delta I_{CC}$  limit specified in DC Electrical Specifications table, e.g., 360µA max at 25°C.


# CD54HC257, CD74HC257, CD54HCT257, CD74HCT257

### Switching Specifications Input tr, tf = 6ns

		TEST		25	°C	-40°C TO 85°C	-55°C TO 125°C		
PARAMETER	SYMBOL	CONDITIONS	V <sub>CC</sub> (V)	ТҮР	MAX	МАХ	МАХ		
HC TYPES									
Propagation Delay In to Y	t <sub>PLH</sub> , t <sub>PHL</sub>	C <sub>L</sub> = 50pF	2	-	150	190	225	ns	
			4.5	-	30	38	45	ns	
		C <sub>L</sub> = 15pF	5	12	-	-	-	ns	
		CL = 50pF	6	-	26	33	38	ns	
Propagation Delay	tPLH, tPHL	C <sub>L</sub> = 50pF	2	-	175	220	265	ns	
S to Y			4.5	-	35	44	53	ns	
		C <sub>L</sub> = 15pF	5	14	-	-	-	ns	
		CL = 50pF	6	-	30	37	45	ns	
Propagation Delay	t <sub>PLZ</sub> , t <sub>PHZ</sub> ,	CL = 50pF	2	-	150	190	225	ns	
OE to Y	<sup>t</sup> PZL <sup>, t</sup> PZH	C <sub>L</sub> = 50pF	4.5	-	30	38	45	ns	
		C <sub>L</sub> = 15pF	5	12	-	-	-	ns	
		CL = 50pF	6	-	26	33	38	ns	
Output Transition Times	t <sub>TLH</sub> , t <sub>THL</sub>	C <sub>L</sub> = 50pF	2	-	60	75	90	ns	
			4.5	-	12	15	18	ns	
			6	-	10	13	15	ns	
Input Capacitance	CI	-	-	-	10	10	10	pF	
Three-State Output Capacitance	CO	-	-	-	20	20	20	pF	
Power Dissipation Capacitance (Notes 3, 4)	C <sub>PD</sub>	-	5	45	-	-	-	pF	
HCT TYPES									
Propagation Delay In to Y	t <sub>PLH</sub> , t <sub>PHL</sub>	$C_L = 50 pF$	4.5	-	33	41	50	ns	
		C <sub>L</sub> = 15pF	5	13	-	-	-	ns	
Propagation Delay	t <sub>PZL</sub> , t <sub>PZH</sub>	$C_L = 50 pF$	4.5	-	38	48	57	ns	
S to Y		C <sub>L</sub> = 15pF	5	12	-	-	-	ns	
Propagation Delay	t <sub>PLZ</sub> , t <sub>PHZ</sub>	C <sub>L</sub> = 50pF	4.5	-	30	38	45	ns	
OE to Y		C <sub>L</sub> = 15pF	5	16	-	-	-	ns	
Output Transition Times	t <sub>TLH</sub> , t <sub>THL</sub>	C <sub>L</sub> = 50pF	4.5	-	12	15	18	ns	
Input Capacitance	Cl	-	-	-	10	10	10	pF	
Three-State Output Capacitance	CO	-	-	-	20	20	20	pF	
Power Dissipation Capacitance (Notes 3, 4)	C <sub>PD</sub>	-	5	45	-	-	-	pF	

NOTES:

3.  $C_{PD}$  is used to determine the dynamic power consumption, per multiplexer. 4.  $P_D = V_{CC}^2 f_i (C_{PD} + C_L)$  where  $f_i$  = Input Frequency,  $C_L$  = Output Load Capacitance,  $V_{CC}$  = Supply Voltage.



#### FIGURE 5. HC AND HCT THREE-STATE PROPAGATION DELAY TEST CIRCUIT



## PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
5962-8970501EA	ACTIVE	CDIP	J	16	25	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	5962-8970501EA CD54HCT257F3A	Samples
CD54HC257F3A	ACTIVE	CDIP	J	16	25	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	8512401EA CD54HC257F3A	Samples
CD54HCT257F3A	ACTIVE	CDIP	J	16	25	Non-RoHS & Green	SNPB	N / A for Pkg Type	-55 to 125	5962-8970501EA CD54HCT257F3A	Samples
CD74HC257E	ACTIVE	PDIP	Ν	16	25	RoHS & Green	NIPDAU	N / A for Pkg Type	-55 to 125	CD74HC257E	Samples
CD74HC257M	OBSOLETE	SOIC	D	16		TBD	Call TI	Call TI	-55 to 125	HC257M	
CD74HC257M96	ACTIVE	SOIC	D	16	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	HC257M	Samples
CD74HCT257E	ACTIVE	PDIP	N	16	25	RoHS & Green	NIPDAU	N / A for Pkg Type	-55 to 125	CD74HCT257E	Samples
CD74HCT257M	OBSOLETE	SOIC	D	16		TBD	Call TI	Call TI	-55 to 125	HCT257M	
CD74HCT257M96	ACTIVE	SOIC	D	16	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-55 to 125	HCT257M	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**ROHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.



#### www.ti.com

## PACKAGE OPTION ADDENDUM

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

#### OTHER QUALIFIED VERSIONS OF CD54HC257, CD54HCT257, CD74HC257, CD74HCT257 :

- Catalog : CD74HC257, CD74HCT257
- Military : CD54HC257, CD54HCT257

#### NOTE: Qualified Version Definitions:

- Catalog TI's standard catalog product
- Military QML certified for Military and Defense Applications



Texas

www.ti.com

## TAPE AND REEL INFORMATION





### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	-	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CD74HC257M96	SOIC	D	16	2500	330.0	16.4	6.5	10.3	2.1	8.0	16.0	Q1
CD74HCT257M96	SOIC	D	16	2500	330.0	16.4	6.5	10.3	2.1	8.0	16.0	Q1



www.ti.com

# PACKAGE MATERIALS INFORMATION

25-Sep-2024



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
CD74HC257M96	SOIC	D	16	2500	340.5	336.1	32.0
CD74HCT257M96	SOIC	D	16	2500	353.0	353.0	32.0

## TEXAS INSTRUMENTS

www.ti.com

25-Sep-2024

## TUBE



## - B - Alignment groove width

### \*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
CD74HC257E	N	PDIP	16	25	506	13.97	11230	4.32
CD74HC257E	N	PDIP	16	25	506	13.97	11230	4.32
CD74HCT257E	N	PDIP	16	25	506	13.97	11230	4.32
CD74HCT257E	N	PDIP	16	25	506	13.97	11230	4.32

J (R-GDIP-T\*\*) 14 LEADS SHOWN

CERAMIC DUAL IN-LINE PACKAGE



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- C. This package is hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
- E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.

# N (R-PDIP-T\*\*)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



NOTES:

- A. All linear dimensions are in inches (millimeters).B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- $\triangle$  The 20 pin end lead shoulder width is a vendor option, either half or full width.



D (R-PDSO-G16)

PLASTIC SMALL OUTLINE



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.
- Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.
- E. Reference JEDEC MS-012 variation AC.



## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated