

***AB-6 COPS Interrupts***



Literature Number: SNOA580

# COPS™ Interrupts

National Semiconductor  
Application Brief 6  
Jim Murashige  
April 1983



This brief describes in detail the timing requirements pertinent to COPS interrupts. *Figure 1* shows a typical enable-interrupt sequence in relation to the SK (Instruction Cycle) Clock. The SK clock is actually derived from the  $\phi 1$  clock which is 180° out of phase with the  $\phi 2$  clock. It is the  $\phi 1$  and  $\phi 2$  clocks to which all operation is referenced but for our purposes the SK will suffice. Program instructions are read on a rising  $\phi 1$  edge and executed during the  $\phi 1, \phi 2$  cycle time. Here we see the EN register interrupt enable bit EN2 being set with an LEI instruction. Interrupts are actually enabled on the  $\phi 2$  leading edge of the second byte of the instruction point ②. Timing for an INTERRUPT DISABLE is essentially the same.

The interrupt line is sampled on the leading edge of  $\phi 1$  as shown and interrupts are recognized if the minimum setup and hold times shown are satisfied. Note that the guaranteed times are longer than the typicals. The interrupt signal conditioning circuitry contains a falling edge detection circuit (a one shot) which requires that in addition to meeting the setup and hold times, the enable interrupt bit EN1 must have been turned on sometime before the end of the WINDOW of OPPORTUNITY shown. If not, the interrupt will be missed and another high to low IN1 transition will be required. EN1 is automatically disabled upon interrupt recognition at point ⑤. Note that although the interrupt is recog-

nized at point ④ it will not be acted upon until all successive transfer of control instructions are executed as defined in the data sheets.

Because of gate delays it is doubtful that if an interrupt had been generated in time to meet the leading  $\phi 1$  edge at point ② that the EN1 enable bit would have been on in time to meet the WINDOW of OPPORTUNITY.

By doing a worst case analysis one can see that in order to guarantee reception of an asynchronous interrupt IN1 must remain low for at least 2 instruction cycles. The analysis is as follows. Assuming that interrupts had been enabled prior to point ①, if the interrupt arrives a little after point ① it will not satisfy the minimum setup requirements bringing us up to a point ③ our total elapsed time becomes ③ - ① = 2  $t_{CYC}$ .

In a dual COPS the interrupt sequence is the same except that now an instruction cycle time is made up of both a Processor X and a Processor Y instruction execution cycle. With one  $\phi 1$  and  $\phi 2$  clock per processor execution cycle the instruction cycle time is made up of 2  $\phi 1$ 's and  $\phi 2$ 's. Therefore 1 instruction cycle time in a dual COPS is equivalent to 2 instruction cycle times in a single COPS as far as  $\phi 1$ 's,  $\phi 2$ 's and interrupts are concerned.




FIGURE 1. COP Interrupt Diagram

TL/DD/5180-1

Parameter	Min	Typ	Max
$t_s$	$\frac{1}{2} t_{CYC}$	200 ns	
$t_n$	$\frac{1}{2} t_{CYC}$	200 ns	
$t_{wo}$	$-\infty$	$\frac{1}{2} t_{CYC} - 600$ ns	0

**LIFE SUPPORT POLICY**

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.



**National Semiconductor Corporation**  
 1111 West Bardin Road  
 Arlington, TX 76017  
 Tel: 1(800) 272-9959  
 Fax: 1(800) 737-7018

**National Semiconductor Europe**  
 Fax: (+49) 0-180-530 85 86  
 Email: cnjwge@tevm2.nsc.com  
 Deutsch Tel: (+49) 0-180-530 85 85  
 English Tel: (+49) 0-180-532 78 32  
 Français Tel: (+49) 0-180-532 93 58  
 Italiano Tel: (+49) 0-180-534 16 80

**National Semiconductor Hong Kong Ltd.**  
 19th Floor, Straight Block,  
 Ocean Centre, 5 Canton Rd.  
 Tsimshatsui, Kowloon  
 Hong Kong  
 Tel: (852) 2737-1600  
 Fax: (852) 2736-9960

**National Semiconductor Japan Ltd.**  
 Tel: 81-043-299-2309  
 Fax: 81-043-299-2408

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
OMAP Mobile Processors	<a href="http://www.ti.com/omap">www.ti.com/omap</a>
Wireless Connectivity	<a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a>

### Applications

Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Transportation and Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2011, Texas Instruments Incorporated