


# GC5325

## Wideband digital pre-distortion transmit IC solution



### Product Bulletin

The Texas Instruments GC5325 wireless transmit processor integrates digital radio functionality previously only available in discrete devices. The GC5325 linearizes the output of the power amplifier (PA) in the transmit signal chain, thus removing the need for more costly high-performance PA components, improving the PA's power efficiency and decreasing the overall power consumption of the base station. High-performance PAs can account for as much as 30 percent of the operational costs of a wireless base station in today's cellular infrastructure. The GC5325 solution gives wireless equipment manufacturers the opportunity to reduce the overall cost of their RF subsystems.

#### Integrated functionality


To optimize the overall system cost and performance of a base station, the GC5325 has integrated the critical functionality required in a wireless transmit processor. The key processing blocks in the GC5325 include CFR and DPD to linearize the output of the PA. Both CFR and DPD increase the power efficiency

of the transmit chain's multi-carrier PA. The DPD algorithm improves the adjacent channel leakage ratio (ACLR) thereby increasing PA output power while still adhering to spectral emission regulations. By integrating these two blocks into one device, the GC5325 simplifies the design of the base station RF subsystem, reduces procurement costs by minimizing chip counts, and decreases circuit board size. Additionally, the inherent flexibility of the software DPD algorithm allows the GC5325 to support multiple existing and emerging standards.

**Crest factor reduction** – Based on field-proven technology, the GC5325's CFR processing block reduces the peak-to-average ratio (PAR) for multi-channel/multi-carrier signals by adding spectrally-shaped cancellation noise. The CFR block has multiple stages, each having configurable peak thresholds. This allows for significant PAR reduction. Breakthrough power efficiencies are achieved in the PA, while maintaining spectral requirements and EVM performance.

#### Key Features

- Integrated functional transmitter blocks include:
  - Crest factor reduction (CFR) for greater PA power efficiency
  - Digital pre-distortion (DPD) for improved PA linearity
- Highly-integrated IC solution reduces design complexity, power consumption, development time, implementation size and BOM costs
- Advanced linearization solution reduces multi-carrier power amplifier design specifications by increasing PA DC operating efficiency
- Flexible DSP algorithm supports existing and emerging wireless standards
- Integrated CFR and DPD increase efficiencies to beyond 25 percent for Class AB PAs and to 40 percent or more for Doherty PAs
- Integrated DPD reduces adjacent channel leakage ratio (ACLR) by 20 dB or more and corrects up to 7th order distortion products
- Integrated IQ imbalance correction and a fully automated channel equalizer
- Extremely fast DPD convergence times, typically less than 2 seconds
- Robust convergence algorithm
- Fast time to market and reduced risk as part of a complete TI-supplied signal chain solution
- Space-saving 352-ball TE-PBGA-II 27 x 27 mm package.



▲ The GC5325 integrates crest factor reduction and digital pre-distortion to improve efficiency

**Digital pre-distortion** – To limit possible distortion in the transmit signal, the GC5325 includes an integrated DPD processing block. The DPD block linearizes the PA, greatly improving the adjacent channel leakage ratio (ACLR). This allows PAs to meet stringent spectral regulations and interference requirements. Depending upon the PA, the DPD block achieves ACLR improvements of 20 to 30 dB or more.


The GC5325 interfaces directly to TI's TMS320C6727 DSP, which executes the real-time adaptation algorithm. A real-time feedback loop monitors the integrity of the output signal to control the DPD's operation. The flexible algorithm supports multiple PA architectures and emerging standards, such as CDMA2000, WCDMA, TD-SCDMA, OFDMA (WiMAX, LTE), HSPA and HSPA+.

**Improved efficiency**


The combination of CFR and DPD functionality in the GC5325 significantly improves the efficiency of LDMOS Doherty PAs, reaching 40 percent or more, while Class AB PAs can reach efficiencies greater than 25 percent. As a result, the PA can be driven harder to yield higher output power. Smaller, less costly PAs can be used, while still ensuring the required output power level. This maximizes overall system performance and cost savings.

**Reduced power consumption**

The resulting efficiency improvement reduces RF subsystem power requirements and provides a reduction in cooling infrastructure and operating costs leading to significantly decreased operating expenses for the base station. This also helps OEMs and wireless operators to meet green initiatives for reduced power, low-energy base stations.



▲ An example of the GC5325 linearizing two 10 MHz WiMAX carriers with 47.8 dBm output power, achieving greater than 42.5% efficiency while meeting all regulatory requirements



▲ A complete dual-antenna digital pre-distortion transmit signal chain with the GC5325SEK (System Evaluation Kit), based on TI high-speed analog and DSP technology

## Complete signal chain solution


The GC5325 DPD architecture is supported by a system evaluation kit (GC5325SEK). The GC5325SEK consists of a dual-transmitter architecture, supporting transmit diversity, multiple-input and multiple-output (MIMO), and beamforming for smart antenna applications. The GC5325 uses a composite baseband input consisting of single or multiple carriers combined into a single digital signal. The fully-tested GC5325SEK is comprised of TI high-performance analog and DSP products and can be used as a reference design to shorten time to market. Since most of the transmit signal chain is provided by TI, applications support is simplified.

The TI devices that complement the GC5325 device in the transmit signal chain include the following:


- TMS320C6727B digital signal processor
- DAC5682Z dual 16-bit, 1 GSPS DAC (transmit path)
- ADS61B49 14-bit 250-MSPS ADC or ADS5517 11-bit 200-MSPS ADC (feedback path)
- CDCM7005 or CDCE72010 clock generator
- TRF3761 integrated VCO/PLL RF synthesizer
- TRF3703 quadrature modulator
- THS9000 IF amplifier
- AMC7823 analog monitoring and control circuit

## For more information

To learn more about the GC5325 wireless transmit processor and other TI products for wireless infrastructure systems, contact your local TI field sales office or see [www.ti.com/gc5325](http://www.ti.com/gc5325)



▲ GC5325SEK: TSW3100 Digital Pattern Generator Card



▲ GC5325SEK: GC5325 EVM Card

# TI Worldwide Technical Support

---

## Internet

### TI Semiconductor Product Information Center Home Page

[support.ti.com](http://support.ti.com)

### TI Semiconductor KnowledgeBase Home Page

[support.ti.com/sc/knowledgebase](http://support.ti.com/sc/knowledgebase)

## Product Information Centers

### Americas

Phone +1(972) 644-5580  
Fax +1(972) 927-6377  
Internet/Email [support.ti.com/sc/pic/americas.htm](http://support.ti.com/sc/pic/americas.htm)

### Europe, Middle East, and Africa

Phone  
European Free Call 00800-ASK-TEXAS  
(00800 275 83927)  
International +49 (0) 8161 80 2121  
Russian Support +7 (4) 95 98 10 701

**Note:** The European Free Call (Toll Free) number is not active in all countries. If you have technical difficulty calling the free call number, please use the international number above.

Fax +49 (0) 8161 80 2045  
Internet [support.ti.com/sc/pic/euro.htm](http://support.ti.com/sc/pic/euro.htm)

### Japan

Fax International +81-3-3344-5317  
Domestic 0120-81-0036  
Internet/Email International [support.ti.com/sc/pic/japan.htm](http://support.ti.com/sc/pic/japan.htm)  
Domestic [www.tij.co.jp/pic](http://www.tij.co.jp/pic)

The platform bar is a trademark of Texas Instruments. All other trademarks are the property of their respective owners.

### Asia

Phone  
International +91-80-41381665  
Domestic Toll-Free Number  
Australia 1-800-999-084  
China 800-820-8682  
Hong Kong 800-96-5941  
India 1-800-425-7888  
Indonesia 001-803-8861-1006  
Korea 080-551-2804  
Malaysia 1-800-80-3973  
New Zealand 0800-446-934  
Philippines 1-800-765-7404  
Singapore 800-886-1028  
Taiwan 0800-006800  
Thailand 001-800-886-0010  
Fax +886-2-2378-6808  
Email [tiasia@ti.com](mailto:tiasia@ti.com) or [ti-china@ti.com](mailto:ti-china@ti.com)  
Internet [support.ti.com/sc/pic/asia.htm](http://support.ti.com/sc/pic/asia.htm)

**Important Notice:** The products and services of Texas Instruments Incorporated and its subsidiaries described herein are sold subject to TI's standard terms and conditions of sale. Customers are advised to obtain the most current and complete information about TI products and services before placing orders. TI assumes no liability for applications assistance, customer's applications or product designs, software performance, or infringement of patents. The publication of information regarding any other company's products or services does not constitute TI's approval, warranty or endorsement thereof.

B010208