

Bill of Materials

TI DESIGNS

TIDM-LEDDRIVER LED BoosterPack BOM

Item	Qty	Reference	Part Description	Manufacturer	Manufacturer Part Number	Note
1	1	L1	INDUCTOR POWER 100UH .77A SMD	Wurth Electronics Inc	74477520	
2	3	L2, L3, L4	INDUCTOR POWER 220UH .30A SMD	Bourns Inc.	SRR7032-221M	
3	8	LED1, LED2, LED3, LED4, LED5, LED6, LED7, LED8	LED RGB ROUND DIFFUSED 6PLCC	TT Electronics/Optek Technology	OVSTRGBB1CR8	
		Dog Dog Dog	DEC 10 OUN 1/0W 10/ 1000 OMD		DI 1000D D100 E	
4	3	R22, R23, R33	RES .10 OHM 1/2W 1% 1206 SMD	Susumu	RL1632R-R100-F	
5	1	R5	RES .02 OHM 1W 1% 2010 SMD	Stackpole Electronics Inc	CSRN2010FK20L0	
6	3	R17, R19, R38	RESISTOR 5.1 OHM 1/10W 5% 0402	Panasonic - ECG	ERJ-2GEJ5R1X	
7	1	R1	RES 10 OHM 1/10W 5% 0402 SMD	Panasonic - ECG	ERJ-2GEJ100X	
8	2	R12, R28	RES 18 OHM 1/10W 5% 0402 SMD	Panasonic - ECG	ERJ-2GEJ180X	
9	3	R16, R18, R37	RES 33 OHM 1/10W 5% 0402 SMD	Panasonic - ECG	ERJ-2GEJ330X	
10	3	R21, R24, R32	RES 39 OHM 1/10W 5% 0402 SMD	Panasonic - ECG	ERJ-2GEJ390X	
11	3	R13, R27, R36	RES 215 OHM 1/10W 1% 0402 SMD	Panasonic - ECG	ERJ-2RKF2150X	
12	1	R9	RES 432 OHM 1/10W 1% 0402 SMD	Panasonic - ECG	ERJ-2RKF4320X	
13	1	R4	RES 475 OHM 1/10W 1% 0402 SMD	Panasonic - ECG	ERJ-2RKF4750X	
14	1	R8	RES 1.62K OHM 1/10W 1% 0402 SMD	Panasonic - ECG	ERJ-2RKF1621X	
15	3	R14, R15, R30	RES 1.91K OHM 1/10W 1% 0402 SMD	Panasonic - ECG	ERJ-2RKF1911X	
16	1	R7	RES 2.0K OHM 1/10W 5% 0402 SMD	Panasonic - ECG	ERJ-2GEJ202X	
17	4	R2, R11, R20, R31	RES 4.99K OHM 1/10W 1% 0402 SMD	Panasonic - ECG	ERJ-2RKF4991X	
18	1	R6	RES 7.32K OHM 1/10W 1% 0402 SMD	Panasonic - ECG	ERJ-2RKF7321X	
19	9	R10, R25, R26, R29, R34, R35, R39, R40, R41	RES 10K OHM 1/10W 5% 0402 SMD	Panasonic - ECG	ERJ-2GEJ103X	
20	2	R42, R43	RES 47.0K OHM 1/10W 1% 0402 SMD	Panasonic - ECG	ERJ-2RKF4702X	
21	1	R3	RES 68.1K OHM 1/10W 1% 0402 SMD	Panasonic - ECG	ERJ-2RKF6812X	
22	3	C19, C20, C26	CAP CER 82PF 50V 5% NP0 0402	Taiyo Yuden	UMK105CG820JV-F	
23	1	C8	CAP CER 220PF 50V 10% X7R 0402	Taiyo Yuden	UMK105B7221KV-F	
24	2	C3, C6	CAP CER 470PF 50V 10% X7R 0402	Taiyo Yuden	UMK105B7471KV-F	
25	1	C12	CAP CER 3300PF 50V 10% X7R 0402	Murata Electronics North America	GRM155R71H332KA01D	
26	1	C7	CAP CER 4700PF 50V 10% X7R 0402	Murata Electronics North America	GRM155R71H472KA01D	
27	1	C4	CAP CER 0.047UF 25V 10% X7R 0402	Taiyo Yuden	TMK105B7473KV-F	
28	9	C2, C5, C11, C16, C18, C24, C30, C31, C32	CAP CER 0.1UF 25V 10% X5R 0402	<u>Taiyo Yuden</u>	TMK105BJ104KV-F	
29	2	C17, C25	CAP CER 0.22UF 6.3V 10% X5R 0402	<u>Taiyo Yuden</u>	JMK105BJ224KV-F	·
30	3	C9, C33, C34	CAP CER 1UF 6.3V 10% X5R 0402	Taiyo Yuden	JMK105BJ105KV-F	

Item	Qty	Reference	Part Description	Manufacturer	Manufacturer Part Number	Note
31	1	C1	CAP CER 4.7UF 25V 10% X5R 1206	Taiyo Yuden	TMK316BJ475KD-T	
32	9	C13, C14, C15, C21, C22, C23, C27, C28, C29	CAP CER 10UF 35V 10% X5R 1210	Taiyo Yuden	GMK325BJ106KN-T	
33	1	C10	CAP CER 22UF 6.3V 20% X5R 1206	Taiyo Yuden	JMK316BJ226ML-T	
34	2	J2, J8	CONN HEADER 2POS VERT T/H	FCI	77311-118-02LF	
35	2	J6, J7	CONN HEADER 10POS .100 STR 30AU	<u>FCI</u>	68000-110HLF	
36	1	35	CONN HEADER 6POS .100 STR TIN	<u>FCI</u>	68000-406HLF	
37	2	J3 & J9, J4 & J10	CONN SOCKET DUAL VERT 20POS GOLD	<u>3M</u>	960220-6303-AR	
38	1	J11	CONN SOCKET SGL VERT 3POS GOLD	<u>3M</u>	960103-6303-AR	
39	1	S1	SWITCH DIP DPST 1POS SMT	CTS Electrocomponents	204-211ST	
40	1	J1	CONN POWER JACK 2.5X5.5MM SMD	CUI Inc	PJ-002B-SMT	
41	1		12V 1A Power Adapter			
42	2	U4, U5	IC OPAMP GP R-R 38MHZ DUAL 8SOIC	Texas Instruments	OPA2350UA	
43	1	U2	IC LDO REG 3.3V 500MA SOT223-6	Texas Instruments	TPS79533DCQR	
44	2	U3, U6	IC MOSFET DRVR DUAL HS 5A 8-SOIC	Texas Instruments	UCC27524D	
45	1	U1	IC NON-SYNC DC/DC CTRLR 8-SOIC	Texas Instruments	TPS40200DRG4	
46	1	U7	IC MCU 16BIT 8KB FLASH 20TSSOP	Texas Instruments	MSP430G2452IPW20R	
47	3	Q1, Q2, Q3	MOSFET N-CH 60V 6A DPAK	Diodes/Zetex	DMN6068LK3-13	
48	1	Q4	MOSFET P-CH 20V 1A SOT-23	ON Semiconductor	NTR1P02T1G	
49	4	D1, D2, D3, D4	DIODE SCHOTTKY 60V 2A SMB	<u>Diodes Inc</u>	B260-13-F	



Bill of Materials

TI DESIGNS

TIDM-LEDDRIVER C2000 LAUNCHPAD BOM

Item	Qty	Reference	Part Description	Manufacturer	Manufacturer Part Number	Note
1	6	R12, R13, R14, R15, R26, R27	RES 330 OHM 1/10W 5% 0402 SMD	Panasonic - ECG	ERJ-2GEJ331X	
2	4	R1, R4, R5, R17	RES 820 OHM 1/10W 5% 0402 SMD	Panasonic - ECG	ERJ-2GEJ821X	
3	2	R22, R23	RES 1.0K OHM 1/10W 5% 0402 SMD	Panasonic - ECG	ERJ-2GEJ102X	
4	5	R6, R8, R9, R10, R31	RES 2.2K OHM 1/10W 5% 0402 SMD	Panasonic - ECG	ERJ-2GEJ222X	
5	2	R11, R29	RES 10K OHM 1/10W 5% 0402 SMD	Panasonic - ECG	ERJ-2GEJ103X	
6	1	R24	RES 12K OHM 1/16W .5% 0402 SMD	Panasonic - ECG	ERA-2AED123X	
7	1	R7	RES 1.0M OHM 1/10W 5% 0402 SMD	Panasonic - ECG	ERJ-2GEJ105X	No-pop
8	9	R16, R18, R19, R20, R21, R25, R28, R30, R32	RES 0.0 OHM 1/4W 1206 SMD	Panasonic - ECG	ERJ-8GEY0R00V	
9	2	L1, L2	FERRITE BEAD 600 OHM 0402	Taiyo Yuden	BK1005HM601-T	
10	1	L3	FERRITE BEAD 220 OHM 0402	Taiyo Yuden	BKP1005HS221-T	
11	1	L4	FERRITE CHIP 60 OHM 1.5A 0402	TDK Corporation	MPZ1005S600C	
12	5	C9, C12, C13, C14, C16	CAP .10UF 16V CERAMIC Y5V 0402	<u>Yageo</u>	CC0402ZRY5V7BB104	
13	1	C7	CAP CER 1.0UF 6.3V X5R 20% 0402	TDK Corporation	C1005X5R0J105M	
14	5	C5, C6, C19, C20, C21	CAP CER 2.2UF 6.3V 20% X5R 0402	Taiyo Yuden	JMK105BJ225MV-F	
15	1	C15	CAP CER 3.3UF 4.0V X5R 0402	Taiyo Yuden	AMK105BJ335MV-F	
16	2	C10, C11	CAP CER 4.7UF 4V X5R 0402	Taiyo Yuden	AMK105BJ475MV-F	
17	2	C3, C4	CAP CER 36PF 50V C0G 0402	TDK Corporation	C1005C0G1H360J	No-pop
18	2	C17, C18	CAP CER 36PF 50V C0G 0402	TDK Corporation	C1005C0G1H360J	
19	1	C8	CAP TANTALUM 100UF 6.3V 10% SMD	Nichicon	F930J107KBA	
20	1	F1	PTC RESETTABLE .50A 15V 1812	Bourns Inc.	MF-MSMF050-2	
21	1	S1	SWITCH DIP 3POS TOP SLIDE SMT	CTS Electrocomponents	204-3ST	
22	1	S4	SWITCH DIP DPST 1POS SMT	CTS Electrocomponents	204-211ST	
23	2	S2, S3	SW TACT SPST-NO MOM 160GF SMD	TE Connectivity	FSM2JSMATR	
24	1	Q1, Q2	Crystal			No-pop
25	1	Q3	CRYSTAL 12.0000 MHZ 18PF SMD	Abracon Corporation	ABLS2-12.000MHZ-D4Y-T	
26	1	D6	LED RED HIGH BRIGHT ESS SMD	Panasonic - SSG	LNJ237W82RA	
27	1	D1	LED GREEN HIGH BRIGHT ESS SMD	Panasonic - SSG	LNJ337W83RA	
28	6	D2, D3, D4, D5, D7, D8	LED BLUE HIGH BRIGHT ESS SMD	Panasonic - SSG	LNJ937W8CRA	
29	3	JP1, JP2, JP3	BERGSTIK II .100" SR STRAIGHT	<u>FCI</u>	68001-102HLF	
30	2	J1 & J5, J2 & J6	CONN HEADER .100 DUAL STR 20POS	<u>3M</u>	929665-03-10-l	

Item	Qty	Reference	Part Description	Manufacturer	Manufacturer Part Number	Note
31	1	J3	CONN HEADER .100 SNGL STR 3POS	<u>3M</u>	929647-03-03-I	
32	1	CON1	CONN RECEPT MINI-USB TYPE B SMT	Mill-Max Manufacturing Corp.	897-43-005-00-100001	
33	1	U4	IC LDO REG 800MA 3.3V SOT223-4	<u>Texas Instruments</u>	TLV1117-33CDCYR	
34	2	U2, U3	IC BUFF/DVR DL NON-INV SOT236	Texas Instruments	SN74LVC2G07DBVR	
35	1	U5	ISOLAT DGTL 2.5KVRMS 4CH 16-SOIC	<u>Texas Instruments</u>	ISO7240CDWR	
36	1	U7	ISOLAT DGTL 3KVRMS 3CH 16-SOIC	<u>Texas Instruments</u>	ISO7231CDWR	
37	1	U6	IC USB HS DUAL UART/FIFO 64-QFN	FTDI, Future Technology Devices International Ltd	FT2232HQ-REEL	
38	1	U8	IC EEPROM 2KBIT 3MHZ SOT23-6	Microchip Technology	93LC56BT-I/OT	
39	1	U1	IC MCU 32BIT 64KB FLASH 48LQFP	Texas Instruments	TMS320F28027PTS	

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.