

Bill of Materials

TIDM-KEYBOARD F5529

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
1		C1, C2	10pF	CAP, CERM, 10pF, 50V, +/-5%, COG/NPO, 0603	Kemet	C0603C100J5GACTU		0603	
2	1	C3	0.1uF	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	Kemet	C0603C104K5RACTU		0603	
3	1	C4	4.7μF	CAP, TA, 4.7uF, 10V, +/-10%, 5 ohm, SMD	Vishay-Sprague	293D475X9010A2TE3		3216-18	
4	1	C5	4.7uF	CAP, CERM, 4.7uF, 10V, +/-10%, X5R, 0603	Kemet	C0603C475K8PACTU		0603	
5	1	C6	0.01uF	CAP, CERM, 0.01uF, 50V, +/-10%, X7R, 0603	MuRata	GRM188R71H103KA01D		0603	
6	1	C7	1uF	CAP, CERM, 1uF, 16V, +/-10%, X5R, 0603	Kemet	C0603C105K4PACTU		0603	
7		C8. C9	0.22uF	CAP, CERM, 0.22uF, 16V, +/-10%, X7R, 0603	TDK	C1608X7R1C224K080AC		0603	
8	2	C10, C11	33pF		TDK	C1608C0G1H330J080AA		0603	
9		C12, C14, C15	0.1uF	CAP, CERM, 0.1uF, 16V, +/-10%, X7R, 0603	Kemet	C0603C104K4RACTU		0603	
		C12, C14, C13	0.141	CAT, CERRIT, 0.101, 10V, 17 1070, X711, 0003	Kemet	COOCCIONANACIO		0003	
10	2	C13, C16	10uF	CAP, TA, 10uF, 10V, +/-20%, 3.4 ohm, SMD	Vishay-Sprague	293D106X0010A2TE3		3216-18	
11	1	C17	0.47uF	CAP, CERM, 0.47uF, 10V, +/-10%, X5R, 0603	Kemet	C0603C474K8PACTU		0603	
12	0	C18, C34	2200pF	CAP, CERM, 2200pF, 100V, +/-5%, X7R, 0603	AVX	06031C222JAT2A		0603	DNP_F5529
13	2	C19, C20	0.1uF	CAP, CERM, 0.1uF, 16V, +/-5%, X7R, 0603	AVX	0603YC104JAT2A		0603	
14	0	C30, C32	0.1uF	CAP, CERM, 0.1uF, 16V, +/-10%, X7R, 0603	Kemet	C0603C104K4RACTU		0603	DNP_F5529
15	0	C31, C33	10uF	CAP, TA, 10uF, 10V, +/-20%, 3.4 ohm, SMD	Vishay-Sprague	293D106X0010A2TE3		3216-18	DNP_F5529
16	3	D1, D2, D3	Green	LED, Green, SMD	Lite-On	LTST-C171GKT		LED LTST-C171	
17		D4	SD103AW-13-F	DIODE, SCHOTTKY, 0.35A, 40V, SOD-123	DIODES INC	SD103AW-13-F		D SOD123	
18		D5	LL103A-GS08	Diode, Schottky, 40V, 0.2A, 3.7x1.6x1.6mm	Vishay-Semiconductor	LL103A-GS08		SOD-80	
19	_	J1	Connector	Header (shrouded), 100 mil, 7x2, Gold, TH	Sullins Connector Solutions			CONN_SBH11-PBPC-D07-ST-BK	
20	2	J2, JP1	Connector	Header, 100mil, 3x1, Gold, TH	Samtec	TSW-103-07-G-S		TSW-103-07-G-S	
21	1	J3	Keyboard connector	CONN FPC 24POS 1MM RT ANG SMD	TE Connectivity	2-84952-4		CON24_SMT-RA_FCC	
22	2	J4, J5	Connector	Connector, Receptacle, 100mil, 10x2, Gold	Samtec	SSW-110-23-F-D		CONN_SSW-110-23-F-D	
23	1	J6	USB Connector	CONNECTOR, MICRO-USB-AB, RECEPTACLE,	HIROSE	ZX62D-AB-5P8		USB-ZX62D-AB-5P8_REVISED	
24		JP2, JP3, JP4, JP5, JP6	Jumper	Header, 100mil, 2x1, Gold, TH	Samtec	TSW-102-07-G-S		TSW-102-07-G-S	1
25		R1	1.40k	RES, 1.40k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06031K40FKEA		0603	
26		R2	1M	RES, 1.0Meg ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06031M00JNEA		0603	
27		R3, R4	27	RES, 27 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060327R0JNEA		0603	
28		R5	33k	RES, 33k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060333K0JNEA		0603	
29		R6	330	RES, 330 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW0603330RJNEA		0603	_
30		R7, R8, R9	560	RES, 560 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW0603560RJNEA		0603	1
31		R10, R11, R12, R13, R14, R15, R16	4/K	RES, 47k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060347K0JNEA	1	0603	1
32		R18, R19	2.21	RES, 0 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06030000Z0EA	1	0603	1
33 34		R21, R22 R30	2.2k 47K	RES, 2.2k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06032K20JNEA CRCW060347K0JNEA		0603 0603	DNP F5529
35	_	R31. R32	0	RES, 47k ohm, 5%, 0.1W, 0603 RES, 0 ohm, 5%, 0.1W, 0603	Vishay-Dale Vishay-Dale	CRCW06030000Z0EA	+	0603	DNP_F5529 DNP_F5529
36	_	K31, K32 U1	MSP430F5529	Mixed Signal MicroController, PN0080A	Texas Instruments	MSP430F5529IPN		PN0080A L	DINP_F3329
37	_	U2	TPD2E001DZDR	IC, LOW-CAPACITANCE 2-Chan ±15-kV ESD-	TEXAS INSTRUMENTS	TPD2E001DZDR		DZD	†
38		U3	MSP430G2744	MSP430G2744. VQFN40	Texas Instruments	MSP430G2744IRHA40R		QFN50P600X600X100-40N	DNP F5529
39	_	U4	TPS73533	Single Output High PSRR LDO, 500 mA, Fixed	Texas Instruments	TPS73533DRBT		DRB8 1P75X1P5	55525
40	_	Y1	XTAL4M	Crystal, 4MHz, 30pF, SMD	Auris-GmbH	Q- 4,000000M-HC49USSMD-F-30-30-D-16-TR	HCM49-4.000MABJT	Auris HC49USSMD	†



Bill of Materials

TIDM-KEYBOARD G2744

						Manufacturer			
Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint	Note
1		C1, C2	10pF	CAP, CERM, 10pF, 50V, +/-5%, C0G/NP0, 0603		C0603C100J5GACTU		0603	
2		C3	0.1uF	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	Kemet	C0603C104K5RACTU		0603	
3	1	C4	4.7μF	CAP, TA, 4.7uF, 10V, +/-10%, 5 ohm, SMD	Vishay-Sprague	293D475X9010A2TE3		3216-18	
4	1	C5	4.7uF	CAP, CERM, 4.7uF, 10V, +/-10%, X5R, 0603	Kemet	C0603C475K8PACTU		0603	
5	1	C6	0.01uF	CAP, CERM, 0.01uF, 50V, +/-10%, X7R, 0603	MuRata	GRM188R71H103KA01D		0603	
6	1	C7	1uF	CAP, CERM, 1uF, 16V, +/-10%, X5R, 0603	Kemet	C0603C105K4PACTU		0603	
7	0	C8, C9	0.22uF	CAP, CERM, 0.22uF, 16V, +/-10%, X7R, 0603	TDK	C1608X7R1C224K080AC		0603	DNP_G2744
8	0	C10, C11	33pF	CAP, CERM, 33pF, 50V, +/-5%, C0G/NP0, 0603		C1608C0G1H330J080AA		0603	DNP_G2744
9	0	C12, C14, C15	0.1uF	CAP, CERM, 0.1uF, 16V, +/-10%, X7R, 0603	Kemet	C0603C104K4RACTU		0603	DNP_G2744
10	0	C13, C16	10uF	CAP, TA, 10uF, 10V, +/-20%, 3.4 ohm, SMD	Vishay-Sprague	293D106X0010A2TE3		3216-18	DNP_G2744
	_								
11	0	C17	0.47uF	CAP, CERM, 0.47uF, 10V, +/-10%, X5R, 0603	Kemet	C0603C474K8PACTU		0603	DNP_G2744
4.0		040 004	2200 5	040 05044 0000 5 400V / 50/ V70 0500		05004 50004 4704		0500	
12		C18, C34	2200pF	CAP, CERM, 2200pF, 100V, +/-5%, X7R, 0603	AVX	06031C222JAT2A		0603	DNP_G2744
13		C19, C20	0.1uF	CAP, CERM, 0.1uF, 16V, +/-5%, X7R, 0603	AVX	0603YC104JAT2A		0603	
14	2	C30, C32	0.1uF	CAP, CERM, 0.1uF, 16V, +/-10%, X7R, 0603	Kemet	C0603C104K4RACTU		0603	
15	2	C31, C33	10uF	CAP, TA, 10uF, 10V, +/-20%, 3.4 ohm, SMD	Vishay-Sprague	293D106X0010A2TE3		3216-18	
16		D1, D2, D3	Green	LED, Green, SMD	Lite-On	LTST-C171GKT		LED_LTST-C171	
17	1	D4	SD103AW-13-F	DIODE, SCHOTTKY, 0.35A, 40V, SOD-123	DIODES INC	SD103AW-13-F		D_SOD123	
18	0	D5	LL103A-GS08	Diode, Schottky, 40V, 0.2A, 3.7x1.6x1.6mm	Vishay-Semiconductor	LL103A-GS08		SOD-80	DNP_G2744
19	1	J1	Connector	Header (shrouded), 100 mil, 7x2, Gold, TH	Sullins Connector Solutions	SBH11-PBPC-D07-ST-BK		CONN SBH11-PBPC-D07-ST-BK	
20	2	J2, JP1	Connector	Header, 100mil, 3x1, Gold, TH	Samtec	TSW-103-07-G-S		TSW-103-07-G-S	
21		J3	Keyboard connector	CONN FPC 24POS 1MM RT ANG SMD	TE Connectivity	2-84952-4		CON24 SMT-RA FCC	
22		J4, J5	Connector	Connector, Receptacle, 100mil, 10x2, Gold	Samtec	SSW-110-23-F-D		CONN SSW-110-23-F-D	
23		J6	USB Connector	CONNECTOR, MICRO-USB-AB, RECEPTACLE,	HIROSE	ZX62D-AB-5P8		USB-ZX62D-AB-5P8 REVISED	
24	4	JP2, JP3, JP4, JP5	Jumper	Header, 100mil, 2x1, Gold, TH	Samtec	TSW-102-07-G-S		TSW-102-07-G-S	
25	0	JP6	Jumper	Header, 100mil, 2x1, Gold, TH	Samtec	TSW-102-07-G-S		TSW-102-07-G-S	DNP_G2744
26	1	R1	1.40k	RES, 1.40k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06031K40FKEA		0603	
27	1	R2	1M	RES, 1.0Meg ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06031M00JNEA		0603	
28		R3, R4	27	RES, 27 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060327R0JNEA		0603	
29		R5	33k	RES, 33k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060333K0JNEA		0603	
30		R6	330	RES, 330 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW0603330RJNEA		0603	
31		R7, R8, R9	560	RES, 560 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW0603560RJNEA		0603	
32 33	9	R10, R11, R12, R13, R14, R15, R16 R20	47k 47k	RES, 47k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060347K0JNEA CRCW060347K0JNEA		0603 0603	DNP G2744
				RES, 47k ohm, 5%, 0.1W, 0603	Vishay-Dale				
34 35		R18, R19 R21, R22	0 2.2k	RES, 0 ohm, 5%, 0.1W, 0603 RES, 2.2k ohm, 5%, 0.1W, 0603	Vishay-Dale Vishay-Dale	CRCW06030000Z0EA CRCW06032K20JNEA	+	0603 0603	DNP_G2744
36		R30	47K	RES, 2.2k ohm, 5%, 0.1W, 0603 RES, 47k ohm, 5%, 0.1W, 0603	Vishay-Dale Vishay-Dale	CRCW060347K0JNEA	1	0603	1
37		R31, R32	0	RES, 0 ohm, 5%, 0.1W, 0603	Vishay-Dale Vishay-Dale	CRCW06030000Z0EA		0603	1
38		K31, K32 U1	MSP430F5529	Mixed Signal MicroController, PN0080A	Texas Instruments	MSP430F5529IPN	1	PN0080A L	DNP G2744
39		U2	TPD2E001DZDR	IC, LOW-CAPACITANCE 2-Chan ±15-kV ESD-	TEXAS INSTRUMENTS	TPD2E001DZDR	<u> </u>	DZD	5.41 _02744
40		U3	MSP430G2744	MSP430G2744, VQFN40	Texas Instruments	MSP430G2744IRHA40R	<u> </u>	QFN50P600X600X100-40N	†
41		U4	TPS73533	Single Output High PSRR LDO, 500 mA, Fixed	Texas Instruments	TPS73533DRBT		DRB8 1P75X1P5	1
42	0		XTAL4M	Crystal, 4MHz, 30pF, SMD	Auris-GmbH	Q- 4,000000M-HC49USSMD-F-30-30-D-16-TR	HCM49-4.000MABJT	Auris_HC49USSMD	DNP_G2744

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, Is GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.