

## Bill of Materials

TIDA-00616

ltem	Qty	Reference	Value	Part Description	Manufacturer Part Number	PCB Footprint
1	3	C1, C10, C14	4.7 uF	CAP, CERM, 4.7uF, 6.3V, +/-20%, X5R, 0402	C1005X5R0J475M050B	402
2	1	C2	2.2 uF	CAP, CERM, 2.2 μF, 6.3 V, +/- 10%, X6S, 0603	GRM188C80J225KE19I	603
3	2	C3, C18	0.01 uF	CAP, CERM, 0.01uF, 10V, +/-10%, X5R, 0402	GRM155R61A103KA01	402
4	4	C4, C6, C7, C9	0.1 uF	CAP, CERM, 0.1 μF, 6.3 V, +/- 10%, X5R, 0402	C1005X5R0J104K	0402L
5	2	C5, C8	10 uF	CAP, CERM, 10 μF, 25 V, +/- 20%, X5R, 0603	1608X5R1E106M080A	0603L
6	3	C11, C12, C13	0.1 uF	CAP, CERM, 0.1uF, 10V, +/-10%, X7R, 0402	GRM155R71A104KA01	0402L
7	1	C19	100 uF	CAP, CERM, 100uF, 6.3V, +/-20%, X5R, 1210	C1210C107M9PACTU	1210
8	1	D1	4.7 V	Diode, Zener, 4.7V, 300mW, SOD-523	BZT52C4V7T-7	SOD-523
9	6	FID1, FID2, FID3, FID4, FID5, FID6		Fiducial mark. There is nothing to buy or mount.	Fiducial	Fiducial10-20
10	1	GND	-	Test Point, Miniature, Black, TH	5001	Keystone5001
11	2	J1, J2	-	Header, 100mil, 3x1, Tin, TH	5-146278-3	TE_5-146278-3
12	2	J3, J4	-	Header, 100mil, 2x1, Tin plated, TH	90120-0122	CONN 90120-0122
13	2	J5, J6	-	Receptacle 100mil 10x1, Tin, TH	PPTC101LFBN-RC	CONN PPTC101LFBN-RC
14	1	J7	-	Receptacle, 100mil, 4x1, Gold, R/A, TH	PPPC041LGBN-RC	SULLINS PPPC041LGBN-RC
15	1	J8	-	Receptacle, 100mil, 3X1, TH	PPTC031LFBN-RC	Sullins PPTC031LFBN-RC
16	5	JP1, JP2, JP3, JP4, JP5	-	Header, 50mil, 3x1, Gold, TH	850-10-003-10-001000	I-Max 850-10-003-10-00100
17	1	JP6	-	Header, 100mil, 2x1, Tin, TH	5-146278-2	TE 5-146278-2
18	1	L2	22 uH	Inductor, Shielded Drum Core, Ferrite, 22uH, 0.83A, 0.36 ohm, SMD	LPS4018-223MLB	LPS4018
19	1	Q1	-	MOSFET, P-CH, -50V, -0.13A, SOT-23	BSS84-7-F	SOT-23
20	1	Q2	-	MOSFET, N-CH, 60 V, 0.17 A, SOT-23	2N7002-7-F	SOT-23
21	6	R1, R9, R10, R11, R14, R15	1 M	RES, 1.00 M, 1%, 0.063 W, 0402	CRCW04021M00FKED	0402L
22	4	R4, R5, R6, R8	49.9 K	RES, 49.9k ohm, 1%, 0.063W, 0402	CRCW040249K9FKED	0402L
23	2	R12, R13	2.43	RES, 2.43, 1%, 0.063 W, 0402	CRCW04022R43FKED	0402L
24	2	R16, R17	1 k	RES, 1.00 k, 1%, 0.1 W, 0402	ERJ-2RKF1001X	0402L
25	1	R20 - ROV1	5.76 M	RES, 5.76 M, 1%, 0.063 W, 0402	CRCW04025M76FKED	0402L
26	1	R21 - ROV2	7.5 M	RES, 7.50 M, 1%, 0.063 W, 0402	CRCW04027M50FKED	0402L
27	1	R22 - ROK1	5.36 M	RES, 5.36 M, 1%, 0.063 W, 0402	CRCW04025M36FKED	0402L
28	1	R23 - ROK2	6.98 M	RES, 6.98 M, 1%, 0.063 W, 0402	CRCW04024M99FKED	0402L
29	1	R24 - ROK3	0.877 M	RES, 0.887 M, 1%, 0.063 W, 0402	CRCW04021M27FKED	0402L
30	1	R25 - ROUT1	6.49 M	RES, 6.49 M, 1%, 0.063 W, 0402	CRCW04026M49FKED	0402L
31	1	R26 - ROUT2	6.65 M	RES, 6.65 M, 1%, 0.063 W, 0402	CRCW04026M65FKED	0402L
32	1	U1	-	Imported	TPS79633_DCQ_6	DCQ6
33	1	U2	-	Nano Power Programmable Timer, DGS0010A	TPL5100DGS	DGS0010A_N
34	2	U3, U4	-	Low-Voltage H-Bridge IC With LDO Regulator, RGY0024B	DRV8850RGY	RGY0024B
35	1	U5	-	Ultra Low Power Harvester Power Management IC with Boost Charger, and Nano-Powered Buck Converter, RGR0020A	BQ25570RGR	RGR0020A
36	1	U6	-	Imported	SN74AUP1G74_DCU_	DCU8
37	2	VBAT, VCC	-	Test Point, Miniature, Red, TH	5000	Keystone5000

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.