

Prototyping Functions

- Step-by-step Functionality (Demos)
 - Miscellaneous
 - *Analog EVM/Boosterpack's*
 - *PinMap Housekeeping*

Joe George, Northeast Digital Field Applications
Texas Instruments
Americas Sales and Marketing

Prototyping Functions

- Step-by-step Functionality (Demos)
 - GP Output (GPIO – General Purpose I/O)->Square Wave->Clock
 - Read A/D
 - I2C/SMBus (Wire)
- Optional WiFi
 - STA (station)
 - AP (access point)
- Optional Energia
- UI
 - Button (GP Input - GPIO, add debounce)
 - LCD Display (“Hello”)
 - Music
- UI - Serial Interface (i.e. Putty for echo “Hello World”)

Analog EVMs with ti.com links – NO Wiring

- Interface of Analog EVM's
 - Building Automation Sensors BoosterPack Module
 - <http://www.ti.com/tool/BOOSTXL-SENSORS>
 - <http://www.ti.com/tool/BOOSTXL-BASSENSORS>
 - DRV8323RH BoosterPack and MSP430F5529LP code – InstaSpin
 - Fast Prototyping 24bit Sigma-Delta ADC with Energia (TI ADS1220): [TIDA-00647](http://www.ti.com/tool/TIDA-00647)

- MSP-EXP430G2 Based Design kits & evaluation modules
<http://www.ti.com/product/MSP430G2553/toolssoftware>

MSP-EXP430G2 Based Design kits & EVMs

- MSP-EXP430G2 Based Design kits & evaluation modules Part #Name
 - BOOST-IR Infrared (IR) BoosterPack Plug-in Module
 - 430BOOST-ADS1118 **ADS1118** BoosterPack
 - 430BOOST-CC110L **CC110L** RF BoosterPack
 - DRV8873SEVM10A H-bridge motor driver with hardware interface and integrated current sensing EVM
 - DRV8873S-Q1EVM Automotive 10A H-Bridge Motor Driver with SPI and Integrated Current Sensing EVM
 - DRV8308EVM DRV8308 Evaluation Module for Three-phase Brushless Motor Pre-driver
 - DRV8313EVM DRV8313 Evaluation Module
 - DRV8701EVM DRV8701 Full Bridge Brushed DC Motor Gate Driver Evaluation Module
 - DRV8702D-Q1EVM Automotive Half-Bridge Brushed DC Motor Gate Driver Evaluation Module D
 - DRV8703D-Q1EVM DRV8703D-Q1 Automotive Half-Bridge Brushed DC Motor Gate Driver With SPI EVM
 - DRV8847EVM DRV8847 Dual H-Bridge Motor Driver Evaluation Module
 - DRV8847SEVM DRV8847S Dual H-Bridge Motor Driver Evaluation Module
 - DRV8850EVM DRV8850EVM - EVMfor Low-Voltage H-Bridge Motor Driver with LDO Voltage Regulator
 - DRV8912-Q1EVM DRV8912-Q1 multi h-bridges motor driver evaluation module
 - DLP-**7970**ABP NFC Transceiver Booster Pack

Demo – Pin Definition Reference

```
– energia-0101E0014\hardware\msp430\variants\launchpad\pins_energia.h
– // Pin names based on the silkscreen
– //
– static const uint8_t P1_0 = 2;
– static const uint8_t P1_1 ≡ 3;
– static const uint8_t P1_2 ≡ 4;
– static const uint8_t P1_3 ≡ 5;
– static const uint8_t P1_4 ≡ 6;
– static const uint8_t P1_5 ≡ 7;
– static const uint8_t P2_0 ≡ 8;
– static const uint8_t P2_1 = 9;
– static const uint8_t P2_2 ≡ 10;
– static const uint8_t P2_3 ≡ 11;
– static const uint8_t P2_4 ≡ 12;
– static const uint8_t P2_5 ≡ 13;
– static const uint8_t P1_6 = 14;
– static const uint8_t P1_7 = 15;
– static const uint8_t P2_7 ≡ 18;
– static const uint8_t P2_6 = 19;
```

		+-\ /-+			
	VCC	1	20	GND	
(A0)	P1.0	2	19	XIN	
(A1)	P1.1	3	18	XOUT	
(A2)	P1.2	4	17	TEST	
(A3)	P1.3	5	16	RST#	
(A4)	P1.4	6	15	P1.7	(A7) (SCL) (MISO)
(A5)	P1.5	7	14	P1.6	(A6) (SDA) (MOSI)
	P2.0	8	13	P2.5	
	P2.1	9	12	P2.4	
	P2.2	10	11	P2.3	
		+-----+			

```
// Pin names based on the silkscreen
```

Demo – Pin Definition Reference

```
– energia-0101E0014\hardware\msp430\variants\launchpad\pins_energia.h
– // Pin names based on the silkscreen
– //
– static const uint8_t P1_0 = 2;
– static const uint8_t P1_1 ≡ 3;
– static const uint8_t P1_2 ≡ 4;
– static const uint8_t P1_3 ≡ 5;
– static const uint8_t P1_4 ≡ 6;
– static const uint8_t P1_5 ≡ 7;
– static const uint8_t P2_0 ≡ 8;
– static const uint8_t P2_1 = 9;
– static const uint8_t P2_2 ≡ 10;
– static const uint8_t P2_3 ≡ 11;
– static const uint8_t P2_4 ≡ 12;
– static const uint8_t P2_5 ≡ 13;
– static const uint8_t P1_6 = 14;
– static const uint8_t P1_7 = 15;
– static const uint8_t P2_7 ≡ 18;
– static const uint8_t P2_6 = 19;
```

		+-\ /-+			
	VCC	1	20	GND	
(A0)	P1.0	2	19	XIN	
(A1)	P1.1	3	18	XOUT	
(A2)	P1.2	4	17	TEST	
(A3)	P1.3	5	16	RST#	
(A4)	P1.4	6	15	P1.7	(A7) (SCL) (MISO)
(A5)	P1.5	7	14	P1.6	(A6) (SDA) (MOSI)
	P2.0	8	13	P2.5	
	P2.1	9	12	P2.4	
	P2.2	10	11	P2.3	
		+-----+			

```
// Pin names based on the silkscreen
```