

## 23mm 低频玻璃封装应答机，只读，EN 14803 编号

查询样品: [TRPGR30ENATGA](#)

### 特性

- 由半双工 (HDX) 技术提供的同类产品最佳性能
- 获专利的应答机调谐提供稳定的和高读取性能
- **80 位只读类型**
- **EN 14803 编号**
- 对几乎所有非金属物质不敏感

### 应用范围

- 废弃集装箱管理

### 说明

德州仪器 (TI) 23mm 低频 (LF) 玻璃应答机提供出色性能并可在 134.2kHz 的共振频率上运行。此产品兼容 ISO/IEC 11784/11785 全球开放式标准。德州仪器 (TI) LF 玻璃应答机使用 TI 获专利的调谐制造工艺生产以提供持续的读取性能。送货前，将对此应答机进行全面的功能和参数测试，为用户提供他们希望从 TI 获得的高质量产品。



### 绝对最大额定值<sup>(1)</sup>

在自然通风温度范围内运行（除非另有说明）

		TRPGR30ENATGA
T <sub>A</sub>	工作温度	-25°C 至 70°C
T <sub>STG</sub>	储存温度	-40°C 至 85°C

(1) 超出绝对最大额定值下列出的值的应力可能会对器件造成永久损坏。这些只是应力额定值，在这些额定值或者任何其它超过技术规格下所标明条件下的器件功能运行在此并未说明。长时间运行在绝对最大额定条件下会影响设备的可靠性。

### 技术规格

参数	TRPGR30ENATGA
功能	只读
存储器（位）	80（64 位唯一 ID + 16 位 BCC）
存储器（页）	1
共振频率	134.6kHz
调制	FSK（频移键控）134.2kHz 和 124.2kHz
发射原理	HDX（半双工）
电源	由读取器信号供电（无电池）
典型读取范围	≤ 110cm <sup>(1)</sup>
典型读取时间	70ms
外壳材料	玻璃
保护玻璃	密封
电磁兼容性 (EMC)	已编辑代码不受自然电磁干扰或 X 射线的影响。
信号渗透率	应答机能透过几乎全部非金属物质进行读取。
机械冲击	IEC 60068-2-32 自由落体测试，高度 1.5m，测试 20 次
尺寸	∅ 3.85 ± 0.05mm x 23.1 ± 0.5mm
重量	0.8g

(1) 取决于使用所在国家的 RF 管理规定，读取器天线配置和环境条件。



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

**PACKAGING INFORMATION**

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
TRPGR30ENATGA	ACTIVE	RFIDT	TGA	0	2000	RoHS & Green	Call TI	N / A for Pkg Type	-25 to 70		Samples

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSELETE:** TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

**RoHS Exempt:** TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

**Green:** TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "-" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.


(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TGA (R-RFID-N0)

RFIDT



A-A



4211903/A 06/11

- NOTES:
- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5-1994.
  - B. This drawing is subject to change without notice.
  - C. HDX+ 23mm Glass TRP Cap on Die.

## 重要声明和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的应用。严禁对这些资源进行其他复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，TI 对此概不负责。

TI 提供的产品受 [TI 的销售条款](#) 或 [ti.com](#) 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265

Copyright © 2023，德州仪器 (TI) 公司