


www.ti.com

#### **FEATURES**

- Optimized for 1.8-V Operation and Is 3.6-V I/O Tolerant to Support Mixed-Mode Signal Operation
- I<sub>off</sub> Supports Partial-Power-Down Mode Operation
- Sub 1-V Operable
- Max t<sub>pd</sub> of 2.1 ns at 1.8 V
- Low Power Consumption, 10-μA Max I<sub>CC</sub>
- ±8-mA Output Drive at 1.8 V
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Protection Exceeds JESD 22
  - 2000-V Human-Body Model (A114-A)
  - 200-V Machine Model (A115-A)
  - 1500-V Charged-Device Model (C101)



### **DESCRIPTION/ORDERING INFORMATION**

This quadruple bus buffer gate is designed for 0.8-V to 2.7-V  $V_{CC}$  operation, but is designed specifically for 1.6-V to 1.95-V  $V_{CC}$  operation.

The SN74AUC126 contains four independent line drivers with 3-state outputs. Each output is disabled when the associated output-enable (OE) input is low.

To ensure the high-impedance state during power up or power down, OE should be tied to GND through a pulldown resistor; the minimum value of the resistor is determined by the current-sourcing capability of the driver.

This device is fully specified for partial-power-down applications using  $I_{off}$ . The  $I_{off}$  circuitry disables the outputs, preventing damaging current backflow through the device when it is powered down.

#### ORDERING INFORMATION

T <sub>A</sub>	PACKAG	E <sup>(1)</sup>	ORDERABLE PART NUMBER	TOP-SIDE MARKING
–40°C to 85°C	QFN – RGY	Tape and reel	SN74AUC126RGYR	MS126

 Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.

## **FUNCTION TABLE**


INPU	JTS	OUTPUT
OE	Α	Y
Н	Н	Н
Н	L	L
L	Χ	Z



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



# **LOGIC DIAGRAM (POSITIVE LOGIC)**



# Absolute Maximum Ratings<sup>(1)</sup>

over operating free-air temperature range (unless otherwise noted)

			MIN	MAX	UNIT
$V_{CC}$	Supply voltage range		-0.5	3.6	V
VI	Input voltage range (2)		-0.5	3.6	V
Vo	Voltage range applied to any output in the hig	h-impedance or power-off state <sup>(2)</sup>	-0.5	3.6	V
Vo	Output voltage range <sup>(2)</sup>		-0.5	V <sub>CC</sub> + 0.5	V
I <sub>IK</sub>	Input clamp current	V <sub>I</sub> < 0		-50	mA
I <sub>OK</sub>	Output clamp current	V <sub>O</sub> < 0		-50	mA
Io	Continuous output current			±20	mA
	Continuous current through V <sub>CC</sub> or GND			±100	mA
$\theta_{JA}$	Package thermal impedance (3)			47	°C/W
T <sub>stg</sub>	Storage temperature range		-65	150	°C

<sup>(1)</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

<sup>(2)</sup> The input negative-voltage and output voltage ratings may be exceeded if the input and output current ratings are observed.

<sup>(3)</sup> The package thermal impedance is calculated in accordance with JESD 51-5.




# SN74AUC126 QUADRUPLE BUS BUFFER GATE WITH 3-STATE OUTPUTS

# Recommended Operating Conditions<sup>(1)</sup>

			MIN	MAX	UNIT
V <sub>CC</sub>	Supply voltage		0.8	2.7	V
		V <sub>CC</sub> = 0.8 V	V <sub>CC</sub>		
$V_{IH}$	High-level input voltage	$V_{CC} = 1.1 \text{ V to } 1.95 \text{ V}$	$0.65 \times V_{CC}$		V
		$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$	1.7		
		V <sub>CC</sub> = 0.8 V		0	
$V_{IL}$	Low-level input voltage	$V_{CC} = 1.1 \text{ V to } 1.95 \text{ V}$		$0.35 \times V_{CC}$	V
		$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$		0.7	
VI	Input voltage		0	3.6	V
V	Output voltage	Active state	0	$V_{CC}$	V
Vo	Vo Output voltage	3-state	0	3.6	V
		V <sub>CC</sub> = 0.8 V		-0.7	
		V <sub>CC</sub> = 1.1 V		-3	
$I_{OH}$	High-level output current	V <sub>CC</sub> = 1.4 V		<b>-</b> 5	mA
		V <sub>CC</sub> = 1.65 V		-8	
		V <sub>CC</sub> = 2.3 V		-9	
		V <sub>CC</sub> = 0.8 V		0.7	
		V <sub>CC</sub> = 1.1 V		3	
$I_{OL}$	DL Low-level output current	V <sub>CC</sub> = 1.4 V		5	mA
		V <sub>CC</sub> = 1.65 V		8	
		V <sub>CC</sub> = 2.3 V		9	
Δt/Δν	Input transition rise or fall rate	·		20	ns/V
T <sub>A</sub>	Operating free-air temperature		-40	85	°C

<sup>(1)</sup> All unused inputs of the device must be held at  $V_{CC}$  or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.

# SN74AUC126 QUADRUPLE BUS BUFFER GATE WITH 3-STATE OUTPUTS





### **Electrical Characteristics**

over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	V <sub>cc</sub>	MIN TYP <sup>(1)</sup> MAX	UNIT
	$I_{OH} = -100 \mu A$	0.8 V to 2.7 V	V <sub>CC</sub> - 0.1	
	$I_{OH} = -0.7 \text{ mA}$	0.8 V	0.55	
V	$I_{OH} = -3 \text{ mA}$	1.1 V	0.8	V
V <sub>OH</sub>	$I_{OH} = -5 \text{ mA}$	1.4 V	1	V
	$I_{OH} = -8 \text{ mA}$	1.65 V	1.2	
	$I_{OH} = -9 \text{ mA}$	2.3 V	1.8	
	I <sub>OL</sub> = 100 μA	0.8 V to 2.7 V	0.2	
	$I_{OL} = 0.7 \text{ mA}$	0.8 V	0.25	
V	I <sub>OL</sub> = 3 mA	1.1 V	0.3	V
V <sub>OL</sub>	$I_{OL} = 5 \text{ mA}$	1.4 V	0.4	V
	I <sub>OL</sub> = 8 mA	1.65 V	0.45	
	I <sub>OL</sub> = 9 mA	2.3 V	0.6	
I <sub>I</sub>	$V_I = V_{CC}$ or GND	0 to 2.7 V	±5	μΑ
I <sub>off</sub>	$V_1$ or $V_0 = 2.7 \text{ V}$	0	±10	μΑ
l <sub>OZ</sub>	$V_O = V_{CC}$ or GND	2.7 V	±10	μΑ
I <sub>cc</sub>	$V_I = V_{CC}$ or GND, $I_O = 0$	0.8 V to 2.7 V	10	μΑ
C <sub>i</sub>	$V_I = V_{CC}$ or GND	2.5 V	2.5	pF
C <sub>o</sub>	$V_O = V_{CC}$ or GND	2.5 V	5	pF

<sup>(1)</sup> All typical values are at  $T_A = 25$ °C.

# **Switching Characteristics**

over recommended operating free-air temperature range,  $C_L = 15 \text{ pF}$  (unless otherwise noted) (see Figure 1)


PARAMETER	FROM (INPUT)	TO (OUTPUT)	V <sub>CC</sub> = 0.8 V	V <sub>CC</sub> = 1 ± <b>0.</b> 1		V <sub>CC</sub> = ± 0.			<sub>C</sub> = 1.8 0.15 V		V <sub>CC</sub> = 1 ± 0.2		UNIT
	(INFOT)	(0011-01)	TYP	MIN	MAX	MIN	MAX	MIN	TYP	MAX	MIN	MAX	1
t <sub>pd</sub>	Α	Υ	5.8	0.7	3.7	0.6	2.6	0.5	1	2.1	0.5	1.3	ns
t <sub>en</sub>	OE	Υ	6.2	0.9	3.8	0.7	2.5	0.6	1	2.2	0.6	1.3	ns
t <sub>dis</sub>	OE	Y	4.3	1.6	4.7	1.5	3.5	1.4	2.4	3.4	1	2.5	ns

# **Switching Characteristics**

over recommended operating free-air temperature range,  $C_L = 30 \text{ pF}$  (unless otherwise noted) (see Figure 1)

PARAMETER	FROM	TO (OUTPUT)	۷ <sub>cc</sub>	; = 1.8 0.15 V	V	V <sub>CC</sub> = ± 0.		UNIT
	(INPUT)	(001701)	MIN	TYP	MAX	MIN	MAX	
t <sub>pd</sub>	A	Υ	0.5	1.8	2.6	0.5	2.1	ns
t <sub>en</sub>	OE	Υ	0.6	1.6	2.7	0.6	2.2	ns
t <sub>dis</sub>	OE	Y	1.2	2.4	3.3	0.8	2.2	ns








# **Operating Characteristics**

 $T_A = 25^{\circ}C$ 

	PARAMETE	R	TEST CONDITIONS	V <sub>CC</sub> = 0.8 V TYP	V <sub>CC</sub> = 1.2 V TYP	V <sub>CC</sub> = 1.5 V TYP	V <sub>CC</sub> = 1.8 V TYP	V <sub>CC</sub> = 2.5 V TYP	UNIT
	Power dissipation	Outputs enabled	f = 10 MHz	15	15	15	16	17	pF
C <sub>pd</sub>	capacitance	Outputs disabled	I = IU WIMZ	2	2	2	3	4	þΓ




### PARAMETER MEASUREMENT INFORMATION



TEST	S1
t <sub>PLH</sub> /t <sub>PHL</sub>	Open
$t_{PLZ}/t_{PZL}$	2×V <sub>CC</sub>
t <sub>PHZ</sub> /t <sub>PZH</sub>	GND

$C_L$	R <sub>L</sub>	$V_\Delta$
15 pF	<b>2 k</b> Ω	0.1 V
15 pF	<b>2 k</b> Ω	0.1 V
15 pF	<b>2 k</b> Ω	0.1 V
15 pF	<b>2 k</b> Ω	0.15 V
15 pF	<b>2 k</b> Ω	0.15 V
30 pF	<b>1 k</b> Ω	0.15 V
30 pF	500 Ω	0.15 V
	15 pF 15 pF 15 pF 15 pF 15 pF 30 pF	15 pF 2 kΩ 15 pF 2 kΩ 30 pF 1 kΩ



- NOTES: A. C<sub>I</sub> includes probe and jig capacitance.
  - B. Waveform 1 is for an output with internal conditions such that the output is low, except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high, except when disabled by the output control.
  - C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz,  $Z_{O}$  = 50  $\Omega$ , slew rate  $\geq$  1 V/ns.
  - D. The outputs are measured one at a time, with one transition per measurement.
  - E.  $t_{PLZ}$  and  $t_{PHZ}$  are the same as  $t_{dis}$ .
  - F. t<sub>PZL</sub> and t<sub>PZH</sub> are the same as t<sub>en</sub>.
  - G. t<sub>PLH</sub> and t<sub>PHL</sub> are the same as t<sub>pd</sub>.
  - H. All parameters and waveforms are not applicable to all devices.

Figure 1. Load Circuit and Voltage Waveforms



# PACKAGE OPTION ADDENDUM

10-Dec-2020

#### PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
							(6)				
SN74AUC126RGYR	ACTIVE	VQFN	RGY	14	3000	RoHS & Green	NIPDAU	Level-2-260C-1 YEAR	-40 to 85	MS126	Samples

(1) The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 3-Jun-2022

## TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

	Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
ĺ	SN74AUC126RGYR	VQFN	RGY	14	3000	330.0	12.4	3.75	3.75	1.15	8.0	12.0	Q1

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 3-Jun-2022




## \*All dimensions are nominal

Ì	Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)	
ı	SN74AUC126RGYR	VQFN	RGY	14	3000	356.0	356.0	35.0	

3.5 x 3.5, 0.5 mm pitch


PLASTIC QUAD FLATPACK - NO LEAD

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.





PLASTIC QUAD FLATPACK - NO LEAD




### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- This drawing is subject to change without notice.
  The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



PLASTIC QUAD FLATPACK - NO LEAD




NOTES: (continued)

4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).



PLASTIC QUAD FLATPACK - NO LEAD



NOTES: (continued)

5. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2025. Texas Instruments Incorporated