MSP430F6736

Single-phase energy meter IC System on Chip



The Texas Instruments MSP430F6736 is a highly integrated, high accuracy, ultra-low power metrology System on Chip (SoC) designed for system cost optimized, flexible and robust metering implementation such as electricity meters and energy measurement.

Optimized for single-phase measurement with anti-tamper, the MSP430F6736 supports up to three independent 24-bit sigma-delta ($\Sigma\Delta$) Analog-to-Digital Converters (ADC) and achieves less than 0.1% error in energy accuracy over a wide dynamic range of 5000:1. In addition, the unique combination of six additional synchronized channels ADC10 give the user the flexibility to develop the lowest cost 2-phase or 3-phase E-meters.


A comprehensive development tool set including hardware reference design and energy libraries in software enables quick development, time to market and certification.

Energy library features

- Single-phase energy measurement with support for anti-tamper
- Class 0.1% accuracy over a 5000:1 dynamic range
- Calibration and key parameters including
 - RMS current and voltage
 - Active, reactive and apparent power
 - Active, reactive and apparent energies
 - Independent pulse output for active and reactive energies
 - Power factor
 - Software phase compensation
 - Frequency
 - Temperature
 - Tamper detection

Key device features and benefits

Feature	Benefit
Three 24-bit sigma delta analog-to-digital converters	Class 0.1% accuracy 1-phase electricity meters + anti- tamper implementation
Six ADC10 synchronized channels	Low-cost 2-phase and 3-phase energy measurement system implementation
25 MIPS	Enables metrology + application code + communication code (like DLMS) on a single chip
Up to 128 kB Flash + 8kB RAM	Metrology + application + communication stacks implementation
Three UARTs and four timers	Interface to communications devices to develop smart meters
 Optimized and robust Real-Time-Clock (RTC) Temperature compensated RTC Ultra-low-power LPM3.5 RTC down to 1.4µA with battery backup auxiliary voltage rail Accurate time stamping 	 Lower system cost with no external compensation needed Extended life-time for the battery backup in case of power outage Enables smarter data logging, and flexible tarriff implementation with time/day/year tracking
Six interrupt lines and pre-scalers	Robust design with alarms and anti-tamper mechanism implementation
Supports multiple LCD format up to 320 segments thanks to eight MUX	Can display Asian and custom characters for global deployment
Energy libraries in software	Flexibility for the user to customize energy measurement to application requirement and to develop application code on top of metrology



🔺 F6736 block diagram



🔺 EVM430-F6736 EVM

EVM key features

- Supports shunts/current transformers for current sensors
- Less than 0.1% error in accuracy for 5000:1 dynamic range
- Flexible and isolated sources for MSP430F6736
- 160 segment LCD display
- 32kHz RTC support
- Two LEDs and two headers for active energy and reactive energy pulses
- Support for anti-tamper detection
- PC communication to MSP430F6736 via RS-232
- Software installed for measuring metering parameters
- PC-based GUI for calibration/results via MSP430F6736
- JTAG connections for simultaneous debug

Relevant documents

MSP430F6736 datasheet

Find out more about TI's MSP430F673x family by visiting the sites below:

- MSP430[™] metering: www.ti.com/430metering
- MSP430 energy library: www.ti.com/msp430f673xenergylibrary
- Smart Grid E2E[™] community: www.ti.com/smartgrid-blog
- TI's smart grid solutions: www.ti.com/smartgrid

TI Worldwide Technical Support

Internet

TI Semiconductor Product Information Center Home Page

support.ti.com TI E2E[™] Community Home Page

e2e.ti.com

Product Information Centers

Americas	Phone	+1(972) 644-5580
Brazil	Phone	0800-891-2616
Mexico	Phone	0800-670-7544
	Fax Internet/Email	+1(972) 927-6377 support.ti.com/sc/pic/a

support.ti.com/sc/pic/americas.htm

Europe, Middle East, and Africa

Phone

European Free Call	00800-ASK-TEXAS (00800 275 83927)
International	+49 (0) 8161 80 2121
Russian Support	+7 (4) 95 98 10 701

Note: The European Free Call (Toll Free) number is not active in all countries. If you have technical difficulty calling the free call number, please use the international number above.

Domestic

Domestic

Domestic

International

International

Fax Internet Direct Email

Japan

Phone

Internet/Email

Fax

+(49) (0) 8161 80 2045 www.ti.com/asktexas asktexas@ti.com

> 0120-92-3326 +81-3-3344-5317 0120-81-0036 support.ti.com/sc/pic/japan.htm www.tij.co.jp/pic

Asia			
Phone			
Internation	nal	+91-80-41381665	
Domestic		Toll-Free Number	
Note: Toll-free numbers do not support			
mobile	and IP phones.		
Austra	lia	1-800-999-084	
China		800-820-8682	
Hong ł	Kong	800-96-5941	
India		1-800-425-7888	
Indone	sia	001-803-8861-1006	
Korea		080-551-2804	
Malays	sia	1-800-80-3973	
New Zealand		0800-446-934	
Philippines		1-800-765-7404	
Singapore		800-886-1028	
Taiwar	ו	0800-006800	
Thailar	nd	001-800-886-0010	
Fax	+8621-23073686		
Email	tiasia@ti.com or ti-china@ti.com		
Internet	support.ti.com/sc/pic/asia.htm		

Important Notice: The products and services of Texas Instruments Incorporated and its subsidiaries described herein are sold subject to TI's standard terms and conditions of sale. Customers are advised to obtain the most current and complete information about TI products and services before placing orders. TI assumes no liability for applications assistance, customer's applications or product designs, software performance, or infringement of patents. The publication of information regarding any other company's products or services does not constitute TI's approval, warranty or endorsement thereof.

B011012

The platform bar, E2E and MSP430 are trademarks of Texas Instruments

All other trademarks are the property of their respective owners.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated