

LMC6762 Dual MicroPower Rail-To-Rail Input CMOS Comparator with Push-Pull Output

Check for Samples: [LMC6762](http://www.ti.com/product/lmc6762#samples)

-
-
-
- of 3V digital systems. **• Rail-To-Rail Input Common Mode Voltage**
- the Supplies, \textcircled{e} V⁺ = 2.7V, and I_{LOAD} = 2.5 mA)
-
- **• Propagation Delay (@ V ⁺ = 5V, 100 mV** resistor. **Overdrive): 4 μs**

-
-
-
- **•• Hand-Held Electronics applications.**
-
- **• Alarm and Monitoring Circuits** version of this device.
- **• Window Comparators, Multivibrators**

Connection Diagram

¹FEATURES DESCRIPTION

The LMC6762 is an ultra low power dual comparator **²• (Typical Unless Otherwise Noted)** with a maximum supply current of 10 μA/comparator. **Low Power Consumption (Max):** $I_s = 10$ It is designed to operate over a wide range of supply
 uA/comp voltages from 2.7V to 15V. The LMC6762 has **μA/comp**
Wide Range of Supply Voltages: 2.7V to 15V voltages, from 2.7V to 15V. The LMC6762 has
ensured specifications at 2.7V to meet the demands **• Wide Range of Supply Voltages: 2.7V to 15V** ensured specifications at 2.7V to meet the demands

Range **Range The LMC6762** has an input common-mode voltage **• Rail-To-Rail Output Swing (Within 100 mV of** range which exceeds both supplies. This is a $\frac{1}{2}$ significant advantage in low-voltage applications. The LMC6762 also features a push-pull output that allows **• Short Circuit Protection: ⁴⁰ mA** direct connections to logic devices without ^a pull-up

A quiescent power consumption of 50 μW/amplifier **APPLICATIONS** (@ V⁺ = 5V) makes the LMC6762 ideal for
applications in portable phones and hand-held **Laptop Computers •** *Computers Computers C* independent of power supply voltage. Ensured **• Mobile Phones** operation at 2.7V and a rail-to-rail performance **Metering Systems**
 • makes this device ideal for battery-powered

RC Timers • *RC* **Timers** *REPOSER Refer* to the LMC6772 datasheet for an open-drain

Typical Application

Zero Crossing Detector

These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Æ Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet. All trademarks are the property of their respective owners.

Absolute Maximum Ratings(1)(2)

(1) Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is intended to be functional, but specific performance is not ensured. For ensured specifications and the test conditions, see the electrical characteristics.

(2) If Military/Aerospace specified devices are required, please contact the TI Sales Office/ Distributors for availability and specifications.

(3) Human body model, 1.5 kΩ in series with 100 pF.

(4) Do not short circuit output to V⁺, when V⁺ is greater than 12V or reliability will be adversely affected.

- (5) Applies to both single-supply and split-supply operation. Continuous short circuit operation at elevated ambient temperature can result in exceeding the maximum allowed junction temperature of 150°C. Output currents in excess of ±30 mA over long term may adversely affect reliability.
- (6) The maximum power dissipation is a function of $T_{J(max)}$, θ_{JA} , and T_A . The maximum allowable power dissipation at any ambient temperature is P_D = $(T_{J(max)} - T_A)/\theta_{JA}$. All numbers apply for packages soldered directly into a PC board.

Operating Ratings(1)

(1) Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is intended to be functional, but specific performance is not ensured. For ensured specifications and the test conditions, see the electrical characteristics.

2.7V Electrical Characteristics

Unless otherwise specified, all limits ensured for T_J = 25°C, V⁺ = 2.7V, V[−] = 0V, V_{CM} = V⁺/2. **Boldface** limits apply at the temperature extremes.

(1) Typical Values represent the most likely parametric norm.

(2) All limits are specified by testing or statistical analysis.

(3) Input Offset Voltage Average Drift is calculated by dividing the accelerated operating life drift average by the equivalent operational time. The Input Offset Voltage Average Drift represents the input offset voltage change at worst-case input conditions.

2.7V Electrical Characteristics (continued)

Unless otherwise specified, all limits ensured for T_J = 25°C, V⁺ = 2.7V, V[−] = 0V, V_{CM} = V⁺/2. **Boldface** limits apply at the temperature extremes.

5.0V and 15.0V Electrical Characteristics

Unless otherwise specified, all limits ensured for T_J = 25°C, V⁺ = 5.0V and 15.0V, V[−] = 0V, V_{CM} = V⁺/2. **Boldface** limits apply at the temperature extremes.

(1) Typical Values represent the most likely parametric norm.

(2) All limits are specified by testing or statistical analysis.

⁽³⁾ Input Offset Voltage Average Drift is calculated by dividing the accelerated operating life drift average by the equivalent operational time. The Input Offset Voltage Average Drift represents the input offset voltage change at worst-case input conditions.

5.0V and 15.0V Electrical Characteristics (continued)

Unless otherwise specified, all limits ensured for T_J = 25°C, V⁺ = 5.0V and 15.0V, V[−] = 0V, V_{CM} = V⁺/2. **Boldface** limits apply at the temperature extremes.

(4) Do not short circuit output to V^+ , when V^+ is greater than 12V or reliability will be adversely affected.

AC Electrical Characteristics

Unless otherwise specified, all limits ensured for T_J = 25°C, V⁺ = 5V, V⁻ = 0V, V_{CM} = V_O = V⁺/2. **Boldface** limits apply at the temperature extreme.

(1) Typical Values represent the most likely parametric norm.

(2) All limits are specified by testing or statistical analysis.

 (3) C_L includes the probe and jig capacitance.

(4) The rise and fall times are measured with a 2V input step. The propagation delays are also measured with a 2V input step.

Typical Performance Characteristics

 V^+ = 5V, Single Supply, T_A = 25°C unless otherwise specified

Case Temperature (°C)

SNOS739D –JULY 1997–REVISED MARCH 2013 **www.ti.com**

 1.00

 0.90

Typical Performance Characteristics (continued) V^+ = 5V, Single Supply, T_A = 25°C unless otherwise specified Δ **V**_{OS} Δ **V**_{OS} **vs vs ΔVCM ΔVCM** $V_S = 2.7V$ $V_S = 5V$ 0.90 0.80 0.70 ΔV_{OS} (mV) 0.60 0.50 0.40 0.30 0.20 0.10 0.00 \mathfrak{Z} $\mathbf 0$ 0.5 $\mathbf{1}$ 1.5 2 2.5 3 3.5 4 4.5 5 ΔV _{CM} (V) (Referenced to Ground) **Figure 7. Figure 8. vs Output Voltage** vs
 vs Output Current (Source NV_{CM} 2001) **2.7 Output Current (Sourcing)** $= 2.7v$ V_S 2.6 Output Voltage (V) 40^o 2.5 ŋ. 2.4 2.3 $+85^\circ$ 2.2 2.1 14 16 $0\quad 0.5$ 1.5 2 2.5 3 3.5 4 4.5 5 $\overline{1}$ Output Current (mA) **Figure 9. Figure 10. Output Voltage vs Output Voltage vs Output Current (Sourcing) Output Current (Sourcing)** v $= 1.5V$ $=5V$ 14.9 14.8 4000 $40°C$ Output Voltage (V) 14.7 14.6 14.5 14.4 14.3 $+85^o$

 14.2

 14.1 14

 $\mathbf 0$

 $\overline{1}$

 $\overline{2}$ 3° $\overline{4}$ $5 6\overline{6}$ $\overline{7}$ $\,$ 8 $\,$ $9 - 10$

Output Current (mA)

Typical Performance Characteristics (continued)

SNOS739D –JULY 1997–REVISED MARCH 2013 **www.ti.com**

Typical Performance Characteristics (continued)

APPLICATION HINTS

Input Common-Mode Voltage Range

At supply voltages of 2.7V, 5V and 15V, the LMC6762 has an input common-mode voltage range which exceeds both supplies. As in the case of operational amplifiers, CMVR is defined by the V_{OS} shift of the comparator over the common-mode range of the device. A CMRR $(ΔV_{OS}/ΔV_{CM})$ of 75 dB (typical) implies a shift of < 1 mV over the entire common-mode range of the device. The absolute maximum input voltage at V^+ = 5V is 200 mV beyond either supply rail at room temperature.

Figure 25. An Input Signal Exceeds the LMC6762 Power Supply Voltages with No Output Phase Inversion

A wide input voltage range means that the comparator can be used to sense signals close to ground and also to the power supplies. This is an extremely useful feature in power supply monitoring circuits.

An input common-mode voltage range that exceeds the supplies, 20 fA input currents (typical), and a high input impedance makes the LMC6762 ideal for sensor applications. The LMC6762 can directly interface to sensors without the use of amplifiers or bias circuits. In circuits with sensors which produce outputs in the tens to hundreds of millivolts, the LMC6762 can compare the sensor signal with an appropriately small reference voltage. This reference voltage can be close to ground or the positive supply rail.

Low Voltage Operation

Comparators are the common devices by which analog signals interface with digital circuits. The LMC6762 has been designed to operate at supply voltages of 2.7V without sacrificing performance to meet the demands of 3V digital systems.

At supply voltages of 2.7V, the common-mode voltage range extends 200 mV (ensured) below the negative supply. This feature, in addition to the comparator being able to sense signals near the positive rail, is extremely useful in low voltage applications.

A4			0.015V					
5V			500 mV			$20 \mu s$		

Figure 26. Even at Low-Supply Voltage of 2.7V, an Input Signal which Exceeds the Supply Voltages Produces No Phase Inversion at the Output

At V⁺ = 2.7V, propagation delays are t_{PLH} = 4 µs and t_{PHL} = 4 µs with overdrives of 100 mV. Please refer to the [performance](#page-4-0) curves for more extensive characterization.

SNOS739D –JULY 1997–REVISED MARCH 2013 **www.ti.com**

Shoot-Through Current

The shoot-through current is defined as the current surge, above the quiescent supply current, between the positive and negative supplies of a device. The current surge occurs when the output of the device switches states. This transient switching current results in glitches in the supply voltage. Usually, glitches in the supply lines are compensated by bypass capacitors. When the switching currents are minimal, the values of the bypass capacitors can be reduced considerably.

Figure 27. LMC6762 Circuit for Measurement of the Shoot-Through Current

Figure 28. Measurement of the Shoot-Through Current

From [Figure](#page-9-0) 27 and [Figure](#page-9-1) 28 the shoot-through current for the LMC6762 can be approximated to be 0.2 mA (200 mV/1 kΩ). The duration of the transient is measured as 1 μs. The values needed for the local bypass capacitors can be calculated as follows:

Area of $\Delta = \frac{1}{2}$ **(1 μs** \times **200 μA)**

 $= 100$ pC

If the local bypass capacitor has to provide this charge of 100 pC, the minimum value of the local capacitor to prevent local degradation of V_{CC} can be calculated. Suppose that the maximum voltage droop that the system can tolerate is 100mV,

$$
\Delta Q = C * (\Delta V)
$$

→C = (ΔQ/ΔV) $= 100$ pC/100 mV $= 0.001 \mu F$

The low internal feedthrough current of the LMC6762 thus requires lower values for the local bypass capacitors. In applications where precision is not critical, this is a significant advantage, as lower values of capacitors result in savings of board space, and cost.

It is worth noting here that the delta shift of the power supply voltage due to the transient currents causes a threshold shift of the comparator. This threshold shift is reduced by the high PSRR of the comparator. However, the value of the PSRR applicable in this instance is the transient PSRR and not the DC PSRR. The transient PSRR is significantly lower than the DC PSRR.

Generally, it is a good goal to reduce the delta voltage on the power supply to a value equal to or less than the hysteresis of the comparator. For example, if the comparator has 50 mV of hysteresis, it would be reasonable to increase the value of the local bypass capacitor to $0.01 \mu F$ to reduce the voltage delta to 10 mV.

Output Short Circuit Current

The LMC6762 has short circuit protection of 40 mA. However, it is not designed to withstand continuous short circuits, transient voltage or current spikes, or shorts to any voltage beyond the supplies. A resistor is series with the output should reduce the effect of shorts. For outputs which send signals off PC boards additional protection devices, such as diodes to the supply rails, and varistors may be used.

Hysteresis

If the input signal is very noisy, the comparator output might trip several times as the input signal repeatedly passes through the threshold. This problem can be addressed by making use of hysteresis as shown below.

Figure 29. Canceling the Effect of Input Capacitance

The capacitor added across the feedback resistor increases the switching speed and provides more short term hysteresis. This can result in greater noise immunity for the circuit.

Spice Macromodel

A Spice Macromodel is available for the LMC6762. The model includes a simulation of:

- Input common-mode voltage range
- Quiescent and dynamic supply current
- Input overdrive characteristics

and many more characteristics as listed on the macromodel disk.

A SPICE macromodel of this and many other op amps is available at no charge from the WEBENCH Design Center Team at <http://www.ti.com/ww/en/analog/webench/>

Typical Applications

One-Shot Multivibrator

Figure 30. One-Shot Multivibrator

A monostable multivibrator has one stable state in which it can remain indefinitely. It can be triggered externally to another quasi-stable state. A monostable multivibrator can thus be used to generate a pulse of desired width.

The desired pulse width is set by adjusting the values of C_2 and R_4 . The resistor divider of R_1 and R_2 can be used to determine the magnitude of the input trigger pulse. The LMC6762 will change state when $V_1 < V_2$. Diode D_2 provides a rapid discharge path for capacitor C_2 to reset at the end of the pulse. The diode also prevents the non-inverting input from being driven below ground.

Bi-Stable Multivibrator

Figure 31. Bi-Stable Multivibrator

A bi-stable multivibrator has two stable states. The reference voltage is set up by the voltage divider of R_2 and R_3 . A pulse applied to the SET terminal will switch the output of the comparator high. The resistor divider of R_1 , R_4 , and R_5 now clamps the non-inverting input to a voltage greater than the reference voltage. A pulse applied to RESET will now toggle the output low.

Zero Crossing Detector

Figure 32. Zero Crossing Detector

A voltage divider of R_4 and R_5 establishes a reference voltage V_1 at the non-inverting input. By making the series resistance of R₁ and R₂ equal to R₅, the comparator will switch when V_{IN} = 0. Diode D₁ insures that V₃ never drops below −0.7V. The voltage divider of R₂ and R₃ then prevents V₂ from going below ground. A small amount of hysteresis is setup to ensure rapid output voltage transitions.

Oscillator

Figure 33. Square Wave Generator

[Figure](#page-12-0) 33 shows the application of the LMC6762 in a square wave generator circuit. The total hysteresis of the loop is set by R_1 , R_2 and R_3 . R_4 and R_5 provide separate charge and discharge paths for the capacitor C. The charge path is set through R₄ and D₁. So, the pulse width t₁ is determined by the RC time constant of R₄ and C. Similarly, the discharge path for the capacitor is set by R_5 and D₂. Thus, the time t₂ between the pulses can be changed by varying R₅, and the pulse width can be altered by R₄. The frequency of the output can be changed by varying both R_4 and R_5 .

SNOS739D –JULY 1997–REVISED MARCH 2013 **www.ti.com**

Figure 34. Time Delay Generator

The circuit shown above provides output signals at a prescribed time interval from a time reference and automatically resets the output when the input returns to ground. Consider the case of $V_{\text{IN}} = 0$. The output of comparator 4 is also at ground. This implies that the outputs of comparators 1, 2, and 3 are also at ground. When an input signal is applied, the output of comparator 4 swings high and C charges exponentially through R. This is indicated above.

The output voltages of comparators 1, 2, and 3 switch to the high state when V_{C1} rises above the reference voltage V_A , V_B and V_C . A small amount of hysteresis has been provided to insure fast switching when the RC time constant is chosen to give long delay times.

www.ti.com SNOS739D –JULY 1997–REVISED MARCH 2013

REVISION HISTORY

PACKAGING INFORMATION

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

PACKAGE OPTION ADDENDUM

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TEXAS

TAPE AND REEL INFORMATION

ISTRUMENTS

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE

Pack Materials-Page 1

PACKAGE MATERIALS INFORMATION

www.ti.com 20-Nov-2024

*All dimensions are nominal

PACKAGE OUTLINE

D0008A SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT

NOTES:

1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.

- 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
- 4. This dimension does not include interlead flash.
- 5. Reference JEDEC registration MS-012, variation AA.

EXAMPLE BOARD LAYOUT

D0008A SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

D0008A SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

9. Board assembly site may have different recommendations for stencil design.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](https://www.ti.com/legal/terms-conditions/terms-of-sale.html) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated