SCBS737A - JULY 2000 - REVISED JULY 2000

- BiCMOS Technology With Low Quiescent Power
- Buffered Inputs
- Direct Clear Input
- 48-mA Output Sink Current
- Output Voltage Swing Limited to 3.7 V
- Controlled Output Edge Rates
- Input/Output Isolation From V_{CC}
- SCR Latch-Up-Resistant BiCMOS Process and Circuit Design
- Applications Include:
 - Buffer/Storage Registers
 - Shift Registers
 - Pattern Generators
- Package Options Include Plastic Small-Outline (M) Package and Standard Plastic (E) DIP

(TOP VIEW) CLR 20 VCC 1Q [] 2 19 8Q 1D 🛮 3 18 8D 2D 🛮 4 17 🛮 7D 2Q [] 5 16 🛮 7Q 3Q ∏ 6 15 ¶ 6Q 3D **1**7 14 6D 4D 🛮 8 13 5D 12 5Q 4Q **∏** 9 GND ∏ 10 11 **∏** CLK

E OR M PACKAGE

description

The CD74FCT273 is a positive-edge-triggered, D-type flip-flop with a direct clear (\overline{CLR}) input. This device uses a small-geometry BiCMOS technology. The output stage is a combination of bipolar and CMOS transistors that limits the output high level to two diode drops below V_{CC} . This resultant lowering of output swing (0 V to 3.7 V) reduces power-bus ringing [a source of electromagnetic interference (EMI)] and minimizes V_{CC} bounce and ground bounce and their effects during simultaneous output switching. The output configuration also enhances switching speed and is capable of sinking 48 mA.

Information at the data (D) inputs meeting the setup time requirements is transferred to the Q outputs on the positive-going edge of the clock (CLK) pulse. Clock triggering occurs at a particular voltage level and is not directly related to the transition time of the positive-going pulse. When CLK is at either the high or low level, the D input has no effect at the output. All eight flip-flops are controlled by a common clock (CLK) and a common reset (CLR). The outputs are placed in a low state when CLR is taken low, independent of the CLK.

The CD74FCT273 is characterized for operation from 0°C to 70°C.

FUNCTION TABLE (each flip-flop)


	INPUTS		ОИТРИТ
CLR	CLK	D	Q
L	Х	Х	L
Н	\uparrow	Н	Н
Н	\uparrow	L	L
Н	L	Χ	Q ₀



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.




logic symbol†




[†] This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

logic diagram (positive logic)



logic diagram, each flip-flop (positive logic)





SCBS737A - JULY 2000 - REVISED JULY 2000

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

DC supply voltage range, V _{CC}	0.5 V to 6 V
DC input diode current, I_{IK} ($V_I < -0.5 \text{ V}$)	
DC output diode current, I_{OK} ($V_O < -0.5$ V)	
DC output sink current per output pin, I _{OL}	
DC output source current per output pin, I _{OH}	
Continuous current through V _{CC} , I _{CC}	
Continuous current through GND	
Package thermal impedance, θ _{JA} (see Note 1): E package	69°C/W
M package	
Storage temperature range, T _{stg}	-65°C to 150°C

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

recommended operating conditions (see Note 2)

		MIN	MAX	UNIT
Vcc	Supply voltage	4.75	5.25	V
VIH	High-level input voltage	2		V
V _{IL}	Low-level input voltage		0.8	V
٧ _I	Input voltage	0	VCC	V
Vo	Output voltage	0	VCC	V
ІОН	High-level output current		-15	mA
loL	Low-level output current		48	mA
Δt/Δν	Input transition rise or fall rate	0	10	ns/V
TA	Operating free-air temperature	0	70	°C

NOTE 2: All unused inputs of the device must be held at V_{CC} or GND to ensure proper device operation. Refer to the TI application report, Implications of Slow or Floating CMOS Inputs, literature number SCBA004.

electrical characteristics over recommended operating temperature range (unless otherwise noted)

PARAMETER	TEST CONDITIONS	Vaa	T _A = 2	25°C	MIN	MAX	UNIT	
FARAMETER	TEST CONDITIONS	VCC	MIN	MAX	IVIIIV	IVIAA	UNIT	
VIK	$I_{I} = -18 \text{ mA}$	4.75 V		-1.2		-1.2	V	
Voн	$I_{OH} = -15 \text{ mA}$	4.75 V	2.4		2.4		V	
V _{OL}	I _{OL} = 48 mA	4.75 V		0.55		0.55	V	
Ι _Ι	$V_I = V_{CC}$ or GND	5.25 V		±0.1		±1	μΑ	
I _{OZ}	$V_O = V_{CC}$ or GND	5.25 V		±0.5		±10	μΑ	
los [‡]	$V_I = V_{CC}$ or GND, $V_O = 0$	5.25 V	-60		-60		mA	
Icc	$V_I = V_{CC}$ or GND, $I_O = 0$	5.25 V		8		80	μΑ	
ΔICC§	One input at 3.4 V, Other inputs at V _{CC} or GND	5.25 V		1.6		1.6	mA	
C _i	$V_I = V_{CC}$ or GND					10	pF	

Not more than one output should be tested at a time, and the duration of the test should not exceed 100 ms.



NOTE 1: The package thermal impedance is calculated in accordance with JESD 51.

[§] This is the increase in supply current for each input at one of the specified TTL voltage levels rather than 0 V or VCC.

CD74FCT273 BiCMOS OCTAL D-TYPE FLIP-FLOP WITH RESET

SCBS737A - JULY 2000 - REVISED JULY 2000

timing requirements over recommended operating conditions (unless otherwise noted) (see Figure 1)

			MIN	MAX	UNIT
fclock	Clock frequency			70	MHz
	Pulse duration	CLR low	7		no
t _W	Pulse duration	CLK high or low	7		ns
	Code in time	Data before CLK↑	3		no
t _{su}	Setup time	CLR before CLK↑	4		ns
th	Hold time	Data after CLK↑	2		ns


switching characteristics over recommended operating conditions, C_L = 50 pF (unless otherwise noted) (see Figure 1)

PARAMETER	FROM	то	T _A = 25°C	MIN	MAX	UNIT
FARAMETER	(INPUT)	(OUTPUT)	TYP	IVIIIN	IVIAA	UNII
f _{max}				70		MHz
	CLK	A O	7	2	13	no
^t pd	CLR	Any Q	8	2	13	ns

operating characteristics, $T_A = 25^{\circ}C$

	PARAMETER	TEST C	ONDITIONS	TYP	UNIT
C _{pd}	Power dissipation capacitance	No load,	f = 1 MHz	36	pF

PARAMETER MEASUREMENT INFORMATION



NOTES: A. C_I includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR \leq 1 MHz, Z_O = 50 Ω , t_f and t_f = 2.5 ns.
- D. The outputs are measured one at a time with one input transition per measurement.
- E. tpLZ and tpHZ are the same as tdis.
- F. tpzL and tpzH are the same as ten.
- G. tpHL and tpLH are the same as tpd.

Figure 1. Load Circuit and Voltage Waveforms



www.ti.com 30-Jul-2024

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
CD74FCT273E	ACTIVE	PDIP	N	20	20	RoHS & Non-Green	NIPDAU	N / A for Pkg Type	0 to 70	CD74FCT273E	Samples
CD74FCT273M	OBSOLETE	SOIC	DW	20		TBD	Call TI	Call TI	0 to 70	74FCT273M	

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 7-Feb-2024

TUBE



*All dimensions are nominal

Device Package Nat		Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)	
CD74FCT273E	N	PDIP	20	20	506	13.97	11230	4.32	

N (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



NOTES:

- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.





SOIC



NOTES:

- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm per side.
- 5. Reference JEDEC registration MS-013.



SOIC



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SOIC



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated