

# TPA5052EVM

## Contents

1	Introduction .....	1
2	Operation .....	2
3	Advanced Features.....	3
4	Reference.....	5
5	TPA5052EVM Schematic Diagram .....	10

## List of Figures

1	Top Layer of TPA5052EVM .....	3
2	Top Layer of TPA5052EVM .....	4
3	Bottom Layer of TPA5052EVM .....	4
4	TPA5052EVM Top Layer .....	5
5	TPA5052EVM Second Layer .....	6
6	TPA5052EVM Third Layer .....	6
7	TPA5052EVM Bottom Layer .....	7

## List of Tables

1	Bill of Materials.....	8
---	------------------------	---

## 1 Introduction

### 1.1 Description

The TPA5052 evaluation module (EVM) consists of a single TPA5052 audio delay device, along with other external components mounted on a printed-circuit board (PCB). It can be used to digitally delay both channels by up to 8191 samples (with a 48-kHz sampling rate, that equates to more than 170 ms of delay).

The TPA5052EVM is designed so that analog music can be input to the board. The music is converted to I<sup>2</sup>S digital format where the TPA5052 delays it. The music then is converted back to analog where it is fed to the TPA4411 audio amplifier. The output of the TPA4411 is connected to a 3.5-mm stereo headphone jack. A simple pair of stereo headphones are all that are required to listen to the music. This allows the user to quickly and easily use the TPA5052EVM to delay the television audio to synchronize with the video. Probe points also are provided.

Additional evaluation may be performed with small modifications that allow for direct interaction with the TPA5052 in I<sup>2</sup>S format.

## 1.2 TPA5052EVM Specifications

+5 V	Supply Voltage	5 V
$I_{DD}$	Supply current	150 mA maximum

## 2 Operation

### 2.1 Quick Start List

Follow these steps to use the TPA5052EVM

### 2.2 Power Supply

1. Ensure that all external power sources are set to OFF.
2. Connect an external regulated power supply set to 5 V to the module +5V (**J8**) and GND (**J9**), taking care to observe marked polarity.

### 2.3 EVM Preparation

3. Ensure that the shunts are open on jumpers **J3** through **J7**. This jumper setting sets the TPA5052 to operate with minimum delay. If more delay is required, shunt the appropriate jumpers. See the TPA5052 data sheet for more information about delay settings.
4. Connect a cable from a music source, such as a CD player, to input jack **J1**. Insert headphones into output jack **J2**.

### 2.4 Operation

5. Turn on the power supply for the TPA5052EVM.
6. The Power On LED glows green, indicating that the EVM has adequate power.
7. Start playing music with the music source.
8. Place headphones on head and listen to the music.




Figure 1. Top Layer of TPA5052EVM

### 3 Advanced Features

The TPA5052EVM is designed to allow for extensive evaluation of the TPA5052. Removing a few components allows for direct access to the TPA5052 and measurement of the delay.

#### 3.1 Configuration for Advanced Measurements

If the need arises to directly evaluate the TPA5052 with digital data, follow these steps.

1. Ensure that no power supply or signal cables are connected to the TPA5052EVM.
2. Locate and remove resistors **R14** and **R15** on layer four of the PCB.
3. Locate and remove resistor **R16** on the top layer of the PCB.
4. Connect LRCLK of the source to **J10**. Be sure to ground the accompanying LRCLK ground to the adjoining GND pin for optimal performance
5. Connect BCLK of the source to **J11**. Be sure to ground the accompanying BCLK ground to the adjoining GND pin for optimal performance
6. Connect DATA of the source to **J12**. Be sure to ground the accompanying DATA ground to the adjoining GND pin for optimal performance
7. Connect the DATA\_OUT pin **J13** and the associated GND to the measurement device.
8. Connect an external regulated power supply set to 5 V to the module +5V (**J8**) and GND (**J9**), taking care to observe marked polarity.
9. Turn on digital audio source.
10. The delay is changed by closing or opening jumpers **J3** through **J7**, and measuring the output with respect to the input.




Figure 2. Top Layer of TPA5052EVM




Figure 3. Bottom Layer of TPA5052EVM

## 4 Reference

### 4.1 TPA5052EVM PCB Layers




Figure 4. TPA5052EVM Top Layer




Figure 5. TPA5052EVM Second Layer




Figure 6. TPA5052EVM Third Layer




Figure 7. TPA5052EVM Bottom Layer

## 4.2 TPA5052EVM Bill of Materials

**Table 1. Bill of Materials**

Part No.	QTY	Value	Description	Distributor No. <sup>(1)</sup>	Manufacturer Part No.
R1, R2	2	1kΩ	Resistor, 1kΩ, 1/10W, 1%, 0603	311-1.00KHRTR-ND	Yageo RC0603FR-071KL
R3, R11	2	470Ω	Resistor, 470Ω, 1/10W, 1%, 0603	311-470HRTR-ND	Yageo RC0603FR-07470RL
R4, R5, R6, R7, R8, R18	6	100kΩ	Resistor, 100kΩ, 1/10W, 1% , 0603	311-100KHRTR-ND	Yageo RC0603FR-07100KL
R9, R14, R15, R16, R17	5	40.2Ω	Resistor, 40.2Ω, 1/10W, 1%, 0603	311-40.2HRTR-ND	Yageo RC0603FR-0740R2L
R10	1	0Ω Jumper	Resistor, 0Ω, 1/10W, 5%, 0603	311-0.0GRTR-ND	Yageo RC0603JR-070RL
R12, R13	2	300Ω	Resistor, 300Ω, 1/10W, 1%, 0603	311-300HRTR-ND	Yageo RC0603FR-07300RL
C1, C3, C5, C10, C13, C16, C22	7	0.1μF	Cap, Ceramic, 0.1μF, 10V, X7R, +/-10%, 0603	399-1095-1-ND	Kemet C0603C104K8RACTU
C2, C4, C11, C12, C14, C15	6	10μF	Cap, Ceramic, 10μF, 10V, 10%, 0805	490-3905-1-ND	Murata GRM21BR71A106KE51 L
C6, C8	4	4700pF	Cap, Ceramic, 4700pF, 50V, 10%, X7R, 0603	445-1310-1-ND	TDK C1608X7R1H472K
C7, C9	2	1μF	Cap, Ceramic, 1μF, 16V, 10%, X7R, 0805	399-1284-1-ND	Kemet C0805C105K4RACTU
C17, C18, C19	3	2.2μF	Cap, Ceramic, 2.2μF, 10V, 20%, X5R, 0603	490-1546-1-ND	Murata GRM188R61A225ME34 D
C20, C21	2	.018μF	Cap, Ceramic, .018μF, 50V, 10%, X7R, 0805	399-1162-1-ND	Kemet C0805C183K5RACTU
C23, C24	2	0.1μF	Cap, Ceramic, .1μF, 16V, 10%, X7R, 0402	399-3521-1-ND	Kemet C0402C104K4RACTU
FB1, FB2, FB3, FB4	4	600Ω Ferrite Bead	Ferrite Bead, 600Ω, 500mA, 200 milliohms DAR, 0805	445-1554-1-ND	TDK MMZ2012R601A
CR1	1	Green LED	Green LED, 0805	67-1553-1-ND	Lumen S.L.-LXT0805GW-TR
CR2	1	Red LED	Red LED, 0805	67-1552-1-ND	Lumen S.L.-LXT0805IW-TR
J1, J2	2		Headphone Jack, 3.5mm, Black		Chaconne, Inc SEX-3500-3N
J3, J4, J5, J6, J7	5		Jumper, Position, 2mm Header	2163S-36-ND	Norcomp 2163-36-01-P2
J3, J4, J5, J6, J7	5		2mm Shunts	A26244-ND	Tyco/AMP 382575-2
J8, J9	2		Banana Jack with Knurled Thumbnut	J587-ND	Johnson 111-2223-001
J10, J11, J12, J13	4		Jumper, Position, 2mm Header	2163S-36-ND	Norcomp 2163-36-01-P2
TP1, TP2, TP3	3		Test Point, Small, SMT	5015KCT-ND	Keystone 5015
Y1	1	12.288MHz	Clock, Oscillator, 12.288 MHZ, 3.3V	CTX266LVCT-ND	CTS CB3LV-3C-12M2880-T
U1	1	TPA5052	IC, TPA5052, Stereo Digital Audio Lip-Sync Delay	Texas Instruments: TPA5052RSA	Texas Instruments

<sup>(1)</sup> Distributor is Digikey, unless otherwise specified.




**Table 1. Bill of Materials (continued)**

Part No.	QTY	Value	Description	Distributor No. <sup>(1)</sup>	Manufacturer Part No.
U2	1	TPA4411	IC, TPA4411, 80mW Cap-Free Stereo Headphone Driver	Texas Instruments: TPA4411RTJ	Texas Instruments
U3	1	PCM1808	IC, PCM1808, Single Ended, Analog-Input 24-Bit, 96kHz Stereo A/D Converter	Texas Instruments: PCM1808PW	Texas Instruments
U4	1	PCM1781	IC, PCM1781, 24-Bit, 192kHz Sampling, Enhanced Multilevel, Delta-Sigma, Audio Digital-to-Analog Converter	Texas Instruments: PCM1781DBQ	Texas Instruments
U5	1	TPS77533	IC, TPS77533, 3.3V 500MA LDO REG	Texas Instruments: TPS77533D	Texas Instruments
	4		Standoff, Aluminum, Hex, 4-40 x .625"	1808K-ND	Keystone 1808
	4		Screw, 4-40 x .25", PPH		

## **5 TPA5052EVM Schematic Diagram**

The TPA5052EVM schematic diagram is appended to this page.



## EVALUATION BOARD/KIT IMPORTANT NOTICE

Texas Instruments (TI) provides the enclosed product(s) under the following conditions:

This evaluation board/kit is intended for use for **ENGINEERING DEVELOPMENT, DEMONSTRATION, OR EVALUATION PURPOSES ONLY** and is not considered by TI to be a finished end-product fit for general consumer use. Persons handling the product(s) must have electronics training and observe good engineering practice standards. As such, the goods being provided are not intended to be complete in terms of required design-, marketing-, and/or manufacturing-related protective considerations, including product safety and environmental measures typically found in end products that incorporate such semiconductor components or circuit boards. This evaluation board/kit does not fall within the scope of the European Union directives regarding electromagnetic compatibility, restricted substances (RoHS), recycling (WEEE), FCC, CE or UL, and therefore may not meet the technical requirements of these directives or other related directives.

Should this evaluation board/kit not meet the specifications indicated in the User's Guide, the board/kit may be returned within 30 days from the date of delivery for a full refund. **THE FOREGOING WARRANTY IS THE EXCLUSIVE WARRANTY MADE BY SELLER TO BUYER AND IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESSED, IMPLIED, OR STATUTORY, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE.**

The user assumes all responsibility and liability for proper and safe handling of the goods. Further, the user indemnifies TI from all claims arising from the handling or use of the goods. Due to the open construction of the product, it is the user's responsibility to take any and all appropriate precautions with regard to electrostatic discharge.

**EXCEPT TO THE EXTENT OF THE INDEMNITY SET FORTH ABOVE, NEITHER PARTY SHALL BE LIABLE TO THE OTHER FOR ANY INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES.**

TI currently deals with a variety of customers for products, and therefore our arrangement with the user **is not exclusive.**

TI assumes **no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein.**

Please read the User's Guide and, specifically, the Warnings and Restrictions notice in the User's Guide prior to handling the product. This notice contains important safety information about temperatures and voltages. For additional information on TI's environmental and/or safety programs, please contact the TI application engineer or visit [www.ti.com/esh](http://www.ti.com/esh).

No license is granted under any patent right or other intellectual property right of TI covering or relating to any machine, process, or combination in which such TI products or services might be or are used.

### FCC Warning

This evaluation board/kit is intended for use for **ENGINEERING DEVELOPMENT, DEMONSTRATION, OR EVALUATION PURPOSES ONLY** and is not considered by TI to be a finished end-product fit for general consumer use. It generates, uses, and can radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC rules, which are designed to provide reasonable protection against radio frequency interference. Operation of this equipment in other environments may cause interference with radio communications, in which case the user at his own expense will be required to take whatever measures may be required to correct this interference.

### EVM WARNINGS AND RESTRICTIONS

It is important to operate this EVM within the voltage supply range of 4.5 V to 5.5 V.

Exceeding the specified input range may cause unexpected operation and/or irreversible damage to the EVM. If there are questions concerning the input range, please contact a TI field representative prior to connecting the input power.

Applying loads outside of the specified output range may result in unintended operation and/or possible permanent damage to the EVM. Please consult the EVM User's Guide prior to connecting any load to the EVM output. If there is uncertainty as to the load specification, please contact a TI field representative.

During normal operation, some circuit components may have case temperatures greater than 85°C. The EVM is designed to operate properly with certain components above 85°C as long as the input and output ranges are maintained. These components include but are not limited to linear regulators, switching transistors, pass transistors, and current sense resistors. These types of devices can be identified using the EVM schematic located in the EVM User's Guide. When placing measurement probes near these devices during operation, please be aware that these devices may be very warm to the touch.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2006, Texas Instruments Incorporated

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

<b>Products</b>		<b>Applications</b>	
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>	Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>	Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>	Broadband	<a href="http://www.ti.com/broadband">www.ti.com/broadband</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>	Digital Control	<a href="http://www.ti.com/digitalcontrol">www.ti.com/digitalcontrol</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>	Military	<a href="http://www.ti.com/military">www.ti.com/military</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>	Optical Networking	<a href="http://www.ti.com/opticalnetwork">www.ti.com/opticalnetwork</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>	Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>	Telephony	<a href="http://www.ti.com/telephony">www.ti.com/telephony</a>
Low Power Wireless	<a href="http://www.ti.com/lpw">www.ti.com/lpw</a>	Video & Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>
		Wireless	<a href="http://www.ti.com/wireless">www.ti.com/wireless</a>

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2007, Texas Instruments Incorporated