



Certificate of Compliance

Certificate: 70220402

Master Contract: 220991

Project: 70220402

Date Issued: 2019-10-04

Issued To: Texas Instruments, Inc.
12500 TI Blvd
MS 8701
Dallas, Texas, 75243
United States

Attention: Saleem Marwat

The products listed below are eligible to bear the CSA Mark shown with adjacent indicator▲



Issued by: Martin Buchanan
Martin Buchanan, P. Eng.

PRODUCTS

CLASS - C907330 - ELECTRONIC COMPONENTS Optoisolators

Component Acceptance of Optoisolator-Like Capacitive Coupling Devices:

Device (SOIC 8W DWV 8)	Ratings		Clauses of Standard/Notice	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
ISO1042BDWV ISO1042DWV ISO1042BQDWVQ1 ISO1042QDWVQ1	5.0	125	CSA 14-18 TЫ1 35, 6.2.1.1, 6.2.1.1/6.2.10, 6.8.1.1 60950-1-07+A1+A2 2.10.3.3, 2.10.4.2, 2 10.4.3, 2 10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1-14 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1 5.3, 4.5.8, 5.4.9.1, 4.1 2 61010-1-12+A1 K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10 60601-1:14 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7	-	-	8.5



Certificate: 70220402
Project: 70220402

Master Contract: 220991
Date Issued: 2019-10-04

Device (SOIC 8W DWV 8)	Ratings		Clauses of Standard/Notice	Internal		External
	kV	°C		Creepage (mm)	Dist Thru (mm)	Creep/Clear (mm)
			IEC 60950-1 2nd Ed.,+A1+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1-14 5.4.3, 5.4.2, 5.4.4.4, 5.4.7, 5.4.1.5.3, 4.5.8, 5.4.9.1, 4.1.2 61010-1 3 rd Ed K.3, K.4, 6.7.1.3, 6.7.2.2.2 A.17, K.6x1.6, K.7x1.6, 10 60601-1 Ed.3+A1 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7 EN 60950-1:2006+A1+A12+A2 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2 62368-1:2014/A11:2017 2.10.3.3, 2.10.4.2, 2.10.4.3, 2.10.5.4a, 2.10.11, 4.5.2, 5.2			

Suffix R may be used after DWV for reel packaging.

Notes:

1. The ISO1042BDWV, ISO1042BQDWVQ1, ISO1042DWV and ISO1042QDWVQ1 devices meet basic insulation requirements for 850Vrms for CSA 60950-1-07+A1+A2, EN 60950-1:2006+A1+A12+A2, IEC 60950-1 2nd Ed.+A1+A2, CSA 62368-1-14, EN 62368-1:2014/A11:2017 and IEC 62368-1 2nd Ed. (pollution degree 2, material group III)
2. The ISO1042DWV and ISO1042QDWVQ1 devices meet reinforced insulation requirements for 425Vrms for CSA 60950-1-07+A1+A2, EN 60950-1:2006+A1+A12+A2, IEC 60950-1 2nd Ed.+A1+A2, CSA 62368-1-14, EN 62368-1:2014/A11:2017 and IEC 62368-1 2nd Ed. (pollution degree 2, material group III)
3. For CSA 61010-1-12+A1 and IEC 61010-1 3rd Ed.+A1 the ISO1042BDWV, ISO1042BQDWVQ1, ISO1042DWV and ISO1042QDWVQ1 devices meet 600Vrms for basic insulation and the ISO1042DWV and ISO1042QDWVQ1 devices 300Vrms for reinforced insulation based on 61010-1 Cl 14.1 a) for use in 61010-1 end products because they meet the requirements of the 62368-1 evaluation. (pollution degree 2, material group III)
4. For CSA 60601-1:14 and IEC60601-1 Ed.3+A1 for 2 MOPP for 268Vrms, the ISO1042DWV and ISO1042QDWVQ1 devices meet clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7. The risk management process is not applicable to these clauses.
5. Case material CTI=600V, erosion depth 0.012mm. (meets material group I)
6. Evaluated by thermal cycling and other tests for a temperature rating of 125C.
7. The creepage and clearance has been evaluated for altitudes ≤ 2000m, in pollution degree 2, material group III and overvoltage category II except where specified above.

These devices are Component Accepted as components for use in other Certified equipment where the suitability of the combination shall be determined by investigation in the final application.



Certificate: 70220402
Project: 70220402

Master Contract: 220991
Date Issued: 2019-10-04

APPLICABLE REQUIREMENTS

CAN/CSA-C22.2 No 14-18 - Industrial Control Equipment
CAN/CSA-C22.2 No 60950-1-07+A1+A2 - Information Technology Equipment - Safety - Part 1:
General Requirements (Bi-national Standard, with UL 60950-1)
CAN/CSA-C22.2 No. 62368-1-14 - Audio/video, information and communication technology
equipment– Part 1: Safety requirements
IEC 60950-1 2nd Ed.+A1+A2 - Information Technology Equipment - Safety - Part 1: General Requirements
IEC 62368-1:2014 Ed. 2 - Audio/video, information and communication technology
equipment– Part 1: Safety requirements
EN 60950-1:2006+A1+A12+A2 - Information Technology Equipment - Safety - Part 1: General Requirements
EN 62368-1:2014/A11:2017 - Audio/video, information and communication technology
equipment - Part 1: Safety requirements (IEC 62368-1:2014,
modified)

Clauses 6.7.1.3, 6.7.2.1 or K.1 to K.4, 6.7.2.2.1, 6.7.2.2.2 or tbK.9, A.17, tbK.5x1.6, K.6x1.6, K.7x1.6, 10
of

CAN/CSA C22.2 No. 61010-1-12, UPD1: 2015, UPD2: 2016, AMD1: 2018 - Safety Requirements for
Electrical Equipment for Measurement, Control, and Laboratory Use, Part
1: General Requirements (Tri-national standard, with UL 61010-1 Ed. 3
(2012), AMD1: 2018 and ANSI/ISA-61010-1 (82.02.01))

and

IEC 61010-1:2010 Ed. 3.1:2017 01 - Safety Requirements for Electrical Equipment for Measurement, Control
and Laboratory Use - Part 1: General Requirements

Clauses 8.5.5.1, 8.8.2, 8.8.3x1.6, 8.9.3.2, 8.9.3.4, 8.9.1.15, 8.9.1.7
of

CAN/CSA C22.2 60601-1:14 - Medical Electrical Equipment Part 1: General requirements for basic safety
and general performance (Adopted IEC60601-1:2005 Edition 3.0
+Amendment 1, 2012-07, MOD)

and

IEC60601-1:2005 Ed 3.0+A1 - Medical Electrical Equipment Part 1: General requirements for basic
safety and general performance

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2023, Texas Instruments Incorporated