

C6-Integra™ OMAP-L1x DSP+ARM® Processors



Multimedia performance and low power with C6-Integra OMAP-L1x DSP+ARM processors

Enabling developers to integrate feature-rich GUIs into their portable designs, the C6-Integra OMAP-L1x generation of DSP+ARM processors includes an ARM9™ core along with a TMS320C674x digital signal processor. Devices contain a variety of peripherals for networking, and will run Linux®, Microsoft® Windows® Embedded CE or the DSP/BIOS™ real-time kernel for operating system flexibility. The product line is also pin-for-pin compatible with select devices in the TMS320C674x fixed-/floating-point DSP generation and AM1x Sitara™ ARM MPU product generation. The combination of peripherals, architectures and price points starting at under U.S. \$17 for 1000-unit quantities allows designers to choose the right processor for their application needs.

Combining broad operating system flexibility with low-cost and easy-to-use development

tools allows for faster prototyping through a familiar and robust development environment.

Designers can take advantage of the 375-/456-MHz ARM9 and choose from Linux, Windows CE or an operating system of their choice to add feature-rich GUIs or touchscreen support.

Through pin-for-pin compatibility with other C6-Integra OMAP-L1x products as well as the C674x DSP generation, C6-Integra OMAP-L1x processors offer an unprecedented level of scalability. The high-performance and high-precision C674x embedded processor cores, flexible cache architecture, enhanced DMA subsystem and dynamic power management (DPM) functionality provide system designers with a flexible and scalable platform to add portability to applications such as software-defined radio (SDR), portable instrumentation, portable data terminals, portable connectivity and other applications needing high performance, rich user interfaces or high-level operating systems.

Key features:

- Integrate feature-rich GUIs into portable designs
- Networking simplified with advanced peripherals
- Operating system flexibility with Linux, Windows Embedded CE or DSP/BIOS real-time kernel
- Pin-for-pin compatible with select devices in the TMS320C674x generation and TI AM1x Sitara ARM MPU devices
- Power consumption ranging from 12 mW* deep-sleep power to 480 mW† total power
- Smaller, ergonomic products with 13×13-mm, 16×16-mm and 17×17-mm packaging


processors give designers not only granularity for frequency and voltage, but also the ability to manipulate the individual peripherals to further optimize power consumption.

Designers will be able to save significant system power and cost through peripheral integration such as 10/100 EMAC, USB 1.1 Host/2.0 Host/Device/OTG, MMC/SD controllers, a universal parallel port (uPP)

Increase the battery life of applications through TI process technology

Combining industry-leading, cutting-edge 65-nm process technology with low-leakage transistor technology, C6-Integra OMAP-L1x processors offer high performance and scalability with power consumption as low as 12 mW* in deep-sleep mode, 37 mW† in standby mode and 480 mW‡ total power in active mode.

The high-performance and low-power silicon architecture and power management software technology used for C6-Integra OMAP-L1x



Note: Not all features in all products.

* Power-use scenario – deep sleep: 1.0-V core, idle ARM® DSP clock OFF, all peripherals clock OFF, RTC ON, PLL disabled, 25°C

† Power-use scenario – standby: 1.0-V core, idle ARM and DSP clock OFF, all peripherals clock OFF, RTC ON, PLL enabled, 25°C

‡ Power-use scenario – active: 70% max load of the DSP running at 300 MHz at 1.2 V, ARM running at 300 MHz doing typical activity (peripheral configurations, other housekeeping activities); mDDR 133 MHz/16 bit accessed 50% of the time, McBSP, SPI and GPIOs peripherals are active, 25°C

Technical details

Architectural features

- 375-/456-MHz ARM9™ processor
- High-precision 32-/64-bit C674x fixed-/floating-point DSP core combined with ARM9

System integration

- Up to 448 KB of internal memory through a combination of L1/L2 cache and internal RAM memory
- VPIF interface for a glueless interface to many image sensors and display drivers

- Universal Parallel Port (uPP) provides a direct interface to FPGAs, high-speed A/Ds, data converters and inter-processor communication
- Up to 64-channel DMA supporting 1D, 2D and 3D data transfers
- NAND flash controller with 8-/16-bit interface for commands, addresses and data
- Connectivity: host DMA port, UARTs, McASP/McBSPs, SPI, I²C, MMC/SD controllers, USB 1.1/ 2.0 interfaces, SATA, eCAP, eQEP
- Variety of memory controller options providing glueless connection to multiple

banks of external mDDR, DDR2, SDRAM, SRAM and Flash

- Multiple package options: QFP, BGA, nFBGA in various sizes and ball pitches [commercial (0°C to 90°C), industrial (-40°C to 105°C) and automotive (-40°C to 125°C) temperature ranges].

Applications

- Software-defined radio
- Portable instrumentation
- Portable data terminals
- Portable connectivity

for interfacing with FPGAs, data converters and other inter-processor communication, UHPI, multi-channel serial ports and an LCD controller negating the need for external processors and/or logic. On-chip memory scalability options of up to 448 KB reduce the need for external memory in some applications saving both power and cost.

Availability of a wide selection of packages on some C6-Integra™ OMAP-L1x devices cater to those applications that have varying size constraints.

Get started quickly

To get started quickly, designers can purchase C6-Integra OMAP-L1x development kits with built-in emulation for less than U.S. \$500 and low-cost Hawkboard community board for less than U.S. \$100. All development kits contain Linux board support packages, Codec Engine and the associated debugging environment. Additional software and tools are also available by TI third parties. C6-Integra OMAP-L1x processors are supported by Linux tools and Code Composer Studio™ (CCStudio) integrated development environment.

For more information on C6-Integra OMAP-L1x DSP+ARM processors, visit

www.ti.com/omapl1x.

TI Worldwide Technical Support

Internet

TI SC Product Information Center Home Page
support.ti.com

TI E2E™ Community Home Page
e2e.ti.com

Product Information Centers

Americas	Phone	+1(972) 644-5580
Brazil	Phone	0800-891-2616
Mexico	Phone	0800-670-7544
	Fax	+1(972) 927-6377
	Internet/E-mail	support.ti.com/sc/pic/americas.htm

Europe, Middle East, and Africa

Phone	
European Free Call	00800-ASK-TEXAS (00800 275 83927)
International	+49 (0) 8161 80 2121
Russian Support	+7 (4) 95 98 10 701

Note: The European Free Call (Toll Free) number is not active in all countries. If you have technical difficulty calling the free call number, please use the international number above.

Fax	+(49) (0) 8161 80 2045
Internet	support.ti.com/sc/pic/euro.htm
Direct Email	asktexas@ti.com

Japan

Phone	Domestic	0120-92-3326
Fax	International	+81-3-3344-5317
	Domestic	0120-81-0036

Internet/Email

International	support.ti.com/sc/pic/japan.htm
Domestic	www.tij.co.jp/pic

Asia

Phone	
International	+91-80-41381665
Domestic	<u>Toll-Free Number</u>

Note: Toll-free numbers do not support mobile and IP phones.

Australia	1-800-999-084
China	800-820-8682
Hong Kong	800-96-5941
India	1-800-425-7888
Indonesia	001-803-8861-1006
Korea	080-551-2804
Malaysia	1-800-80-3973
New Zealand	0800-446-934
Philippines	1-800-765-7404
Singapore	800-886-1028
Taiwan	0800-006800
Thailand	001-800-886-0010

Fax +8621-23073686

Email tiasia@ti.com

ti-china@ti.com

Internet support.ti.com/sc/pic/asia.htm

Important Notice: The products and services of Texas Instruments Incorporated and its subsidiaries described herein are sold subject to TI's standard terms and conditions of sale. Customers are advised to obtain the most current and complete information about TI products and services before placing orders. TI assumes no liability for applications assistance, customer's applications or product designs, software performance, or infringement of patents. The publication of information regarding any other company's products or services does not constitute TI's approval, warranty or endorsement thereof.

The platform bar C64x+, C6-Integra, Code Composer Studio, DSP/BIOS, E2E, Sitara and TMS320C64x+ are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.

B122010

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
RF/IF and ZigBee® Solutions	www.ti.com/lprf

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video
Wireless	www.ti.com/wireless-apps

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated