

## PMP40960 REV E1 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C1, C21, C22, C24	4	0.1uF	C0603C104K5RACAUTO	Kemet	CAP, CERM, 0.1 $\mu$ F, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
C2, C3, C4, C5	4	22uF	GCM31CR71A226KE02L	MuRata	CAP, CERM, 22 uF, 10 V, +/- 20%, X7R, 1206	1206
C6, C28	2	0.1uF	CL21B104MBCNNNC	Samsung	CAP, CERM, 0.1 $\mu$ F, 50 V, +/- 20%, X7R, 0805	0805
C7, C9, C11, C30, C35	5	10uF	GRT31CR61H106KE01L	MuRata	CAP, CERM, 10 uF, 50 V, +/- 10%, X5R, AEC-Q200 Grade 1, 1206	1206
C12, C14	2	2.2uF	885012106018	Würth Elektronik	CAP, CERM, 2.2 uF, 16 V, +/- 20%, X5R, 0603	0603
C13	1	10uF	C2012X7R1A106M125AC	TDK	CAP, CERM, 10 uF, 10 V, +/- 20%, X7R, 0805	0805
C15, C31, C37, C39, C40, C41, C42	7	0.1uF	GRM155R71C104JA88D	MuRata	CAP, CERM, 0.1 uF, 16 V, +/- 5%, X7R, 0402	0402
C17, C19	2	2.2uF	GCM31CR71H225KA55L	MuRata	CAP, CERM, 2.2 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 1206	1206
C18, C20	2	2200pF	C0603C222K5RACTU	Kemet	CAP, CERM, 2200 pF, 50 V, +/- 10%, X7R, 0603	0603
C27	1	120uF	EEHZKV121XUP	Panasonic	CAP, AL, 120 uF, 35 V, +/- 20%, 0.035 ohm, AEC-Q200, SMD	
C49	1	4700pF	GCM188R71H472KA37D	MuRata	CAP, CERM, 4700 pF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
J1	1		1757242	Phoenix Contact	Header (Shrouded), 5.08 mm, 2x1, Tin, R/A, TH	Header, 5.08 mm,
J3	1		632723300011	Würth Elektronik	Connector, Receptacle, USB Type C, R/A	Connector,
L1	1	880 ohm	74279252	Würth Elektronik	Ferrite Bead, 880 ohm @ 100 MHz, 4 A, 1812	1812
L2	1	1uH	XAL5030-102MEB	Coilcraft	Inductor, Shielded, CAPPR7.5-16X20, 1 $\mu$ H, 11.1 A, 0.0094 ohm, AEC-Q200 Grade 1, SMD	5.3x31.x5.5mm
L3	1	4.7uH	XAL8080-472ME	Coilcraft	Inductor, Shielded, Composite, 4.7 uH, 10.5 A, 0.00889 ohm, SMD	8.1 x 8 x 8.6mm
L8, L9	2	0	CRCW12060000Z0EAHP	Vishay-Dale	RES, 0, 0.75 W, AEC-Q200 Grade 0, 1206	1206
R1	1	10	CRCW060310R0JNEA	Vishay-Dale	RES, 10, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R2	1	20k	CRCW040220K0JNED	Vishay-Dale	RES, 20 k, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R3, R12	2	5.1k	CRCW04025K10JNED	Vishay-Dale	RES, 5.1 k, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R4, R8	2	39k	ERJ-2GEJ393X	Panasonic	RES, 39 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0402	0402
R5, R9, R11	3	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
R7	1	8.87k	CRCW04028K87FKED	Vishay-Dale	RES, 8.87 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R10	1	0	MCR01MZPJ000	Rohm	RES, 0, 5%, 0.063 W, 0402	0402
RT1	1	470k	NCP18WM474J03RB	MuRata	Thermistor NTC, 470k ohm, 5%, 0603	0603
U1	1		TPS25854QRPQRQ1	TI	Single 3-A USB Type-C® Charging Port With Synchronous Step-Down DC/DC Converter and Programmable Current Limit	
H1	1				Circuit Board Shielding, SMT	
C8	0	22uF	GCM31CR71A226KE02L	MuRata	CAP, CERM, 22 uF, 10 V, +/- 20%, X7R, 1206	1206
C10, C34, C47, C48	0	10uF	GRT31CR61H106KE01L	MuRata	CAP, CERM, 10 uF, 50 V, +/- 10%, X5R, AEC-Q200 Grade 1, 1206	1206
C26	0	2.2uF	GCM31CR71H225KA55L	MuRata	CAP, CERM, 2.2 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 1206	1206
C29, C50	0	2200pF	C0603C222K5RACTU	Kemet	CAP, CERM, 2200 pF, 50 V, +/- 10%, X7R, 0603	0603
C32	0	0.1uF	C0603C104K5RACAUTO	Kemet	CAP, CERM, 0.1 $\mu$ F, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
C38	0	0.1uF	CEU4J2X7R1H104K125AE	TDK	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0805	0805
R6	0	5.1k	CRCW04025K10JNED	Vishay-Dale	RES, 5.1 k, 5%, 0.063 W, AEC-Q200 Grade 0, 0402	0402

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](http://ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2021, Texas Instruments Incorporated