

Comment	Description	Designator	Footprint	LibRef	Quantity
Printed Circuit Board	Printed Circuit Board	IPC81		CMP-0003618-2	1
C1005X7R1H104K050BB	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, 0402	C1, C7, C8	0402	CMP-0006297-2	3
GCM21BR71C475KA73L	CAP, CERM, 4.7 uF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0805	C2	0805_HV	CMP-0008020-2	1
04025A101FAT2A	CAP, CERM, 100 pF, 50 V, +/- 1%, COG/NPO, 0402	C3, C4, C13, C14, C16, C17	0402	CMP-0006196-2	6
C1005XR1E105K050BC	CAP, CERM, 1 uF, 25 V, +/- 10%, X5R, 0402	C5, C6	0402	CMP-0006276-2	2
C1608XR1V475K080AC	CAP, CERM, 4.7 uF, 35 V, +/- 10%, X5R, 0603	C9, C10, C21	0603	CMP-0007022-5	3
C3216X7R1E106M160AE	CAP, CERM, 10 uF, 25 V, +/- 20%, X7R, 1206_190	C11, C12	1206_190	CMP-0008692-2	2
CLO5B224KO5NNNC	CAP, CERM, 0.22 uF, 16 V, +/- 10%, X7R, 0402	C15, C19	0402	CMP-0860563-1	2
GRT155R61E225KE13D	CAP, CERM, 2.2 uF, 25 V, +/- 10%, X5R, AEC-Q200 Grade 3, 0402	C18, C20	0402	CMP-0006716-2	2
C1206C223KDRACTU	CAP, CERM, 0.022 uF, 1000 V, +/- 10%, X7R, AEC-Q200 Grade 1, 1206	C22, C23	1206_190	CMP-0084048-1	2
C1812W104KDRACTU	CAP, CERM, 0.1 uF, 1000 V, +/- 10%, X7R, 1812	C24, C25	1812_254	CMP-0009326-2	2
GB01SLT06-214	Diode, Schottky, 650 V, 1 A, SMB	D1	SMB	CMP-0076998-2	1
MBR0520LT1G	Diode, Schottky, 20 V, 0.5 A, SOD-123	D2, D3	SOD-123	CMP-0028524-2	2
M50-3900642		J1	FP-M50-3900642_HDR12-MFG	CMP-0093439-1	1
SDEM20161T-4R7MS	4.7uH Unshielded Inductor 1.1A 426mOhm Max 0806 (2016 Metric)	L1, L2	FP-SDEM20161T-4R7MS_SMD2-MFG	CMP-0089347-1	2
ACM2520-601-2P-T002	Coupled inductor, 0.2 A, 0.45 ohm, SMD	L3	TDK_ACM2520-2P	CMP-0013161-2	1
3621-0-32-15-00-00-08-0		PGND, SW, TP1, TP2, TP3, Vbulk+	MIII-Max_3621-0-32-xx-00-00-08-0	CMP-0082316-1	6
RC0402FR-0749R9L	RES, 49.9, 1%, 0.063 W, 0402	R1, R2, R5, R6	0402	CMP-0026738-1	4
ERJ-2GE0R00X	RES, 0, 5%, 0.1 W, AEC-Q200 Grade 0, 0402	R4	0402	CMP-0026992-3	1
CRCW040220K0FKED	RES, 20.0 k, 1%, 0.063 W, 0402	R7, R9	0402	CMP-0026162-1	2
ERJ-8GEY0R00V	RES, 0, 5%, 0.25 W, AEC-Q200 Grade 0, 1206	R8	1206	CMP-0018748-3	1
760390014	Transformer, 475uH, SMT	T1	Wurth_760390013	CMP-0030718-1	1
SN6505BDBVR	Low-Noise 1 A, 420 kHz Transformer Driver, DBV0006A (SOT-23-6)	U1	DBV0006A_N	CMP-0076095-1	1
ISO7710FQDQ1	Automotive, High Speed, Robust EMC Reinforced Single-Channel Digital Isolator, D0008B (SOIC-8)	U2	D0008B_HV	CMP-0082403-1	1
ISO7731FDBQR	High Speed, Robust EMC Triple-Channel Digital Isolators, DBQ0016A (SSOP-16)	U3	DBQ0016A_N	CMP-0078719-1	1
LMG3525R030Q	650-V 30-mΩ GaN FET with Integrated Driver and Protection	U4, U5	RQS0052A-MFG	CMP-0089968-1	2

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](http://ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2022, Texas Instruments Incorporated