

Filename: Pro8DFE.tmp
 Variant: 001
 Generated: 6/1/2017 3:07:42 PM
 TID #: N/A



PMP20809 REV A Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1	1	82uF	LLS2G820MELZ	Nichicon	CAP, AL, 82 µF, 400 V, +/- 20%, TH	D22xL27mm
2	C2	1	330pF	GRM31A5C2J331JW01D	MuRata	CAP, CERM, 330 pF, 630 V, +/- 5%, COG/NP0, 1206	1206
3	C3	1	0.1uF	890324025017	Würth Elektronik	CAP, Film, 0.1 µF, 275 V, +/- 10%, TH	18x6mm
4	C4, C5	2	220uF	EKZE350ELL221MJC5S	Chemi-Con	CAP, AL, 220 µF, 35 V, +/- 20%, TH	TH, 2-Leads, Body 10x12.5mm, Pin Spacing 5mm
5	C6	1	6.8uF	C2012X5R1V685K125AC	TDK	CAP, CERM, 6.8 µF, 35 V, +/- 10%, X5R, 0805	0805
6	C7	1	0.1uF	C1608X5R1H104K080AA	TDK	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X5R, 0603	0603
7	C8	1	1500pF	DE2E3KY152MN3AM02F	MuRata	CAP, CERM, 1500 pF, V, +/- 20%, E, TH, 2- Leads, Body 7x5mm, Pin Spacing 7.5mm	TH, 2- Leads, Body 7x5mm, Pin Spacing 7.5mm
8	C9	1	1uF	GRM188R61H105KAALD	MuRata	CAP, CERM, 1 µF, 50 V, +/- 10%, X5R, 0603	0603
9	C10	1	0.22uF	GRM155R71C224KA12D	MuRata	CAP, CERM, 0.22 µF, 16 V, +/- 10%, X7R, 0402	0402
10	C11	1	1uF	GRM155R61E105KA12D	MuRata	CAP, CERM, 1 µF, 25 V, +/- 10%, X5R, 0402	0402
11	C12, C13	2	100pF	GRM1555C1H101JA01D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, COG/NP0, 0402	0402
12	C14	1	0.01uF	GRM155R71H103KA88D	MuRata	CAP, CERM, 0.01 µF, 50 V, +/- 10%, X7R, 0402	0402
13	Cx1	1	47uF	EEU-FC1V470	Panasonic	CAP, AL, 47 µF, 35 V, +/- 20%, AEC-Q200 Grade 2, TH	D6.3xL11.2mm
14	D1	1	600V	Z4DGP406L-HF	Comchip Technology	Diode, P-N-Bridge, 600 V, 4 A, Z4-D	Z4-D
15	D2	1	150V	SMCJ150A-TP	Micro Commercial Components	Diode, TVS, Uni, 150 V, 243 Vc, SMC	SMC
16	D3	1	200V	MBRB20200CTT4G	ON Semiconductor	Diode, Schottky, 200 V, 20 A, DDPAK	DDPAK
17	D4	1	600V	MURA160T3G	ON Semiconductor	Diode, Ultrafast, 600 V, 1 A, AEC-Q101, SMA	SMA
18	D5	1	200V	DFLS1200-7	Diodes Inc.	Diode, Schottky, 200 V, 1 A, PowerDI123	PowerDI123
19	F1	1		0443003.DR	Littelfuse	Fuse, 3 A, 250VAC/VDC, SMD	FUSE 10.1x3.12x3.13mm
20	L1	1	1mH	744821201	Würth Elektronik	Coupled inductor, 1 mH, 2 A, 0.045 ohm, TH	15 x 18 x 7.5mm
21	L2	1	1uH	B82462G4102M	TDK	Inductor, Shielded Drum Core, Ferrite, 1 µH, 3.4 A, 0.016 ohm, AEC-Q200 Grade 0, SMD	6.3x3.0x6.3mm
22	Q1	1	600V	AOD4S60	AOS	MOSFET, N-CH, 600 V, 4 A, DPAK	DPAK
23	R1	1	20.0	CRCW12062R00FKEA	Vishay-Dale	RES, 20.0, 1%, 0.25 W, 1206	1206
24	R2	1	2.00	CRCW12062R00FKEA	Vishay-Dale	RES, 2.00, 1%, 0.25 W, 1206	1206
25	R3, R4	2	200k	CRCW2010200KJNEF	Vishay-Dale	RES, 200 k, 5%, 0.75 W, AEC-Q200 Grade 0, 2010	2010
26	R5	1	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
27	R6	1	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
28	R7	1	1.0k	CRCW04021K00JNED	Vishay-Dale	RES, 1.0 k, 5%, 0.063 W, 0402	0402
29	R8	1	22.1k	CRCW040222K1FKED	Vishay-Dale	RES, 22.1 k, 1%, 0.063 W, 0402	0402
30	R9	1	0.25	CSR1206FKR250	Stackpole Electronics Inc	RES, 0.25, 1%, 0.5 W, 1206	1206
31	R10	1	2.49k	CRCW04022K49FKED	Vishay-Dale	RES, 2.49 k, 1%, 0.063 W, 0402	0402
32	R11	1	162k	CRCW0402162KFKED	Vishay-Dale	RES, 162 k, 1%, 0.063 W, 0402	0402
33	R12	1	1.0k	CRCW06031K00JNEA	Vishay-Dale	RES, 1.0 k, 5%, 0.1 W, 0603	0603
34	R13	1	18.7k	CRCW040218K7FKED	Vishay-Dale	RES, 18.7 k, 1%, 0.063 W, 0402	0402
35	T1	1	200uH	RLTI-1228	Renco Electronics	Transformer, 200 uH, TH	966x945mil
36	TP1, TP2	2		5012	Keystone	Test Point, Multipurpose, White, TH	White Multipurpose Testpoint
37	TP3	1		5010	Keystone	Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint
38	TP4	1		5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint
39	U1	1		LM5021MM-2/NOPB	Texas Instruments	AC-DC Current Mode PWM Controller, 8-pin MSOP, Pb-Free	MUA08A
40	U2	1		VOS617A-7X001T	Vishay-Semiconductor	Optocoupler, 3.75 kV, 80-160% CTR, SMT	7x2.12x2.6mm
41	U3	1		TL431AIDBZR	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated