

Filename: ProB385.tmp
 Variant: 001
 Generated: 6/30/2017 11:52:22 AM
 TID #: TIDA-01250



TIDA-01250 REV E1 Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1, C4	2	150pF	GRM1555C1H151JA01D	MuRata	CAP, CERM, 150 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
2	C2	1	1uF	CGA4J3X7S2A105K125AB	TDK	CAP, CERM, 1 uF, 100 V, +/- 10%, X7S, AEC-Q200 Grade 1, 0805	0805
3	C3, C6	2	1uF	GRM155R61A105KE15D	MuRata	CAP, CERM, 1 uF, 10 V, +/- 10%, X5R, 0402	0402
4	C5, C7	2	0.1uF	GRM155R71C104JA88D	MuRata	CAP, CERM, 0.1 uF, 16 V, +/- 5%, X7R, 0402	0402
5	C8	1	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
6	C9, C10	2	10pF	GRM1555C1H100RA01D	MuRata	CAP, CERM, 10 pF, 50 V, +/- 4%, C0G/NP0, 0402	0402
7	D1	1	600V	MURS160-13-F	Diodes Inc.	Diode, Ultrafast, 600 V, 1 A, SMB	SMB
8	D2	1	Rgb	SMLP36RGB2W3	Rohm	LED, Rgb, SMD	1.5x1mm
9	D3, D4, D5	3	Green	150060VS75000	Würth Elektronik	LED, Green, SMD	LED_0603
10	H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
11	H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
12	H9	1		1803578	Phoenix Contact	Terminal Block Plug, 3.81mm, 2x1, Green	
13	J1	1				M12 Socket, Backmounting, 4Pos, Gold, R/A, TH	
14	J2, J13	2		61300311121	Würth Elektronik	Header, 2.54 mm, 3x1, Gold, TH	Header, 2.54mm, 3x1, TH
15	J3, J4, J7, J8, J9, J10	6		61300211121	Würth Elektronik	Header, 2.54 mm, 2x1, Gold, TH	Header, 2.54mm, 2x1, TH
16	J5	1		1803277	Phoenix Contact	Terminal Block, 2x1, 3.81mm, R/A, TH	Connector, 2 pos. 3.8mm RA
17	J11, J12	2		61301011121	Würth Elektronik	Header, 2.54mm, 10x1, Gold, TH	Header, 2.54mm, 10x1, TH
18	J14	1		612 014 217 21	Würth Elektronik	Header (Shrouded), 2.54 mm, 7x2, Gold, R/A, TH	Header, 2.54 mm, 7x2, R/A, TH
19	J15	1		61300611121	Würth Elektronik	Header, 2.54 mm, 6x1, Gold, TH	Header, 2.54mm, 6x1, TH
20	LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650 x 0.200 inch
21	Q1	1	60V	DMN61D8L-7	Diodes Inc.	MOSFET, N-CH, 60 V, 0.47 A, AEC-Q101, SOT-23	SOT-23
22	R1, R2	2	10.0k	CRCW020110K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.05 W, 0201	0201
23	R3	1	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
24	R4	1	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
25	R5	1	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
26	R6	1	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	0603
27	R7, R8	2	140	CRCW0402140RFKED	Vishay-Dale	RES, 140, 1%, 0.063 W, 0402	0402
28	R9	1	499	CRCW0402499RFKED	Vishay-Dale	RES, 499, 1%, 0.063 W, 0402	0402
29	R10	1	1.00	CRCW25121R00FNED	Vishay-Dale	RES, 1.00, 1%, 1 W, AEC-Q200 Grade 0, 2512	2512
30	R11, R13, R14	3	68.1	CRCW040268R1FKED	Vishay-Dale	RES, 68.1, 1%, 0.063 W, 0402	0402
31	R12	1	47.5k	CRCW060347K5FKEA	Vishay-Dale	RES, 47.5 k, 1%, 0.1 W, 0603	0603
32	S1, S2	2		434121025816	Würth Elektronik	Switch, Tactile, SPST, 12 V, SMD	SMD, 6x3.9mm
33	SH-J3, SH-J7, SH-J8, SH-J9, SH-J13	5		60900213421	Würth Elektronik	Shunt, 2.54mm, Gold, Black	Shunt, 2.54mm, Black
34	U1	1		TIOL111	Texas Instruments	IO-Link Device Transceiver with Integrated Surge Protection, TIOL111 (WSON-10)	TIOL111
35	U2	1		MSP430FR5969IRGZR	Texas Instruments	MSP430FR5969 16 MHz Ultra-Low-Power Microcontroller featuring 64 KB FRAM, 2 KB SRAM, 40 IO, RGZ0048B (VQFN-48)	RGZ0048B
36	Y1	1		MS3V-T1R 32.768KHZ 7.0 PF	Micro Crystal AG	Crystal, 32.768 KHz, 7pF, SMD	1.4x1.4x5.0mm SMD
37	C11	0	1000pF	885012205061	Würth Elektronik	CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0402	0402
38	FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	N/A

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated