

[Sample &](http://www.ti.com/product/LM5045?dcmp=dsproject&hqs=sandbuy&#samplebuy) Buy



SNVS699H –FEBRUARY 2011–REVISED JANUARY 2015

Support & **[Community](http://www.ti.com/product/LM5045?dcmp=dsproject&hqs=support&#community)** 

22

# **LM5045 Full-Bridge PWM Controller With Integrated MOSFET Drivers**

**Technical** [Documents](http://www.ti.com/product/LM5045?dcmp=dsproject&hqs=td&#doctype2)

- 
- 
- 
- 
- 
- 
- 
- 
- 
- 
- Programmable Line UVLO and OVP thermal shutdown.

# <span id="page-0-2"></span>**2 Applications Device Information[\(1\)](#page-0-0)**

- 
- Military: Radar and Electronic Warfare
- Power: Telecom DC-DC Module: Analog
- <span id="page-0-0"></span>
- Solar Power Inverters
- Vector Signal Generators
- Microwave Ovens
- Point-to-Point Microwave Backhaul
- Power: Telecom/Server AC/DC Supply: Dual Controller: Analog
- Solar Micro-Inverters
- TETRA Base Stations
- Washing Machine: Low-End

# <span id="page-0-1"></span>**1 Features 3 Description**

Tools & **[Software](http://www.ti.com/product/LM5045?dcmp=dsproject&hqs=sw&#desKit)** 

<span id="page-0-3"></span>Highest Integration Controller for Small Form **The LM5045 PWM** controller contains all of the Factor, High-Density Power Converters **necessary to implement full-bridge topology** power converters using either current mode or • High-Voltage Start-Up Regulator voltage mode control. This device is intended to operate on the primary side of an isolated DC-DC Turnon Into Prebiased Loads converter with input voltage up to 100 V. This highly • Synchronous Rectifiers Disabled in UVLO mode integrated controller-driver provides dual 2-A high-<br>side and low-side gate drivers for the four external and Hiccup Mode<br>bridge MOSFETs plus control signals for the<br>secondary-side synchronous rectifier MOSFETs • Two Independent, Programmable Synchronous secondary-side synchronous rectifier MOSFETs. External resistors program the leading and trailing • Four High-Current 2-A Bridge Gate Drivers edge dead-time between the main and synchronous Wide-Bandwidth Optocoupler Interface<br>
• synchronous rectifiers allows monotonic turnon of the<br>
• power converter even with prebias load conditions Configurable for Either Current Mode or Voltage power converter even with prebias load conditions.<br>Mode Control power additional features include cycle-by-cycle current Additional features include cycle-by-cycle current Dual-Mode Overcurrent Protection and the limiting, hiccup mode restart, programmable soft-Resistor Programmed 2-MHz Oscillator **Example 3 and Start, synchronous rectifier soft-start**, and a 2-MHz capable oscillator with synchronization capability and



• Private Branch Exchange (PBX) (1) For all available packages, see the orderable addendum at the end of the data sheet.



### **Simplified Full-Bridge Power Converter**



# **Table of Contents**





# <span id="page-1-0"></span>**4 Revision History**

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

### **Changes from Revision G (March 2013) to Revision H Page**

• Added *Pin Configuration and Functions* section, *ESD Ratings* table, *Feature Description* section, *Device Functional Modes*, *Application and Implementation* section, *Power Supply Recommendations* section, *Layout* section, *Device and Documentation Support* section, and *Mechanical, Packaging, and Orderable Information* section .............................. [1](#page-0-3)



**ISTRUMENTS** 

**EXAS** 



# <span id="page-2-0"></span>**5 Pin Configuration and Functions**



**[LM5045](http://www.ti.com/product/lm5045?qgpn=lm5045)**

SNVS699H –FEBRUARY 2011–REVISED JANUARY 2015 **[www.ti.com](http://www.ti.com)**

Texas<br>Instruments





# **Pin Functions (continued)**



# <span id="page-5-0"></span>**6 Specifications**

# <span id="page-5-1"></span>**6.1 Absolute Maximum Ratings (1)**



(1) Absolute Maximum Ratings are limits beyond which damage to the device may occur. Operating Ratings are conditions under which operation of the device is intended to be functional. For ensured specifications and test conditions, see the *Electrical [Characteristics](#page-6-0)*.

(2) The negative HS voltage must never be more negative than VCC–16 V. For example, if VCC = 12 V, the negative transients at HS must not exceed –4 V.

(3) These pins are output pins and as such should not be connected to an external voltage source. The voltage range listed is the limits the internal circuitry is designed to reliably tolerate in the application circuit.

# <span id="page-5-2"></span>**6.2 ESD Ratings**



(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

(2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

# <span id="page-5-3"></span>**6.3 Recommended Operating Conditions**

over operating free-air temperature range (unless otherwise noted)



## <span id="page-5-4"></span>**6.4 Thermal Information**



(1) For more information about traditional and new thermal metrics, see the *IC Package Thermal Metrics* application report, [SPRA953](http://www.ti.com/lit/pdf/spra953).

## <span id="page-6-0"></span>**6.5 Electrical Characteristics**

Limits in standard typeface are for  $T_J = 25^{\circ}C$  only; MIN and MAX limits apply the junction temperature range of  $-40^{\circ}C$  to 125°C. Unless otherwise specified, the following conditions apply: V<sub>IN</sub> = 48 V, RT = 25 kΩ, RD1 = RD2 = 20 kΩ. No load on HO1, HO2, LO1, LO2, SR1, SR2, COMP = 0 V, UVLO = 2.5 V, OVP = 0 V, SSOFF = 0 V.



Copyright © 2011–2015, Texas Instruments Incorporated *Submit [Documentation](http://www.go-dsp.com/forms/techdoc/doc_feedback.htm?litnum=SNVS699H&partnum=LM5045) Feedback* 7

# **Electrical Characteristics (continued)**

Limits in standard typeface are for  $T_J = 25^{\circ}C$  only; MIN and MAX limits apply the junction temperature range of -40°C to 125°C. Unless otherwise specified, the following conditions apply: V<sub>IN</sub> = 48 V, RT = 25 kΩ, RD1 = RD2 = 20 kΩ. No load on HO1, HO2, LO1, LO2, SR1, SR2, COMP = 0 V, UVLO = 2.5 V, OVP = 0 V, SSOFF = 0 V.



## **Electrical Characteristics (continued)**

Limits in standard typeface are for  $T_J = 25^{\circ}C$  only; MIN and MAX limits apply the junction temperature range of -40°C to 125°C. Unless otherwise specified, the following conditions apply: V<sub>IN</sub> = 48 V, RT = 25 kΩ, RD1 = RD2 = 20 kΩ. No load on HO1, HO2, LO1, LO2, SR1, SR2, COMP = 0 V, UVLO = 2.5 V, OVP = 0 V, SSOFF = 0 V.





# **6.6 Typical Characteristics**

<span id="page-9-0"></span>



# **Typical Characteristics (continued)**





# <span id="page-11-0"></span>**7 Detailed Description**

## <span id="page-11-1"></span>**7.1 Overview**

The LM5045 PWM controller contains all of the features necessary to implement a full-bridge topology power converter using either current mode or voltage mode control. This device is intended to operate on the primary side of an isolated DC-DC converter with input voltage up to 100 V. This highly integrated controller-driver provides dual 2-A high-side and low-side gate drivers for the four external bridge MOSFETs plus control signals for secondary side synchronous rectifiers. External resistors program the leading and trailing edge dead-time between the main and synchronous rectifier control signals. Intelligent start-up of synchronous rectifier allows turnon of the power converter into the prebias loads. Cycle-by-cycle current limit protects the power components from load transients while hiccup mode protection limits average power dissipation during extended overload conditions. Additional features include programmable soft-start, soft-start of the synchronous rectifiers, and a 2- MHz capable oscillator with synchronization capability and thermal shutdown.



### <span id="page-12-0"></span>**7.2 Functional Block Diagram**





## <span id="page-13-0"></span>**7.3 Feature Description**

## **7.3.1 High-Voltage Start-Up Regulator**

The LM5045 contains an internal high-voltage start-up regulator that allows the input pin (VIN) to be connected directly to the supply voltage over a wide range from 14 V to 100 V. The input can withstand transients up to 105 V. When the UVLO pin potential is greater than 0.4 V, the VCC regulator is enabled to charge an external capacitor connected to the VCC pin. The VCC regulator provides power to the voltage reference (REF) and the gate drivers (HO1/HO2 and LO1/LO2). When the voltage on the VCC pin exceeds its undervoltage (UV) threshold, the internal voltage reference (REF) reaches its regulation set point of 5 V and the UVLO voltage is greater than 1.25 V, the soft-start capacitor is released and normal operation begins. The regulator output at VCC is internally current limited. The value of the VCC capacitor depends on the total system design, and its start-up characteristics. The recommended range of values for the VCC capacitor is 0.47 μF to 10 µF.

The internal power dissipation of the LM5045 can be reduced by powering VCC from an external supply. The output voltage of the VCC regulator is initially regulated to 9.5 V. After the synchronous rectifiers are engaged (which is approximately when the output voltage in within regulation), the VCC voltage is reduced to 7.7 V. In typical applications, an auxiliary transformer winding is connected through a diode to the VCC pin. This winding must raise the VCC voltage above 8V to shut off the internal start-up regulator. Powering VCC from an auxiliary winding improves efficiency while reducing the power dissipation of the controller. The VCC UV circuit will still function in this mode, requiring that VCC never falls below its UV threshold during the start-up sequence. The VCC regulator series pass transistor includes a diode between VCC and VIN that should not be forward biased in normal operation. Therefore, the auxiliary VCC voltage should never exceed the VIN voltage.

An external DC bias voltage can be used instead of the internal regulator by connecting the external bias voltage to both the VCC and the VIN pins. This implementation is shown in the *Application and [Implementation](#page-24-0)* section. The external bias must be greater than 10 V and less than the VCC maximum voltage rating of 14 V.

### **7.3.2 Line Undervoltage Detector**

The LM5045 contains a dual level undervoltage lockout (UVLO) circuit. When the UVLO pin voltage is below 0.4 V, the controller is in a low current shutdown mode. When the UVLO pin voltage is greater than 0.4 V but less than 1.25 V, the controller is in standby mode. In standby mode the VCC and REF bias regulators are active while the controller outputs are disabled. When the VCC and REF outputs exceed their respective under-voltage thresholds and the UVLO pin voltage is greater than 1.25 V, the soft-start capacitor is released and the normal operation begins. An external set-point voltage divider from VIN to GND can be used to set the minimum operating voltage of the converter. The divider must be designed such that the voltage at the UVLO pin will be greater than 1.25 V when VIN enters the desired operating range. UVLO hysteresis is accomplished with an internal 20 μA current sink that is switched on or off into the impedance of the set-point divider. When the UVLO threshold is exceeded, the current sink is deactivated to quickly raise the voltage at the UVLO pin. When the UVLO pin voltage falls below the 1.25 V threshold, the current sink is enabled causing the voltage at the UVLO pin to quickly fall. The hysteresis of the 0.4 V shutdown comparator is internally fixed at 50 mV.

The UVLO pin can also be used to implement various remote enable / disable functions. Turning off the converter by forcing the UVLO pin to standby condition  $(0.4 \text{ V} <$  UVLO  $<$  1.25 V) provides a controlled soft-stop. Refer to the *[Soft-Stop](#page-19-0)* section for more details.

## **7.3.3 Overvoltage Protection**

An external voltage divider can be used to set either an overvoltage or an overtemperature protection. During an OVP condition, the SS and SSSR capacitors are discharged and all the outputs are disabled. The divider must be designed such that the voltage at the OVP pin is greater than 1.25 V when overvoltage/temperature condition exists. Hysteresis is accomplished with an internal 20 μA current source. When the OVP pin voltage exceeds 1.25 V, the 20 μA current source is activated to quickly raise the voltage at the OVP pin. When the OVP pin voltage falls below the 1.25 V threshold, the current source is deactivated causing the voltage at the OVP to quickly fall. Refer to the *Application and [Implementation](#page-24-0)* section for more details.

### **7.3.4 Reference**

The REF pin is the output of a 5-V linear regulator that can be used to bias an optocoupler transistor and external housekeeping circuits. The regulator output is internally current limited to 15 mA. The REF pin must be locally decoupled with a ceramic capacitor, the recommended range of values are from 0.1 μF to 10 μF



### **7.3.5 Oscillator, Sync Input**

The LM5045 oscillator frequency is set by a resistor connected between the RT pin and AGND. The RT resistor should be located very close to the device. To set a desired oscillator frequency ( $F_{\rm OSC}$ ), the necessary value of RT resistor can be calculated from the following equation:

$$
R_{T} = \frac{1}{F_{\text{OSC}} \times 1 \times 10^{-10}}
$$
 (1)

For example, if the desired oscillator frequency is 400 kHz, that is, each phase (LO1 or LO2) at 200 kHz, the value of R<sub>T</sub> will be 25 kΩ. If the LM5045 is to be synchronized to an external clock, that signal must be coupled into the RT pin through a 100 pF capacitor. The RT pin voltage is nominally regulated at 2.0 V and the external pulse amplitude should lift the pin to between 3.5 V and 5.0  $\overline{V}$  on the low-to-high transition. The synchronization pulse width should be between 15 and 200 ns. The RT resistor is always required, whether the oscillator is free running or externally synchronized and the SYNC frequency must be equal to, or greater than the frequency set by the RT resistor. When syncing to an external clock, it is recommended to add slope compensation by connecting an appropriate resistor from the VCC pin to the CS pin. Also disable the SLOPE pin by grounding it.

### **7.3.6 Cycle-by-Cycle Current Limit**

The CS pin is to be driven by a signal representative of the primary current of the transformer. If the voltage on the CS pin exceeds 0.75 V, the current sense comparator immediately terminates the PWM cycle. A small RC filter connected to the CS pin and located near the controller is recommended to suppress noise. An internal 18- Ω MOSFET discharges the external current sense filter capacitor at the conclusion of every cycle. The discharge MOSFET remains on for an additional 40 ns after the start of a new PWM cycle to blank leading edge spikes. The current sense comparator is very fast and may respond to short duration noise pulses. Layout is critical for the current sense filter and the sense resistor. The capacitor associated with CS filter must be placed very close to the device and connected directly to the CS and AGND pins. If a current sense transformer is used, both the leads of the transformer secondary should be routed to the filter network, which should be located close to the IC. When designing with a current sense resistor, all of the noise sensitive low power ground connections should be connected together near the AGND pin, and a single connection should be made to the power ground (sense resistor ground point).

### **7.3.7 Hiccup Mode**

The LM5045 provides a current limit restart timer to disable the controller outputs and force a delayed restart (such as Hiccup mode) if a current limit condition is repeatedly sensed. The number of cycle-by-cycle current limit events required to trigger the restart is programmed by the external capacitor at the RES pin. During each PWM cycle, the LM5045 either sources or sinks current from the RES capacitor. If current limit is detected, the 5 μA current sink is disabled and a 30μA current source is enabled. If the RES voltage reaches the 1.0 V threshold, the following restart sequence occurs, as shown in [Figure](#page-15-0) 10:

- The SS and SSSR capacitors are fully discharged
- The 30 μA current source is turned-off and the 10 μA current source is turned-on.
- Once the voltage at the RES pin reaches 4.0 V the 10 μA current source is turned-off and a 5μA current sink is turned-on, ramping the voltage on the RES capacitor down to 2.0 V.
- Once RES capacitor reaches 2.0 V, threshold, the 10 μA current source is turned-on again. The RES capacitor voltage is ramped between 4.0 V and 2.0 V eight times.
- When the counter reaches eight, the RES pin voltage is pulled low and the soft-start capacitor is released to begin a soft-start sequence. The SS capacitor voltage slowly increases. When the SS voltage reaches 1.0 V, the PWM comparator will produce the first narrow pulse.
- If the overload condition persists after restart, cycle-by-cycle current limiting will begin to increase the voltage on the RES capacitor again, repeating the hiccup mode sequence.
- If the overload condition no longer exists after restart, the RES pin will be held at ground by the 5 μA current sink and the normal operation resumes.

The hiccup mode function can be completely disabled by connecting the RES pin to the AGND pin. In this configuration the cycle-by-cycle protection will limit the maximum output current indefinitely, no hiccup restart sequences will occur.



**Figure 10. Hiccup Mode Delay and Soft-Start Timing Diagram**

### <span id="page-15-0"></span>**7.3.8 PWM Comparator**

The LM5045 pulse width modulator (PWM) comparator is a three input device, it compares the signal at the RAMP pin to the loop error signal or the soft-start, whichever is lower, to control the duty cycle. This comparator is optimized for speed to achieve minimum controllable duty cycles. The loop error signal is received from the external feedback and isolation circuit in the form of a control current into the COMP pin. The COMP pin current is internally mirrored by a matching pair of NPN transistors which sink current through a 5-kΩ resistor connected to the 5-V reference. The resulting control voltage passes through a 1-V offset, followed by a 2:1 resistor divider before being applied to the PWM comparator.

An optocoupler detector can be connected between the REF pin and the COMP pin. Because the COMP pin is controlled by a current input, the potential difference across the optocoupler detector is nearly constant. The bandwidth limiting phase delay which is normally introduced by the significant capacitance of the optocoupler is thereby greatly reduced. Higher loop bandwidths can be realized because the bandwidth limiting pole associated with the optocoupler is now at a much higher frequency. The PWM comparator polarity is configured such that with no current flowing into the COMP pin, the controller produces maximum duty cycle.

## **7.3.9 Ramp Pin**

The voltage at the RAMP pin provides the modulation ramp for the PWM comparator. The PWM comparator compares the modulation ramp signal at the RAMP pin to the loop error signal to control the duty cycle. The modulation ramp signal can be implemented either as a ramp proportional to the input voltage, known as feedforward voltage mode control, or as a ramp proportional to the primary current, known as current mode control. The RAMP pin is reset by an internal MOSFET with an R<sub>DS(ON)</sub> of 5.5  $\Omega$  at the conclusion of each PWM cycle. The ability to configure the RAMP pin for either voltage mode or current mode allows the controller to be implemented for the optimum control method depending upon the design constraints. Refer to the *[Application](#page-24-0) and [Implementation](#page-24-0)* section for more details on configuring the RAMP pin for feed-forward voltage mode control and peak current mode control.

### **7.3.10 Slope Pin**

For duty cycles greater than 50% (25% for each phase), peak current mode control is subject to sub-harmonic oscillation. Sub-harmonic oscillation is normally characterized by observing alternating wide and narrow duty cycles. This can be eliminated by adding an artificial ramp, known as slope compensation, to the modulating signal at the RAMP pin. The SLOPE pin provides a current source ramping from 0 to 100μA, at the frequency set by the RT resistor, for slope compensation. The ramping current source at the SLOPE pin can be used in several different ways to add slope compensation to the RAMP signal:

As shown in [Figure](#page-16-0) 11(a), the SLOPE and RAMP pins can be connected together through an appropriate resistor to the CS pin. This configuration will inject current sense signal plus slope compensation to the RAMP



pin but CS pin will not see any slope compensation. Therefore, in this scheme slope compensation will not affect the current limit.

In a second configuration, as shown in [Figure](#page-16-0) 11(b), the SLOPE, RAMP and CS pins can be tied together. In this configuration the ramping current source from the SLOPE pin will flow through the filter resistor and filter capacitor, therefore both the CS pin and the RAMP pin will see the current sense signal plus the slope compensation ramp. In this scheme, the current limit is compensated by the slope compensation and the current limit onset point will vary.

If the slope compensation is not required for example, in feed-forward voltage mode control, the SLOPE pin must be connected to the AGND pin. When the RT pin is synched to an external clock, it is recommended to disable the SLOPE pin and add slope compensation externally by connecting an appropriate resistor from the VCC pin to the CS pin. Refer to the *Application and [Implementation](#page-24-0)* section for more details.



- A. Slope Compensation Configured for PWM Only (No Current Limit Slope)
- B. Slope Compensation Configured for PWM and Current Limit

### **Figure 11. Slope Compensation Configuration**

### <span id="page-16-0"></span>**7.3.11 Soft-Start**

The soft-start circuit allows the power converter to gradually reach a steady state operating point, thereby reducing the start-up stresses and current surges. When bias is supplied to the LM5045, the SS capacitor is discharged by an internal MOSFET. When the UVLO, VCC and REF pins reach their operating thresholds, the SS capacitor is released and is charged with a 20-µA current source. Once the SS pin voltage crosses the 1-V offset, SS controls the duty cycle. The PWM comparator is a three input device; it compares the RAMP signal against the lower of the signals between the soft-start and the loop error signal. In a typical isolated application, as the secondary bias is established, the error amplifier on the secondary side soft-starts and establishes closedloop control, steering the control away from the SS pin.

One method to shutdown the regulator is to ground the SS pin. This forces the internal PWM control signal to ground, reducing the output duty cycle quickly to zero. Releasing the SS pin begins a soft-start cycle and normal operation resumes. A second shutdown method is presented in the *UVLO and OVP Voltage Divider [Selection](#page-26-0)* section.

### **7.3.12 Gate Driver Outputs**

The LM5045 provides four gate drivers: two floating high-side gate drivers HO1 and HO2 and two ground referenced low-side gate drivers LO1 and LO2. Each internal driver is capable of source 1.5-A peak and sinking 2-A peak. Initially, the diagonal HO1 and LO2 are turned-on together, followed by an off-time when all the four gate driver outputs are off. In the subsequent phase the diagonal HO2 and LO1 are turned on together followed by an off-time. The low-side gate drivers are powered directly by the VCC regulator. The HO1 and HO2 gate



drivers are powered from a bootstrap capacitor connected between BST1/BST2 and HS1/HS2, respectively. An external diode connected between VCC (anode pin) and BST (cathode pin) provides the high-side gate driver power by charging the bootstrap capacitor from VCC when the corresponding switch node (HS1/HS2 pin) is low. When the high side MOSFET is turned on, BST1 rises to a peak voltage equal to VCC +  $V_{HS1}$  where  $V_{HS1}$  is the switch node voltage.

The BST and VCC capacitors should be placed close to the pins of the LM5045 to minimize voltage transients due to parasitic inductances because the peak current sourced to the MOSFET gates can exceed 1.5 A. The recommended value of the BST capacitor is 0.1 μF or greater. A low ESR / ESL capacitor, such as a surface mount ceramic, should be used to prevent voltage droop during the HO transitions.

If the COMP pin is open circuit, the outputs will operate at maximum duty cycle. The maximum duty cycle for each phase is limited by the dead-time set by the RD1 resistor. If the RD1 resistor is set to zero then the maximum duty cycle is slightly less than 50% due to the internally fixed dead-time. The internally fixed dead-time is 30ns which does not vary with the operating frequency. The maximum duty cycle for each output can be calculated from the following equation:

$$
D_{MAX} = \frac{\left(\frac{1}{F_{OSC}}\right) \cdot (T1)}{\left(\frac{2}{F_{OSC}}\right)}
$$

where

• T1 is the time set by the RD1 resistor

 $F_{\text{osc}}$  is the frequency of the oscillator (2)

For example, if the oscillator frequency is set at 400 kHz and the T1 time set by the RD1 resistor is 60 ns, the resulting  $D_{MAX}$  will be equal to 0.488.



### **Figure 12. Timing Diagram Illustrating the Maximum Duty Cycle and Dead-Time Set by RD1**

## **7.3.13 Synchronous Rectifier Control Outputs (SR1 and SR2)**

Synchronous rectification (SR) of the transformer secondary provides higher efficiency, especially for low output voltage converters, compared to the diode rectification. The reduction of rectifier forward voltage drop (0.5 V to 1.5 V) to 10 mV to 200 mV VDS voltage for a MOSFET significantly reduces rectification losses. In a typical application, the transformer secondary winding is center tapped, with the output power inductor in series with the center tap. The SR MOSFETs provide the ground path for the energized secondary winding and the inductor current. From [Figure](#page-18-0) 13 it can be seen that when the HO1/LO2 diagonal is turned ON, power transfer is enabled from the primary. During this period, the SR1 MOSFET is enabled and the SR2 MOSFET is turned-off. The secondary winding connected to the SR2 MOSFET drain is twice the voltage of the center tap at this time. At the



conclusion of the HO1/LO2 pulse, the inductor current continues to flow through the SR2 MOSFET body diode. Because the body diode causes more loss than the SR MOSFET, efficiency can be improved by minimizing the T2 period while maintaining sufficient timing margin over all conditions (component tolerances, etc.) to prevent the shoot-through current. When HO2/LO1 enables power transfer from the primary, the SR2 MOSFET is enabled and the SR1 MOSFET is off.

During the freewheeling period, the inductor current is almost equally shared between both the SR1 and SR2 MOSFETs which effectively shorts the transformer secondary. The SR2 MOSFET is disabled before HO1/LO2 is turned-on. The SR2 MOSFET body diode continues to carry about the half inductor current until the primary power raises the SR2 MOSFET drain voltage and reverse biases the body diode. Ideally, dead-time T1 would be set to the minimum time that allows the SR MOSFET to turn off before the SR MOSFET body diode starts conducting.

The SR drivers are powered by the REF regulator and each SR output is capable of sourcing 0.1 A and sinking 0.4-A peak. The amplitude of the SR drivers is limited to 5 V. The 5-V SR signals enable the LM5045 to transfer SR control across the isolation barrier either through a solid-state isolator or a pulse transformer. The actual gate sourcing and sinking currents for the synchronous MOSFETs are provided by the secondary-side bias and gate drivers.

T1 and T2 can be programmed by connecting a resistor between RD1 and RD2 pins and AGND. It should be noted that while RD1 effects the maximum duty cycle, RD2 does not. The RD1 and RD2 resistors should be located very close to the device. The formula for RD1 and RD2 resistors are given below:

$$
RD(1,2) = \frac{T(1,2)}{3 \text{ pF}}
$$
; For 20k < (1,2) < 100k

(3)



If the desired dead-time for T1 is 60ns, then the RD1 will be 20 kΩ.



## <span id="page-18-0"></span>**7.3.14 Soft-Start of the Synchronous Rectifiers**

In addition to the basic soft-start already described, the LM5045 contains a second soft-start function that gradually turns on the synchronous rectifiers to their steady-state duty cycle. This function keeps the synchronous rectifiers off during the basic soft-start allowing a linear start-up of the output voltage even into prebiased loads. Then the SR output duty cycle is gradually increased to prevent output voltage disturbances due to the difference in the voltage drop between the body diode and the channel resistance of the synchronous MOSFETs. Initially, when bias is supplied to the LM5045, the SSSR capacitor is discharged by an internal MOSFET. When the SS capacitor reaches a 2-V threshold and once it is established that COMP is in control of the duty cycle such as  $I_{\text{COMP}}$  < 800 µA, the SSSR discharge is released and SSSR capacitor begins charging with a 20-µA current source. Once the SSSR cap crosses the internal 1-V threshold, the LM5045 begins the softstart of the synchronous FETs. The SR soft-start follows a leading edge modulation technique such as the leading edge of the SR pulse is soft-started as opposed trailing edge modulation of the primary FETs. As shown in the [Figure](#page-19-1) 14(a), SR1 and SR2 are turned-on simultaneously with a narrow pulse-width during the

Copyright © 2011–2015, Texas Instruments Incorporated *Submit [Documentation](http://www.go-dsp.com/forms/techdoc/doc_feedback.htm?litnum=SNVS699H&partnum=LM5045) Feedback* 19



freewheeling cycle. At the end of the freewheel cycle, that is, at the rising edge of the internal CLK, the SR FET in-phase with the next power transfer cycle is kept on while the SR FET out of phase with it is turned-off. The inphase SR FET is kept on throughout the power transfer cycle and at the end of it, both the primary FETs and the in-phase SR FETs are turned-off together. The synchronous rectifier outputs can be disabled by grounding the SSSR pin.



- A. Waveforms during Soft-Start
- B. Waveforms after Soft-Start



### <span id="page-19-1"></span>**7.3.15 Prebias Startup**

A common requirement for power converters is to have a monotonic output voltage start-up into a prebiased load such as a precharged output capacitor. In a prebiased load condition, if the synchronous rectifiers are engaged prematurely they will sink current from the precharged output capacitors resulting in an undesired output voltage dip. This condition is undesirable and could potentially damage the power converter. The LM5045 uses unique control circuitry to ensure intelligent turnon of the synchronous rectifiers such that the output has a monotonic start-up. Initially, the SSSR capacitor is held at ground to disable the synchronous MOSFETs allowing the body diode to conduct. The synchronous rectifier soft-start is initiated once it is established the duty cycle is controlled by the COMP instead of the soft-start capacitor, that is,  $I_{\text{COMP}}$  < 800 µA and the voltage at the SS pin > 2 V. The SSSR capacitor is then released and is charged by a 20-µA current source. Further, as shown in [Figure](#page-20-0) 15, a 1-V offset on the SSSR pin is used to provide additional delay. This delay ensures the output voltage is in regulation avoiding any reverse current when the synchronous MOSFETs are engaged.

### <span id="page-19-0"></span>**7.3.16 Soft-Stop**

As shown in [Figure](#page-20-1) 16, if the UVLO pin voltage falls below the 1.25-V standby threshold, but above the 0.4-V shutdown threshold, the SSSR capacitor is soft-stopped with a 60-µA current source (3 times the charging current). Once the SSSR pin reaches the 1.0-V threshold, both the SS and SSSR pins are immediately discharged to GND. Soft-stopping the power converter gradually winds down the energy in the output capacitors and results in a monotonic decay of the output voltage. During the hiccup mode, the same sequence is executed except that the SSSR is discharged with a 120-µA current source (6 times the charging current). In case of an OVP, VCC UV, thermal limit or a VREF UV condition, the power converter hard-stops, whereby all of the control outputs are driven to a low state immediately.





**Figure 15. Prebias Voltage Start-up Waveforms**

### <span id="page-20-0"></span>**7.3.17 Soft-Stop Off**

The Soft-Start Off (SSOFF) pin gives additional flexibility by allowing the power converter to be configured for hard-stop during line UVLO and hiccup mode condition. If the SS OFF pin is pulled up to the 5-V REF pin, the power converter hard-stops in any fault condition. Hard-stop drives each control output to a low state immediately. Refer to [Table](#page-21-1) 1 for more details.



<span id="page-20-1"></span>**Figure 16. Stop-Stop Waveforms During a UVLO Event**

**NSTRUMENTS** 

Texas

# **Feature Description (continued)**



<span id="page-21-1"></span>

(1) Note: All the above conditions are valid with SSOFF pin tied to GND. If SSOFF=5V, the LM5045 hard-stops in all the conditions. The SS pin remains high in all the conditions until the SSSR pin reaches 1V.

### **7.3.18 Thermal Protection**

Internal thermal shutdown circuitry is provided to protect the integrated circuit in the event the maximum rated junction temperature is exceeded. When activated, typically at 160°C, the controller is forced into a shutdown state with the output drivers, the bias regulators (VCC and REF) disabled. This helps to prevent catastrophic failures from accidental device overheating. During thermal shutdown, the SS and SSSR capacitors are fully discharged and the controller follows a normal start-up sequence after the junction temperature falls to the operating level (140°C).

## <span id="page-21-0"></span>**7.4 Device Functional Modes**

### **7.4.1 Control Method Selection**

The LM5045 is a versatile PWM control IC that can be configured for either current mode control or voltage mode control. The choice of the control method usually depends upon the designer preference. The following must be taken into consideration while selecting the control method. Current mode control can inherently balance flux in both phases of the full-bridge topology. The full-bridge topology, like other double ended topologies, is susceptible to the transformer core saturation. Any asymmetry in the volt-second product applied between the two alternating phases results in flux imbalance that causes a dc buildup in the transformer. This continual dc buildup may eventually push the transformer into saturation. The volt-second asymmetry can be corrected by employing current mode control. In current mode control, a signal representative of the primary current is compared against an error signal to control the duty cycle. In steady-state, this results in each phase being terminated at the same peak current by adjusting the pulse-width and thus applying equal volt-seconds to both the phases.

Current mode control can be susceptible to noise and sub-harmonic oscillation, while voltage mode control employs a larger ramp for PWM and is usually less susceptible. Voltage-mode control with input line feedforward also has excellent line transient response. When configuring for voltage mode control, a dc blocking capacitor can be placed in series with the primary winding of the power transformer to avoid any flux imbalance that may cause transformer core saturation.

## **7.4.2 Voltage Mode Control Using the LM5045**

To configure the LM5045 for voltage mode control, an external resistor ( $R_{FF}$ ) and capacitor ( $C_{FF}$ ) connected to VIN, AGND, and the RAMP pins is required to create a saw-tooth modulation ramp signal shown in [Figure](#page-22-0) 17. The slope of the signal at RAMP will vary in proportion to the input line voltage. The varying slope provides line feed-forward information necessary to improve line transient response with voltage mode control. With a constant error signal, the on-time  $(T_{ON})$  varies inversely with the input voltage (VIN) to stabilize the Volt- Second product of the transformer primary. Using a line feed-forward ramp for PWM control requires very little change in the voltage regulation loop to compensate for changes in input voltage, as compared to a fixed slope oscillator ramp. Furthermore, voltage mode control is less susceptible to noise and does not require leading edge filtering. Therefore, it is a good choice for wide input range power converters. Voltage mode control requires a Type-III compensation network, due to the complex-conjugate poles of the L-C output filter.



## **Device Functional Modes (continued)**



**Figure 17. Feed-Forward Voltage Mode Configuration**

<span id="page-22-0"></span>The recommended capacitor value range for  $C_{FF}$  is from 100 pF to 1800 pF. Referring to [Figure](#page-22-0) 17, it can be seen that  $C_{FF}$  value must be small enough to be discharged with in the clock pulse-width which is typically within 50ns. The R<sub>DS(ON)</sub> of the internal discharge FET is 5.5 Ω.

The value of  $R_{FF}$  required can be calculated from

$$
R_{FF} = \frac{-1}{F_{\text{OSC}} \times C_{FF} \times \ln\left(1 - \frac{V_{\text{RAMP}}}{V \cdot W_{\text{MIN}}}\right)}
$$

For example, assuming a  $V_{RAMP}$  of 1.5 V (a good compromise of signal range and noise immunity), at VIN<sub>MIN</sub> of 36 V (oscillator frequency of 400 kHz and C<sub>FF</sub> = 470 pF results in a value for R<sub>FF</sub> of 125 kΩ.

### **7.4.3 Current Mode Control Using the LM5045**

The LM5045 can be configured for current mode control by applying a signal proportional to the primary current to the RAMP pin. One way to achieve this is shown in [Figure](#page-23-0) 18. The primary current can be sensed using a current transformer or sense resistor, the resulting signal is filtered and applied to the RAMP pin through a resistor used for slope compensation. It can be seen that the signal applied to the RAMP pin consists of the primary current information from the CS pin plus an additional ramp for slope compensation, added by the resistor  $R_{SLOPE}$ .

The current sense resistor is selected such that during over current condition, the voltage across the current sense resistor is above the minimum CS threshold of 728 mV.

In general, the amount of slope compensation required to avoid sub-harmonic oscillation is equal to at least onehalf the down-slope of the output inductor current, transformed to the primary. To mitigate sub-harmonic oscillation after one switching period, the slope compensation must be equal to one times the down slope of the filter inductor current transposed to primary. This is known as deadbeat control. The slope compensation resistor required to implement dead-beat control can be calculated as follows:

$$
R_{\text{SLOPE}} = \frac{V_{\text{OUT}} \times R_{\text{CS}}}{L_{\text{FILTER}} \times F_{\text{OSC}} \times I_{\text{SLOPE}} \times N_{\text{TR}}}
$$

where

 $N_{TR}$  is the turns-ratio with respect to the secondary (5) (5)

(4)

For example, for a 3.3 V output converter with a turns-ratio between primary and secondary of 9:1, an output filter inductance (L<sub>FILTER</sub>) of 800 nH and a current sense resistor (R<sub>SENSE</sub>) of 150 mΩ, R<sub>SLOPE</sub> of 1.67 kΩ will suffice.

# <span id="page-23-0"></span>**Device Functional Modes (continued)**



**Figure 18. Current Mode Configuration**



# <span id="page-24-0"></span>**8 Application and Implementation**

### **NOTE**

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

### <span id="page-24-1"></span>**8.1 Application Information**

The LM5045 is a highly integrated PWM controller that contains all of the features necessary for implementing full-bridge topology power converters using either current mode or voltage mode control. The device targets DC-DC converter applications with input voltages of up to 100 Vdc and output power in the range 100 W to 1 kW.

## <span id="page-24-2"></span>**8.2 Typical Application**

The following schematic shows an example of a 100W full-bridge converter controlled by LM5045. The operating input voltage range is 36 V to 75 V, and the output voltage is 3.3 V. The output current capability is 30 A. The converter is configured for current mode control with external slope compensation. An auxiliary winding is used to raise the VCC voltage to reduce the controller power dissipation.

<span id="page-24-3"></span>



### **8.2.1 Design Requirements**



Copyright © 2011–2015, Texas Instruments Incorporated *Submit [Documentation](http://www.go-dsp.com/forms/techdoc/doc_feedback.htm?litnum=SNVS699H&partnum=LM5045) Feedback* 25

### **Typical Application (continued)**



### **8.2.2 Detailed Design Procedure**

### 8.2.2.1 *VIN* and  $V_{CC}$

The voltage applied to the VIN pin, which may be the same as the system voltage applied to the power transformer's primary ( $V_{PWR}$ ), can vary in the range of the 14 to 100 V. It is recommended that the filter shown in [Figure](#page-25-0) 20 be used to suppress the transients that may occur at the input supply. This is particularly important when VIN is operated close to the maximum operating rating of the LM5045. The current into VIN depends primarily on the operating current of the LM5045, the switching frequency, and any external loads on the VCC pin, that typically include the gate capacitances of the power MOSFETs. In typical applications, an auxiliary transformer winding is connected through a diode to the VCC pin. This pin must raise VCC voltage above 8 V to shut off the internal start-up regulator.

After the outputs are enabled and the external VCC supply voltage has begun supplying power to the IC, the current into the VIN pin drops below 1mA. VIN should remain at a voltage equal to or above the VCC voltage to avoid reverse current through the internal body diode of the internal VCC regulator.

### *8.2.2.2 For Applications With > 100 VIN*

For applications where the system input voltage exceeds 100 V, VIN can be powered from an external start-up regulator as shown in [Figure](#page-25-1) 21. In this configuration, the VIN and VCC pins should be connected together. The voltage at the VCC and VIN pins must be greater than 10 V (> Max VCC reference voltage) yet not exceed 16 V. To enable operation the VCC voltage must be raised above 10 V. The voltage at the VCC pin must not exceed 16 V. The voltage source at the right side of [Figure](#page-25-1) 21 is typically derived from the power stage, and becomes active once the LM5045's outputs are active.



**Figure 20. Input Transient Protection**

<span id="page-25-0"></span>

<span id="page-25-1"></span>**Figure 21. Start-Up Regulator For**  $V_{PWR}$  **> 100 V** 



### <span id="page-26-0"></span>*8.2.2.3 UVLO and OVP Voltage Divider Selection*

Two dedicated comparators connected to the UVLO and OVP pins are used to detect undervoltage and overvoltage conditions. The threshold values of both these comparators are set at 1.25 V. The two functions can be programmed independently with two separate voltage dividers from VIN to AGND as shown in [Figure](#page-26-1) 22 and [Figure](#page-27-0) 23, or with a three-resistor divider as shown in [Figure](#page-27-1) 24. Independent UVLO and OVP pins provide greater flexibility for the user to select the operational voltage range of the system. When the UVLO pin voltage is below 0.4 V, the controller is in a low current shutdown mode. For a UVLO pin voltage greater than 0.4 V but less than 1.25 V the controller is in standby mode. Once the UVLO pin voltage is greater than 1.25 V, the controller is fully enabled. Two external resistors can be used to program the minimum operational voltage for the power converter as shown in [Figure](#page-26-1) 22. When the UVLO pin voltage falls below the 1.25 V threshold, an internal 20 µA current sink is enabled to lower the voltage at the UVLO pin, thus providing threshold hysteresis. Resistance values for  $R_1$  and  $R_2$  can be determined from the following equations:

$$
R_1 = \frac{V_{HYS}}{20 \,\mu A}
$$

$$
R_2 = \frac{1.25V \times R_1}{V_{PWR\text{-OFF}} - 1.25V - (20 \,\mu A \times R1)}
$$

where

- $V_{PWR}$  is the desired turnon voltage
- $V_{HYS}$  is the desired UVLO hysteresis at  $V_{PWR}$  (6)

For example, if the LM5045 is to be enabled when  $V_{PWR}$  reaches 33 V, and disabled when  $V_{PWR}$  is decreased to 31 V, R<sub>1</sub> should be 100 kΩ, and R<sub>2</sub> should be 4.2 kΩ. The voltage at the UVLO pin should not exceed 7 V at any time.

Two external resistors can be used to program the maximum operational voltage for the power converter as shown in [Figure](#page-27-0) 23. When the OVP pin voltage rises above the 1.25 V threshold, an internal 20-µA current source is enabled to raise the voltage at the OVP pin, thus providing threshold hysteresis. Resistance values for  $R_1$  and  $R_2$  can be determined from the following equations:

$$
R_1 = \frac{V_{HYS}}{20 \mu A}
$$

$$
R_2 = \frac{1.25V \times R_1}{V_{PWR} - 1.25V + (20 \mu A \times R1)}
$$

(7)

<span id="page-26-1"></span>If the LM5045 is to be disabled when  $V_{PWR\text{-}OFF}$  reaches 80 V and enabled when it is decreased to 78 V.  $R_1$ should be 100 kΩ, and R<sub>2</sub> should be 1.5 kΩ. The voltage at the OVP pin should not exceed 7 V at any time.



**Figure 22. Basic UVLO Configuration**





**Figure 23. Basic OVP Configuration**

<span id="page-27-0"></span>

**Figure 24. UVLO/OVP Divider**

<span id="page-27-1"></span>The UVLO and OVP can also be set together using a 3 resistor divider ladder as shown in [Figure](#page-27-1) 24.  $R_1$  is calculated as explained in the basic UVLO divider selection. Using the same values, as in the above two examples, for the UVLO and OVP set points,  $R_1$  and  $R_3$  remain the same at 100 kΩ and 1.5 kΩ. The  $R_2$  is 2.7 kΩ obtained by subtracting R<sub>3</sub> from 4.2 kΩ.

Remote configuration of the controller's operational modes can be accomplished with open drain device(s) connected to the UVLO pin as shown in [Figure](#page-28-0) 25.

[Figure](#page-28-1) 26 shows an application of the OVP comparator for Remote Thermal Protection using a thermistor (or multiple thermistors) which may be located near the main heat sources of the power converter. The negative temperature coefficient (NTC) thermistor is nearly logarithmic, and in this example a 100 kΩ thermistor with the β material constant of 4500 Kelvin changes to approximately 2 kΩ at 130°C. Setting R<sub>1</sub> to one-third of this resistance (665 Ω) establishes 130°C as the desired trip point (for VREF = 5 V). In a temperature band from 20ºC below to 20ºC above the OVP threshold, the voltage divider is nearly linear with 25mV per ºC sensitivity.

R<sub>2</sub> provides temperature hysteresis by raising the OVP comparator input by R<sub>2</sub> x 20µA. For example, if a 22k $\Omega$ resistor is selected for R<sub>2</sub>, then the OVP pin voltage will increase by 22 kΩ x 20 µA = 506 mV. The NTC temperature must therefore fall by 506 mV / 25 mV per  $^{\circ}C = 20^{\circ}C$  before the LM5045 switches from standby mode to the normal mode.





**Figure 25. Remote Standby and Disable Control**



**Figure 26. Remote Thermal Protection**

### <span id="page-28-1"></span><span id="page-28-0"></span>*8.2.2.4 Current Sense*

The CS pin receives an input signal representative of its transformer's primary current, either from a current sense transformer or from a resistor located at the junction of source pin of the primary switches, as shown in [Figure](#page-29-0) 27 and Figure 28, respectively. In both the cases, the filter components  $R_F$  and  $C_F$  should be located as close to the IC as possible, and the ground connection from the current sense transformer, or  $R_{\text{SENSE}}$  should be a dedicated trace to the appropriate GND pin. Please refer to the *[Layout](#page-33-1)* section for more layout tips.

The current sense components must provide a signal  $> 710$  mV at the CS pin during an over-load event. Once the voltage on the CS pin crosses the current limit threshold, the current sense comparator terminates the PWM pulse and starts to charge the RES pin. Depending on the configuration of the RES pin, the LM5045 will eventually initiate a hiccup mode restart or be in continuous current limit.

<span id="page-28-2"></span>

**Figure 27. Transformer Current Sense**





**Figure 28. Resistor Current Sense**

### <span id="page-29-0"></span>*8.2.2.5 Hiccup Mode Current Limit Restart*

The operation of the hiccup mode restart circuit is explained in the section. During a continuous current limit condition, the RES pin is charged with 30 µA current source. The restart delay time required to reach the 1.0 V threshold is given by:

$$
T_{CS} = \frac{C_{RES} \times 1.0V}{30 \mu A}
$$
 (8)

This establishes the time allowed before the IC initiates a hiccup restart sequence. For example, if the  $C_{RES}$  = 0.01 µF, the time TCS as noted in [Figure](#page-29-1) 29 below is 334 µs. Once the RES pin reaches 1.0 V, the 30 µA current source is turned-off and a 10 µA current source is turned-on during the ramp up to 4 V and a 5 µA is turned on during the ramp down to 2 V. The hiccup mode off-time is given by:

$$
T_{\text{HICCUP}} = \frac{C_{\text{RES}} \times (2.0 \text{V} \times 8)}{5 \mu \text{A}} + \frac{C_{\text{RES}} \times ((2.0 \text{V} \times 8) + 1.0 \text{V})}{10 \mu \text{A}}
$$
(9)

With a  $C_{RES}$  = 0.01 µF, the hiccup time is 49 ms. Once the hiccup time is finished, the RES pin is pulled low and the SS pin is released allowing a soft-start sequence to commence. Once the SS pin reaches 1 V, the PWM pulses will commence. The hiccup mode provides a cool-down period for the power converter in the event of a sustained overload condition thereby lowering the average input current and temperature of the power components during such an event.



<span id="page-29-1"></span>



### *8.2.2.6 Augmenting the Gate Drive Strength*

The LM5045 includes powerful 2-A integrated gate drivers. However, in certain high-power applications (> 500 W), it might be necessary to augment the strength of the internal gate driver to achieve higher efficiency and better thermal performance. In high power applications, typically, the I<sup>2</sup>xR loss in the primary MOSFETs is significantly higher than the switching loss. To minimize the l<sup>2</sup>xR loss, either the primary MOSFETs are paralleled or MOSFETs with low  $R_{DS (on)}$  are employed. Both these scenarios increase the total gate charge to be driven by the controller IC. An increase in the gate charge increases the FET transition time and hence increases the switching losses. Therefore, to keep the total losses within a manageable limit the transition time must be reduced.

Generally, during the Miller capacitance charge/discharge the total available driver current is lower during the turnoff process than during the turnon process and often it is enough to speed-up the turnoff time to achieve the efficiency and thermal goals. This can be achieved simply by employing a PNP device, as shown in [Figure](#page-30-0) 30, from gate to source of the power FET. During the turnon process, when the LO1 goes high, the current is sourced through the diode D1 and the BJT Q1 provides the path for the turnoff current. Q1 should be located as close to the power FET as possible so that the turnoff current has the shortest possible path to the ground and does not have to pass through the controller.



**Figure 30. Circuit to Speed-Up the Turnoff Process**

<span id="page-30-0"></span>Depending on the gate charge characteristics of the primary FET, if it is required to speed up both the turnon and the turnoff time, a bipolar totem pole structure as shown in [Figure](#page-31-0) 31 can be used. When LO1 goes high, the gate to source current is sourced through the NPN transistor Q1 and similar to the circuit shown in [Figure](#page-30-0) 30 when LO1 goes low, the PNP transistor Q2 expedites the turnoff process.





**Figure 31. Bipolar Totem Pole Arrangement**

<span id="page-31-0"></span>Alternatively, a low-side gate driver such as LM5112 can be used instead of the discrete totem pole. The LM5112 comes in a small package with a 3A source and a 7A sink capability. While driving the high-side FET, the HS1 acts as a local ground and the boot capacitor between the BST and HS pins acts as VCC.



**Figure 32. Using a Low-Side Gate Driver to Augment Gate Drive Strength**



# **8.2.3 Application Curve**



**Figure 33. Application Board Efficiency**



# <span id="page-33-0"></span>**9 Power Supply Recommendations**

The LM5045 can be used to control power levels up to 1 kW. Therefore the current levels can be considerable. Care should be taken that components with the correct current rating are chosen. This would include magnetic components, power MOSFETS and diodes, connectors and wire sizes. Input and output capacitors should have the correct ripple current rating. The use of a multilayer PCB is recommended with a copper area chosen to ensure the LM5045 is operating below its maximum junction temperature.

Full power loading should never be attempted with providing with providing adequate cooling.

# <span id="page-33-1"></span>**10 Layout**

## <span id="page-33-2"></span>**10.1 Layout Guidelines**

The LM5045 current sense and PWM comparators are very fast and respond to short duration noise pulses. The components at the CS, COMP, SLOPE, RAMP, SS, SSSR, RES, UVLO, OVP, RD1, RD2, and RT pins should be physically close as possible to the IC, thereby minimizing noise pickup on the PC board trace inductance. Eliminating or minimizing via's in these critical connections are essential. Layout consideration is critical for the current sense filter. If a current sense transformer is used, both leads of the transformer secondary should be routed to the sense filter components and to the IC pins. The ground side of the transformer should be connected via a dedicated PC board trace to the AGND pin, rather than through the ground plane. If the current sense circuit employs a sense resistor in the drive transistor source, low inductance resistors should be used. In this case, all the noise sensitive, low-current ground trace should be connected in common near the IC, and then a single connection made to the power ground (sense resistor ground point).

The gate drive outputs of the LM5045 should have short, direct paths to the power MOSFETs to minimize inductance in the PC board. The boot-strap capacitors required for the high side gate drivers should be located very close to the IC and connected directly to the BST and HS pins. The VCC and REF capacitors should also be placed close to their respective pins with short trace inductance. Low ESR and ESL ceramic capacitors are recommended for the boot-strap, VCC and the REF capacitors. The two ground pins (AGND, PGND) must be connected together directly underneath the IC with a short, direct connection, to avoid jitter due to relative ground bounce.



## <span id="page-34-0"></span>**10.2 Layout Example**



**Figure 34. Layout of Components Around RAMP, CS, SLOPE, COMP, RT, RD1, RD2, RES, SS, and SSR**

Texas **NSTRUMENTS** 

# **Layout Example (continued)**



**Figure 35. Layout of Components Around VIN, VCC, AGND, PGND UVLO, OVP, REF, BST1, BST2, HS1, and HS2**



# <span id="page-36-0"></span>**11 Device and Documentation Support**

# <span id="page-36-1"></span>**11.1 Trademarks**

PowerPAD is a trademark of Texas Instruments. All other trademarks are the property of their respective owners.

# <span id="page-36-2"></span>**11.2 Electrostatic Discharge Caution**



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

## <span id="page-36-3"></span>**11.3 Glossary**

[SLYZ022](http://www.ti.com/lit/pdf/SLYZ022) — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.

# <span id="page-36-4"></span>**12 Mechanical, Packaging, and Orderable Information**

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



# **PACKAGING INFORMATION**



**(1)** The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

**(3)** MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

**(4)** There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

**(6)** Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



# **PACKAGE OPTION ADDENDUM**

www.ti.com 10-Dec-2020

continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.



**TEXAS** 

# **TAPE AND REEL INFORMATION**

**ISTRUMENTS** 





### **QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE**







# **PACKAGE MATERIALS INFORMATION**

www.ti.com 31-Oct-2024



\*All dimensions are nominal



# **TEXAS INSTRUMENTS**

www.ti.com 31-Oct-2024

# **TUBE**



# **B - Alignment groove width**

\*All dimensions are nominal



# **MECHANICAL DATA**



- B. This drawing is subject to change without notice.
- $C.$ QFN (Quad Flatpack No-Lead) Package configuration.

The package thermal pad must be soldered to the board for thermal and mechanical performance.<br>See the Product Data Sheet for details regarding the exposed thermal pad dimensions. ⚠

- 
- E. Falls within JEDEC MO-220.





# **PACKAGE OUTLINE**

# **PWP0028A PowerPAD - 1.1 mm max height** TM

PLASTIC SMALL OUTLINE



NOTES:

PowerPAD is a trademark of Texas Instruments.

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm, per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm, per side.
- 5. Reference JEDEC registration MO-153, variation AET.



# **EXAMPLE BOARD LAYOUT**

# **PWP0028A** PowerPAD™ - 1.1 mm max height

PLASTIC SMALL OUTLINE



NOTES: (continued)

- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.
- 8. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature numbers SLMA002 (www.ti.com/lit/slma002) and SLMA004 (www.ti.com/lit/slma004).
- 9. Size of metal pad may vary due to creepage requirement.



# **EXAMPLE STENCIL DESIGN**

# **PWP0028A** PowerPAD™ - 1.1 mm max height

PLASTIC SMALL OUTLINE



NOTES: (continued)

10. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.

11. Board assembly site may have different recommendations for stencil design.



# **IMPORTANT NOTICE AND DISCLAIMER**

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](https://www.ti.com/legal/terms-conditions/terms-of-sale.html) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated