

## Design Note

**UC1525B/UC1527B DEVICES**  
 Comparison Summary to UC1525A/27A Devices

The UC1525B and UC1527B devices are enhanced versions of the previous generation of UC1525A and UC1527A devices. They are pin-for-pin compatible and direct replacements for the "A" versions in

almost all applications. Significant improvements have been made in the 5.1 V reference voltage and the output drivers as itemized in the tables below.

PARAMETER	NEW: UC1515B/27B	OLD: UC1525A/27A
REFERENCE VOLTAGE		
$V_{REF}$ (min)	5.062 V	5.05 v
$V_{REF}$ (max)	5.138 V	5.15 v
Line Regulation (max)	+/- 10 mV	+/-20 mV
Load Regulation (max)	+/-15 mV	+/-50 mV
Temperature Stability (max)	+/-30 mV	+/-50 mV
Total Output Variation (max)	5.036 V to 5.164 V	5.00 V to 5.20V
Long Term Stability (max)	+/-10 mV	+/-50 mV
Temperature Coefficient (typ)	8 ppm/deg. C	
PWM OUTPUT SECTION		
Minimum On-Time (typ)	350 nS	600 nS
Cross Conduction	30 nC	150 nC
SUPPLY CURRENT		
ICC Increase (40 kHz to 400 kHz)	15 mA (max)	40 mA (typ)
ESD PROTECTION		
Discharge Withstand Voltage (typ)	2 kV (typ all pins)	no protection

## IMPORTANT NOTICE

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgement, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF TI PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE FULLY AT THE CUSTOMER'S RISK.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.