

# Assembly Bill of Materials

# Texas Instruments

Enter search term in cell K2 below

[Search Findchips.com](#)

[Search Digi-Key](#)

[Search Mouser](#)

[Search Newark](#)

[Search RS Components](#)

Project Name:	DP83867ERGZ-R-EVM
Project File:	SV601189A.PrjPcb
Base ID:	SV601189
Schematic Rev:	A
Assembly Variant:	None
Build Quantity:	100
Generated:	10/2/2015 2:01:58 PM

Item	Designator	Description	RoHS	Manufacturer	PartNumber	Quantity	Required	Supplier 1	Supplier Part Number 1	Supplier 2	Supplier Part Number 2	Alternate Manufacturer	Alternate PartNumber
1	5V, GND	Terminal, Turret, TH, Double	Y	Keystone	1502-2	2	200	Digi-Key	1502-2K-ND				
2	C1, C4, C8, C37, C38	CAP, CERM, 1 µF, 10 V, +/- 10%, X5R, 0402	Y	TDK	C1005X5R1A105K050BB	5	500	Digi-Key	445-4114-1-ND	Mouser	810-C1005X5R1A105K		
3	C2, C9, C39, C40	CAP, CERM, 0.1 µF, 10 V, +/- 10%, X5R, 0402	Y	TDK	C1005X5R1A104K050BA	4	400	Digi-Key	445-1265-1-ND	Mouser	810-C1005X5R1A104K		
4	C3, C5, C10, C11, C13, C49	CAP, CERM, 1000 pF, 25 V, +/- 5%, X7R, 0402	Y	Kemet	C0402C102J3RACTU	6	600	Digi-Key	399-7752-1-ND	Mouser	80-C0402C102J3R		
5	C6	CAP, CERM, 0.01 µF, 50 V, +/- 10%, X7R, 0402	Y	MuRata	GRM155R71H103KA88D	1	100	Digi-Key	490-4516-1-ND	Mouser	81-GRM155R71H103KA8D		
6	C12, C29	CAP, CERM, 0.01 µF, 50 V, +/- 5%, X7R, 0402	Y	Kemet	C0402C103J5RACTU	2	200	Digi-Key	399-7758-1-ND	Mouser	80-C0402C103J5R		
7	C14, C36, C44, C47, C48, C55, C61	CAP, CERM, 100 pF, 50 V, +/- 5%, COG/NP0, 0402	Y	Yageo America	CC0402JRNPO9BN101	7	700	Digi-Key	311-1024-1-ND	Mouser	603-CC402JRNPO9BN101		
8	C15, C16, C64	CAP, CERM, 27 pF, 50 V, +/- 1%, COG/NP0, 0603	Y	Samsung Electro-Mechanics, Samsung Electro-Mechanics, Samsung	CL10C270FB8NNNC	3	300	[NoValue], [NoValue], Digi-Key	[NoValue], [NoValue], 1276-2245-6-ND				
9	C17, C19, C20, C22, C23, C25, C26, C28	CAP, CERM, 0.033 µF, 6.3 V, +/- 10%, X5R, 0201	Y	MuRata	GRM033R60J333KE01D	8	800	Digi-Key	490-3170-1-ND	Mouser	81-GRM033R60J333KE01		
10	C18, C21, C24, C27	CAP, CERM, 0.1 µF, 6.3 V, +/- 10%, X5R, 0402	Y	TDK	C1005X5R0J104K	4	400	Digi-Key	445-1266-1-ND	Farnell	1844104		
11	C30, C31	CAP, CERM, 4700 pF, 2000 V, +/- 10%, X7R, 1812	Y	AVX	1812GC472KAT1A	2	200	Digi-Key	478-3003-1-ND	Mouser	581-1812GC472K		
12	C32	CAP, TA, 220 µF, 6.3 V, +/- 10%, 0.7 ohm, SMD	Y	Kemet	T491D227K006AT	1	100	Digi-Key	399-8378-1-ND	Mouser	80-T491D227K006		
13	C33, C50, C56, C57	CAP, CERM, 10 µF, 35 V, +/- 20%, X7R, 1206_190	Y	TDK	C3216X7R1V106M160AC	4	400	Digi-Key	445-8034-1-ND	Mouser	810-C3216X7R1V106M		
14	C34, C35, C42, C53, C59	CAP, CERM, 0.01 µF, 50 V, +/- 5%, X7R, 0603	Y	Kemet	C0603C103J5RACTU	5	500	Digi-Key	399-1092-1-ND	Mouser	80-C0603C103J5R		
15	C41, C52, C62	CAP, TA, 100 µF, 10 V, +/- 20%, 0.1 ohm, SMD	Y	Vishay-Sprague	593D107X0010D2TE3	3	300	Digi-Key	718-1100-1-ND	Mouser	74-593D107X0010D2TE3		
16	C43, C54, C60	CAP, CERM, 1000 pF, 50 V, +/- 10%, COG/NP0, 0603	Y	AVX	06035A102KAT2A	3	300	Digi-Key	478-3718-1-ND	Mouser	581-06035A102KAT2A		
17	C45, C46	CAP, CERM, 1000 pF, 25 V, +/- 10%, X5R, 0402	Y	MuRata	GRM155R61E102KA01D	2	200	Digi-Key	GRM155R61E102KA01D-ND	Mouser	81-GRM155R61E102KA1D		
18	C51	CAP, CERM, 1 µF, 6.3 V, +/- 10%, X7R, 0603	Y	Samsung	CL10B105K08NNNC	1	100	Digi-Key	1276-1024-2-ND				
19	C58	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0603	Y	Samsung	CL10B104K08NNNC	1	100	Digi-Key	1276-1005-2-ND				
20	C63	CAP, CERM, 1 µF, 16 V, +/- 10%, X5R, 0805	Y	AVX	0805YD105KAT2A	1	100	Digi-Key	478-1411-1-ND	Mouser	581-0805YD105K		
21	C65	CAP, CERM, 4.7 µF, 10 V, +/- 20%, Y5V, 0805	Y	Yageo America	CC0805ZRY5V6BB475	1	100	Digi-Key	311-1371-2-ND	Farnell	2370725		
22	C66, C67, C68	CAP, CERM, 4700 pF, 100 V, +/- 10%, X7R, 0805	Y	AVX	08051C472KAT2A	3	300	Digi-Key	478-1356-1-ND	Mouser	581-08051C472K		
23	FID1, FID2, FID3	Fiducial mark. There is nothing to buy or mount.	Y	N/A	N/A	3	300						
24	J1	Connector, Header, High Speed, 20 pairs, SMT	Y	Samtec	QTE-020-01-L-D-A	1	100	Digi-Key	SAM8128-ND				
25	J2, J3	Header, 100mil, 20x2, Gold, TH	Y	Samtec	TSW-120-07-G-D	2	200	Digi-Key	SAM1028-20-ND				
26	J4, J5, J6	Header, 100mil, 3x1, Gold, TH	Y	Samtec	TSW-103-07-G-S	3	300	Digi-Key	SAM1029-03-ND				
27	J7, J8, J9, J10	Header, 100mil, 2x1, Gold, TH	Y	Samtec	HTSW-102-07-G-S	4	400	Digi-Key	SAM8736-ND				
28	J11, J12	Mini-RFCable Connector 50 Ohm	Y	Samtec	MICX-J-P-H-ST-SM1	2	200	Digi-Key	MIMCX-J-P-H-ST-SM1-ND				
29	J13	RJ-45, Right Angle, No LED, tab up	Y	AMP	1-406541-1	1	100	Digi-Key	A97716-ND				
30	J14	Connector, Receptacle, USB Type A, 9 Pins, R/A, TH	Y	FCI	10117835-002LF	1	100	Digi-Key	609-4662-ND	Mouser	649-10117835-002LF		
31	LBL1	Thermal Transfer Printable Labels, 1.250" W x 0.250" H - 10,000 per roll	Y	Brady	THT-13-457-10	1	100	Newark	04H3909				
32	LD1, LD2, LD3, LD4, LD5, LD6, LD7	LED, Green, SMD	Y	Everlight	QTLP630C4TR	7	700	Digi-Key	1080-1411-1-ND	Mouser	638-QTLP630C4TR		
33	P1	Header, 100mil, 4x2, Gold, TH	Y	Samtec	TSW-104-07-G-D	1	100	Digi-Key	SAM1028-04-ND				
34	P2	Header, 100mil, 5x2, Gold, TH	Y	Samtec	TSW-105-07-G-D	1	100	Digi-Key	SAM1028-05-ND				
35	R1, R2, R15, R16, R18, R87, R88, R89, R90	RES, 0, 5%, 0.063 W, 0402	Y	Vishay-Dale	CRCW04020000Z0ED	9	900	Digi-Key	541-0.0JCT-ND	Mouser	71-CRCW0402-0-E3		
36	R3, R4, R5, R6, R7, R8, R9, R10, R11, R12, R13, R14, R91, R92, R93, R94, R95, R96, R97, R98, R99, R100, R101, R102, R103, R104, R105, R106	RES, 0, 5%, 0.05 W, 0201	Y	Panasonic	ERJ-1GE0R00C	28	2800	Digi-Key	P0.0AGCT-ND	Mouser	667-ERJ-1GE0R00C		
37	R17, R50, R51, R54, R57, R58, R59, R67, R68, R70, R71, R72, R74, R77, R78, R79, R81, R82, R86	RES, 0, 5%, 0.1 W, 0603	Y	Yageo America	RC0603JR-070RL	19	1900	Digi-Key	311-0.0GRCT-ND	Mouser	603-RC0603JR-070RL		

38	R19, R24, R28, R34, R37, R40	RES, 470, 1%, 0.1 W, 0603	Y	Yageo America	RC0603FR-07470RL	6	600	Digi-Key	311-470HRCT-ND	Mouser	603-RC0603FR-07470RL		
39	R20	RES, 6.04 k, 1%, 0.1 W, 0603	Y	Vishay-Dale	CRCW06036K04FKEA	1	100	Digi-Key	541-6.04KHCT-ND	Mouser	71-CRCW0603-6.04K-E3		
40	R21	RES, 6.04 k, 1%, 0.1 W, 0603	Y	Yageo America	RC0603FR-076K04L	1	100	Digi-Key	311-6.04KHRCT-ND	Mouser	603-RC0603FR-076K04L		
41	R22, R23, R32, R39	RES, 2.49 k, 1%, 0.1 W, 0603	Y	Yageo America	RC0603FR-072K49L	4	400	Digi-Key	311-2.49KHRCT-ND	Mouser	603-RC0603FR-072K49L		
42	R25, R26, R27, R29, R31, R33, R35, R36, R44	RES, 0, 5%, 0.1 W, 0603	Y	Vishay-Dale	CRCW0603000Z0EA	9	900	Digi-Key	541-0.0GCT-ND	Mouser	71-CRCW0603-0-E3		
43	R30, R38	RES, 11.0 k, 1%, 0.1 W, 0603	Y	Yageo America	RC0603FR-07111KL	2	200	Digi-Key	311-11.0KHRCT-ND	Mouser	603-RC0603FR-07111KL		
44	R41	RES, 22, 5%, 0.1 W, 0603	Y	Vishay-Dale	CRCW060322R0JNEA	1	100	Digi-Key	541-22GCT-ND	Mouser	71-CRCW0603J-22-E3		
45	R42	RES, 100, 1%, 0.1 W, 0603	Y	Vishay-Dale	CRCW0603100RFKEA	1	100	Digi-Key	541-100HCT-ND	Mouser	71-CRCW0603-100-E3		
46	R43, R47, R48, R52, R53, R56	RES, 2.2 k, 5%, 0.063 W, 0402	Y	Vishay-Dale	CRCW04022K20JNED	6	600	Digi-Key	541-2.2KJCT-ND	Mouser	71-CRCW0402J-2.2K-E3		
47	R45	RES, 11.0 k, 1%, 0.1 W, 0603	Y	Vishay-Dale	CRCW060311K0FKEA	1	100	Digi-Key	541-11.0KHCT-ND	Mouser	71-CRCW0603-11K-E3		
48	R46	RES, 4.7 k, 5%, 0.1 W, 0603	Y	Vishay-Dale	CRCW06034K70JNEA	1	100	Digi-Key	541-4.7KGCT-ND	Mouser	71-CRCW0603J-4.7K-E3		
49	R55, R65, R66	RES, 1.00 M, 1%, 0.063 W, 0402	Y	Yageo America	RC0402FR-0711ML	3	300	Digi-Key	311-1.00MLRCT-ND	Mouser	603-RC0402FR-0711ML		
50	R61, R62, R63, R64	RES, 75.0, 1%, 0.063 W, 0402	Y	Vishay-Dale	CRCW040275R0FKED	4	400	Digi-Key	541-75.0LCT-ND	Mouser	71-CRCW0402-75-E3		
51	R69	RES, 750, 5%, 0.1 W, 0603	Y	Yageo America	RC0603JR-07750RL	1	100	Digi-Key	311-750GRCT-ND	Mouser	603-RC0603JR-07750RL		
52	R73	RES, 48.7 k, 1%, 0.1 W, 0603	Y	Vishay-Dale	CRCW060348K7FKEA	1	100	Digi-Key	541-48.7KHCT-ND	Mouser	71-CRCW0603-48.7K-E3		
53	R76	RES, 45.3 k, 1%, 0.1 W, 0603	Y	Yageo America	RC0603FR-0745K3L	1	100	Digi-Key	311-45.3KHRCT-ND	Mouser	603-RC0603FR-0745K3L		
54	R80	RES, 10.0 k, 1%, 0.1 W, 0603	Y	Yageo America	RC0603FR-0710KL	1	100	Digi-Key	311-10.0KHRCT-ND	Mouser	603-RC0603FR-0710KL		
55	R83	RES, 1.13 k, 1%, 0.1 W, 0603	Y	Vishay-Dale	CRCW06031K13FKEA	1	100	Digi-Key	541-1.13KHCT-ND	Mouser	71-CRCW0603-1.13K-E3		
56	R85	RES, 4.53 k, 1%, 0.1 W, 0603	Y	Vishay-Dale	CRCW06034K53FKEA	1	100	Digi-Key	541-4.53KHCT-ND	Mouser	71-CRCW0603-4.53K-E3		
57	S1	Switch, Tactile, SPST-NO, 0.05A, 12V, SMT	Y	TE Connectivity	4-1437565-1	1	100	Digi-Key	450-1129-ND	Mouser	506-FSM4J5MA		
58	SH-J4, SH-J5, SH-J6	Shunt, 100mil, Gold plated, Black	Y	3M	969102-0000-DA	3	300	Digi-Key	3M9580-ND	Mouser	517-9691020000DA	Samtec	SNT-100-BK-G
59	T1	Transformer, 325 uH, SMT	Y	Pulse Engineering	HX5008NL	1	100	Digi-key	553-1344-ND	Mouser	673-HX5008NL		
60	U1	Robust, Low Power 10/100/1000 Ethernet Physical Layer Transceiver, RGZ0048B	Y	Texas Instruments	DP83867RGZR	1	100					Texas Instruments	DP83867RGZT
61	U2	OSC, 25 MHz, 1.6 to 3.6 V, SMD	Y	Epson	SG-210STF25.000000MHZY	1	100						
62	U3, U4	1, 4, 6 CHANNEL PROTECTION SOLUTION FOR SUPER-SPEED (UP TO 6 GBPS) INTERFACE, DOA0010A	Y	Texas Instruments	TPD4E05U06DQAR	2	200					Texas Instruments	
63	U5	Single Output High PSRR LDO, 500 mA, Adjustable 1.25 to 6 V Output, 2.7 to 6.5 V Input, with Low IQ, 6-pin SON (DRV), -40 to 125 degC, Green (RoHS & no Sb/Br)	Y	Texas Instruments	TPS73501DRVR	1	100	Digi-Key	296-34785-2-ND	Digi-Key	296-34785-1-ND	None	Equivalent
64	U6	Single Output LDO, 500 mA, Adjustable 0.8 to 3.6 V Output, 0.8 to 5.5 V Input, with Programmable Soft Start, 10-pin SON (DRC), -40 to 125 degC, Green (RoHS & no Sb/Br)	Y	Texas Instruments	TPS74701DRCR	1	100	Digi-Key	296-22987-2-ND	Digi-Key	296-22987-1-ND	None	Equivalent
65	XTAL1	Crystal, 25 MHz, 18 pF, SMD	Y	Abracon Corporation	ABM3-25.000MHZ-D2W-T	1	100						

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
OMAP Applications Processors	<a href="http://www.ti.com/omap">www.ti.com/omap</a>
Wireless Connectivity	<a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a>

### Applications

Automotive and Transportation	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>

### TI E2E Community

[e2e.ti.com](http://e2e.ti.com)