

**COP820CJ,COP840CJ,COP880C,COP884BC,
COP888CF,COP888CL,COP888EK,COP888FH,
COP888GW,COP8ACC5,COP8AME9,COP8CBE9,
COP8CBR9,COP8CCE9,COP8CCR9,COP8CDR9,
COP8SAA7,COP8SAC7,COP8SBR9,COP8SCR9,
COP8SDR9,COP8SGE5,COP8SGE7,COP8SGG5,
COP8SGH5,COP8SGK5,COP8SGR5,COP8SGR7,
COP912C**

AN-952 Low Cost A/D Conversion Using COP800



Literature Number: SNOA328

Low Cost A/D Conversion Using COP800

National Semiconductor
Application Note 952
Robert Weiss
September 1994



INTRODUCTION

Many microcontroller applications require a low cost analog to digital conversion. In most cases the controller applications do not need high accuracy and short conversion time. This appnote describes a simple method for performing analog to digital conversion by reducing external elements and costs.

PRINCIPLE OF A/D CONVERSION

The principle of the single slope conversion technique is to measure the time it takes for the RC network to charge up to the threshold level on the port pin, by using Timer T1 in the input capture mode. The cycle count obtained in Timer T1 can be converted into voltage, either by direct calculation or by using a suitable approximation.

Figure 1 shows the block diagram for the simple A/D conversion which measures the temperature.

BASIC CIRCUIT IMPLEMENTATION

Usually most applications use a comparator to measure the time it takes for a RC network to charge up to the voltage level on the comparator input. To reduce cost, it is possible to switch both inputs as shown in Figure 2.

Port G3 is the Timer T1 input. Ports G2/G1 are general purpose I/O pins that can be configured using the I/O configurations (push-pull output/tristate). All Port G pins are Schmitt Trigger inputs. R_{LIM} is required to reduce the discharge current.

GENERAL IMPLEMENTATION

The temperature is measured with a NTC which is linearized with a parallel resistor. Using a parallel resistor, a linearization in the range of 100 Kelvin can be reached. The value of the resistor can be calculated as follow:

$$R_p = R_{tm} * (B - 2T_m) / (B + 2T_m)$$

- R_{tm} Value of the NTC at a medium temperature
- T_m Medium Temperature
- B NTC-material constant

The linearization reduces the code, improves the accuracy and the tolerance of the NTC-R network (e.g. NTC = 100 kΩ ±10%, R = 12 kΩ ±1%, NTC//R ±2%). Using that method the useful range does not cover the whole operating temperature range of the NTC.

GENERAL ACCURACY CONSIDERATIONS

Using a single slope A/D conversion the accuracy is dependent on the following parameters:

- Stability of the Clock frequency
- Time constant of the RC network
- Accuracy of the Schmitt Trigger level
- Non-linearity of the RC-network

Figure 3. The maximum failure that appears when a sawtooth is generated without using a current source. In the current application the maximum failure would be more than 15% without using methods for reducing the non-linearities of RC-network/NTC-network.




FIGURE 2. Basic Circuit Implementation





FIGURE 1. Simple A/D Conversion

TL/DD/12075-2

TL/DD/12075-1




TL/DD/12075-3

FIGURE 3. Single Slope A/D Conversion

The maximum error occurs when the gradient of the exponential function (RC) equals the gradient of the straight line (counter).

To reduce the error that is caused by the non-linearity of the RC-network a offset should be added to the calculated value. The offset reduce the failure to the middle.

Further, the accuracy can be improved by using a relative measurement method. The following diagram shows the method.



TL/DD/12075-4

FIGURE 4. Accuracy Improvement

Measurement:


- Timer Capture mode: $R_{CAL} * C$ is measured
- Timer Capture mode: $R_{NTC}/R * C$ is measured

Calculation:

- Build the vertical-component ($R_{TMIN} - R_{TMAX}$) of the triangle
- Calculate the slope
- Calculate the actual temperature

Using this method the accuracy is primarily dependent on the accuracy of R_{TMIN} and R_{TMAX} and independent of the stability of the system clock, the capacitor and the threshold of the Schmitt Trigger level. The variation of the capacitor only leads to variation of the resolution.

The following diagram shows the ideal resistance/temperature characteristic of a NTC which is linearized with a parallel resistor.



TL/DD/12075-5

FIGURE 5. Resistance vs Temperature Characteristics

APPLICATION EXAMPLE

The following application example for temperature measurement demonstrates the procedure. The temperature is measured from 20° to 100° and is displayed on a Triplex LCD display.

- NTC₂₀ = 100 kΩ ± 10%
- R_P = 12 kΩ ± 1%
- T_m = 333 Kelvin → 60 Degrees
- B = 4800 Kelvin
- NTC₂₀/R_P = 10.7 kΩ ± 2%
- R_{CAL} = 10.7 kΩ ± 1%
- T_{MIN} = 20 Degree
- R_{TMIN} = 10.7 kΩ
- T_{MAX} = 100 Degree

- R_{TMAX} = 2.8 kΩ
- C = 1 μF
- RC-Clock = 2 MHz → 200 kHz instruction cycle, 5 μs
- Timeconst. = R_{CAL} * C → 0.0107s
- Resolution = 2140 → 11 byte, depends which Cap. value is used
- Accuracy = ±2 Degree

This temperature measurement example shows a low cost technique ideally suited for cost sensitive applications which do not need high accuracy.

Figure 6 shows the complete circuit of the demoboard using the Triplex LCD method and the low cost A/D conversion technique.

The Triplex LCD drive technique is documented in a separate application note.





FIGURE 6. Circuit Diagram

Pressing key 1, key 2 the temperature is displayed in Degree/Fahrenheit.
Pressing key 3, key 4 Up/Down counter is displayed.

SOURCE CODE

Figure 7 shows the flow chart of the program.



TL/DD/12075-8

FIGURE 7. Flow Chart

The following code is required to implement the function. It does not include the code for the Triplex LCD drive.

```

RAM = 17 Byte;
ROM = 450 Byte; Optimization is possible about 50 byte if the B - pointer consistent is used!
;*****A/D-CONVERSION*****
;
;
;*****VAR. DECLARATION*****
.SECT REGPAGE,REG
COUNT1: .DSB 1
COUNT2: .DSB 1
;
.SECT BASEPAGE,BASE
ZL:      .DSB 1      ;TEMPORARY
YL:      .DSB 1      ;TEMPORARY
;
.SECT RAMPAGE,RAM
CALIBLO: .DSB 1      ;CALIBRATION-VALUE
CALIBHI: .DSB 1
NTCLO:   .DSB 1      ;NTC-VALUE
NTCHI:   .DSB 1
TEMP:    .DSB 2      ;TEMP.-VALUE
KORRL:   .DSB 2
COMPL:   .DSB 1
COMPH:   .DSB 1
CONTROL: .DSB 1      ;STATUS REGISTER
;*****START MAIN PROGRAM*****
MAIN: LD  SP,#06F      ;INIT SPACKPOINTER
      JSR DISCH        ;DISCHARGE C (A/D-CONVERSION)
      JSR CALB         ;INIT CAPTURE MODE FOR UREF. MEASURMENT
POLL: IFBIT 3,PORTGP  ;POLL - MODE (TIO - PORT)
      JP  CAL
      JP  POLL
CAL:  LD  B,#CALIBLO
      JSR CAPTH        ;STOP TIMER, STORE CAPTURE VALUE
      JSR CALCR        ;SLOPE IS CALCULATED
NEW:  JSR DISCH        ;DISCHARGE C (A/D-CONVERSION)
      JSR NTC          ;INIT CAPTURE MODEFOR UNTC MEASURMENT
POLL1: IFBIT 3,PORTGP ;POLL-MODE
      JP  CAL1
      JP  POLL1
CAL1: LD  B,#NTCLO
      JSR CAPTH        ;STOP TIMER, STORE CAPTURE VALUE
      JSR CALCN        ;TEMPERATURE IS CALCULATED
      JSR DISCH        ;DISCHARGE C (A/D-CONVERSION)
      JSR DCHECK       ;REDUCE THE DISPLAY FLICKERING
      JMP NEW
.ENDSECT
;*****

```

TL/DD/12075-9

```

*****
;
;SECT CODE1,ROM
;THIS ROUTINE IS REQUIRED TO REDUCE THE NOICE ON THE LINE AND THE
;DISPLAY FLICKERING.
;SECT CODE1,ROM
DCHECK:
LD A,CONTROL ;COMPARE TWO VALUES, IF EQUAL THEN
XOR A,#080 ;DISPLAY IT, OTHERWISE THE OLD VALUE
X A,CONTROL ;IS DISPLAYED
IFBIT 7,CONTROL
JSR SAVE ;TEMP. SAVE
JSR COMP ;COMPARE
RET
*****
; HANDLER FOR CAPTURE MODE
CAPTH: RBIT TPND,PSW ;RESET TIMER PENDING
RBIT TRUN,PSW ;STOP TIMER
LD A,#0FF
SC
SUBC A,TAULO
X A,[B+] ;STORE THE CAPTURED VALUE
LD A,#0FF
SUBC A,TAUHI
X A,[B+] ;STORE THE CAPTURED VALUE
RET
*****
; CALIBRATION SUBROUTINE, UREF IS MEASURED
CALB:
RBIT 3,PORTGD
RBIT 3,PORTGC ;TRISTATE TIO
LD PORTCD,#00
LD PORTCC,#00 ;TRISTATE PORT C
TICAP HIGH ;INIT CAPTURE MODE. HIGH SENSITIVE (MACRO)
LD B,#CALIBLO
SBIT 0,PORTCD ;CONFIGURE C0 TO OUTPUT HIGH
SBIT 0,PORTCC ;CHARGE CAP.
SBIT TRUN,CNTRL ;START TIMER CAPTURE MODE
RET
*****
; NTC SUBROUTINE, UNTC IS MEASURED
NTC:
RBIT 3,PORTGD
RBIT 3,PORTGC ;TRISTAT TIO
LD PORTCD,#00
LD PORTCC,#00 ;TRISTATE PORT C
TICAP HIGH ;INIT CAPTURE MODE. HIGH SENSITIVE (MACRO)
LD B,#NTCLO
SBIT 1,PORTCD ;CONFIGURE C1 TO OUTPUT HIGH
SBIT 1,PORTCC ;CHARGE CAP.
SBIT TRUN,CNTRL ;START TIMER CAPTURE MODE
RET
*****

```

TL/DD/12075-10

```

;*****
;DISCHARGE - ROUTINE
DISCH:
    LD PORTCD,#000
    LD PORTCC,#000
    RBIT TIO,PORTGD ;DISCHARGE CAP.
    SBIT TIO,PORTGC
    LD COUNT1,#H(500) ;DISCHARGE TIME
    LD COUNT2,#L(500)
    JSR C1 ;DELAY ROUTINE FOR DISCHARGE TIME
    RET
;*****
;THIS SUBROUTINE CALCULATES THE SLOPE
;THE FOLLOWING CALCULATIONS ARE DONE
;KORR=CALIB/11KOHM (RCALIB.=11KOHM)
;KORR=KORR*2,8KOHM (T=100 DEGREE, RNTC=2,8KOHM)
;CALIB=CALIB-KORR
;DIV=CALIB\80 (TEMPRANGE=80 DEGREE,100-20), SLOPE IS CALCULATED
CALCR:
;KORR=CALIB/11KOHM
    LD ZL,#L(110)
    LD ZL+1,#H(110)
    LD A,CALIBLO
    X A,YL
    LD A,CALIBHI
    X A,YL+1
    JSR DIVBIN16 ;SUBROUTINE BINARY DIVIDE 16 BIT BY 16 BIT
    LD A,YL
    X A,KORRL
;*****
;KORR=KORR*28
    LD A,KORRL
    X A,ZL
    LD A,#28
    X A,YL
    JSR MULBIN8 ;SUBROUTINE MULTIPLY TWO 8 BIT VALUES
    LD A,YL
    X A,KORRL
    LD A,YL+1
    X A,KORRL+1
;*****
;KORR=CALIB-KORR
    LD B,#CALIBLO
    LD A,[B+]
    SC
    SUBC A,KORRL
    X A,KORRL
    LD A,[B]

```

TL/DD/12075-11


```

SUBC A,KORRL+1
X A,KORRL+1
;*****
;DIV=KORR/80
LD ZL,#L(80)
LD ZL+1,#H(80)
LD A,KORRL
X A,YL
LD A,KORRL+1
X A,YL+1
JSR DIVBIN16      ;SUBROUTINE BINARY DIVIDE 16 BIT BY 16 BIT
LD A,YL
X A,DIV
RET
;*****
;THIS SUBROUTINE CALCULATES THE TEMPERATURE
;THE FOLLOWING CALCULATIONS ARE DONE
;TEMP=CALIB-NTC
;TEMP=TEMP/DIV
;ADD OFFSET 20 DEGREE
;CONVERSION FROM HEX TO BCD
;*****
;TEMP=CALIB-NTC
CALCN: LD B,#CALIBLO
LD A,[B+]
SC
SUBC A,NTCLO
X A,TEMP
LD A,[B]
SUBC A,NTCHI
IFNC
JMP ERR
X A,TEMP+1
;*****
;TEMP=TEMP/DIV
LD A,TEMP
X A,YL
LD A,TEMP+1
X A,YL+1
LD A,DIV
X A,ZL
CLRA
X A,ZL+1
JSR DIVBIN16      ;SUBROUTINE BINARY DIVIDE 16 BIT BY 16 BIT
LD A,YL
ADD A,#20        ;ADD TEMPERATURE OFFSET
IFGT A,#56       ;IF TEMPERATURE IS HIGER THAN 56 DEGREE THEN
JSR CORR        ;ADD CORRECTION. OFFSET
;*****

```

TL/DD/12075-12

```

;*****
;
;HEX TO BCD CONVERSION
  X A,ZL
  LD A,ZL
  IFGT A,#100      ;IF TEMPERATURE IS MORE THAN 100 DEGREE THEN
  JP ERR          ;ERROR
  JSR BINBCD      ;SUBROUTINE BINARY TO BCD CONVERSION;
  LD A,BCDLO
  X A,TEMP
  LD A,BCDLO+1
  X A,TEMP+1
  RET
ERR: LD A,#00E    ;ERROR MESSAGE IS DISPLAYED
  X A,TEMP
  CLR A
  X A,TEMP+1
  RET
;*****
;
COMP: LD  A,COMPL  ;IF THE LAST BOTH MEASURMENTS ARE EQUAL
      SC          ;THEN DISPLAY
      SUBC A,TEMP
      IFEQ A,#0
      JP  DISPLAY
      RET          ;OTHERWISE DISPLAY THE OLD VALUE
DISPLAY:LD  A,TEMP
        X   A,PB+2
        LD  A,TEMP+1
M1:    X   A,PB+3
        JSR LCDDR  ;UPDATE THE DISPLAY
        JSR DEL    ;DELAY TIME
        RET
;*****
;
SAVE: LD  A,TEMP  ;TEMPORARY SAVE
      X   A,COMPL
      LD  A,TEMP+1
      X   A,COMPH
      RET
;*****
;

```

TL/DD/12075-13

LIFE SUPPORT POLICY

NATIONAL'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF NATIONAL SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.



National Semiconductor Corporation
 2900 Semiconductor Drive
 P.O. Box 58090
 Santa Clara, CA 95052-8090
 Tel: 1(800) 272-9959
 TWX: (910) 339-9240

National Semiconductor GmbH
 Livny-Gargan-Str. 10
 D-82256 Fürstfeldbruck
 Germany
 Tel: (81-41) 35-0
 Telex: 527849
 Fax: (81-41) 35-1

National Semiconductor Japan Ltd.
 Sumitomo Chemical
 Engineering Center
 Bldg. 7F
 1-7-1, Nakase, Mihama-Ku
 Chiba-City,
 Ciba Prefecture 261
 Tel: (043) 299-2300
 Fax: (043) 299-2500

National Semiconductor Hong Kong Ltd.
 13th Floor, Straight Block,
 Ocean Centre, 5 Canton Rd.
 Tsimshatsui, Kowloon
 Hong Kong
 Tel: (852) 2737-1600
 Fax: (852) 2736-9960

National Semicondutores Do Brazil Ltda.
 Rue Deputado Lacorda Franco
 120-3A
 Sao Paulo-SP
 Brazil 05418-000
 Tel: (55-11) 212-5066
 Telex: 391-1131931 NSBR BR
 Fax: (55-11) 212-1181

National Semiconductor (Australia) Pty, Ltd.
 Building 16
 Business Park Drive
 Monash Business Park
 Nottingham, Melbourne
 Victoria 3168 Australia
 Tel: (3) 558-9999
 Fax: (3) 558-9998

National does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and National reserves the right at any time without notice to change said circuitry and specifications.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Mobile Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated