Functional Safety Information

LMR516xx Functional Safety FIT Rate, FMD and Pin FMA



Table of Contents

| 1 Overview | |
|---|---|
| 2 Failure Mode Distribution (FMD) | (|
| 3 Functional Safety Failure In Time (FIT) Rates | |
| 4 Pin Failure Mode Analysis (Pin FMA) | |

Trademarks

All trademarks are the property of their respective owners.

STRUMENTS Overview www.ti.com

1 Overview

This document contains information for the LMR516xx in the SOT-23 package to aid in a functional safety system design. Information provided are:

- Functional Safety Failure In Time (FIT) rates of the semiconductor component estimated by the application of industry reliability standards
- Component failure modes and their distribution (FMD) based on the primary function of the device
- Pin failure mode analysis (Pin FMA)

Figure 1-1 shows the device functional block diagram for reference.




Figure 1-1. Functional Block Diagram

LMR516xx was developed using a quality-managed development process, but was not developed in accordance with the IEC 61508 or ISO 26262 standards.



2 Failure Mode Distribution (FMD)

The failure mode distribution estimation for LMR516xx in Table 2-1 comes from the combination of common failure modes listed in standards such as IEC 61508 and ISO 26262, the ratio of sub-circuit function size and complexity are from best engineering judgment.

The failure modes listed in this section reflect random failure events and do not include failures due to misuse or overstress.

Table 2-1. Die Failure Modes and Distribution

| Die Failure Modes | Failure Mode Distribution (%) |
|--|-------------------------------|
| SW Output | 50% |
| SW output not in specification voltage or timing | 45% |
| SW driver FET suck on | 5% |



3 Functional Safety Failure In Time (FIT) Rates

This section provides Functional Safety Failure In Time (FIT) rates for the LMR516xx based on the following two different industry-wide used reliability standards:

- Table 3-1 provides FIT rates based on IEC TR 62380 / ISO 26262 part 11
- Table 3-2 provides FIT rates based on the Siemens Norm SN 29500-2

Table 3-1. Component Failure Rates per IEC TR 62380 / ISO 26262 Part 11

| FIT IEC TR 62380 / ISO 26262 | FIT (Failures Per 10 ⁹ Hours) |
|------------------------------|--|
| Total Component FIT Rate | 14 |
| Die FIT Rate | 11 |
| Package FIT Rate | 3 |

The failure rate and mission profile information in Table 3-1 comes from the Reliability data handbook IEC TR 62380 / ISO 26262 part 11:

Mission Profile: Motor Control from Table 11

Power dissipation: 600 mW
Climate type: World-wide Table 8
Package factor (lambda 3): Table 17b

Substrate Material: FR4EOS FIT rate assumed: 0 FIT

Table 3-2. Component Failure Rates per Siemens Norm SN 29500-2

| Table | Category | Reference FIT Rate | Reference Virtual T _J |
|-------|---|--------------------|----------------------------------|
| 5 | CMOS/BICMOS ASICs Analog & Mixed =<50V supply | 25 | 55°C |

The Reference FIT Rate and Reference Virtual T_J (junction temperature) in Table 3-2 come from the Siemens Norm SN 29500-2 tables 1 through 5. Failure rates under operating conditions are calculated from the reference failure rate and virtual junction temperature using conversion information in SN 29500-2 section 4.



4 Pin Failure Mode Analysis (Pin FMA)

This section provides a Failure Mode Analysis (FMA) for the pins of the LMR516xx. The failure modes covered in this document include the typical pin-by-pin failure scenarios:

- Pin short-circuited to Ground (see Table 4-2)
- Pin open-circuited (see Table 4-3)
- Pin short-circuited to an adjacent pin (see Table 4-4)
- Pin short-circuited to VIN (see Table 4-5)

Table 4-2 through Table 4-5 also indicate how these pin conditions can affect the device as per the failure effects classification in Table 4-1.

| Table 1-1 | TI | Classification | of Failuro | Effocts |
|------------|----|----------------|------------|---------|
| Table 4-1. | | Ciassilication | OI FAIIUIE | |

| Class | Failure Effects |
|-------|---|
| А | Potential device damage that affects functionality |
| В | No device damage, but loss of functionality |
| С | No device damage, but performance degradation |
| D | No device damage, no impact to functionality or performance |

Following are the assumptions of use and the device configuration assumed for the pin FMA in this section:

- Device used within the 'Recommended Operating Conditions' and the 'Absolute Maximum Ratings' found in the appropriate device data sheet.
- Configuration as shown in the 'Example Application Circuit' found in the appropriate device data sheet.

Figure 4-1 shows the LMR50410-Q1 pin diagram for the SOT-23-6 package. For a detailed description of the device pins please refer to the 'Pin Configuration and Functions' section in the appropriate device data sheet.




Figure 4-1. Pin Diagram



Table 4-2. Pin FMA for Device Pins Short-Circuited to Ground

| Pin Name | Pin No. | Description of Potential Failure Effect(s) | Failure Effect Class |
|----------|---------|---|----------------------------|
| СВ | 1 | No output voltage | В |
| GND | 2 | Normal Operation | D |
| FB | 3 | The regulator will operate at maximum duty cycle. Output voltage will rise to nearly the input voltage (VIN) level. Possible damage to customer load and/or output stage components may occur. No effect on device. | В |
| EN | 4 | Loss of ENABLE functionality Device will remain in shut-down mode. | В |
| VIN | 5 | Device will not operate. No output voltage will be generated. Output capacitors will discharge through input short. Large reverse current may damage device. | А |
| SW | 6 | Damage to internal FET. | Α |

Table 4-3. Pin FMA for Device Pins Open-Circuited

| Table 4 of 1 mil mil to bottee 1 me open encanea | | | | |
|--|---------|---|----------------------------|--|
| Pin Name | Pin No. | Description of Potential Failure Effect(s) | Failure Effect Class | |
| СВ | 1 | No output voltage | В | |
| GND | 2 | VOUT might be abnormal due to switching noise on analog circuits | В | |
| FB | 3 | VOUT will be higher than programmed output voltage. | В | |
| EN | 4 | Loss of ENABLE functionality. Erratic operation; probable loss of regulation. | В | |
| VIN | 5 | No output voltage | В | |
| SW | 6 | No output voltage | В | |



Table 4-4. Pin FMA for Device Pins Short-Circuited to Adjacent Pin

| Pin Name | Pin No. | Shorted to | Description of Potential Failure Effect(s) | Failure Effect Class |
|----------|---------|------------|---|----------------------------|
| СВ | 1 | GND | No output voltage | А |
| GND | 2 | FB | The regulator will operate at maximum duty cycle. Output voltage will rise to nearly the input voltage (VIN) level. Possible damage to customer load and/or output stage components may occur. No effect on device. | В |
| FB | 3 | GND | The regulator will operate at maximum duty cycle. Output voltage will rise to nearly the input voltage (VIN) level. Possible damage to customer load and/or output stage components may occur. No effect on device. | В |
| EN | 4 | VIN | No damage to device. Loss of ENABLE functionality. | В |
| VIN | 5 | SW | Damage to internal FET. | Α |
| SW | 6 | VIN | Damage to internal FET. | Α |

Table 4-5. Pin FMA for Device Pins Short-Circuited to VIN

| Pin Name | Pin No. | Description of Potential Failure Effect(s) | Failure Effect Class |
|----------|---------|---|----------------------------|
| СВ | 1 | No output voltage. CBOOT ESD clamp will run current to destruction. | А |
| GND | 2 | No output voltage. Damage to other pins referred to GND. | А |
| FB | 3 | If VIN exceeds 5.5V damage will occur. No output voltage. | А |
| EN | 4 | No damage to device. Loss of ENABLE functionality. | В |
| VIN | 5 | No effect | D |
| SW | 6 | Damage to Low Side MOSFET. | А |

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated