

Migrating Designs to LP3470A Low Iq Voltage Supervisor for Improved Power Supply Monitoring

Michael DeSando



LP3470A is a low-power consumption voltage supervisor that features programmable reset delay via an external capacitor and an open-drain output. The device monitors undervoltage faults at 2.63 V, 2.75 V, 2.93 V, 3.08 V, 3.65 V, 4.0 V, 4.38 V, and 4.63 V and is available in 5-pin SOT23 package.

How Does LP3470A Compare to the Older LP3470?

The new LP3470A is available in the standard SOT23 5-pin package with the same pinout and threshold voltages but has lower supply current, a wider temperature range, and a wider input voltage range compared to the LP3470. The LP3470A is an easy migration path for users seeking a pin-to-pin replacement with LP3470 but with better specifications as shown in [Table 1](#).

The rest of the specifications between LP3470A and LP3470 are nearly identical. Please note that although both of these devices feature programmable delay via an external capacitor meaning the layout is the same, the capacitor value to reset delay relationship is different so be sure to refer to the reset delay equation

in the [LP3470A datasheet](#) to determine the appropriate capacitor value. For example, using a 100 nF capacitor on LP3470 SRT pin provides a reset delay time of 200 ms whereas a 100 nF capacitor on the LP3470A SRT pin provides 61 ms.

What Applications Does LP3470A Benefit?

The three main performance benefits offered by LP3470A are low power, wide input voltage range, and wide temperature range. This device is perfect for monitoring batteries or for applications powered by batteries such as remote controls and wireless electronics due to the low supply current of only 300 nA. Because of the wide input voltage range, LP3470A can also monitor multiple batteries in series such as three 3.3 V batteries for a total of 9.9 V due to the recommended operating maximum input voltage of 10 V. Lastly, the wide temperature range allows LP3470A to be used in more industrial applications that require -40°C to 125°C.

Table 1. Performance Comparison Between LP3470A and LP3470

	LP3470A	LP3470
Input Voltage Range	0.95 V to 10 V	0.5 V to 5.5 V
Supply Current (Typical)	0.3 μ A	16 μ A
Operating Temperature Range	-40°C to 125°C	-20°C to 85°C

1 References

[LP3470A Datasheet](#)

1.1 Trademarks

All trademarks are the property of their respective owners.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2022, Texas Instruments Incorporated