

PMP23392 REV -1 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
I PCB1	1		PMP23392	Any	Printed Circuit Board	
C1	1	390µF	EEE-TP1K391V	Panasonic	Cap Aluminum Lytic 390uF 80V 20% (16 X 16.5mm) SMD 0.1 Ohm 1900mA 3000h 125°C Automotive T/R	SMT_CAP_17MM0_17MM0
C2, C3, C7, C8, C9	5	0.01uF	GCM188R72A103KA37J	MuRata	CAP, CERM, 0.01 µF, 100 V,+/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
C4	1	2.2uF	CGA5L3X7S2A225K160AB	TDK	CAP, CERM, 2.2 uF, 100 V, +/- 10%, X7S, AEC-Q200 Grade 1, 1206	1206
C5	1	4.7uF	C3225X7S2A475K200AB	TDK	CAP, CERM, 4.7 uF, 100 V, +/- 10%, X7S, 1210	1210
C6	1	4.7uF	CGA6M3X7S2A475K200AB	TDK	CAP, CERM, 4.7 uF, 100 V, +/- 10%, X7S, AEC-Q200 Grade 1, 1210	1210
C10, C11	2	1uF	08051C105K4Z2A	AVX	CAP, CERM, 1 µF, 100 V,+/- 10%, X7R, AEC-Q200 Grade 1, 0805	0805
C12, C13, C14, C15, C16, C54, C55, C56, C57, C58, C100, C101	12	4.7µF	GCJ32DC72A475KE01L	Murata	4.7uF ±10% 100V Ceramic Capacitor X7S 1210 (3225 Metric)	1210
C17, C18, C19, C20, C59, C60, C61, C62	8	0.1uF	GCJ188R72A104KA01D	MuRata	CAP, CERM, 0.1 uF, 100 V,+/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
C30, C72	2	0.47uF	KAF21KR72A474KU	Kyocera AVX	CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference]	0805
C31, C32, C73, C74	4	0.01uF	GRM155R71H103KA88D	MuRata	CAP, CERM, 0.01 uF, 50 V, +/- 10%, X7R, 0402	0402
C33, C48, C75, C90	4	0.1uF	C0402C104K8RACAUTO	Kemet	CAP, CERM, 0.1 µF, 10 V,+/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402
C34, C76	2	4.7uF	GRM188Z71A475ME15D	MuRata	CAP, CERM, 4.7 uF, 10 V, +/- 20%, X7R, 0603	0603
C36, C37	2	100µF	GRT32EC70J107ME13K	Murata	Multi-Layer Ceramic Capacitor 100uF 6.3V X7S ±20% 1210 Emboss T/R	1210
C38, C39, C40, C41, C43, C44, C45, C46, C80, C81, C82, C83, C85, C86, C87, C88	16	100uF	GRT32EC70J107ME13K	Murata	CAP, CERM, 100uF, 6.3V, X7S, 20%, 1210	1210
C42, C47, C84, C89	4	0.1uF	C0603C104K5RACTU	Kemet	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, 0603	0603
C49, C91	2	0.033uF	CGA2B1X7R1E333K050BC	TDK	CAP, CERM, 0.033 uF, 25 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402
C50, C92	2	0.22uF	CGA2B1X7R1V224K050BC	TDK	CAP, CERM, 0.22uF, 35V, X7R, 10%, 0402	0402
C51, C93	2	22pF	CGA2B2NP01H220J050BA	TDK	CAP, CERM, 22 pF, 50 V, +/- 5%, C0G/NP0, AEC-Q200 Grade 1, 0402	0402
C52	1	0.022uF	GCM155R71E223KA55D	MuRata	CAP, CERM, 0.022 uF, 25 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402
C53, C95	2	270pF	GRM155R72A271KA01D	MuRata	CAP, CERM, 270 pF, 100 V, +/- 10%, X7R, 0402	0402
C78, C79	2	100µF	T598D227M010ATE025	Murata	Multi-Layer Ceramic Capacitor 100uF 6.3V X7S ±20% 1210 Emboss T/R	1210
C96, C97, C98, C99	4	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
D1, D5	2	100V	BAT46WJ,115	Nexperia	Diode, Schottky, 100 V, 0.25 A, SOD-323F	SOD-323F
D2, D6	2	5.6V	TDZ5V6J,115	Nexperia	Diode, Zener, 5.6V, 2%, 500mW, SOD-323F	SOD-323F
D3, D7	2	40V	SS10P4HM3_A/H	Vishay	Diode 40 V 10A Surface Mount TO-277A (SMPC)	SMPC
H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
J1, J2, J7, J9, J10, J11	6		5102	Keystone	Shorting Jumper, 5.375mm, 2 Position, Tin, SMT	Shorting Jumper, 5.375mm, 2 Position, SMT
J3, J4	2		108-0902-001	Cinch Connectivity	Banana Jack Insul Nylon Red, TH	Banana Jack Insul Nylon Red, TH
J5, J6	2		108-0903-001	Cinch Connectivity	Banana Jack Insul Nylon Black, TH	Banana Jack Insul Nylon Black, TH
J8, J12	2		TSW-102-07-G-S	Samtec	Header, 100mil, 2x1, Gold, TH	2x1 Header
L4, L6	2	1.5uH	XAL1010-152MEB	Coilcraft	Inductor, Shielded, Composite, 1.5 uH, 36.6 A, 0.0016 ohm, SMD	Inductor, 11.3x10x10mm
LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650 x 0.200 inch
R1, R2	2	1	CRCW25121R00JNEG	Vishay-Dale	RES, 1.0, 5%, 1 W, AEC-Q200 Grade 0, 2512	2512
R3, R4, R7, R20, R21, R27, R28, R31, R32, R43, R47, R49, R62, R63	14	0	CRCW04020000Z0EDHP	Vishay-Dale	RES, 0, 0%, 0.2 W, AEC-Q200 Grade 0, 0402	0402
R6	1	150k	CRCW0603150KFKEA	Vishay-Dale	RES, 150 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R8, R33	2	1.2m	Y14830R00120F9R	Vishay Foil Resistors	1.2 mOhms \pm 1% 5W Chip Resistor 2512 (6432 Metric) Automotive AEC-Q200, Current Sense, Non-Inductive Metal Element	2512
R9	1	6.81k	CRCW04026K81FKED	Vishay-Dale	RES, 6.81 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R12, R37	2	49.9	CRCW040249R9FKED	Vishay-Dale	RES, 49.9, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R13, R38	2		RMCF0402ZT0R00	Stackpole	RMCF/RMCP Series General Purpose Thick Film Standard Power and High Power Chip Resistor	0402 (1005 metric)
R17	1	49.9	CRCW060349R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R18, R44	2	73.2k	CRCW040273K2FKED	Vishay-Dale	RES, 73.2 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R23, R35	2	100k	RMCF0402FT100K	Stackpole Electronics Inc	RES, 100 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R24	1	3.01k	CRCW04023K01FKED	Vishay-Dale	RES, 3.01 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R25	1	54.9k	CRCW040254K9FKED	Vishay-Dale	RES, 54.9 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R26	1	19.1k	CRCW040219K1FKED	Vishay-Dale	RES, 19.1 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R52	1	90.9k	CRCW040290K9FKED	Vishay-Dale	RES, 90.9 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R53	1	0	RMCF0402ZT0R00	Stackpole	RMCF/RMCP Series General Purpose Thick Film Standard Power and High Power Chip Resistor	0402 (1005 metric)
R54, R55, R56, R57	4	3.32	CRCW04023R32FKED	Vishay-Dale	RES, 3.32, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
SH-J1, SH-J2	2		60900213421	Würth Elektronik	Shunt, 2.54mm, Gold, Black	Shunt, 2.54mm, Black
T1, T2, T3	3		CB70-14-CY	Panduit	Terminal 90A Lug	CB70-14-CY
TP1	1	+Vin_Main	5016	Keystone Electronics	Test Point, Compact, SMT	Testpoint_Keystone_Compact
TP2	1	GND_In	5016	Keystone Electronics	Test Point, Compact, SMT	Testpoint_Keystone_Compact
TP3, TP9	2		5010	Keystone	Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint
TP4, TP5, TP6, TP10, TP11, TP12	6		5012	Keystone	Test Point, Multipurpose, White, TH	White Multipurpose Testpoint
TP7, TP8	2		5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint
U1, U3, U4, U6	4		LMG3100R017	Texas Instruments	100-V, 64-A GaN with Integrated Driver	VQFN-FCRLF15
U2, U5	2		LM5148PSQRGYRQ1	Texas Instruments	80-V, Automotive, Synchronous, Buck DC/DC Controller with Ultra-Low IQ and Dual Random Spread Spectrum	VQFN20

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C21, C22, C23, C24, C29, C63, C64, C65, C66, C67, C102, C103	0	4.7µF	GCJ32DC72A475KE01L	Murata	4.7uF ±10% 100V Ceramic Capacitor X7S 1210 (3225 Metric)	1210
C25, C26, C27, C28, C68, C69, C70, C71	0	0.1uF	GCJ188R72A104KA01D	MuRata	CAP, CERM, 0.1 uF, 100 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
C35, C77	0	330pF	GCM1885C2A331JA16D	Murata	CAP, CERM, 330F, 100V, C0G, 5%, 0603	0603
C94	0	5600pF	GRM155R71E562KA01D	MuRata	CAP, CERM, 5600 pF, 25 V, +/- 10%, X7R, 0402	0402
D4, D8	0	100V	PMEG10020AELRX	Nexperia	Diode, Schottky, 100V, 2A, SOD-123	SOD-123W
D9, D10, D11, D12	0	30V	NSVRB521S30T1G	ON Semi	Diode, Schottky, 30V, 200mA, SOD-523	SOD-523
FID1, FID2, FID3, FID4, FID5, FID6	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	N/A
L1	0	1uH	XGL6060-102MEC	Coilcraft	1 µH Shielded Molded Inductor 22 A 2.9mOhm Max Nonstandard	SMT2_6MM51_6MM71
L2	0		ACM12V-701-2PL-TL00	TDK	Coupled inductor, ohm, AEC-Q200 Grade 1, SMD	12x11mm
L3	0	2uH	PLT10HH101150PNL	MuRata	Coupled inductor, 2 uH, A, 1.8 ohm, SMD	12.9x6.6mm
L5, L7	0	2.5uH	VCUD128T-2R5MS8	CYNTec	Power Choke Coil 2.5uH 20% 100kHz 2.53mOhm 32A AECQ200 13.3x12.8x8.0mm SMT	SMT_IND_13MM3_12MM8
R5, R30, R66, R67	0	500µ	PML100HZPJV0L5	Rohm Semiconductor	Res Current Sense Thick Film 1225 0.5m Ohm 5% 2W ±150ppm/°C Molded Emboss T/R	1225
R10, R19, R46, R50	0	100k	RMCF0402FT100K	Stackpole Electronics Inc	RES, 100 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R11, R16, R36, R41	0		Used in BOM report	Used in BOM report	RES, xxx ohm, x%, xW, [PackageReference]	Used in PnP output and some BOM reports
R14, R39	0	1	RMCF1210JT4R70	Stackpole	RES, 1.0 ohm, 5%, 0.5W, 1210	1210
R15, R40, R45, R58, R59, R60, R61	0	0	CRCW04020000Z0EDHP	Vishay-Dale	RES, 0, 0%, 0.2 W, AEC-Q200 Grade 0, 0402	0402
R22	0	48.7k	CRCW040248K7FKED	Vishay-Dale	RES, 48.7 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R29	0	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R34	0	4.75k	CRCW04024K75FKED	Vishay-Dale	RES, 4.75 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R42	0	49.9	CRCW060349R9FKEA	Vishay-Dale	RES, 49.9, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R48	0	7.50k	CRCW04027K50FKED	Vishay-Dale	RES, 7.50 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R51	0	0	RMCF0402ZT0R00	Stackpole	RMCF/RMCP Series General Purpose Thick Film Standard Power and High Power Chip Resistor	0402 (1005 metric)
R64, R65	0	1.2m	Y14830R00120F9R	Vishay Foil Resistors	1.2 mOhms ±1% 5W Chip Resistor 2512 (6432 Metric) Automotive AEC-Q200, Current Sense, Non-Inductive Metal Element	2512

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2024, Texas Instruments Incorporated