

ISE4039 REV E4 Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	IPCB	1		ISE4039	Any	Printed Circuit Board	
2	BT1	1		BS-7	Memory Protection Devices	Battery Holder, CR2032, Retainer clip, TH	CR2032 holder
3	C1, C2, C18	3	4.7uF	C1005X5R1A475K050BC	TDK	CAP, CERM, 4.7 uF, 10 V, +/- 10%, X5R, 0402	0402
4	C3, C4	2	0.1uF	GRM155R70J104KA01D	MuRata	CAP, CERM, 0.1 uF, 6.3 V, +/- 10%, X7R, 0402	0402
5	C5	1	0.01uF	C0402C103J5RACTUJ	Kemet	CAP, CERM, 0.01 uF, 50 V, +/- 5%, X7R, 0402	0402
6	C6, C7, C8, C9, C10, C11, C12, C13, C14, C15, C16, C17, C48	13	100uF	C3216X5R1A107M160AC	TDK	CAP, CERM, 100 uF, 10 V, +/- 20%, X5R, 1206_190	1206_190
7	C19	1	1uF	GRM155R61A105KE15D	MuRata	CAP, CERM, 1 uF, 10 V, +/- 10%, X5R, 0402	0402
8	C20, C22, C23, C24, C26, C28, C29, C43	8	0.1uF	GRM155R71C104KA88D	MuRata	CAP, CERM, 0.1 uF, 16 V, +/- 10%, X7R, 0402	0402
9	C25, C27	2	22uF	C1608X5R0J226M080AC	TDK	CAP, CERM, 22 uF, 6.3 V, +/- 20%, X5R, 0603	0603
10	C31, C32	2	2200pF	C1005X7R1H222K	TDK	CAP, CERM, 2200 pF, 50 V, +/- 10%, X7R, 0402	0402
11	C33, C36	2	3.6pF	GRM1555C1H3R6CA01D	MuRata	CAP, CERM, 3.6 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
12	C34	1	0.6pF	GJM1555C1HR60BB01D	MuRata	CAP, CERM, 0.6 pF, 50V, NP0/C0G, +/-0.1pF, 0402	0402
13	C37	1	2.7pF	GRM1555C1H2R7CA01D	MuRata	CAP, CERM, 2.7 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
14	C38	1	6.2pF	GRM1555C1H6R2CA01D	MuRata	CAP, CERM, 6.2 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
15	C39	1	3.3pF	GRM1555C1H3R3CA01D	MuRata	CAP, CERM, 3.3 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
16	C40, C42	2	100pF	GRM1555C1H101JA01D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
17	C41	1	1uF	C1005X5R1C105K050BC	TDK	CAP, CERM, 1 uF, 16 V, +/- 10%, X5R, 0402	0402
18	C46, C47	2	12pF	GRM1555C1E120JA01D	MuRata	CAP, CERM, 12 pF, 25 V, +/- 5%, C0G/NP0, 0402	0402
19	D1, D2	2	5V	1S3151TPH3F	Toshiba	Diode, Schottky, 5V, 0.03A, SOD-323	SOD-323
20	E1	1		ANTENNA, HELICAL	N/A	PCB Antenna. There is nothing to buy or mount.	Antenna
21	H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
22	H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
23	J1	1		PEC02SAAN	Sullins Connector Solutions	Header, 100mil, 2x1, Tin, TH	Header, 2 PIN, 100mil, Tin
24	J4	1		PEC04SAAN	Sullins Connector Solutions	Header, 100mil, 4x1, Tin, TH	Header, 4x1, 100mil, TH
25	J7	1		GRPBO52VWVN-RC	Sullins Connector Solutions	Header, 50mil, 5x2, Gold, TH	Header, 5x2, 50mil
26	L1	1	22uH	LPS4018-223MLB	Coilcraft	Inductor, Shielded Drum Core, Ferrite, 22 uH, 0.83 A, 0.36 ohm, SMD	LPS4018
27	L2	1	1500 ohm	BLM18HE152SN1D	MuRata	Ferrite Bead, 1500 ohm @ 100 MHz, 0.5 A, 0603_950	0603_950
28	L3	1	6.8uH	MLZ2012N6R8L T000	TDK	Inductor, Multilayer, Ferrite, 6.8 uH, 0.11 A, 0.25 ohm, SMD	0805
29	L4, L8	2	7.5nH	LQW15AN7N5G00D	MuRata	Inductor, Wirewound, 7.5 nH, 0.57 A, 0.13 ohm, SMD	1x.5x.5mm
30	L5	1	18nH	LQW15AN18NJ00D	MuRata	Inductor, Wirewound, 18 nH, 0.37 A, 0.27 ohm, SMD	1x.5x.5mm
31	L6, L7	2	6.8nH	LQW15AN6N8G00D	MuRata	Inductor, Wirewound, 6.8 nH, 0.7 A, 0.09 ohm, SMD	1x.5x.5mm
32	L9	1	11nH	LQW15AN11NG00D	MuRata	Inductor, Wirewound, 11 nH, 0.5 A, 0.14 ohm, SMD	1x.5x.5mm
33	Q1, Q2	2	-20V	CSD75208W1015	Texas Instruments	MOSFET, P-CH, -20 V, -1.6 A	
34	R1	1	4.12Meg	CRCW04024M12FKED	Vishay-Dale	RES, 4.12 M, 1%, 0.063 W, 0402	0402
35	R2	1	5.76Meg	CRCW04025M76FKED	Vishay-Dale	RES, 5.76 M, 1%, 0.063 W, 0402	0402
36	R4, R5, R18	3	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
37	R6, R10	2	6.19Meg	CRCW04026M19FKED	Vishay-Dale	RES, 6.19 M, 1%, 0.063 W, 0402	0402
38	R7	1	3.09Meg	CRCW04023M09FKED	Vishay-Dale	RES, 3.09 M, 1%, 0.063 W, 0402	0402
39	R8	1	6.65Meg	CRCW04026M65FKED	Vishay-Dale	RES, 6.65 M, 1%, 0.063 W, 0402	0402
40	R9	1	3.57Meg	CRCW04023M57FKED	Vishay-Dale	RES, 3.57 M, 1%, 0.063 W, 0402	0402
41	R12, R13	2	47.5k	CRCW040247K5FKED	Vishay-Dale	RES, 47.5 k, 1%, 0.063 W, 0402	0402
42	R14, R15	2	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
43	R16, R17	2	4.75k	CRCW04024K75FKED	Vishay-Dale	RES, 4.75 k, 1%, 0.063 W, 0402	0402
44	S1, S2	2		B3U-1000P	Omron Electronic Components	SWITCH TACTILE SPST-NO 0.05A 12V	3x1.6x2.5mm
45	SH-J1, SH-J2, SH-J3, SH-J4, SH-J5	5	1x2	2SN-BK-G	Samtec	Shunt, 2mm, Gold plated, Black	2mm Shunt, Closed Top
46	TP1, TP2, TP3, TP5, TP6, TP7, TP8, TP9	8	Red	5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
47	TP4	1	Black	5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
48	U1, U2	2	0.5V	KXOB22-12X1L	IXYS	Monocrystalline Solar Cell, 22 X 7mm, SMD	22x7mm
49	U3	1		BQ25505RGR	Texas Instruments	Ultra Low Power Boost Converter with Battery Management for Energy Harvester Applications. RGR0020A	RGR0020A
50	U4	1		OPT3001DNP	Texas Instruments	Ambient Light Sensor, DNP0006A	DNP0006A
51	U5, U6, U8, U9	4		TPD1E10B06DPYR	Texas Instruments	ESD in 0402 Package with 10 pF Capacitance and 6 V Breakdown, 1 Channel, -40 to +125 degC, 2-pin X2SON (DPY), Green (RoHS & no Sb/Br)	DPY0002A
52	U7	1		CC1310F128RGZR	Texas Instruments	Sub-1 GHz and 2.4 GHz Multi-standard RF IC Family, RG20048A	RG20048A
53	U10	1		HDC1000YPAR	Texas Instruments	HDC1000 Low power integrated humidity and temperature Sensor, YPA0008AGAE	YPA0008AGAE
54	Y1	1		TSX3225 24.0000MF20G-AC3	Epson	Crystal, 24 MHz, 9 pF, SMD	SMD, 4-Leads, Body 2.65x3.35mm, Height 0.6mm
55	Y2	1		FC-12M 32.7680KA-A3	Epson	Crystal, 32.768kHz, 12.5pF, SMD	Crystal 2.05x.6x1.2mm
56	C21	0		Used in BOM report	Used in BOM report	CAP, CERM, xxxF, xxV, [TempCo], xx%, [PackageReference]	Used in PnP output and some BOM reports
57	C30	0	0.1uF	GRM155R71C104KA88D	MuRata	CAP, CERM, 0.1 uF, 16 V, +/- 10%, X7R, 0402	0402
58	C44, C45	0	12pF	GRM1555C1E120JA01D	MuRata	CAP, CERM, 12 pF, 25 V, +/- 5%, C0G/NP0, 0402	0402
59	FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
60	J5	0		TSW-106-07-G-S	Samtec	Header, 100mil, 6x1, Gold, TH	6x1 Header
61	J6	0		CONSMAD01-SMD-G	Linx Technologies	Jack, SMA, PCB, Gold, SMT	SMA Jack
62	R3, R11, R19	0	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

TI's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

TI's standard terms of sale for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2016, Texas Instruments Incorporated