

TIDA-00757 REV B Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
I PCB1	1		TIDA-00757	Any	Printed Circuit Board	
BT1, BT2	2		2462	Keystone	2x AA Battery Holder, Through-hole mount	TH, 2x AA Battery Holder
C1, C2, C9	3	10uF	EMK212BB7106MG-T	Taiyo Yuden	CAP, CERM, 10 µF, 16 V, +/- 20%, X7R, 0805	0805
C3	1	100uF	C3216X5R1A107M160AC	TDK	CAP, CERM, 100 µF, 10 V, +/- 20%, X5R, 1206_190	1206_190
C4, C5, C10, C11, C40	5	1uF	GRM155R61A105KE15D	MuRata	CAP, CERM, 1 µF, 10 V, +/- 10%, X5R, 0402	0402
C6, C7, C12, C14	4	0.47uF	C1005X5R1A474K050BB	TDK	CAP, CERM, 0.47 µF, 10 V, +/- 10%, X5R, 0402	0402
C8	1	0.01uF	C1005X7R1C103K050BA	TDK	CAP, CERM, 0.01 µF, 16 V, +/- 10%, X7R, 0402	0402
C13	1	2.2uF	C0603C225K9PACTU	Kemet	CAP, CERM, 2.2 µF, 6.3 V, +/- 10%, X5R, 0603	0603
C16, C17, C19, C21, C22	5	0.1uF	GRM155R71A104KA01D	MuRata	CAP, CERM, 0.1 µF, 10 V, +/- 10%, X7R, 0402	0402
C18, C20	2	10uF	GRM21BR71A106KE51L	MuRata	CAP, CERM, 10 µF, 10 V, +/- 10%, X7R, 0805	0805
C24	1	0.1uF	CGA2B3X7R1E104K050BB	TDK	CAP, CERM, 0.1 µF, 25 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402
C25, C26, C27	3	2200pF	C1005X7R1H222K	TDK	CAP, CERM, 2200 pF, 50 V, +/- 10%, X7R, 0402	0402
C30	1	6.8pF	GRM1555C1H6R8CA01D	MuRata	CAP, CERM, 6.8 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
C31, C32, C35	3	12pF	GRM1555C1H120JA01D	MuRata	CAP, CERM, 12 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
C34, C38, C41	3	1pF	GJM1555C1H1R0BB01D	MuRata	CAP, CERM, 1 pF, 50 V, +/- 10%, C0G/NP0, 0402	0402
C36	1	1.8pF	GRM1555C1H1R8CA01D	MuRata	CAP, CERM, 1.8 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
C37	1	1.2pF	GRM1555C1H1R2CA01D	MuRata	CAP, CERM, 1.2 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
D1, D2, D3, D4, D5, D6	6	Rgb	ASMT-YTC2-0AA02	Avago	LED, Rgb, SMD	LED, 3x2x3.6 mm
E1	1		ANTENNA_IIFA	N/A	PCB Antenna. There is nothing to buy or mount.	PCB Antenna, 2-Leads
H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
H5, H6, H7, H8	4		1902E	Keystone	Standoff, Hex, 1"L #4-40 Nylon	Standoff
J1, J2	2		61300211121	Würth Elektronik eiSos	Header, 2.54 mm, 2x1, Gold, TH	Header, 2.54mm, 2x1, TH
J3	1		OSTTE020161	On-Shore Technology	Terminal Block, 2x1, 3.5mm, TH	2x1 Terminal Block
L1	1	4.7uH	CBC3225T4R7MR	Taiyo Yuden	Inductor, Wirewound, 4.7 µH, 1.01 A, 0.1 ohm, SMD	3.2x2.5x2.5mm
L2	1	10uH	CKS2125100M-T	Taiyo Yuden	Inductor, Multilayer, Ferrite, 10 µH, 0.11 A, 0.52 ohm, SMD	0805
L3	1	1500 ohm	BLM18HE152SN1D	MuRata	Ferrite Bead, 1500 ohm @ 100 MHz, 0.5 A, 0603	0603
L4, L7	2	2.4nH	LQG15HN2N4S02D	MuRata	Inductor, Multilayer, Air Core, 2.4 nH, 0.3 A, 0.16 ohm, SMD	0402 polarized
L5, L6	2	2nH	LQG15HS2N0S02D	MuRata	Inductor, Multilayer, Air Core, 2 nH, 0.3 A, 0.1 ohm, SMD	0402 polarized
LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x 0.200"W
Q1	1	-20V	CSD25310Q2	Texas Instruments	MOSFET, P-CH, -20 V, -20 A, SON 2x2mm	SON 2x2mm
R1	1	38.3k	RC0603FR-0738K3L	Yageo America	RES, 38.3 k, 1%, 0.1 W, 0603	0603
R2	1	30.0k	ERJ-3EKF3002V	Panasonic	RES, 30.0 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R3	1	0.1	CSR1206FKR100	Stackpole Electronics Inc	RES, 0.1, 1%, 0.5 W, 1206	1206
R4	1	1.00k	ERJ-3EKF1001V	Panasonic	RES, 1.00 k, 1%, 0.1 W, 0603	0603
R5	1	100k	RMCF0402FT100K	Stackpole Electronics Inc	RES, 100 k, 1%, 0.063 W, AEC-Q200 Grade 0, 0402	0402
R6, R7, R8	3	47.5k	CRCW040247K5FKED	Vishay-Dale	RES, 47.5 k, 1%, 0.063 W, 0402	0402
R9, R10	2	4.7k	ERJ-3GEYJ472V	Panasonic	RES, 4.7 k, 5%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R12, R13	2	10.0k	ERJ-3EKF1002V	Panasonic	RES, 10.0 k, 1%, 0.1 W, 0603	0603
S1, S2, S3, S4	4		4-1437565-1	TE Connectivity	Switch, Tactile, SPST-NO, 0.05A, 12V, SMT	SW, SPST 6x6 mm
SH-J1, SH-J2	2	1x2	969102-0000-DA	3M	Shunt, 100mil, Gold plated, Black	Shunt
TP1, TP2	2	Red	5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
TP3, TP4, TP10	3	Black	5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
TP5, TP6	2	Yellow	5004	Keystone	Test Point, Miniature, Yellow, TH	Yellow Miniature Testpoint
TP8, TP9	2	White	5002	Keystone	Test Point, Miniature, White, TH	White Miniature Testpoint
U1	1		TPS62745DSSR	Texas Instruments	Dual-cell Ultra Low IQ Step Down Converter for Low Power Wireless Applications, DSS0012A	DSS0012A
U2, U4	2		LP55231SQX/NOPB	Texas Instruments	LP55231 Programmable 9-Output LED Driver, RTW0024A	RTW0024A
U3	1		DRV8833PWPR	Texas Instruments	Dual H-Bridge Motor Driver, PWP0016C	PWP0016C
U5, U6, U7	3		TPD1E10B06DPYR	Texas Instruments	ESD in 0402 Package with 10 pF Capacitance and 6 V Breakdown, 1 Channel, -40 to +125 degC, 2-pin X2SON (DPY), Green (RoHS & no Sb/Br)	DPY0002A
U8	1		CC2640R2FTWRGZTQ1	Texas Instruments	Automotive Qualified SimpleLink Bluetooth low energy Wireless MCU, RGZ0048N (VQFN-48)	RGZ0048N
Y1	1		TSX-3225 24.0000MF20G-AC3	Epson	Crystal, 24 MHz, 9 pF, SMD	SMD, 4-Leads, Body 2.65x3.35mm, Height 0.6mm
Y2	1		FC-12M 32.7680KA-A3	Epson	Crystal, 32.768kHz, 12.5pF, SMD	Crystal 2.05x.6x1.2mm
C15	0	10uF	C1608X5R1A106M080AC	TDK	CAP, CERM, 10 µF, 10 V, +/- 20%, X5R, 0603	0603
C23	0	0.1uF	885012205037	Würth Elektronik	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0402	0402
C28, C29	0	12pF	GRM1555C1H120JA01D	MuRata	CAP, CERM, 12 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
C33	0	1.8pF	GRM1555C1H1R8CA01D	MuRata	CAP, CERM, 1.8 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
C39	0	1.2pF	GRM1555C1H1R2CA01D	MuRata	CAP, CERM, 1.2 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial
J4	0		GRPB052VWVN-RC	Sullins Connector Solutions	Header, 50mil, 5x2, Gold, TH	Header, 5x2, 50mil
J5	0		SMA-10V21-TGG	Hus-Tsan Group Co., Ltd.	Connector, SMA, Vertical, Gold, SMT	SMD, 4-Leads, Body 7.1x7.1mm
R11	0	2.20k	RC0603FR-072K2L	Yageo America	RES, 2.20 k, 1%, 0.1 W, 0603	0603
R14	0	0	ERJ-2GE0R00X	Panasonic	RES, 0, 5%, 0.063 W, 0402	0402

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2018, Texas Instruments Incorporated