

Filename: Pro76C2.tmp
 Variant: 002
 Generated: 6/20/2017 1:59:12 PM
 TID #: N/A



PMP20807 REV A Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	IPCB1	1		PMP20807	Any	Printed Circuit Board	
2	C1, C6, C7	3	0.1uF	GRM155R71C104KA88D	MuRata	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0402	0402
3	C2	1	10uF	GRM219R61A106KE44D	MuRata	CAP, CERM, 10 µF, 10 V, +/- 10%, X5R, 0805	0805
4	C3, C10	2	1uF	GRM155R6YA105KE11D	MuRata	CAP, CERM, 1 µF, 35 V, +/- 10%, X5R, 0402	0402
5	C4	1	0.01uF	GRM155R71H103KA88D	MuRata	CAP, CERM, 0.01 µF, 50 V, +/- 10%, X7R, 0402	0402
6	C5	1	0.27uF	GRM155R60J274KE01D	MuRata	CAP, CERM, 0.27 µF, 6.3 V, +/- 10%, X5R, 0402	0402
7	C8, C9	2	470pF	GRM155R71H471KA01D	MuRata	CAP, CERM, 470 pF, 50 V, +/- 10%, X7R, 0402	0402
8	C11	1	0.47uF	GRM155R61E474KE01D	MuRata	CAP, CERM, 0.47 µF, 25 V, +/- 10%, X5R, 0402	0402
9	C12, C13, C15, C16	4	10uF	GRM32ER71H106KA12L	MuRata	CAP, CERM, 10 µF, 50 V, +/- 10%, X7R, 1210	1210
10	C14, C17	2	0.047uF	GRM188R71H473KA61D	MuRata	CAP, CERM, 0.047 µF, 50 V, +/- 10%, X7R, 0603	0603
11	C18, C19, C20, C21, C22	5	47uF	GRM32ER71A476KE15L	MuRata	CAP, CERM, 47 µF, 10 V, +/- 10%, X7R, 1210	1210
12	C24	1	0.1uF	0402YC104KAT2A	AVX	CAP, CERM, 0.1 µF, 16 V, +/- 10%, X7R, 0402	0402
13	C26	1	4.7uF	GCM21BR71C475KA73L	MuRata	CAP, CERM, 4.7 µF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0805	0805
14	D1	1	40V	B340A-13-F	Diodes Inc.	Diode, Schottky, 40 V, 3 A, SMA	SMA
15	GND	2		5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint
16	J1	1		632 723 300 011	Würth Elektronik	Connector, Receptacle, USB Type C, R/A	Connector, Receptacle, USB Type C, R/A, THT/SMT
17	L1	1	10uH	74439358100	Würth Elektronik	Inductor, Shielded, Composite, 10 µH, 5.8 A, 0.022 ohm, SMD	8.8x8.3mm
18	Q1, Q2	2	30V	CSD17575Q3	Texas Instruments	MOSFET, N-CH, 30 V, 60 A, DQG0008A	DQG0008A
19	R1	1	0.005	WSL12065L000FEA18	Vishay-Dale	RES, 0.005, 1%, 0.5 W, 1206	1206
20	R2, R11, R17	3	100k	CRCW0402100KFKED	Vishay-Dale	RES, 100 k, 1%, 0.063 W, 0402	0402
21	R3, R4, R5	3	10	CRCW040210R0JNED	Vishay-Dale	RES, 10, 5%, 0.063 W, 0402	0402
22	R6	1	100	CRCW0402100RJNED	Vishay-Dale	RES, 100, 5%, 0.063 W, 0402	0402
23	R7	1	1.00k	CRCW04021K00FKED	Vishay-Dale	RES, 1.00 k, 1%, 0.063 W, 0402	0402
24	R8	1	120	RG2012P-121-B-T5	Susumu Co Ltd	RES, 120, 0.1%, 0.125 W, 0805	0805
25	R9	1	2.43k	CRCW04022K43FKED	Vishay-Dale	RES, 2.43 k, 1%, 0.063 W, 0402	0402
26	R10	1	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
27	R12	1	3.0	CRCW04023R00JNED	Vishay-Dale	RES, 3.0, 5%, 0.063 W, 0402	0402
28	R13	1	49.9	CRCW040249R9FKED	Vishay-Dale	RES, 49.9, 1%, 0.063 W, 0402	0402
29	R15	1	49.9k	CRCW040249K9FKED	Vishay-Dale	RES, 49.9 k, 1%, 0.063 W, 0402	0402
30	R16	1	12.1k	CRCW040212K1FKED	Vishay-Dale	RES, 12.1 k, 1%, 0.063 W, 0402	0402
31	R18	1	0	RC0402JR-070RL	Yageo America	RES, 0, 5%, 0.063 W, 0402	0402
32	R19	1	100k	CRCW1206100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.25 W, 1206	1206
33	R20	1	221k	CRCW0402221KFKED	Vishay-Dale	RES, 221 k, 1%, 0.063 W, 0402	0402
34	TP1	1		5013	Keystone	Test Point, Multipurpose, Orange, TH	Orange Multipurpose Testpoint
35	U1	1		TPS25740ARGER	Texas Instruments	USB Power Delivery (PD) Provider-Only and Type-C Downward Facing Port (DFP) Port Controller, RGE0024F	RGE0024F
36	U2	1		LMS3635ARNLRQ1	Texas Instruments	3.5/5.5A Synchronous Buck Regulator for Automotive Applications, RNL0022A (VQFN-HR-22)	RNL0022A
37	VBUS, VIN, VOUT	3		5010	Keystone	Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint
38	C23	0	47uF	GRM32ER71A476KE15L	MuRata	CAP, CERM, 47 µF, 10 V, +/- 10%, X7R, 1210	1210
39	C25	0	20pF	GRM1555C1H200JA01D	MuRata	CAP, CERM, 20 pF, 50 V, +/- 5%, C0G/NP0, 0402	0402
40	R14	0	0	RC0402JR-070RL	Yageo America	RES, 0, 5%, 0.063 W, 0402	0402

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated