

TIDA-01471 REV E2 Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	PCB1	1		TIDA-01471	Any	Printed Circuit Board	
2	C1, C3, C7, C16, C21, C26, C29, C39	8	0.1uF	06033C104JAT2A	AVX	CAP, CERM, 0.1 uF, 25 V, +/- 5%, X7R, 0603	0603
3	C2, C4, C8, C17, C27, C30	6	10uF	GRM188R61E106MA73D	MuRata	CAP, CERM, 10 uF, 25 V, +/- 20%, X5R, 0603	0603
4	C5, C9, C10, C20, C22, C28	6	1uF	GRM188R71E105KA12D	MuRata	CAP, CERM, 1 uF, 25 V, +/- 10%, X7R, 0603	0603
5	C6, C19	2	2200pF	GRM1885C1H222JA01D	MuRata	CAP, CERM, 2200 pF, 50 V, +/- 5%, COG/NPO, 0603	0603
6	C11	1	10uF	GRM1885C2A100JA01D	MuRata	CAP, CERM, 10 uF, 100 V, +/- 5%, COG/NPO, 0603	0603
7	C12	1	0.22uF	GRM188R71E224KA88D	MuRata	CAP, CERM, 0.22 uF, 25 V, +/- 10%, X7R, 0603	0603
8	C13	1	4700pF	C0603C472JGAC7867	Kemet	CAP, CERM, 4700 pF, 100 V, +/- 5%, COG/NPO, 0603	0603
9	C14	1	1000pF	C0603C102JGAC	Kemet	CAP, CERM, 1000 pF, 50 V, +/- 5%, COG/NPO, 0603	0603
10	C15	1	0.022uF	GRM21B5C1H222JA01L	MuRata	CAP, CERM, 0.022 uF, 50 V, +/- 5%, COG/NPO, 0805	0805
11	C18	1	5pF	GRM1885C2A5R0CA01D	MuRata	CAP, CERM, 5 pF, 100 V, +/- 5%, COG/NPO, 0603	0603
12	C23, C25	2	0.01uF	GRM1885C1H103JA01D	MuRata	CAP, CERM, 0.01 uF, 50 V, +/- 5%, COG/NPO, 0603	0603
13	C24	1	22uF	GRM32ER71E226KE15L	MuRata	CAP, CERM, 22 uF, 25 V, +/- 10%, X7R, 1210	1210
14	C31, C32, C34, C36, C37, C38	6	0.1uF	GRM188R71H104KA93D	MuRata	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, 0603	0603
15	C33	1	100pF	06035A101JAT2A	AVX	CAP, CERM, 100 pF, 50 V, +/- 5%, COG/NPO, 0603	0603
16	C35	1	1uF	UMK107AB7105KA-T	Taiyo Yuden	CAP, CERM, 1 uF, 50 V, +/- 10%, X7R, 0603	0603
17	C40	1	0.022uF	C6A3E2XR2A223K080AA	TDK	CAP, CERM, 0.022 uF, 100 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
18	C41, C42, C43	3	1000pF	885012206034	Würth Elektronik	CAP, CERM, 1000 pF, 16 V, +/- 10%, X7R, 0603	0603
19	C44	1	2pF	C0603C209C5GACTU	Kemet	CAP, CERM, 2 pF, 50 V, +/- 12.5%, COG/NPO, 0603	0603
20	D1, D2	2	Red	LTST-C190CKT	Lite-On	LED, Red, SMD	Red LED, 1.6x0.8x0.8mm
21	D3	1	30V	BAT54S-E3-08	Vishay-Semiconductor	Diode, Schottky, 30 V, 0.2 A, SOT-23	SOT-23
22	H1, H2, H3, H4	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
23	H5, H6, H7, H8	4		1902C	Keystone	Standoff, Hex, 0.5" L #4-40 Nylon	Standoff
24	J1	1		TSW-120-08-L-S-RA-013	Samtec	Header, 100mil, 20x1 minus 13, Gold with Tin Tail, R/A, TH	20x1 R/A Header - Pin 13 removed
25	J2	1		TSW-110-07-G-S	Samtec	Header, 100mil, 10x1, Gold, TH	10x1 Header
26	J3, J4, J7, J8, J9, J10	6		TSW-102-07-G-S	Samtec	Header, 100mil, 2x1, Gold, TH	2x1 Header
27	J5	1		TSW-104-07-L-D	Samtec	Header, 2.54mm, 4x2, Gold, TH	Header, 2.54mm, 4x2, TH
28	J6	1		1-1478035-0	TE Connectivity	Connector, BNC, Jack, 50 ohm, R/A, TH	Connector, BNC, Jack, 50 ohm, R/A, TH
29	LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650" x 0.200" W
30	Q1	1	60 V	MMBT2907A	Fairchild Semiconductor	Transistor, PNP, 60 V, 0.8 A, SOT-23	SOT-23
31	Q2	1	460V	BSFP13PH46327XTSA1	Infinion Technologies	MOSFET, P-CH, -60 V, -2.9 A, SOT-223	SOT-223
32	R1, R2, R3, R4, R5	5	499	RT0603BRD07499RL	Yageo America	RES, 499, 0.1%, 0.1 W, 0603	0603
33	R6, R24, R45, R52, R53	5	2.00k	RC0603FR-072KL	Yageo America	RES, 2.00 k, 1%, 0.1 W, 0603	0603
34	R7, R18, R20, R21, R22, R32, R50, R51	8	1.00k	RC0603FR-071KL	Yageo America	RES, 1.00 k, 1%, 0.1 W, 0603	0603
35	R8, R13, R15	3	10.0	CRT0603-BY-10R0ELF	Bourns	RES, 10.0, 0.1%, 0.1 W, 0603	0603
36	R9, R64, R68	3	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
37	R10, R11, R16, R17	4	1.00k	RT0603BRD071KL	Yageo America	RES, 1.00 k, 0.1%, 0.1 W, 0603	0603
38	R12, R14, R40, R41	4	15.0	CRCW060315R0FKEA	Vishay-Dale	RES, 15.0, 1%, 0.1 W, 0603	0603
39	R19	1	60.4k	RT0603DRE0760K4L	Yageo America	RES, 60.4 k, 0.5%, 0.1 W, 0603	0603
40	R23, R25, R28, R29, R30, R31, R34, R35, R36, R37, R65	11	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
41	R26	1	820	RC0603JR-07820RL	Yageo America	RES, 820, 5%, 0.1 W, 0603	0603
42	R27	1	15k	CRCW060315K0JNEA	Vishay-Dale	RES, 15 k, 5%, 0.1 W, 0603	0603
43	R33, R60	2	0	CRCW0603000020EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
44	R38	1	0.047	ERJ-LD3KF47MV	Panasonic	RES, 0.047, 1%, 0.1 W, 0603	0603
45	R39	1	121k	RC0603FR-07121KL	Yageo America	RES, 121 k, 1%, 0.1 W, 0603	0603
46	R42	1	1.47k	RT0603BRD071K47L	Yageo America	RES, 1.47 k, 0.1%, 0.1 W, 0603	0603
47	R43, R44	2	10k	CRCW060310KJNEA	Vishay-Dale	RES, 10 k, 5%, 0.1 W, 0603	0603
48	R46	1	6.04k	CRCW0603604KFKEA	Vishay-Dale	RES, 6.04 k, 1%, 0.1 W, 0603	0603
49	R47	1	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
50	R48	1	14.0k	RC0603FR-0714KL	Yageo America	RES, 14.0 k, 1%, 0.1 W, 0603	0603
51	R49	1	1.10Meg	CRCW060311M0FKEA	Vishay-Dale	RES, 1.10 M, 1%, 0.1 W, 0603	0603
52	R54	1	127k	RT0603DRE07127KL	Yageo America	RES, 127 k, 0.5%, 0.1 W, 0603	0603
53	R55	1	63.4k	RT0603DRE0763K4L	Yageo America	RES, 63.4 k, 0.5%, 0.1 W, 0603	0603
54	R56	1	31.6k	RT0603DRE0731K6L	Yageo America	RES, 31.6 k, 0.5%, 0.1 W, 0603	0603
55	R57, R58	2	15.8k	RT0603DRE0715K8L	Yageo America	RES, 15.8 k, 0.5%, 0.1 W, 0603	0603
56	R59	1	150k	CRCW0603150KFKEA	Vishay-Dale	RES, 150 k, 1%, 0.1 W, 0603	0603
57	R61, R63, R66, R67	4	100k	RC0603FR-07100KL	Yageo America	RES, 100 k, 1%, 0.1 W, 0603	0603
58	R62	1	4.99Meg	CRCW06034M99FKEA	Vishay-Dale	RES, 4.99 M, 1%, 0.1 W, 0603	0603
59	SH-J3, SH-J4, SH-J5, SH-J7, SH-J8, SH-J9, SH-J10	7	1x2	969102-0000-DA	3M	Shunt, 100mil, Gold plated, Black	Shunt
60	TP1, TP2, TP3, TP4	4	Double	1573-2	Keystone	Terminal, Turret, TH, Double	Keystone1573-2
61	TP10, TP12	2	SMT	5015	Keystone	Test Point, Miniature, SMT	Testpoint_Keystone_Miniature
62	U1	1		ADS127L01PBSR	Texas Instruments	24-Bit, 512kSPS, Delta-Sigma ADC, PBS0032A (TOFP-32)	PBS0032A
63	U2	1		THS4551IRGTR	Texas Instruments	Low Noise, Precision, 150MHz, Fully Differential Amplifier, RGT0016C (VOFN-16)	RGT0016C
64	U3	1		SN74HC595PW	Texas Instruments	8-Bit Shift Registers With 3-State Output Registers, PW0016A, TUBE	PW0016A
65	U4	1		REF6025DGKR	Texas Instruments	High-Precision Voltage Reference with Integrated High-Bandwidth Buffer, DCK0006A (VSSOP-8)	DCK0006A
66	U5	1		DACS311IDCKR	Texas Instruments	8bit, Single Channel, 80uA, 1.8V-5.5V DAC in SC70 Package, DCK0006A (SOT-SC70-6)	DCK0006A
67	U6	1		TS3A5017RSVR	Texas Instruments	14-Ohm Dual SP4T Analog Switch 3.3-V/2.5-V Analog Multiplexer/Demultiplexer, RSV0016A (UQFN-16)	RSV0016A
68	U7	1		XTR111AIDGQT	Texas Instruments	Precision Voltage-to-Current Converter/Transmitter, DGQ0010D	DGQ0010D
69	U8, U10	2		LMV715M/NOPB	Texas Instruments	Low Noise, Low Offset, Single CMOS Input Op Amp, DBV0005A	DBV0005A
70	U9	1		LP2901D	Texas Instruments	Quad, Low-Power, General Purpose Differential Comparator, D0014A	D0014A
71	Y1	1		ASEMB-8.000MHZ-LY-T	Abracon Corporation	OSC, 8 MHz, 1.8 - 3.3V, SMD	4-Pin SMD, Body 3.2 x 2.5 mm, Height 0.8 mm
72	FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated