

ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SVN REV: 1460 [Modified]
LAYER NAME = Top Overlay	TID #: N/A		
PLOT NAME = Top Overlay	GENERATED : 20-07-2023 12:30:19		TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SVN REV: 1460 [Modified]
LAYER NAME = Top Solder	TID #: N/A		
PLOT NAME = Top Solder Mask	GENERATED : 20-07-2023 12:30:20		TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SVN REV: 1460 [Modified]
LAYER NAME = Top Layer	TID #: N/A		
PLOT NAME = Top Layer	GENERATED : 20-07-2023 12:30:20		TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SVN REV: 1460 [Modified]
LAYER NAME = L2_GND1	TID #: N/A		
PLOT NAME = Signal Layer 1	GENERATED : 20-07-2023 12:30:20		TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SVN REV: 1460 [Modified]
LAYER NAME = L3_SIG1	TID #: N/A		
PLOT NAME = Signal Layer 2	GENERATED : 20-07-2023 12:30:20		TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SVN REV: 1460 [Modified]
LAYER NAME = L5_PWR2	TID #: N/A		
PLOT NAME = Signal Layer 3	GENERATED : 20-07-2023 12:30:20		TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SVN REV: 1460 [Modified]
LAYER NAME = L7_GND2	TID #: N/A		
PLOT NAME = Signal Layer 4	GENERATED : 20-07-2023 12:30:20		TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SVN REV: 1460 [Modified]
LAYER NAME = L4_PWR1	TID #: N/A		
PLOT NAME = Signal Layer 5	GENERATED : 20-07-2023 12:30:20		TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SVN REV: 1460 [Modified]
LAYER NAME = L6_SIG2	TID #: N/A		
PLOT NAME = Signal Layer 6	GENERATED : 20-07-2023 12:30:20		TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SVN REV: 1460 [Modified]
LAYER NAME = Bottom Layer	TID #: N/A		
PLOT NAME = Bottom Layer	GENERATED : 20-07-2023 12:30:21		TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SVN REV: 1460 [Modified]
LAYER NAME = Bottom Solder	TID #: N/A		
PLOT NAME = Bottom Solder Mask	GENERATED : 20-07-2023 12:30:21		TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SVN REV: 1460 [Modified]
LAYER NAME = **Bottom Overlay**	TID #: N/A		
PLOT NAME = Bottom Overlay	GENERATED : 20-07-2023 12:30:21		TEXAS INSTRUMENTS

Symbol	Count	Hole Size	Plated	Hole Tolerance (+)	Hole Tolerance (-)	Hole Length
	1	39.37mil (1.000mm)	PTH	3.94mil (0.100mm)	3.94mil (0.100mm)	137.79mil (3.500mm)
	2	23.62mil (0.600mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	51.18mil (1.300mm)
	2	33.47mil (0.850mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
	2	39.37mil (1.000mm)	PTH	3.94mil (0.100mm)	3.94mil (0.100mm)	118.11mil (3.000mm)
	2	40.16mil (1.020mm)	NPTH	2.00mil (0.051mm)	2.00mil (0.051mm)	-
	3	43.31mil (1.100mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
	4	118.11mil (3.000mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
	4	160.00mil (4.064mm)	NPTH	2.00mil (0.051mm)	2.00mil (0.051mm)	-
	7	23.62mil (0.600mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
	10	40.00mil (1.016mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
	2905	8.00mil (0.203mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
	2942 Total					

Slot definitions : **Routed Path Length** = Calculated from tool start centre position to tool end centre position.
Hole Length = Routed Path Length + Tool Size = Slot length as defined in the PCB layout



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SVN REV: 1460 [Modified]
LAYER NAME = Drill Drawing	TID #: N/A		
PLOT NAME = Drill Drawing	GENERATED : 20-07-2023 12:30:21		TEXAS INSTRUMENTS

Symbol	Count	Hole Size	Plated	Hole Tolerance (+)	Hole Tolerance (-)	Hole Length
⊕	1	39.37mil (1.000mm)	PTH	3.94mil (0.100mm)	3.94mil (0.100mm)	137.79mil (3.500mm)
⧈	2	23.62mil (0.600mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	51.18mil (1.300mm)
◇	2	33.47mil (0.850mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
⧓	2	39.37mil (1.000mm)	PTH	3.94mil (0.100mm)	3.94mil (0.100mm)	118.11mil (3.000mm)
✲	2	40.16mil (1.020mm)	NPTH	2.00mil (0.051mm)	2.00mil (0.051mm)	-
⧓	3	43.31mil (1.100mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
□	4	118.11mil (3.000mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
○	4	160.00mil (4.064mm)	NPTH	2.00mil (0.051mm)	2.00mil (0.051mm)	-
⧈	7	23.62mil (0.600mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
⋔	10	40.00mil (1.016mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
▽	2905	8.00mil (0.203mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
	2942 Total					

Slot definitions : **Routed Path Length** = Calculated from tool start centre position to tool end centre position.
Hole Length = Routed Path Length + Tool Size = Slot length as defined in the PCB layout



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SVN REV: 1460 [Modified]
LAYER NAME = M1 Board Outline Drill Drawing	TID #: N/A		
PLOT NAME = Drill Drawing	GENERATED : 20-07-2023 12:30:24		TEXAS INSTRUMENTS



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SVN REV: 1460 [Modified]
LAYER NAME = M2 Board Dimensions	TID #: N/A		
PLOT NAME = Board Dimensions	GENERATED : 20-07-2023 12:30:27		TEXAS INSTRUMENTS