

TPS53515 Step-Down Converter Evaluation Module User's Guide



Table of Contents

| | |
|--|----|
| 1 Introduction | 2 |
| 2 Description | 2 |
| 2.1 Typical Applications..... | 2 |
| 2.2 Features..... | 2 |
| 3 Electrical Performance Specifications | 2 |
| 4 Schematic | 3 |
| 5 Test Setup | 4 |
| 5.1 Test Equipment..... | 4 |
| 5.2 Recommended Test Setup..... | 5 |
| 6 Configurations | 6 |
| 6.1 Switching Frequency Selection..... | 6 |
| 6.2 Mode Selection..... | 6 |
| 6.3 VDD Pin Supply Selection..... | 6 |
| 7 Test Procedure | 7 |
| 7.1 Line and Load Regulation and Efficiency Measurement Procedure..... | 7 |
| 7.2 Control-Loop Gain and Phase-Measurement Procedure..... | 7 |
| 7.3 List of Test Points..... | 8 |
| 7.4 Equipment Shutdown..... | 8 |
| 8 EVM Assembly Drawing and PCB Layout | 9 |
| 9 Bill of Materials | 13 |
| 10 Revision History | 14 |

1 Introduction

The TPS53515EVM-PWR587 evaluation module (EVM) uses the TPS53515 device. The TPS53515 device is a D-CAP3™ mode, 12-A synchronous buck-converter with integrated MOSFETs. The device provides a fixed 1.2-V output at up to 12 A from a 12-V input bus.

2 Description

The TPS53515EVM-PWR587 is designed for a regulated 12-V bus to produce a regulated 1.2-V output at up to 12 A of load current. The TPS53515EVM-PWR587 is designed to demonstrate the TPS53515 device in a typical low-voltage application while providing a number of test points to evaluate the performance of the TPS53515 device.

2.1 Typical Applications

- Servers and storage
- Workstations and desktops
- Telecommunication infrastructure

2.2 Features

The TPS53515EVM-PWR587 features include the following:

- 12-A DC steady-state output current
- Support for a prebias-output voltage at startup
- Jumper, J2, for enable function
- Jumper, J5, for auto-skip and forced-continuous-conduction-mode (FCCM) selection
- Jumper, J7, for extra 5-V input for further power saving purpose
- Convenient test points for probing critical waveforms


3 Electrical Performance Specifications

Table 3-1. TPS53515EVM-PWR587 Electrical Performance Specifications⁽¹⁾

| PARAMETER | TEST CONDITIONS | MIN | TYP | MAX | UNITS |
|--------------------------------|--|-----|------|-----|-------|
| Input Characteristics | | | | | |
| Voltage range | V_{IN} | 5 | 12 | 18 | V |
| Maximum input current | $V_{IN} = 5\text{ V}$, $I_O = 8\text{ A}$ | | 2.5 | | A |
| No load input current | $V_{IN} = 12\text{ V}$, $I_O = 0\text{ A}$ with auto-skip mode | | 1 | | mA |
| Output Characteristics | | | | | |
| Output voltage V_{OUT} | | | 1.2 | | V |
| Output voltage regulation | Line regulation ($V_{IN} = 5\text{ V} - 14\text{ V}$) with FCCM | | 0.2 | | % |
| | Load regulation ($V_{IN} = 12\text{ V}$, $I_O = 0\text{ A} - 8\text{ A}$) with FCCM | | 0.5 | | |
| Output voltage ripple | $V_{IN} = 12\text{ V}$, $I_O = 8\text{ A}$ with FCCM | | 10 | | mVpp |
| Output load current | | 0 | | 12 | A |
| Output over current | | | 15 | | A |
| Soft-start | | | 1 | | ms |
| Systems Characteristics | | | | | |
| Switching frequency | $V_{IN} = 12\text{ V}$, 1.2 V / 4 A | | 1000 | | kHz |
| Peak efficiency | $V_{IN} = 12\text{ V}$, 1.2 V / 8 A | | 88.5 | | % |
| Full load efficiency | | | 86.9 | | % |
| Operating temperature | | | 25 | | °C |

(1) Jumpers set to default locations, See [Section 6](#).

4 Schematic



NOTES:



VARIANT PINOUT FOR U1

| TABLE 1 | | | |
|---------|----------|----------|----------|
| IC | TPS53915 | TPS53513 | TPS53515 |
| PIN 26 | ALERT# | NC | NC |
| PIN 27 | SDA | GND1 | GND1 |
| PIN 28 | SCL | GND2 | GND2 |

Figure 4-1. TPS53515EVM-PWR587 Schematic

5 Test Setup

5.1 Test Equipment

- Oscilloscope** A digital or analog oscilloscope measures the output ripple. The oscilloscope must be set for the following: 1-M Ω impedance, 20-MHz bandwidth, AC coupling, 1- μ s / division horizontal resolution, 20-mV / division vertical resolution. Test points TP7 and TP9 measure the output ripple voltage by placing the oscilloscope probe tip through TP7 and holding the ground barrel on TP9 as shown in [Figure 5-1](#). Using a leaded ground connection can induce additional noise due to the large ground loop.
- Voltage Source** The input voltage source V_{IN} must be a 0 to 14-V variable-DC source capable of supplying 10 ADC. Connect V_{IN} to J1 as shown in [Figure 5-2](#).
- Multimeters** V1: V_{IN} at TP1 (V_{IN}) and TP4 (GND).
V2: V_{OUT} at TP7 (V_{OUT}) and TP9 (GND).
- Output Load** The output load must be an electronic constant-resistance-mode load capable of 0 to 15 ADC at 1.2 V.




Figure 5-1. Tip and Barrel Measurement for V_{OUT} Ripple

Recommended Wire Gauge:

1. V_{IN} to J1 (12-V input)
 - The recommended wire size is 1 \times AWG number 14 per input connection, with the total length of wire less than 4 feet (2 feet input, 2 feet return).
2. J3 to LOAD
 - The minimum recommended wire size is 2 \times AWG number 14, with the total length of wire less than 4 feet (2 feet output, 2 feet return).

5.2 Recommended Test Setup




Figure 5-2. TPS53515EVM-587 Top Layer for Test Setup

Input Connections:

1. Prior to connecting the DC input-source, VIN, TI recommends to limit the source current from VIN to 10 A maximum. Ensure that VIN is initially set to 0 V and connected as shown in [Figure 5-2](#).
2. Connect the voltmeter V1 at TP1 (VIN) and TP4 (GND) to measure the input voltage.

Output Connections:

1. Connect the load to J3 and set the load to constant-resistance-mode to sink 0 ADC before VIN is applied.
2. Connect the voltmeter V2 at TP7 (VOUT) and TP9 (GND) to measure the output voltage.

6 Configurations

All Jumper selections must be made prior to applying power to the EVM. Configure this EVM using the following configuration selections.

6.1 Switching Frequency Selection

Switching frequency can be changed as shown in [Table 6-1](#).

Table 6-1. Switching Frequency Selection

| SWITCHING FREQUENCY ⁽¹⁾ (f_{sw}) (kHz) | RESISTOR DIVIDER RATIO (R_{DR}) | EXAMPLE RF FREQUENCY COMBINATIONS | |
|--|--|-----------------------------------|---------------------------|
| | | R_{RF_H} (k Ω) | R_{RF_L} (k Ω) |
| 1000 | > 0.557 | 1 | 300 |
| 850 | 0.461 | 180 | 154 |
| 750 | 0.375 | 200 | 120 |
| 600 | 0.297 | 249 | 105 |
| 500 | 0.229 | 240 | 71.5 |
| 400 | 0.16 | 249 | 47.5 |
| 300 | 0.096 | 255 | 27 |
| 200 | < 0.041 | 270 | 11.5 |

(1) Default Setting: 1 MHz.

For different switching frequency setting, please change R3 and R4 as shown in [Table 6-1](#).

6.2 Mode Selection

The MODE can be set by J5.

Table 6-2. Mode Selection

| JUMPER SET TO: | MODE SELECTION |
|-----------------------------------|---|
| 1 to 2 pin shorted | FCCM with 2x RC time constant |
| 3 to 4 pin shorted ⁽¹⁾ | FCCM ⁽²⁾ with 1x RC time constant ⁽¹⁾ |
| 5 to 6 pin shorted | FCCM ⁽²⁾ with 2x RC time constant |
| 7 to 8 pin shorted | Auto-skip mode with 2x RC time constant |
| 9 to 10 pin shorted | Auto-skip mode with 1x RC time constant |

(1) Default setting.

(2) The device enters FCCM after PGOOD goes high.

6.3 VDD Pin Supply Selection

The controller can be enabled and disabled by J7.

Table 6-3. Enable Selection

| SET ON CONNECTION | ENABLE SELECTION |
|---------------------------------|--|
| R19 = 0 Ω ⁽¹⁾ | VDD pin connected to VIN pins ⁽¹⁾ |
| R19 = Open | VDD pin disconnected to VIN pins |

(1) Default setting: the VDD pin connected to the VIN pins through R19.

For power-up, input J7 with proper voltage. The VDD pin input voltage range is from 4.5 V to 25 V.

7 Test Procedure

7.1 Line and Load Regulation and Efficiency Measurement Procedure

1. Set up the EVM as described in [Section 5](#) and [Figure 5-2](#).
2. Ensure the load is set to constant-resistance mode and to sink at 0 ADC.
3. Ensure all jumper settings are configured as shown in [Section 6](#).
4. Ensure the jumper provided in the EVM shorts on J2 before VIN is applied.
5. Increase VIN from 0 to 12 V. Use V1 to measure input voltage.
6. Remove the jumper on J2 to enable the controller.
7. Use V2 to measure the VOUT voltage.
8. Vary the load from 0 to 10 ADC, VOUT must remain in load regulation.
9. Vary VIN from 8 to 14 V, VOUT must remain in line regulation.
10. To disable the converter, place the jumper on J2.
11. Decrease the load to 0 A.
12. Decrease VIN to 0 V.

7.2 Control-Loop Gain and Phase-Measurement Procedure

The TPS53515EVM-PWR587 contains a 10-Ω series resistor in the feedback loop for loop response analysis.

1. Set up the EVM as described in [Section 5](#) and [Figure 5-2](#).
2. Connect the isolation transformer to the test points marked TP5 and TP8.
3. Connect the input-signal amplitude-measurement probe (channel A) to TP10. Connect the output-signal amplitude-measurement probe (channel B) to TP11.
4. Connect the ground lead of channel A and channel B to TP15.
5. Inject around 20 mV or less signal through the isolation transformer.
6. To measure control-loop gain and phase margin, change the frequency from 100 Hz to 1 MHz using a 10-Hz or less post filter.
7. Disconnect the isolation transformer from the bode-plot test points before making other measurements.
 - Signal injection into feedback can interfere with the accuracy of other measurements.

7.3 List of Test Points

Table 7-1. Test Point Functions

| TEST POINTS | NAME | DESCRIPTION |
|-------------|-------|--------------------------------|
| TP1 | VIN | Converter input supply voltage |
| TP2 | VREG | LDO voltage |
| TP3 | PGOOD | Power good output |
| TP4 | PGND | Power ground |
| TP5 | CHB | Input B for loop injection |
| TP6 | SW | Switch Node |
| TP7 | VOUT | VOUT terminal + |
| TP8 | CHA | Input A for loop injection |
| TP9 | PGND | Power ground |
| TP10 | RF | RF pin |
| TP11 | TRIP | TRIP pin |
| TP12 | EN | Enable pin |
| TP13 | VDD | VDD pin |
| TP14 | MODE | MODE pin |
| TP15 | AGND | Analog ground |

7.4 Equipment Shutdown

Follow these steps when shutting down the equipment.

1. Shut down load
2. Shut down VIN

8 EVM Assembly Drawing and PCB Layout

The following figures show the design of the TPS53515EVM-PWR587 printed circuit board (see [Figure 8-1](#), [Figure 8-2](#), [Figure 8-3](#), [Figure 8-4](#), [Figure 8-5](#), [Figure 8-6](#), [Figure 8-7](#), and [Figure 8-8](#)). The EVM has been designed using a six-layer, 2-oz copper-circuit board.




Figure 8-1. TPS53515EVM-587 Top-Layer Assembly Drawing




Figure 8-2. TPS53515EVM-587 Bottom-Layer Assembly Drawing




Figure 8-3. TPS53515EVM-587 Top Layer, Copper




Figure 8-4. TPS53515EVM-587 Layer Two, Copper




Figure 8-5. TPS53515EVM-587 Layer Three, Copper




Figure 8-6. TPS53515EVM-587 Layer Four, Copper




Figure 8-7. TPS53515EVM-587 Layer Five, Copper




Figure 8-8. TPS53515EVM-587 Bottom Layer, Copper

9 Bill of Materials

Table 9-1. EVM Components List (Based on the Schematic, See Figure 4-1)

| Designator | Quantity | Value | Description | Package Reference | Part Number | Manufacturer |
|---|----------|-------------|--|---|---------------------------|---------------|
| C1, C2, C3, C4 | 4 | 22 μ F | Capacitor, Ceramic, 25 V, X5R, 10% | 1206 | GRM31CR61E226KE15L | Murata |
| C5 | 1 | 0.1 μ F | CAP CER 0.1 μ F 25 V 10% X5R 0402 | 0402 | GRM155R61E104KA87D | Murata |
| C6, C10, C11, C12, C13, C14, C19, C21, C22, C23 | 10 | 22 μ F | Capacitor, Ceramic, 6.3 V, X5R, 20% | 1206 | GRM31CR60J226KE19L | Murata |
| C7 | 1 | 0.1 μ F | CAP CER 0.1 μ F 50 V 10% X7R 0603 | 0603 | GRM188R71H104KA93D | Murata |
| C8 | 1 | 470 pF | CAP CER 470 pF 50 V 10% X7R 0603 | 0603 | GRM188R71H471KA01D | Murata |
| C9, C17 | 0 | Open | Capacitor, Ceramic, 50 V, X7R, 10% | 0603 | Standard | Standard |
| C15, C16, C24, C27 | 0 | Open | Capacitor, POSCAP, SMT, 2.5 V, 330 μ F, 8 m Ω | 7343(D) | 2R5TPE330M9 or 6TPE330MIL | Sanyo |
| C18, C20, C25, C26 | 4 | 1 μ F | CAP CER 1 μ F 16 V 10% X7R 0603 | 0603 | GRM188R71C105KA12J | Murata |
| FID1, FID2, FID3, FID4, FID5, FID6 | 0 | | Fiducial mark. There is nothing to buy or mount. | Fiducial | N/A | N/A |
| J1, J3 | 2 | ED120/2DS | Terminal Block, 2-pin, 15-A, 5.1 mm | 0.4 \times 0.35 inch | ED120/2DS | OST |
| J2 | 1 | PEC02SAAN | Header, Male 2-pin, 100-mil spacing, | 0.1 \times 2 inch | PEC02SAAN | Sullins |
| J4, J5, J6 | 3 | PEC05DAAN | Header, Male 2 \times 5-pin, 100-mil spacing | 0.1 \times 2 \times 5 inch | PEC05DAAN | Sullins |
| J7 | 1 | ED555/2DS | Terminal Block, 2-pin, 6-A, 3.5 mm | 0.27 \times 0.25 inch | ED555/2DS | OST |
| L1 | 1 | 1 μ H | Inductor, Power Chokes SMD | 6.6 \times 7.1 mm | PIMB065T-1R0MS | Cyntec |
| L1A | 0 | DNP | Inductor, High Fq Power, \pm 15% | 0.283 \times 0.433 inch | 69P987xN | Vitec |
| LBL1 | 1 | | Thermal Transfer Printable Labels, 0.650 (W) \times 0.2 inch (H) — 10,000 per roll | PCB Label 0.65 (H) \times 0.2 inch (W) | THT-14-423-10 | Brady |
| R1, R2, R14, R15 | 4 | 100k | RES, 100 k Ω , 1%, 0.1 W, 0603 | 0603 | CRCW0603100KFKEA | Vishay-Dale |
| R3 | 1 | 1k | RES, 1 k Ω , 1%, 0.1 W, 0603 | 0603 | CRCW06031K00FKEA | Vishay-Dale |
| R4 | 1 | 300k | RES, 300 k Ω , 1%, 0.1 W, 0603 | 0603 | RC0603FR-07300KL | Yageo America |
| R5, R8, R19 | 3 | 0 | RES, 0 Ω , 5%, 0.1 W, 0603 | 0603 | CRCW0603000Z0EA | Vishay-Dale |
| R6 | 1 | 200k | RES, 200 k Ω , 1%, 0.1 W, 0603 | 0603 | CRCW0603200KFKEA | Vishay-Dale |
| R7 | 0 | Open | Resistor, Chip, 1/16 W, 1% | 0603 | Standard | Standard |
| R9 | 1 | 3.01 | RES, 3.01 Ω , 1%, 0.125 W, 0805 | 0805 | CRCW08053R01FKEA | Vishay-Dale |
| R10 | 1 | 57.6k | RES, 57.6 k Ω , 1%, 0.1 W, 0603 | 0603 | RC0603FR-0757K6L | Yageo America |
| R11 | 1 | 20k | RES, 20.0 k Ω , 1%, 0.1 W, 0603 | 0603 | CRCW060320K0FKEA | Vishay-Dale |
| R12, R13 | 2 | 150k | RES, 150 k Ω , 1%, 0.1 W, 0603 | 0603 | CRCW0603150KFKEA | Vishay-Dale |
| R16 | 1 | 1 | RES, 1 Ω , 1%, 0.1 W, 0603 | 0603 | CRCW06031R00FKEA | Vishay-Dale |
| R20, R21 | 2 | 10k | RES, 10 k Ω , 1%, 0.1 W, 0603 | 0603 | CRCW060310K0FKEA | Vishay-Dale |
| R22 | 1 | 10 | RES, 10 Ω , 1%, 0.1 W, 0603 | 0603 | CRCW060310R0FKEA | Vishay-Dale |
| TP1, TP2, TP3, TP5, TP6, TP7, TP8, TP10, TP11, TP12, TP13, TP14, TP15 | 13 | 5000 | Test Point, Red, Thru Hole Color Keyed | 0.1 \times 0.1 inch | 5000 | Keystone |
| TP4, TP9 | 2 | 5001 | Test Point, Black, Thru Hole Color Keyed | 0.1 \times 0.1 inch | 5001 | Keystone |
| U1 | 1 | TPS53515RVE | IC, High Performance, 12-A Single Sync. Step-Down Converter with PMBus. | | TPS53515RVE | TI |

10 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Revision B (February 2014) to Revision C (May 2021) Page

- Changed user's guide title..... 2
- Updated the numbering format for tables, figures, and cross-references throughout the document. 2

Changes from Revision A (December 2013) to Revision B (February 2014) Page

- Changed the test points in the *Tip and Barrel Measurement for VOUT Ripple* image from TPS5 and TPS7 to TPS7 and TPS9 (respectively from left to right)..... 4
-

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2022, Texas Instruments Incorporated