

TIDA-010015 REV E1 Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
IPC1	1		TIDA-010015	Any	Printed Circuit Board	
C1	1	220uF	ESMR451VSN221MQ30S	Chemi-Con	CAP ALUM 220UF 20% 450V SNAP	25.4x25mm
C2, C3	2	0.047uF	B32652A0473K000	EPCOS (TDK)	CAP FILM 0.047UF 10% 1KVDC RAD	18x7mm
C4	1	0.47uF	450MPK474J	Rubycon	CAP, Film, 0.47 µF, 450 V, +/- 5%, TH	18x6.5mm
C5, C61	2	0.33uF	ECW-FE2W334K	Panasonic Electronic Compon	0.33µF Film Capacitor 450V Polypropylene (PP), Metallized Radial	13x12x6mm
C6, C8, C11, C47, C49	5	2200pF	AY2222M35Y5US63L7	Vishay-Bccomponents	CAP, CERM, 2200 pF, 300 V, +/- 20%, Y5U, AEC-Q200 Grade 1, D9.5xT5mm	D9.5xT5mm
C7, C65	2	470pF	VJ1210Y471KXEAT5Z	Vishay-Vitramon	CAP, CERM, 470 pF, 500 V, +/- 10%, X7R, 1210	1210
C9, C10	2	0.33uF	B32922C3334K	TDK	CAP, Film, 0.33 µF, X2 305 VAC, +/- 10%, TH	B32922_14.5mm
C12, C13, C14, C76	4	680uF	EEU-FS1H681B	Panasonic Electronic Compon	680µF 50V Aluminum Electrolytic Capacitors Radial, Can 10000 Hrs @ 105°C	0.492" Dia (12.50mm)
C15, C23	2	2.2uF	08053C225KAT2A	AVX	CAP, CERM, 2.2 uF, 25 V, +/- 10%, X7R, 0805	0805
C16, C52	2	0.1uF	C1608X7R1H104K080AA	TDK	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, 0603	0603
C17	1	0.01uF	GRM188R71C103KA01D	MuRata	CAP, CERM, 0.01 uF, 16 V, +/- 10%, X7R, 0603	0603
C18	1	100pF	885012006023	Würth Electronics Inc.	CAP CER 100PF 16V C0G/NP0 0603	0603
C19	1	3.3pF	08055A3R3CAT2A	AVX	CAP, CERM, 3.3 pF, 50 V, +/- 8%, C0G/NP0, 0805	0805
C20	1	10pF	06035A100JAT2A	AVX	CAP, CERM, 10 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C21, C37	2	6800pF	GRM188R71E682KA01D	MuRata	CAP, CERM, 6800 pF, 25 V, +/- 10%, X7R, 0603	0603
C22	1	6800pF	GRM188R71H682KA01D	MuRata	CAP, CERM, 6800 pF, 50 V, +/- 10%, X7R, 0603	0603
C24, C25	2	22pF	C0603C220J5GACTU	Kemet	CAP, CERM, 22 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C26	1	0.1uF	C0805C104K1RACTU	Kemet	CAP, CERM, 0.1 µF, 100 V, +/- 10%, X7R, 0805	0805
C27, C28	2	0.1uF	C0603C104J3RACTU	Kemet	CAP, CERM, 0.1 uF, 25 V, +/- 5%, X7R, 0603	0603
C29, C33	2	1000pF	C1608X7R1H102K	TDK	CAP, CERM, 1000 pF, 50 V, +/- 10%, X7R, 0603	0603
C30	1	1uF	GRM188R71E105KA12D	MuRata	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0603	0603
C31	1	0.22uF	06033D224KAT2A	AVX	CAP, CERM, 0.22 µF, 25 V, +/- 10%, X5R, 0603	0603
C32	1	0.1uF	GRM188R72A104KA35J	MuRata	CAP, CERM, 0.1 µF, 100 V, +/- 10%, X7R, 0603	0603
C34	1	820pF	06035A821JAT2A	AVX	CAP, CERM, 820 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C35	1	4.7uF	GRM188R61E475KE11D	MuRata	CAP, CERM, 4.7 uF, 25 V, +/- 10%, X5R, 0603	0603
C36	1	2.2uF	0805YD225KAT2A	AVX	CAP, CERM, 2.2 µF, 16 V, +/- 10%, X5R, 0805	0805
C38	1	0.22uF	GRM188R71H224KAC4D	MuRata	CAP, CERM, 0.22 uF, 50 V, +/- 10%, X7R, 0603	0603
C39	1	150pF	GRM31A7U3A151JW31D	MuRata	CAP, CERM, 150 pF, 1000 V, +/- 5%, U2J, 1206	1206
C40	1	82pF	GRM31A7U3A820JW31D	MuRata	CAP CER 82PF 1KV U2J 1206	1206
C41	1	1000pF	06031C102MAT2A	AVX	CAP, CERM, 1000 pF, 100 V, +/- 20%, X7R, 0603	0603
C42	1	0.047uF	06033C473JAT2A	AVX	CAP, CERM, 0.047 uF, 25 V, +/- 5%, X7R, 0603	0603
C43	1	680pF	GRM188R71H681KA01D	MuRata	CAP, CERM, 680 pF, 50 V, +/- 10%, X7R, 0603	0603
C44, C45	2	330pF	12061A331JAT2A	AVX	CAP, CERM, 330 pF, 100 V, +/- 5%, C0G/NP0, 1206	1206
C46, C48	2	1uF	C0805C105K3RACTU	Kemet	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0805	0805
C50	1	10pF	06035A100JAT2A	AVX	CAP, CERM, 10 pF, 50 V, +/- 5%, C0G/NP0, 0603	0603
C51	1	1uF	GRM319R61E105KC36D	MuRata	CAP, CERM, 1uF, 25V, +/-10%, X5R, 1206	1206
C53, C54	2	2.2uF	GRM188R6YA225KA12D	MuRata	CAP, CERM, 2.2 uF, 35 V, +/- 10%, X5R, 0603	0603
C55, C57	2	1uF	C1608X5R1E105K080AC	TDK	CAP, CERM, 1 uF, 25 V, +/- 10%, X5R, 0603	0603
C56	1	4.7uF	GRT188R61C475KE13D	MuRata	CAP, CERM, 4.7 µF, 16 V, +/- 10%, X5R, AEC-Q200 Grade 3, 0603	0603
C58, C59	2	100pF	08055A101JAT2A	AVX	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, 0805	0805

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C60	1	1000µF	EEU-FS1V102LB	Panasonic	1000µF 35V Aluminum Electrolytic Capacitors Radial, Can 10000 Hrs @ 105°C	
C67, C68, C72, C73	4	4.7uF	C3225X7S2A475K200AE	TDK	CAP, CERM, 4.7 µF, 100 V, +/- 10%, X7S, 1210	1210
D1, D5	2	600V	MUR860G	ON Semiconductor	Diode, Ultrafast, 600 V, 8 A, TH	TO-220AC
D2, D6	2	0.35V	BAT54HT1G	ON Semiconductor	Diode, Schottky, 30V, 0.2A, SOD-323	SOD-323
D3	1	GBU2510-G	GBU2510-G	Comchip Technology	RECT BRIDGE GPP 1000V 25A GBU	GBU
D4	1	15V	BZX384-C15,115	NXP Semiconductor	Diode, Zener, 15 V, 300 mW, SOD-323	SOD-323
D7, D8, D11	3	30V	SD103BW-7-F	Diodes Inc.	Diode, Schottky, 30 V, 0.35 A, SOD-123	SOD-123
D9, D10	2	1000V	RS1MB-13-F	Diodes Inc.	Diode, P-N, 1000 V, 1 A, SMB	SMB
D18	1	600V	US1J-13-F	Diodes Inc.	Diode, Ultrafast, 600 V, 1 A, SMA	SMA
D20	1	5.1V	BZT52C5V1S-7-F	Diodes Inc.	Diode, Zener, 5.1 V, 200 mW, SOD-323	SOD-323
F1	1	10A	38321000000	LITTELFUSE INC	FUSE, BOARD MOUNT, 10 A, 300 V, TH-2P	
H1, H2, H3, H4, H5, H6	6		SJ-5303 (CLEAR)	3M	Bumpon, Hemisphere, 0.44 X 0.20, Clear	Transparent Bumpon
H7	1		V6560W	Assman WSW	HEATSINK, ALUM, ANOD, for TO-220	29x12mm
J1	1		61300111121	Würth Elektronik	Header, 2.54 mm, 1x1, Gold, TH	Header, 2.54 mm, 1x1, TH
J2	1		800-10-002-10-001000	Mill-Max	Header, 100mil, 2x1, TH	Header, 2x1, 100mil, TH
J3	1		350429-1	TE Connectivity	Header(Shrouded), 6.35mm, 3x1, Tin, TH	Header(Shrouded), 6.35mm, 3x1, TH
J4	1		22284033	Molex	Header, 2.54mm, 3x1, Tin, TH	Header, 2.54mm, 3x1, TH
J5	1		22284023	Molex	Header, 2.54mm, 2x1, Tin, TH	Header, 2.54mm, 2x1, TH
L1, L6	2	150 µH	Custom		Transformer, 160 uH, TH	43x38mm
L2	1	150uH	7447076	Würth Elektronik	Inductor, Toroid, Powdered Iron, 150 µH, 5A, TH	
L3, L5	2	1mH	7448031501	Würth Electronics	FILTER, WE-CMBNC COMMON MODE POWER LINE CHOKE, 1mH, 15A, VERTICAL, TH-4P	
L4	1	300nH	PA2607.301NLT	Pulse Engineering	Inductor, Ferrite, 300 nH, 32 A, 0.00031 ohm, SMD	10.31x7.65mm
L7	1				Inductor, Ferrite, 330 µH, 6.1 A, 0.074 ohm, TH	
M1, M2, M3, M4, M5, M6, M7, M8	8		WA-T220-101E	OHMITE	HEATSINK, ALUMINIUM WITH CLIP, VERTICAL MOUNT, SOLDERABLE PIN, TO-220	
Q1, Q2, Q3, Q12	4	650V	IPA60R120P7XKSA1	Infineon Technologies	MOSFET N-CHANNEL 600V 26A TO220	TO-220AB
Q4	1	60 V	MMBTA05LT1G	ON Semiconductor	Transistor, NPN, 60 V, 0.5 A, AEC-Q101, SOT-23	SOT-23
Q5, Q7	2	80V	CSD19505KCS	Texas Instruments	MOSFET, N-CH, 80 V, 100 A, KCS0003B (TO-220-3)	KCS0003B
Q6	1	30 V	MMBT2222LT1G	ON Semiconductor	Transistor, NPN, 30 V, 0.6 A, SOT-23	SOT-23
Q10	1	600V	AOD4S60	AOS	MOSFET, N-CH, 600 V, 4 A, DPAK	DPAK
Q13, Q14	2	30 V	BC858C-7-F	Diodes Inc.	Transistor, PNP, 30 V, 0.1 A, SOT-23	SOT-23
R1, R2, R55, R64, R72	5	10k	RNCF0603TKY10K0	Stackpole Electronics Inc	RES, 10 k, 0.01%, 0.063 W, 0603	0603
R3	1	200	RG2012P-201-B-T5	Susumu Co Ltd	RES, 200, 0.1%, 0.125 W, 0805	0805
R4, R5, R18	3	18.2	CRCW080518R2FKEA	Vishay-Dale	RES, 18.2, 1%, 0.125 W, 0805	0805
R6, R19, R74	3	10.0k	CRCW080510K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.125 W, 0805	0805
R7, R8	2	0.03	CSRN2512FK30L0	Stackpole Electronics Inc	RES, 0.03, 1%, 2 W, 2512	2512
R9	1	59.7k	RT0603BRD0759K7L	Yageo America	RES, 59.7 k, 0.1%, 0.1 W, 0603	0603
R10, R22, R31	3	1.00k	CRCW12061K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.25 W, 1206	1206

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
R11, R37, R39, R41	4	66.5k	CRCW060366K5FKEA	Vishay-Dale	RES, 66.5 k, 1%, 0.1 W, 0603	0603
R12, R49	2	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
R14	1	49.9k	ERJ-3EKF4992V	Panasonic	RES, 49.9 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R15, R16	2	2.2	CRCW08052R20JNEA	Vishay-Dale	RES, 2.2, 5%, 0.125 W, 0805	0805
R17, R47, R71, R73	4	6.04k	CRCW06036K04FKEA	Vishay-Dale	RES, 6.04 k, 1%, 0.1 W, 0603	0603
R20	1	3.0Meg	CRCW12063M00JNEA	Vishay-Dale	RES, 3.0 M, 5%, 0.25 W, AEC-Q200 Grade 0, 1206	1206
R21, R23, R33, R87	4	2.7Meg	CRCW12062M70JNEA	Vishay-Dale	RES, 2.7 M, 5%, 0.25 W, AEC-Q200 Grade 0, 1206	1206
R24, R26	2	16.5k	CRCW060316K5FKEA	Vishay-Dale	RES, 16.5 k, 1%, 0.1 W, 0603	0603
R25	1	750k	CRCW0603750KFKEA	Vishay-Dale	RES, 750 k, 1%, 0.1 W, 0603	0603
R27, R34, R46, R86	4	2.74Meg	CRCW08052M74FKEA	Vishay-Dale	RES, 2.74 M, 1%, 0.125 W, 0805	0805
R28, R77	2	511k	CRCW1206511KFKEA	Vishay-Dale	RES, 511k ohm, 1%, 0.25W, 1206	1206
R29, R36	2	330k	CRCW1206330KJNEA	Vishay-Dale	RES, 330 k, 5%, 0.25 W, 1206	1206
R30	1	100	CRCW0603100RFKEA	Vishay-Dale	RES, 100, 1%, 0.1 W, 0603	0603
R32, R70	2	487k	CRCW0603487KFKEA	Vishay-Dale	RES, 487 k, 1%, 0.1 W, 0603	0603
R35	1	133k	CRCW0603133KFKEA	Vishay-Dale	RES, 133 k, 1%, 0.1 W, 0603	0603
R38, R40	2	22	CRCW060322R0JNEA	Vishay-Dale	RES, 22, 5%, 0.1 W, 0603	0603
R42	1	7.50k	CRCW06037K50FKEA	Vishay-Dale	RES, 7.50 k, 1%, 0.1 W, 0603	0603
R43	1	374k	CRCW1206374KFKEA	Vishay-Dale	RES, 374 k, 1%, 0.25 W, 1206	1206
R44, R45	2	4.7k	CR0603-JW-472GLF	Bourns	RES, 4.7 k, 5%, 0.1 W, 0603	0603
R48	1	147k	CRCW0603147KFKEA	Vishay-Dale	RES, 147 k, 1%, 0.1 W, 0603	0603
R50	1	16.9k	CRCW060316K9FKEA	Vishay-Dale	RES, 16.9 k, 1%, 0.1 W, 0603	0603
R51, R63	2	113k	CRCW0603113KFKEA	Vishay-Dale	RES, 113 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R52, R53	2	10	CRCW080510R0JNEA	Vishay-Dale	RES, 10, 5%, 0.125 W, 0805	0805
R56	1	100k	RT0603BRD07100KL	Yageo America	RES, 100 k, 0.1%, 0.1 W, 0603	0603
R58, R59	2	10.0	CRCW060310R0FKEAHP	Vishay-Dale	RES, 10.0, 1%, 0.25 W, 0603	0603
R60, R61	2	4.7	CRCW08054R70JNEA	Vishay-Dale	RES, 4.7, 5%, 0.125 W, 0805	0805
R62	1	6.81k	RC0603FR-076K81L	Yageo	RES, 6.81 k, 1%, 0.1 W, 0603	0603
R65	1	0.0005	WSL2512L5000FEA18	Vishay-Dale	RES, 0.0005, 1%, 2 W, 2512	2512
R66, R78	2	10.0	CRCW060310R0FKEAHP	Vishay-Dale	RES, 10.0, 1%, 0.25 W, AEC-Q200 Grade 0, 0603	0603
R67	1	1.00Meg	CRCW08051M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.125 W, AEC-Q200 Grade 0, 0805	0805
R68	1	1.00Meg	MCT06030C1004FP500	Vishay/Beyschlag	RES, 1.00 M, 1%, 0.125 W, 0603	0603
R69	1	330k	ERJ-3EKF3303V	Panasonic	RES, 330 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R75	1	1.10Meg	CRCW06031M10FKEA	Vishay-Dale	RES, 1.10 M, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R76	1	49.9k	CRCW120649K9FKEA	Vishay-Dale	RES, 49.9k ohm, 1%, 0.25W, 1206	1206
R88	1	124k	ERJ-3EKF1243V	Panasonic	RES, 124 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R89	1	95.3k	CRCW060395K3FKEA	Vishay-Dale	RES, 95.3 k, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603
R90	1	82.5k	CRCW060382K5FKEA	Vishay-Dale	RES, 82.5 k, 1%, 0.1 W, 0603	0603
RF1	1	47	EMC2-47RKI	TT Electronics/IRC	RES, 47, 10%, 2 W, Fusible, TH	Axial resistor
RV1	1		S10K275E2	EPCOS Inc	Varistor 275V RMS 10MM Radial, TH	10mm Radial
T1	1		PQ3230	Payton	Transformer, TH	51x33mm
U1, U9	2		UCC27517DBVR	Texas Instruments	4A/4A Single Channel High-speed Low-side Gate Driver, DBV0005A (SOT-23-5)	DBV0005A
U2	1		UCC25630-1DDBR	Texas Instruments	Enhanced LLC Resonant Controller with Driver, DDB0014A (SOIC-14)	DDB0014A
U3	1		UCC28064ADR	Texas Instruments	Natural Interleaving Transition Mode PFC Controller with Improved Light Load Efficiency, D0016A (SOIC-16)	D0016A
U4	1		LP2951ACMX/NOPB	Texas Instruments	Series of Adjustable Micropower Voltage Regulators, D0008A (SOIC-8)	D0008A

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
U5	1		TL431ACDBZR	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, 0 to 70 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A
U6, U12	2		VO618A	Vishay-Semiconductor	Optocoupler, 5.3 kV, 50-600% CTR, TH	DIP, 4-Leads, Body 6.86x4.83mm, Pitch 2.54mm
U7, U8	2		UCC24612-1DBVR	Texas Instruments	UCC24612-1DBV, DBV0005A (SOT-23-5)	DBV0005A
U10	1		LP2981-50	Texas Instruments	Micropower 100 mA Ultra Low-Dropout Regulator, 5-pin SOT-23, Pb-Free	DBV0005A
U11	1		TL331IDBVR	Texas Instruments	SINGLE DIFFERENTIAL COMPARATOR, DBV0005A (SOT-23-5)	DBV0005A
U13	1		TLV171IDBVR	Texas Instruments	36V, Low-Power, RRO, General-Purpose Operational Amplifier, DBV0005A (SOT-23-5)	DBV0005A
U14	1		INA181A4IDBV	Texas Instruments	Bidirectional, Low- and High-Side Measurement, Multichannel, Voltage Output, Current-Sense Amplifier, DBV0006A (SOT-6)	DBV0006A
FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2018, Texas Instruments Incorporated