




Top Solder




Top Signal




GND




PWR



Bottom Signal




Bottom Solder



Symbol	Quantity	Finished Hole Size	Plated	Hole Type	Drill Layer Pair	Hole Tolerance
	2	35.43mil (0.900mm)	NPTH	Round	Top Signal - Bottom Signal	±1.97mil
	4	125.00mil (3.175mm)	NPTH	Round	Top Signal - Bottom Signal	
	7	7.87mil (0.200mm)	PTH	Round	Top Signal - Bottom Signal	
	726	9.84mil (0.250mm)	PTH	Round	Top Signal - Bottom Signal	
	22	11.81mil (0.300mm)	PTH	Round	Top Signal - Bottom Signal	
	17	15.75mil (0.400mm)	PTH	Round	Top Signal - Bottom Signal	
	8	25.00mil (0.635mm)	PTH	Round	Top Signal - Bottom Signal	
	80	40.16mil (1.020mm)	PTH	Round	Top Signal - Bottom Signal	
	10	43.31mil (1.100mm)	PTH	Round	Top Signal - Bottom Signal	
	20	43.31mil (1.100mm)	PTH	Round	Top Signal - Bottom Signal	
	27	45.28mil (1.150mm)	PTH	Round	Top Signal - Bottom Signal	
	2	27.56mil (0.700mm)	PTH	Slot	Top Signal - Bottom Signal	
	2	59.06mil (1.500mm)	PTH	Slot	Top Signal - Bottom Signal	
	2	74.80mil (1.900mm)	PTH	Slot	Top Signal - Bottom Signal	
929 Total						

Slot definitions : Routed Path Length = Calculated from tool start centre position to tool end centre position,
Hole Length = Routed Path Length + Tool Size = Slot length as defined in the PCB layout

Drill Drawing



M2 Board Dimensions