Functional Safety Information TLV710-Q1 Functional Safety FIT Rate, FMD and Pin FMA

TEXAS INSTRUMENTS

Table of Contents

1 Overview	2
2 Functional Safety Failure In Time (FIT) Rates	3
3 Failure Mode Distribution (FMD)	
4 Pin Failure Mode Analysis (Pin FMA)	
······································	

Trademarks


All trademarks are the property of their respective owners.

1 Overview

This document contains information for the TLV710-Q1 (SON package) to aid in a functional safety system design. Information provided are:

- Functional safety failure in time (FIT) rates of the semiconductor component estimated by the application of industry reliability standards
- Component failure modes and their distribution (FMD) based on the primary function of the device
- Pin failure mode analysis (pin FMA)

Figure 1-1 shows the device functional block diagram for reference.



GND

Figure 1-1. Functional Block Diagram

The TLV710-Q1 was developed using a quality-managed development process, but was not developed in accordance with the IEC 61508 or ISO 26262 standards.

2 Functional Safety Failure In Time (FIT) Rates

This section provides functional safety failure in time (FIT) rates for the TLV710-Q1 based on two different industry-wide used reliability standards:

- Table 2-1 provides FIT rates based on IEC TR 62380 / ISO 26262 part 11
- Table 2-2 provides FIT rates based on the Siemens Norm SN 29500-2

Table 2-1. Component Failure Rates per IEC TR 62380 / ISO 26262 Part 11

FIT IEC TR 62380 / ISO 26262	FIT (Failures Per 10 ⁹ Hours)
Total component FIT rate	8
Die FIT rate	6
Package FIT rate	2

The failure rate and mission profile information in Table 2-1 comes from the reliability data handbook IEC TR 62380 / ISO 26262 part 11:

- · Mission profile: Motor control from table 11
- Power dissipation: 250mW
- Climate type: World-wide table 8
- Package factor (lambda 3): Table 17b
- Substrate material: FR4
- EOS FIT rate assumed: 0 FIT

Table 2-2. Component Failure Rates per Siemens Norm SN 29500-2

Table	Category	Reference FIT Rate	Reference Virtual T _J
5	CMOS, BICMOS Digital, analog, or mixed	25 FIT	55°C

The reference FIT rate and reference virtual T_J (junction temperature) in Table 2-2 come from the Siemens Norm SN 29500-2 tables 1 through 5. Failure rates under operating conditions are calculated from the reference failure rate and virtual junction temperature using conversion information in SN 29500-2 section 4.



3 Failure Mode Distribution (FMD)

The failure mode distribution estimation for the TLV710-Q1 in Table 3-1 comes from the combination of common failure modes listed in standards such as IEC 61508 and ISO 26262, the ratio of sub-circuit function size and complexity, and from best engineering judgment.

The failure modes listed in this section reflect random failure events and do not include failures resulting from misuse or overstress.

Die Failure Modes	Failure Mode Distribution (%)
VOUT high (following VIN)	40
VOUT not in specification (voltage or timing)	10
VOUT low (no output)	40
Short circuit any two pins	10

Table 3-1. Die Failure Modes and Distribution

4 Pin Failure Mode Analysis (Pin FMA)

This section provides a failure mode analysis (FMA) for the pins of the TLV710-Q1. The failure modes covered in this document include the typical pin-by-pin failure scenarios:

- Pin short-circuited to ground (see Table 4-2)
- Pin open-circuited (see Table 4-3)

Texas

www.ti.com

INSTRUMENTS

- Pin short-circuited to an adjacent pin (see Table 4-4)
- Pin short-circuited to VIN (see Table 4-5)

Table 4-2 through Table 4-5 also indicate how these pin conditions can affect the device as per the failure effects classification in Table 4-1.

Class	Failure Effects
A	Potential device damage that affects functionality.
В	No device damage, but loss of functionality.
С	No device damage, but performance degradation.
D	No device damage, no impact to functionality or performance.

Table 4-1. TI Classification of Failure Effects

Figure 4-1 shows the TLV710-Q1 pin diagram. For a detailed description of the device pins, see the *Pin Configuration and Functions* section in the TLV710-Q1 data sheet.




Figure 4-1. Pin Diagram

Following are the assumptions of use and the device configuration assumed for the pin FMA in this section:

- Device contains DSE pin configuration. Device operates at free-air temperatures between -40°C and 125°C.
- Device operates at an input voltage less than 5.5V and more than 2V.
- Device operates according to all recommended operating conditions and does not exceed the absolute maximum ratings.

Pin Name	Pin No.	Description of Potential Failure Effects	Failure Effect Class
EN1	1	LDO 1 is always off due to EN being grounded.	В
IN	2	Output voltage is at or near ground.	В
EN2	3	LDO 2 is always off due to EN being grounded.	В
GND	4	No effect. Normal operation.	D
OUT2	5	Output voltage 2 is at or near ground. Device is in current limit. The device can cycle in and out of thermal shutdown depending on power dissipation.	В
OUT1	6	Output voltage 1 is at or near ground. Device is in current limit. The device can cycle in and out of thermal shutdown depending on power dissipation.	В

Table 4.2	Din FMA	for Device Pi	ns Short-Circ	uited to Ground
I able 4-2. r		IOI Device FI	ns snort-circ	

Table 4-3. Pin FMA for Device Pins Open-Circuited

Pin Name	Pin No.	Description of Potential Failure Effects	Failure Effect Class
EN1	1	LDO is in unknown state.	В
IN	2	No input to LDO. Output is at or near ground.	В
EN2	3	LDO is in unknown state.	В
GND	4	There is no current loop for internal biasing; device cannot operate.	В
OUT2	5	Device 2 output is unregulated and the load is not powered.	В
OUT1	6	Device 1 output is unregulated and the load is not powered.	В

Table 4-4. Pin FMA for Device Pins Short-Circuited to Adjacent Pin

Pin Name	Pin No.	Shorted to	Description of Potential Failure Effects	Failure Effect Class
EN1	1	IN	If EN is positive voltage above the IN absolute maximum rating, IN can be damaged.	А
IN	2	EN2	If EN is positive voltage above the IN absolute maximum rating, IN can be damaged.	А
GND	4	OUT2	Output voltage is at or near ground. Device is in current limit. The device can cycle in and out of thermal shutdown depending on power dissipation.	В
OUT2	5	OUT1	Output voltage is driven to unknown voltage. High current drive between pins is possible leading to potential thermal shutdown.	A

Table 4-5. Pin FMA for Device Pins Short-Circuited to VIN

Pin Name	Pin No.	Description of Potential Failure Effects	Failure Effect Class
EN1	1	If EN is positive voltage above the IN absolute maximum rating, IN can be damaged.	Α
IN	2	No effect. Normal operation.	D
EN2	3	If EN is positive voltage above the IN absolute maximum rating, IN can be damaged.	Α
GND	4	Output voltage is at or near ground.	В
OUT2	5	Regulation for LDO 2 is not possible. The output voltage equals input voltage.	В
OUT1	6	Regulation for LDO 1 is not possible. The output voltage equals input voltage.	В

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated