

5

4

3

2

1

Notes/Revision Information

V0.01 - Initial Release

- 01 - Title Page
- 02 - MCU
- 03 - AFE031
- 04 - Passive Filters
- 05 - Power
- 06 - Connector

D

D

C

C

B

B

A

A

TIDC-HYBRID-WMBUS-PLC




5

4


3

2

1




OPTIONAL if BOR is handled by the system or Host processor



**TIDC-HYBRID-WMBUS-PLC**

Bootmode selection can be hard wired if required modes are known.

<b>TI</b>		
Title: T1 SOMPLC-F28PLC84 MODULE		
Page Contents: 02 - MCU		
Size: B	<Doc>	Revision: 0.18
Date: Monday, March 03, 2014	Sheet 2 of 6	



U6 MUST BE on TOP (OUTER, FREE-AIR) side of board!!!!



Optional Components:  
necessary for G1 only, use  
2700 pF 6V for C62 and  
a 510R 5% for R42

Optional Components:  
necessary for G1 only, use  
2700 pF 6V for C61 and  
a 510R 5% for R41

NOTE:  
For CENELEC A band use 680pf for C10 and C11  
For CENELEC B/C band use 560pf for C10 and  
270pf for C11.



as close to U6 as possible  
Minimize Trace Length

Place Near U6



### TIDC-HYBRID-WMBUS-PLC

Title: TI SOMPLC-F28PLC84 MODULE		<b>TI</b>
Page Contents: 03 - AFE031		
Size: B	<Doc>	Revision: 0.18
Date: Thursday, February 27, 2014	Sheet 3 of 6	






NOTE: Several components on this page have been removed or changed in the BOM.


TIDC-HYBRID-WMBUS-PLC

Title: TI SOMPLC-F28PLC84 MODULE		<b>TI</b>
Page Contents: 04 - AFE1 (Passive RX Filter)		
Size: B	<Doc>	Revision: 0.18
Date: Wednesday, February 26, 2014	Sheet 4 of 6	

OPTIONAL: Heatsink is not needed.




Place caps under U1



Place caps under U1

OPTIONAL: to source VDD with the on chip LDO, do not populate R43 and place a 10k resistor on R27. Additionally, the optional components below are not needed.





OPTIONAL: For reduced power consumption use a DC/DC converter instead of the On-Chip Linear Supply

Note: Follow Layout Procedures described in TPS62240 Datasheet

### TIDC-HYBRID-WMBUS-PLC

Title: T1 SOMPLC-F28PLC84 MODULE		<b>TI</b>
Page Contents: 05 - Power		
Size: B	<Doc>	Revision: 0.18
Date: Wednesday, February 26, 2014	Sheet 5 of 6	



## TIDC-HYBRID-WMBUS-PLC

Title: T1 SOMPLC-F28PLC84 MODULE		<b>TI</b>
Page Contents: 06 - Connector		
Size: B	<Doc>	Revision: 0.18
Date: Monday, March 03, 2014	Sheet 6 of 6	

Notes/Revision Information

V0.01 - Initial Release

V0.02 - 10/10/12

- p2
  - Changed C2 value
- p3
  - Added C29
  - Removed 5V rail
  - Changed LD1, LD2 to D6, D7 and connected to 3V3
- p4
  - Removed 5V power supply
  - Changed R35 to 1.87k

V0.03 - 10/18/12

- p4
  - Changed C23, C24 parts (BOM)
  - Changed symbol for M1 added multiple pins

V0.04 - 10/22/12

- p3
  - Updated part U5 Symbol

V0.05 - 11/12/12

- p4
  - Added MHL, 2, 3, 4
- p5
  - Added M2, M3
  - Added R36, TP1
  - Removed J5, J6 and J7

V0.06 - 12/05/12

- p2
  - Connected MHL to Earth GND
- p4
  - Removed Ground from MH4
- p5
  - Moved TP1 to the other side of R36
  - Changed M2 Part (BOM)

V0.07 - 12/07/12

- p5
  - Moved TP1 to the other side of R36 (again)

V0.08 - 01/14/13 (R2 Release)

- p2
  - Updated Part D1 (BOM)

V0.09 - 05/13/13 (R2 Release)

- p2
  - Changed C22 to DNP
  - Added C30

V0.10 - 12/5/13 (R2 Release)

- p2
  - Changed U1 to 10V



V0.11 - 2/26/14 (R5 Release)

- p2
  - Added U11
  - Added C31, C32


- 01 - Title / Notes
- 02 - Coupling Circuit
- 03 - USB JTAG/UART
- 04 - System Power
- 05 - Connectors

TIDC-HYBRID-WMBUS-PLC

Title: SOMPLC-DOCKV1 R2		<b>TI</b>	
Page Contents: 01 - Title / Notes			
Size: B	<Doc>	Revision: 0.8	
Date: Wednesday, February 26, 2014	Sheet 1 of 5		



HIGH VOLTAGE !








TIDC-HYBRID-WMBUS-PLC

<b>TI</b>	
Title: SOMPLC-DOCKV1 R2	
Page Contents: 02 - Coupling Circuit	
Size: B	Revision: 0.8
Date: Wednesday, February 26, 2014	Sheet 2 of 5









TIDC-HYBRID-WMBUS-PLC

Title: SOMPLC-DOCKV1 R2		<b>TI</b>
Page Contents: 04 - System Power		
Size: B	<Doc>	Revision: 0.8
Date: Wednesday, February 26, 2014	Sheet 4 of 5	





### TIDC-HYBRID-WMBUS-PLC


<b>TI</b>		<b>Title:</b> SOMPLC-DOCKV1 R2	
		<b>Page Contents:</b> 05 - Connectors	
<b>Size:</b> B	<Doc>	<b>Revision:</b> 0.8	
<b>Date:</b> Wednesday, February 26, 2014		Sheet 5 of	5

VDDS decoupling capacitors

VDDR decoupling capacitors




Place L331 and C331 close to pin 33.  
Low inductance ground for C331





U1B		U1A	
DIO_1	6	DIO_17	27
DIO_2	7	DIO_18	28
DIO_3	8	DIO_19	29
DIO_4	9	DIO_20	30
DIO_5	10	DIO_21	31
DIO_6	11	DIO_22	32
DIO_7	12	DIO_23	36
DIO_8	14	DIO_24	37
DIO_9	15	DIO_25	38
DIO_10	16	DIO_26	39
DIO_11	17	DIO_27	40
DIO_12	18	DIO_28	41
DIO_13	19	DIO_29	42
DIO_14	20	DIO_30	43
DIO_15	21		
DIO_16 / JTAG TDO	26		

Mount either R11 or R12 to select SMA or PCB ant.

EM connector 1



EM connector 2



TIDC-HYBRID-WMBUS-PLC

Title: <b>CC13xxEM-7XD-7793, main</b>		
Drawn: a0132595		
Checked: <Check name>		
Size: A3	Rev: 1.3.3	Sheet: 1 of 2
Date:	Tuesday, August 25, 2015	

R 1.0.0

-----  
-Initial release revision

R1.0.1

-----  
L3 -> Changed from LQG to LQW  
L4 -> Changed from LQG to LQW

R1.1.0

-----  
-New CC13xx symbol with different DIO to pin mapping  
-New Crystal (9 pF, from 7 pF. But 9 pF has been assembled on previous EMs).  
-New reference numbers on components.

R1.2.0

-----  
- Updating RF filter for better harmonic supression.  
- Remove test point on RXTX pin.

R1.3.0

-----  
- For PG2  
- C15 33pF -> 100pF  
- L12, L21 8.2nH -> 7.5nH  
- C13 4.7nH -> 6.2nH  
- C14 2.2nH -> 3.3nH

R1.3.1

-----  
L331 10uH -> 6.8uH


R1.3.2

-----  
C341 10uF -> 22uF

R1.3.3

-----  
C331 10uF -> 22uF

TIDC-HYBRID-WMBUS-PLC

Title: CC13xxEM-7XD-7793, rev history		
Drawn: a0132595		
Checked: <Check name>		
Size: A4	Rev: 1.3.3	Sheet: 2 of 2
Date: Tuesday, August 25, 2015		

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Designer(s)") who are developing systems that incorporate TI products. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.

TI's provision of reference designs and any other technical, applications or design advice, quality characterization, reliability data or other information or services does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such reference designs or other items.

TI reserves the right to make corrections, enhancements, improvements and other changes to its reference designs and other items.

Designer understands and agrees that Designer remains responsible for using its independent analysis, evaluation and judgment in designing Designer's systems and products, and has full and exclusive responsibility to assure the safety of its products and compliance of its products (and of all TI products used in or for such Designer's products) with all applicable regulations, laws and other applicable requirements. Designer represents that, with respect to its applications, it has all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. Designer agrees that prior to using or distributing any systems that include TI products, Designer will thoroughly test such systems and the functionality of such TI products as used in such systems. Designer may not use any TI products in life-critical medical equipment unless authorized officers of the parties have executed a special contract specifically governing such use. Life-critical medical equipment is medical equipment where failure of such equipment would cause serious bodily injury or death (e.g., life support, pacemakers, defibrillators, heart pumps, neurostimulators, and implantables). Such equipment includes, without limitation, all medical devices identified by the U.S. Food and Drug Administration as Class III devices and equivalent classifications outside the U.S.

Designers are authorized to use, copy and modify any individual TI reference design only in connection with the development of end products that include the TI product(s) identified in that reference design. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of the reference design or other items described above may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS AND OTHER ITEMS DESCRIBED ABOVE ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY DESIGNERS AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS AS DESCRIBED IN A TI REFERENCE DESIGN OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

TI's standard terms of sale for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>) apply to the sale of packaged integrated circuit products. Additional terms may apply to the use or sale of other types of TI products and services.

Designer will fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of Designer's non-compliance with the terms and provisions of this Notice.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2016, Texas Instruments Incorporated