


TAPE AND REEL INFORMATION

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE


*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-----------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| ISO7760FQDBQRQ1 | SSOP | DBQ | 16 | 2500 | 330.0 | 12.4 | 6.4 | 5.2 | 2.1 | 8.0 | 12.0 | Q1 |
| ISO7760FQDWRQ1 | SOIC | DW | 16 | 2000 | 330.0 | 16.4 | 10.75 | 10.7 | 2.7 | 12.0 | 16.0 | Q1 |
| ISO7760QDBQRQ1 | SSOP | DBQ | 16 | 2500 | 330.0 | 12.4 | 6.4 | 5.2 | 2.1 | 8.0 | 12.0 | Q1 |
| ISO7760QDWRQ1 | SOIC | DW | 16 | 2000 | 330.0 | 16.4 | 10.75 | 10.7 | 2.7 | 12.0 | 16.0 | Q1 |
| ISO7761FQDBQRQ1 | SSOP | DBQ | 16 | 2500 | 330.0 | 12.4 | 6.4 | 5.2 | 2.1 | 8.0 | 12.0 | Q1 |
| ISO7761FQDWRQ1 | SOIC | DW | 16 | 2000 | 330.0 | 16.4 | 10.75 | 10.7 | 2.7 | 12.0 | 16.0 | Q1 |
| ISO7761QDBQRQ1 | SSOP | DBQ | 16 | 2500 | 330.0 | 12.4 | 6.4 | 5.2 | 2.1 | 8.0 | 12.0 | Q1 |
| ISO7761QDWRQ1 | SOIC | DW | 16 | 2000 | 330.0 | 16.4 | 10.75 | 10.7 | 2.7 | 12.0 | 16.0 | Q1 |
| ISO7762FQDBQRQ1 | SSOP | DBQ | 16 | 2500 | 330.0 | 12.4 | 6.4 | 5.2 | 2.1 | 8.0 | 12.0 | Q1 |
| ISO7762FQDWRQ1 | SOIC | DW | 16 | 2000 | 330.0 | 16.4 | 10.75 | 10.7 | 2.7 | 12.0 | 16.0 | Q1 |
| ISO7762QDBQRQ1 | SSOP | DBQ | 16 | 2500 | 330.0 | 12.4 | 6.4 | 5.2 | 2.1 | 8.0 | 12.0 | Q1 |
| ISO7762QDWRQ1 | SOIC | DW | 16 | 2000 | 330.0 | 16.4 | 10.75 | 10.7 | 2.7 | 12.0 | 16.0 | Q1 |
| ISO7763FQDBQRQ1 | SSOP | DBQ | 16 | 2500 | 330.0 | 12.4 | 6.4 | 5.2 | 2.1 | 8.0 | 12.0 | Q1 |
| ISO7763FQDWRQ1 | SOIC | DW | 16 | 2000 | 330.0 | 16.4 | 10.75 | 10.7 | 2.7 | 12.0 | 16.0 | Q1 |
| ISO7763QDBQRQ1 | SSOP | DBQ | 16 | 2500 | 330.0 | 12.4 | 6.4 | 5.2 | 2.1 | 8.0 | 12.0 | Q1 |
| ISO7763QDWRQ1 | SOIC | DW | 16 | 2000 | 330.0 | 16.4 | 10.75 | 10.7 | 2.7 | 12.0 | 16.0 | Q1 |

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|-----------------|--------------|-----------------|------|------|-------------|------------|-------------|
| ISO7760FQDBQRQ1 | SSOP | DBQ | 16 | 2500 | 350.0 | 350.0 | 43.0 |
| ISO7760FQDWRQ1 | SOIC | DW | 16 | 2000 | 350.0 | 350.0 | 43.0 |
| ISO7760QDBQRQ1 | SSOP | DBQ | 16 | 2500 | 367.0 | 367.0 | 38.0 |
| ISO7760QDWRQ1 | SOIC | DW | 16 | 2000 | 350.0 | 350.0 | 43.0 |
| ISO7761FQDBQRQ1 | SSOP | DBQ | 16 | 2500 | 367.0 | 367.0 | 38.0 |
| ISO7761FQDWRQ1 | SOIC | DW | 16 | 2000 | 350.0 | 350.0 | 43.0 |
| ISO7761QDBQRQ1 | SSOP | DBQ | 16 | 2500 | 367.0 | 367.0 | 38.0 |
| ISO7761QDWRQ1 | SOIC | DW | 16 | 2000 | 350.0 | 350.0 | 43.0 |
| ISO7762FQDBQRQ1 | SSOP | DBQ | 16 | 2500 | 367.0 | 367.0 | 38.0 |
| ISO7762FQDWRQ1 | SOIC | DW | 16 | 2000 | 350.0 | 350.0 | 43.0 |
| ISO7762QDBQRQ1 | SSOP | DBQ | 16 | 2500 | 367.0 | 367.0 | 38.0 |
| ISO7762QDWRQ1 | SOIC | DW | 16 | 2000 | 350.0 | 350.0 | 43.0 |
| ISO7763FQDBQRQ1 | SSOP | DBQ | 16 | 2500 | 350.0 | 350.0 | 43.0 |
| ISO7763FQDWRQ1 | SOIC | DW | 16 | 2000 | 350.0 | 350.0 | 43.0 |
| ISO7763QDBQRQ1 | SSOP | DBQ | 16 | 2500 | 367.0 | 367.0 | 38.0 |
| ISO7763QDWRQ1 | SOIC | DW | 16 | 2000 | 350.0 | 350.0 | 43.0 |

TUBE


*All dimensions are nominal

| Device | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (μm) | B (mm) |
|----------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| ISO7760FQDBQQ1 | DBQ | SSOP | 16 | 75 | 505.46 | 6.76 | 3810 | 4 |
| ISO7760FQDWQ1 | DW | SOIC | 16 | 40 | 506.98 | 12.7 | 4826 | 6.6 |
| ISO7760QDBQQ1 | DBQ | SSOP | 16 | 75 | 505.46 | 6.76 | 3810 | 4 |
| ISO7760QDWQ1 | DW | SOIC | 16 | 40 | 506.98 | 12.7 | 4826 | 6.6 |
| ISO7761FQDBQQ1 | DBQ | SSOP | 16 | 75 | 505.46 | 6.76 | 3810 | 4 |
| ISO7761FQDWQ1 | DW | SOIC | 16 | 40 | 506.98 | 12.7 | 4826 | 6.6 |
| ISO7761QDBQQ1 | DBQ | SSOP | 16 | 75 | 505.46 | 6.76 | 3810 | 4 |
| ISO7761QDWQ1 | DW | SOIC | 16 | 40 | 506.98 | 12.7 | 4826 | 6.6 |
| ISO7762FQDBQQ1 | DBQ | SSOP | 16 | 75 | 505.46 | 6.76 | 3810 | 4 |
| ISO7762FQDWQ1 | DW | SOIC | 16 | 40 | 506.98 | 12.7 | 4826 | 6.6 |
| ISO7762QDBQQ1 | DBQ | SSOP | 16 | 75 | 505.46 | 6.76 | 3810 | 4 |
| ISO7762QDWQ1 | DW | SOIC | 16 | 40 | 506.98 | 12.7 | 4826 | 6.6 |
| ISO7763FQDBQQ1 | DBQ | SSOP | 16 | 75 | 505.46 | 6.76 | 3810 | 4 |
| ISO7763FQDWQ1 | DW | SOIC | 16 | 40 | 506.98 | 12.7 | 4826 | 6.6 |
| ISO7763QDBQQ1 | DBQ | SSOP | 16 | 75 | 505.46 | 6.76 | 3810 | 4 |
| ISO7763QDWQ1 | DW | SOIC | 16 | 40 | 506.98 | 12.7 | 4826 | 6.6 |