

MAX211 具有 ±15kV ESD 保护的 5V 多通道 RS-232 线路驱动器和接收器

1 特性

- 使用人体放电模型 (HBM) 时，RS-232 总线引脚 ESD 保护大于 ±15kV
- 符合或超出 TIA/EIA-232-F 和 ITU v.28 标准的要求
- 由 5V V_{CC} 电源供电
- 四个驱动器和五个接收器
- 速率高达 120kbit/s
- 关断模式下的低电源电流：5μA (典型值)
- 外部电容器：4 × 0.1μF
- 闩锁性能超过 100mA，符合 JESD 78 II 类规范的要求

2 应用

- 电池供电型系统
- PDA
- 笔记本电脑
- 便携式计算机
- 掌上电脑
- 手持设备

3 说明

MAX211 器件由四个线路驱动器、五个线路接收器和一个双电荷泵电路组成，具有引脚对引脚 (串行端口连接引脚，包括 GND) ±15kV ESD 保护。该器件符合 TIA/EIA-232-F 的要求并在异步通信控制器与串行端口连接器之间提供电气接口。电荷泵和四个小型外部电容器支持由单个 5V 电源供电。这些器件以高达 120kbit/s 的数据信号传输速率和最高 30V/μs 的驱动器输出压摆率运行。


MAX211 具有关断 (SHDN) 和使能控制 (\overline{EN}) 功能。在关断模式下，电荷泵会关闭，V+ 会下拉至 V_{CC}、V- 会下拉至 GND，且发送器输出被禁用。这通常会将电源电流降低至 1μA。EN 用于将接收器输出置于高阻抗状态，从而实现两个 RS-232 端口的有线 OR 连接。这对 RS-232 驱动器或电荷泵没有影响。

封装信息

器件型号	封装 ⁽¹⁾	封装尺寸 ⁽²⁾
MAX211	DB (SSOP , 28)	10.2mm × 7.8mm
	DW (SOIC , 28)	17.9mm × 10.3mm

(1) 有关更多信息，请参阅节 11。

(2) 封装尺寸 (长 × 宽) 为标称值，并包括引脚 (如适用)。



逻辑图 (正逻辑)

Table of Contents

1 特性	1	6 Parameter Measurement Information	8
2 应用	1	7 Device Functional Modes	11
3 说明	1	8 Application and Implementation	12
4 Pin Configuration and Functions	3	8.1 Application Information.....	12
5 Specifications	5	9 Device and Documentation Support	15
5.1 Absolute Maximum Ratings.....	5	9.1 接收文档更新通知.....	15
5.2 ESD Protection.....	5	9.2 支持资源.....	15
5.3 Recommended Operating Conditions.....	5	9.3 Trademarks.....	15
5.4 Thermal Information.....	6	9.4 静电放电警告.....	15
5.5 Electrical Characteristics.....	6	9.5 术语表.....	15
5.6 Electrical Characteristics, Driver.....	6	10 Revision History	15
5.7 Switching Characteristics, Driver.....	6	11 Mechanical, Packaging, and Orderable Information	15
5.8 Electrical Characteristics, Receiver.....	7		
5.9 Switching Characteristics, Receiver.....	7		

4 Pin Configuration and Functions




图 4-1. DB or DW Package (Top View)

表 4-1. Pin Functions

PIN		TYPE ⁽¹⁾	DESCRIPTION
NAME	DB or DW		
DOUT3	1	O	RS232 line data output (to remote RS232 system)
DOUT1	2	O	RS232 line data output (to remote RS232 system)
DOUT2	3	O	RS232 line data output (to remote RS232 system)
RIN2	4	I	RS232 line data input (from remote RS232 system)
ROUT2	5	O	Logic data output (to UART)
DIN2	6	I	Logic data input (from UART)
DIN1	7	I	Logic data input (from UART)
ROUT1	8	O	Logic data output (to UART)
RIN1	9	I	RS232 line data input (from remote RS232 system)
GND	10	-	Ground
V _{CC}	11	--	Supply Voltage, Connect to external 3V to 5.5V power supply
C1+	12	--	Positive lead of C1 capacitor
V+	13	O	Positive charge pump output for storage capacitor only
C1-	14	--	Negative lead of C1 capacitor
C2+	15	--	Positive lead of C2 capacitor
C2-	16	--	Negative lead of C2 capacitor
V-	17	O	Negative charge pump output for storage capacitor only
RIN5	18	I	RS232 line data input (from remote RS232 system)
ROUT5	19	O	Logic data output (to UART)
DIN3	20	I	Logic data input (from UART)
DIN4	21	I	Logic data input (from UART)
ROUT4	22	O	Logic data output (to UART)
RIN4	23	I	RS232 line data input (from remote RS232 system)
EN	24	--	Active low enable
SHDN	25	--	Active high shutdown
ROUT3	26	O	Logic data output (to UART)
RIN3	27	I	RS232 line data input (from remote RS232 system)
DOUT4	28	O	RS232 line data output (to remote RS232 system)

表 4-1. Pin Functions (续)

PIN		TYPE ⁽¹⁾	DESCRIPTION
NAME	DB or DW		
Thermal Pad	-	--	Exposed thermal pad. Can be connected to GND or left floating.

(1) Signal Types: I = Input, O = Output, I/O = Input or Output.

5 Specifications

5.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)⁽¹⁾

			MIN	MAX	UNIT
V _{CC} ⁽²⁾	Supply voltage range		-0.3	6	V
V ₊ ⁽²⁾	Positive charge pump voltage range		V _{CC} - 0.3	14	V
V ₋ ⁽²⁾	Negative charge pump voltage range		0.3	-14	V
V _I	Input voltage range	Drivers	-0.3	V ₊ + 0.3	V
		Receivers (DW package)		±30	V
		Receivers (DB package)		±25	V
V _O	Output voltage range	Drivers	V ₋ - 0.3V	V ₊ + 0.3	V
		Receivers	-0.3	V _{CC} + 0.3	V
	Short-circuit duration	DOUT	Continuous		
T _J	Operating virtual junction temperature			150	°C
T _{stg}	Storage temperature range		-65	150	°C

- (1) Stresses beyond those listed under “absolute maximum ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under “recommended operating conditions” is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) All voltages are with respect to network GND.

5.2 ESD Protection

PIN	TEST CONDITIONS	TYP	UNIT
D _{OUT} , R _{IN}	Human-Body Model	±15	kV

5.3 Recommended Operating Conditions

(see⁽¹⁾ and [图 6-4](#))

			MIN	NOM	MAX	UNIT
Supply voltage			1.5	5	5.5	V
V _{IH}	Driver high-level input voltage	DIN	2			V
	Control high-level input voltage	E _N , SHDN	2.4			V
V _{IL}	Driver and control low-level input voltage	DIN, E _N , SHDN			0.8	V
V _I	Driver and control input voltage	DIN, E _N , SHDN	0		5.5	V
	Receiver input voltage	DW Package	-30		30	V
		DB Package	-25		25	V
T _A	Operating free-air temperature	MAX211C	0		70	°C
		MAX211I	-40		85	°C

- (1) Test conditions are C1-C4 = 0.1μF at V_{CC} = 5V ± 0.5V.

5.4 Thermal Information

THERMAL METRIC ⁽¹⁾		DB	DW	UNIT
		28-PINS		
$R_{\theta JA}$	Junction-to-ambient thermal resistance	66.1	46	°C/W
$R_{\theta JC(top)}$	Junction-to-case (top) thermal resistance	33.2	33.5	°C/W
$R_{\theta JB}$	Junction-to-board thermal resistance	37.0	37.1	°C/W
ψ_{JT}	Junction-to-top characterization parameter	4.6	7.5	°C/W
ψ_{JB}	Junction-to-board characterization parameter	36.5	37.1	°C/W
$R_{\theta JC(bot)}$	Junction-to-case (bottom) thermal resistance	n/a	n/a	°C/W

(1) For more information about traditional and new thermal metrics, see the [Semiconductor and IC package thermal metrics](#) application report.

5.5 Electrical Characteristics

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see ⁽²⁾)

PARAMETER		TEST CONDITIONS		MIN	TYP ⁽¹⁾	MAX	UNIT
I_{CC}	Supply current	No load,	See 图 8-1		14	20	mA
	Shutdown supply current (DB package)	$T_A = 25^\circ\text{C}$	See 图 6-1		5	10	μA
	Shutdown supply current (DW package)	$T_A = 25^\circ\text{C}$	See 图 6-1		1	20	μA

(1) All typical values are at $V_{CC} = 5\text{V}$, and $T_A = 25^\circ\text{C}$.

(2) Test conditions are $C1-C4 = 0.1\mu\text{F}$ at $V_{CC} = 5\text{V} \pm 0.5\text{V}$.

5.6 Electrical Characteristics, Driver

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see ⁽³⁾ and [图 6-4](#))

PARAMETER		TEST CONDITIONS		MIN	TYP ⁽¹⁾	MAX	UNIT
V_{OH}	High-level output voltage	DOUT at $R_L = 3\text{k}\Omega$ to GND		5	9		V
V_{OL}	Low-level output voltage	DOUT at $R_L = 3\text{k}\Omega$ to GND		-5	-9		V
I_{IH}	Driver high-level input current	$DIN = V_{CC}$			15	200	μA
	Control high-level input current	$\overline{EN}, \text{SHDN} = V_{CC}$			3	10	
I_{IL}	Driver low-level input current	$DIN = 0\text{V}$			-15	-200	μA
	Control low-level input current	$\overline{EN}, \text{SHDN} = 0\text{V}$			-3	-10	
I_{OS} ⁽²⁾	Short-circuit output current	$V_{CC} = 5.5\text{V}$,	$V_O = 0\text{V}$		± 10	± 60	mA
r_o	Output resistance	$V_{CC}, V+, \text{ and } V- = 0\text{V}$,	$V_O = \pm 2\text{V}$	300			Ω

(1) All typical values are at $V_{CC} = 5\text{V}$, and $T_A = 25^\circ\text{C}$.

(2) Short-circuit durations should be controlled to prevent exceeding the device absolute power dissipation ratings, and not more than one output should be shorted at a time.

(3) Test conditions are $C1-C4 = 0.1\mu\text{F}$ at $V_{CC} = 5\text{V} \pm 0.5\text{V}$.

5.7 Switching Characteristics, Driver

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see ⁽³⁾)

PARAMETER		TEST CONDITIONS		MIN	TYP ⁽¹⁾	MAX	UNIT
	Maximum data rate	$C_L = 50\text{pF}$ to 1000pF , One DOUT switching,	$R_L = 3\text{k}\Omega$ to $7\text{k}\Omega$, See 图 6-2	120			kbit/s
$t_{PLH(D)}$	Propagation delay time, low- to high-level output	$C_L = 2500\text{pF}$, All drivers loaded,	$R_L = 3\text{k}\Omega$, See 图 6-2		2		μs
$t_{PHL(D)}$	Propagation delay time, high- to low-level output	$C_L = 2500\text{pF}$, All drivers loaded,	$R_L = 3\text{k}\Omega$, See 图 6-2		2		μs

5.7 Switching Characteristics, Driver (续)

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see ⁽³⁾)

PARAMETER		TEST CONDITIONS	MIN	TYP ⁽¹⁾	MAX	UNIT
$t_{sk(p)}$	Pulse skew ⁽²⁾	$C_L = 150\text{pF}$ to 2500pF , $R_L = 3\text{k}\Omega$ to $7\text{k}\Omega$, See 图 6-3		300		ns
SR(tr)	Slew rate, transition region (see 图 6-2)	$C_L = 50\text{pF}$ to 1000pF , $V_{CC} = 5\text{V}$, $R_L = 3\text{k}\Omega$ to $7\text{k}\Omega$,	3	6	30	V/ μ s

- (1) All typical values are at $V_{CC} = 5\text{V}$, and $T_A = 25^\circ\text{C}$.
- (2) Pulse skew is defined as $|t_{PLH} - t_{PHL}|$ of each channel of the same device.
- (3) Test conditions are C1-C4 = $0.1\mu\text{F}$ at $V_{CC} = 5\text{V} \pm 0.5\text{V}$.

5.8 Electrical Characteristics, Receiver

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see ⁽²⁾ and 图 8-1)

PARAMETER		TEST CONDITIONS	MIN	TYP ⁽¹⁾	MAX	UNIT
V_{OH}	High-level output voltage	$I_{OH} = -1\text{mA}$	3.5	$V_{CC}-0.$	4 V	V
V_{OL}	Low-level output voltage	$I_{OL} = 1.6\text{mA}$			0.4	V
V_{IT+}	Positive-going input threshold voltage	$V_{CC} = 5\text{V}$, $T_A = 25^\circ\text{C}$		1.7	2.4	V
V_{IT-}	Negative-going input threshold voltage	$V_{CC} = 5\text{V}$, $T_A = 25^\circ\text{C}$	0.8	1.2		V
V_{hys}	Input hysteresis ($V_{IT+} - V_{IT-}$)		0.2	0.5	1	V
r_i	Input resistance	$V_{CC} = 5\text{V}$, $T_A = 25^\circ\text{C}$	3	5	7	$\text{k}\Omega$
	Output leakage current	$\overline{EN} = V_{CC}$, $0 \leq R_{OUT} \leq V_{CC}$		± 0.05	± 10	μA

- (1) All typical values are at $V_{CC} = 5\text{V}$, and $T_A = 25^\circ\text{C}$.
- (2) Test conditions are C1-C4 = $0.1\mu\text{F}$ at $V_{CC} = 5\text{V} \pm 0.5\text{V}$.

5.9 Switching Characteristics, Receiver

over recommended ranges of supply voltage and operating free-air temperature (unless otherwise noted) (see ⁽³⁾)

PARAMETER		TEST CONDITIONS	MIN	TYP ⁽¹⁾	MAX	UNIT
$t_{PLH(R)}$	Propagation delay time, low- to high-level output	$C_L = 150\text{pF}$, See 图 6-4		0.5	10	μs
$t_{PHL(R)}$	Propagation delay time, high- to low-level output	$C_L = 150\text{pF}$, See 图 6-4		0.5	10	μs
t_{en}	Output enable time	$C_L = 150\text{pF}$, See 图 6-5, $R_L = 1\text{k}\Omega$,		600		ns
t_{dis}	Output disable time	$C_L = 150\text{pF}$, See 图 6-5, $R_L = 1\text{k}\Omega$,		200		ns
$t_{sk(p)}$	Pulse skew ⁽²⁾	See 图 6-3		300		ns

- (1) All typical values are at $V_{CC} = 5\text{V}$, and $T_A = 25^\circ\text{C}$.
- (2) Pulse skew is defined as $|t_{PLH} - t_{PHL}|$ of each channel of the same device.
- (3) Test conditions are C1-C4 = $0.1\mu\text{F}$, at $V_{CC} = 5\text{V} \pm 0.5\text{V}$.

6 Parameter Measurement Information






图 6-1. Shutdown Current Test Circuit



A. C_L includes probe and jig capacitance.

B. The pulse generator has the following characteristics: PRR = 120kbit/s, $Z_O = 50\Omega$, 50% duty cycle, $t_r \leq 10\text{ns}$, $t_f \leq 10\text{ns}$.


图 6-2. Driver Slew Rate and Propagation Delay Times



A. C_L includes probe and jig capacitance.

B. The pulse generator has the following characteristics: PRR = 120kbit/s, $Z_O = 50\Omega$, 50% duty cycle, $t_r \leq 10\text{ns}$, $t_f \leq 10\text{ns}$.


图 6-3. Driver Pulse Skew



A. C_L includes probe and jig capacitance.

B. The pulse generator has the following characteristics: $Z_O = 50\Omega$, 50% duty cycle, $t_r \leq 10\text{ns}$, $t_f \leq 10\text{ns}$.

图 6-4. Receiver Propagation Delay Times



A. C_L includes probe and jig capacitance.

B. The pulse generator has the following characteristics: $Z_O = 50\Omega$, 50% duty cycle, $t_r \leq 10\text{ns}$, $t_f \leq 10\text{ns}$.

C. t_{PLZ} and t_{PHZ} are the same as t_{dis} .

D. t_{pZL} and t_{pZH} are the same as t_{en} .

 **6-5. Receiver Enable and Disable Times**

7 Device Functional Modes

表 7-1. Function Table

INPUTS ⁽¹⁾		DRIVER	RECEIVER	DEVICE STATUS
SHDN	EN			
L	L	All active	All active	Normal operation
L	H	All active	Z	Normal operation
H	X	Z	Z	Shutdown

(1) X = don't care, Z = high impedance

表 7-2. Function Table Each Driver

INPUTS ⁽¹⁾		OUTPUT DOUT	DRIVER STATUS
DIN	SHDN		
L	L	H	Normal operation
H	L	L	
X	H	Z	Powered off

(1) X = don't care, Z = high impedance

表 7-3. Function Table Each Receiver

INPUTS ⁽¹⁾		OUTPUT ROUT	RECEIVER STATUS
RIN	EN		
L	L	H	Normal operation
H	L	L	
X	H	Z	Powered off


(1) X = don't care, Z = high impedance

8 Application and Implementation

备注

以下应用部分中的信息不属于 TI 器件规格的范围，TI 不担保其准确性和完整性。TI 的客户应负责确定器件是否适用于其应用。客户应验证并测试其设计，以确保系统功能。

8.1 Application Information



备注

C3 can be connected to V_{CC} or GND.

- Resistor values shown are nominal.
- Nonpolarized ceramic capacitors are acceptable. If polarized tantalum or electrolytic capacitors are used, connect the capacitors as shown.

图 8-1. Typical Operating Circuit and Capacitor Values

8.1.1 Capacitor Selection

The capacitor type used for C1–C4 is not critical for proper operation. The MAX211 requires 0.1 μ F capacitors, although capacitors up to 10 μ F can be used without harm. Ceramic dielectrics are suggested for the 0.1 μ F capacitors. When using the minimum recommended capacitor values, make sure the capacitance value does not degrade excessively as the operating temperature varies. If in doubt, use capacitors with a larger (2 \times) nominal value. The capacitors' effective series resistance (ESR), which usually rises at low temperatures, influences the amount of ripple on V+ and V–.

Use larger capacitors (up to 10 μ F) to reduce the output impedance at V+ and V–.

Bypass V_{CC} to ground with at least 0.1 μ F. In applications sensitive to power-supply noise generated by the charge pumps, decouple V_{CC} to ground with a capacitor the same size as (or larger than) the charge-pump capacitors (C1–C4).

8.1.2 Electrostatic Discharge (ESD) Protection

Texas Instruments MAX211 devices have standard ESD protection structures incorporated on the pins to protect against electrostatic discharges encountered during assembly and handling. In addition, the RS232 bus pins (driver outputs and receiver inputs) of these devices have an extra level of ESD protection. Advanced ESD structures were designed to successfully protect these bus pins against ESD discharge of ± 15 kV when powered down.

8.1.3 ESD Test Conditions

ESD testing is stringently performed by TI, based on various conditions and procedures. Please contact TI for a reliability report that documents test setup, methodology, and results.

8.1.4 Human-Body Model

The Human-Body Model (HBM) of ESD testing is shown in 图 8-2. 图 8-3 shows the current waveform that is generated during a discharge into a low impedance. The model consists of a 100pF capacitor charged to the ESD voltage of concern and subsequently discharged into the DUT through a 1.5k Ω resistor.




图 8-2. HBM ESD Test Circuit




图 8-3. Typical HBM Current Waveform

8.1.5 Machine Model

The Machine Model (MM) ESD test applies to all pins, using a 200pF capacitor with no discharge resistance. The purpose of the MM test is to simulate possible ESD conditions that can occur during the handling and assembly processes of manufacturing. In this case, ESD protection is required for all pins, not just RS-232 pins. However, after PC board assembly, the MM test no longer is as pertinent to the RS-232 pins.

9 Device and Documentation Support

TI offers an extensive line of development tools. Tools and software to evaluate the performance of the device, generate code, and develop solutions are listed below.

9.1 接收文档更新通知

要接收文档更新通知，请导航至 ti.com 上的器件产品文件夹。点击 [通知](#) 进行注册，即可每周接收产品信息更改摘要。有关更改的详细信息，请查看任何已修订文档中包含的修订历史记录。

9.2 支持资源

[TI E2E™ 中文支持论坛](#) 是工程师的重要参考资料，可直接从专家处获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题，获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的 [使用条款](#)。

9.3 Trademarks

TI E2E™ is a trademark of Texas Instruments.
所有商标均为其各自所有者的财产。

9.4 静电放电警告



静电放电 (ESD) 会损坏这个集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理和安装程序，可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级，大至整个器件故障。精密的集成电路可能更容易受到损坏，这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

9.5 术语表

[TI 术语表](#) 本术语表列出并解释了术语、首字母缩略词和定义。

10 Revision History

注：以前版本的页码可能与当前版本的页码不同

Changes from Revision E (January 2004) to Revision F (July 2024)	Page
• 通篇更改了表格、图和交叉参考的编号格式.....	1
• Changed the Input voltage range for Receivers from $\pm 30V$ to $\pm 25V$ for the DB package in the <i>Absolute Maximum Ratings</i> and the <i>Recommended Operating Conditions</i>	5
• Changed the Shutdown supply current for DB package TYP value from $1\mu A$ to $5\mu A$ <i>Electrical Characteristics</i>	6

11 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
MAX211CDBR	OBSOLETE	SSOP	DB	28		TBD	Call TI	Call TI	0 to 70	MAX211C	
MAX211CDW	OBSOLETE	SOIC	DW	28		TBD	Call TI	Call TI	0 to 70	MAX211C	
MAX211CDWR	ACTIVE	SOIC	DW	28	1000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	0 to 70	MAX211C	Samples
MAX211IDB	OBSOLETE	SSOP	DB	28		TBD	Call TI	Call TI	-40 to 85	MAX211I	
MAX211IDBR	ACTIVE	SSOP	DB	28	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	MAX211I	Samples
MAX211IDBRG4	ACTIVE	SSOP	DB	28	2000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	MAX211I	Samples
MAX211IDW	OBSOLETE	SOIC	DW	28		TBD	Call TI	Call TI	-40 to 85	MAX211I	
MAX211IDWR	ACTIVE	SOIC	DW	28	1000	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	MAX211I	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "-" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TAPE AND REEL INFORMATION

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE


*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
MAX211CDWR	SOIC	DW	28	1000	330.0	32.4	11.35	18.67	3.1	16.0	32.0	Q1
MAX211IDBR	SSOP	DB	28	2000	330.0	16.4	8.2	10.5	2.5	12.0	16.0	Q1
MAX211IDWR	SOIC	DW	28	1000	330.0	32.4	11.35	18.67	3.1	16.0	32.0	Q1

TAPE AND REEL BOX DIMENSIONS




*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
MAX211CDWR	SOIC	DW	28	1000	350.0	350.0	66.0
MAX211IDBR	SSOP	DB	28	2000	356.0	356.0	35.0
MAX211IDWR	SOIC	DW	28	1000	350.0	350.0	66.0

DW (R-PDSO-G28)

PLASTIC SMALL OUTLINE



4040000-6/G 01/11

- NOTES:
- All linear dimensions are in inches (millimeters). Dimensioning and tolerancing per ASME Y14.5M-1994.
 - This drawing is subject to change without notice.
 - Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).
 - Falls within JEDEC MS-013 variation AE.


DB0028A



PACKAGE OUTLINE

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



4214853/B 03/2018

NOTES:


1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
5. Reference JEDEC registration MO-150.

EXAMPLE BOARD LAYOUT


DB0028A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE: 10X



4214853/B 03/2018

NOTES: (continued)


- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

DB0028A

SSOP - 2 mm max height

SMALL OUTLINE PACKAGE



NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

重要声明和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的应用。严禁对这些资源进行其他复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，TI 对此概不负责。

TI 提供的产品受 [TI 的销售条款](#) 或 [ti.com](#) 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265

Copyright © 2024，德州仪器 (TI) 公司