SDAS187A - APRIL 1982 - REVISED DECEMBER 1994

 Package Options Include Plastic Small-Outline (D) Packages, Ceramic Chip Carriers (FK), and Standard Plastic (N) and Ceramic (J) 300-mil DIPs

description


These devices contain four independent 2-input positive-NAND gates. They perform the Boolean functions $Y = \overline{A} \cdot \overline{B}$ or $Y = \overline{A} + \overline{B}$ in positive logic.

The SN54ALS00A and SN54AS00 are characterized for operation over the full military temperature range of -55°C to 125°C. The SN74ALS00A and SN74AS00 are characterized for operation from 0°C to 70°C.

FUNCTION TABLE (each gate)

| INP | UTS | OUTPUT |
|-----|-----|--------|
| Α | В | Υ |
| Н | Н | L |
| L | X | Н |
| Х | L | Н |


logic symbol†




[†] This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

Pin numbers shown are for the D, J, and N packages.

SN54ALS00A, SN54AS00 . . . J PACKAGE SN74ALS00A, SN74AS00 . . . D OR N PACKAGE (TOP VIEW)



SN54ALS00A, SN54AS00 . . . FK PACKAGE (TOP VIEW)




NC - No internal connection

SN54ALS00A, SN54AS00, SN74ALS00A, SN74AS00 QUADRUPLE 2-INPUT POSITIVE-NAND GATES

SDAS187A - APRIL 1982 - REVISED DECEMBER 1994

logic diagram (positive logic)



Pin numbers shown are for the D, J, and N packages.

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)

| Supply voltage, V _{CC} | 7 V |
|---|---------------|
| Input voltage, V _I | 7 V |
| Operating free-air temperature range, T _A : SN54ALS00A | 55°C to 125°C |
| SN74ALS00A | 0°C to 70°C |
| Storage temperature range | 65°C to 150°C |

[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

recommended operating conditions

| | | SN | 54ALS0 | 0A | SN | 74ALS0 | 0A | |
|-----------------|--------------------------------|-----|--------|------|-----|--------|------|------|
| | | MIN | NOM | MAX | MIN | NOM | MAX | UNIT |
| VCC | Supply voltage | 4.5 | 5 | 5.5 | 4.5 | 5 | 5.5 | V |
| ٧ _{IH} | High-level input voltage | 2 | | | 2 | | | V |
| ,, | | | | 0.8‡ | | | 0.8 | |
| VIL | Low-level input voltage | | | 0.7§ | | | | V |
| IOH | High-level output current | | | -0.4 | | | -0.4 | mA |
| lOL | Low-level output current | | | 4 | | | 8 | mA |
| TA | Operating free-air temperature | -55 | | 125 | 0 | | 70 | °C |

[‡] Applies over temperature range -55°C to 70°C

[§] Applies over temperature range 70°C to 125°C

SN54ALS00A, SN54AS00, SN74ALS00A, SN74AS00 QUADRUPLE 2-INPUT POSITIVE-NAND GATES

SDAS187A - APRIL 1982 - REVISED DECEMBER 1994

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| | | TEST CONDITIONS | | | | | 74ALS00 | 0A | |
|-----------------|---|----------------------------|-------|------------------|------|--------------------|---------|------|------|
| PARAMETER | TEST C | ONDITIONS | MIN | TYP [†] | MAX | MIN | TYP† | MAX | UNIT |
| VIK | V _{CC} = 4.5 V, | I _I = -18 mA | | | -1.2 | | | -1.5 | V |
| V _{OH} | $V_{CC} = 4.5 \text{ V to } 5.5 \text{ V},$ | $I_{OH} = -0.4 \text{ mA}$ | Vcc - | 2 | | V _{CC} -2 | 2 | | V |
| V | 45.7 | $I_{OL} = 4 \text{ mA}$ | | 0.25 | 0.4 | | 0.25 | 0.4 | V |
| V _{OL} | V _{CC} = 4.5 V | $I_{OL} = 8 \text{ mA}$ | | | | | 0.35 | 0.5 | V |
| lį | V _{CC} = 5.5 V, | V _I = 7 V | | | 0.1 | | | 0.1 | mA |
| lіН | $V_{CC} = 5.5 \text{ V},$ | V _I = 2.7 V | | | 20 | | | 20 | μΑ |
| I _{IL} | $V_{CC} = 5.5 \text{ V},$ | V _I = 0.4 V | | | -0.1 | | | -0.1 | mA |
| IO [‡] | V _{CC} = 5.5 V, | V _O = 2.25 V | -20 | | -112 | -30 | | -112 | mA |
| Іссн | V _{CC} = 5.5 V, | V _I = 0 | | 0.5 | 0.85 | | 0.5 | 0.85 | mA |
| ICCL | V _{CC} = 5.5 V, | V _I = 4.5 V | | 1.5 | 3 | | 1.5 | 3 | mA |

 $[\]uparrow$ All typical values are at V_{CC} = 5 V, T_A = 25°C.

switching characteristics (see Figure 1)

| PARAMETER | FROM (INPUT) | TO (OUTPUT) | C _L R _L T _A | = 50 pF = 500 £ = MIN t | o MAX§ | | UNIT |
|------------------|-----------------|----------------|--|-------------------------------|---------------|-----|------|
| | | | SN54AI MIN | MAX | SN74AI MIN | MAX | |
| t _{PLH} | A = = D | V | 3 | 15 | 3 | 11 | |
| t _{PHL} | A or B | Y | 2 | 9 | 2 | 8 | ns |

[§] For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

[‡] The output conditions have been chosen to produce a current that closely approximates one half of the true short-circuit output current, IOS.

SN54ALS00A, SN54AS00, SN74ALS00A, SN74AS00 QUADRUPLE 2-INPUT POSITIVE-NAND GATES

SDAS187A - APRIL 1982 - REVISED DECEMBER 1994

absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

| Supply voltage, V _{CC} | | 7 V |
|--|----------|-----------------|
| Input voltage, V _I | | 7 V |
| Operating free-air temperature range, T _A : | | |
| , , , , , , , , , , , , , , , , , , , | SN74AS00 | 0°C to 70°C |
| Storage temperature range | | 65°C to 150°C |

recommended operating conditions

| | | S | N54AS0 | 0 | S | 0 | LINUT | |
|----------------|--------------------------------|-----|--------|-----|-----|-----|-------|------|
| | | MIN | NOM | MAX | MIN | NOM | MAX | UNIT |
| Vcc | Supply voltage | 4.5 | 5 | 5.5 | 4.5 | 5 | 5.5 | V |
| VIH | High-level input voltage | 2 | | | 2 | | | V |
| VIL | Low-level input voltage | | | 8.0 | | | 8.0 | V |
| IOH | High-level output current | | | -2 | | | -2 | mA |
| lOL | Low-level output current | | | 20 | | | 20 | mA |
| T _A | Operating free-air temperature | -55 | | 125 | 0 | | 70 | °C |

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| | | TEST CONDITIONS | | | | S | N74AS0 | 0 | LINUT |
|-----------------|---|--------------------------|-------|------|------|--------|--------|------|-------|
| PARAMETER | TEST C | ONDITIONS | MIN | TYP‡ | MAX | MIN | TYP‡ | MAX | UNIT |
| VIK | $V_{CC} = 4.5 \text{ V},$ | I _I = -18 mA | | | -1.2 | | | -1.2 | V |
| Voн | $V_{CC} = 4.5 \text{ V to } 5.5 \text{ V},$ | $I_{OH} = -2 \text{ mA}$ | VCC - | 2 | | VCC -2 |) | | V |
| V _{OL} | $V_{CC} = 4.5 V,$ | $I_{OL} = 20 \text{ mA}$ | | 0.35 | 0.5 | | 0.35 | 0.5 | V |
| lį | $V_{CC} = 5.5 V,$ | V _I = 7 V | | | 0.1 | | | 0.1 | mA |
| lіН | $V_{CC} = 5.5 V,$ | V _I = 2.7 V | | | 20 | | | 20 | μΑ |
| I _{IL} | $V_{CC} = 5.5 V,$ | $V_{ } = 0.4 V$ | | | -0.5 | | | -0.5 | mA |
| ΙΟ [§] | $V_{CC} = 5.5 \text{ V},$ | V _O = 2.25 V | -30 | | -112 | -30 | | -112 | mA |
| Іссн | $V_{CC} = 5.5 V,$ | V _I = 0 | | 2 | 3.2 | | 2 | 3.2 | mA |
| ICCL | V _{CC} = 5.5 V, | V _I = 4.5 V | | 10.8 | 17.4 | | 10.8 | 17.4 | mA |

[‡] All typical values are at $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$.

switching characteristics (see Figure 1)

| PARAMETER | FROM (INPUT) | TO (OUTPUT) | C _L R _L | = 50 pF = 500 Ω = MIN t | | | UNIT |
|------------------|-----------------|----------------|----------------------------------|-------------------------------|---|-----|------|
| ^t PLH | A or B | ~ | 1 | 5 | 1 | 4.5 | no |
| t _{PHL} | AUID | T | 1 | 5 | 1 | 4 | ns |


 $[\]P$ For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.



[†] Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

[§] The output conditions have been chosen to produce a current that closely approximates one half of the true short-circuit output current, IOS.

PARAMETER MEASUREMENT INFORMATION SERIES 54ALS/74ALS AND 54AS/74AS DEVICES



NOTES: A. C_L includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. When measuring propagation delay items of 3-state outputs, switch S1 is open.
- D. All input pulses have the following characteristics: PRR \leq 1 MHz, $t_{\Gamma} = t_{f} = 2$ ns, duty cycle = 50%.
- E. The outputs are measured one at a time with one transition per measurement.

Figure 1. Load Circuits and Voltage Waveforms





27-Sep-2024



www.ti.com

PACKAGING INFORMATION

| Orderable Device | Status | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead finish/ Ball material | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|----------|--------------|--------------------|------|----------------|---------------------|-------------------------------|--------------------|--------------|---|---------|
| 5962-86833012A | ACTIVE | LCCC | FK | 20 | 55 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962- 86833012A SNJ54ALS 00AFK | Samples |
| 5962-8683301DA | ACTIVE | CFP | W | 14 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962-8683301DA SNJ54ALS00AW | Samples |
| JM38510/37001B2A | ACTIVE | LCCC | FK | 20 | 55 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 37001B2A | Samples |
| JM38510/37001BCA | ACTIVE | CDIP | J | 14 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 37001BCA | Samples |
| M38510/37001B2A | ACTIVE | LCCC | FK | 20 | 55 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 37001B2A | Samples |
| M38510/37001BCA | ACTIVE | CDIP | J | 14 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | JM38510/ 37001BCA | Samples |
| SN54ALS00AJ | ACTIVE | CDIP | J | 14 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | SN54ALS00AJ | Samples |
| SN54AS00J | ACTIVE | CDIP | J | 14 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | SN54AS00J | Samples |
| SN74ALS00AD | OBSOLETE | SOIC | D | 14 | | TBD | Call TI | Call TI | 0 to 70 | ALS00A | |
| SN74ALS00ADBR | ACTIVE | SSOP | DB | 14 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | 0 to 70 | G00A | Samples |
| SN74ALS00ADR | ACTIVE | SOIC | D | 14 | 2500 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | 0 to 70 | ALS00A | Samples |
| SN74ALS00AN | ACTIVE | PDIP | N | 14 | 25 | RoHS & Green | NIPDAU | N / A for Pkg Type | 0 to 70 | SN74ALS00AN | Samples |
| SN74ALS00ANSR | ACTIVE | SO | NS | 14 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | 0 to 70 | ALS00A | Samples |
| SN74AS00D | OBSOLETE | SOIC | D | 14 | | TBD | Call TI | Call TI | 0 to 70 | AS00 | |
| SN74AS00DR | ACTIVE | SOIC | D | 14 | 2500 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | 0 to 70 | AS00 | Samples |
| SN74AS00N | ACTIVE | PDIP | N | 14 | 25 | RoHS & Green | NIPDAU | N / A for Pkg Type | 0 to 70 | SN74AS00N | Samples |
| SN74AS00NSR | ACTIVE | SO | NS | 14 | 2000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | 0 to 70 | 74AS00 | Samples |
| SNJ54ALS00AFK | ACTIVE | LCCC | FK | 20 | 55 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962- 86833012A | Samples |

www.ti.com 27-Sep-2024

| Orderable Device | Status | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead finish/ Ball material | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|--------|--------------|--------------------|------|----------------|---------------------|-------------------------------|--------------------|--------------|--------------------------------|---------|
| | | | | | | | (0) | | | SNJ54ALS 00AFK | |
| SNJ54ALS00AJ | ACTIVE | CDIP | J | 14 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | SNJ54ALS00AJ | Samples |
| SNJ54ALS00AW | ACTIVE | CFP | W | 14 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | 5962-8683301DA SNJ54ALS00AW | Samples |
| SNJ54AS00J | ACTIVE | CDIP | J | 14 | 25 | Non-RoHS & Green | SNPB | N / A for Pkg Type | -55 to 125 | SNJ54AS00J | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

PACKAGE OPTION ADDENDUM

www.ti.com 27-Sep-2024

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF SN54ALS00A, SN54AS00, SN74ALS00A, SN74AS00:

• Catalog : SN74ALS00A, SN74AS00

• Military : SN54ALS00A, SN54AS00

NOTE: Qualified Version Definitions:

• Catalog - TI's standard catalog product

• Military - QML certified for Military and Defense Applications

PACKAGE MATERIALS INFORMATION

www.ti.com 16-Apr-2024

TAPE AND REEL INFORMATION





| A0 | Dimension designed to accommodate the component width |
|----|---|
| В0 | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | Package Type | Package Drawing | | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|---------------|-----------------|--------------------|----|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| SN74ALS00ADBR | SSOP | DB | 14 | 2000 | 330.0 | 16.4 | 8.35 | 6.6 | 2.4 | 12.0 | 16.0 | Q1 |
| SN74ALS00ADR | SOIC | D | 14 | 2500 | 330.0 | 16.4 | 6.5 | 9.0 | 2.1 | 8.0 | 16.0 | Q1 |
| SN74ALS00ANSR | so | NS | 14 | 2000 | 330.0 | 16.4 | 8.2 | 10.5 | 2.5 | 12.0 | 16.0 | Q1 |
| SN74AS00DR | SOIC | D | 14 | 2500 | 330.0 | 16.4 | 6.5 | 9.0 | 2.1 | 8.0 | 16.0 | Q1 |
| SN74AS00NSR | so | NS | 14 | 2000 | 330.0 | 16.4 | 8.2 | 10.5 | 2.5 | 12.0 | 16.0 | Q1 |



www.ti.com 16-Apr-2024



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|---------------|--------------|-----------------|------|------|-------------|------------|-------------|
| SN74ALS00ADBR | SSOP | DB | 14 | 2000 | 356.0 | 356.0 | 35.0 |
| SN74ALS00ADR | SOIC | D | 14 | 2500 | 356.0 | 356.0 | 35.0 |
| SN74ALS00ANSR | SO | NS | 14 | 2000 | 356.0 | 356.0 | 35.0 |
| SN74AS00DR | SOIC | D | 14 | 2500 | 356.0 | 356.0 | 35.0 |
| SN74AS00NSR | SO | NS | 14 | 2000 | 356.0 | 356.0 | 35.0 |

www.ti.com 16-Apr-2024

TUBE



*All dimensions are nominal

| Device | Package Name | Package Type | Pins | SPQ | L (mm) | W (mm) | T (µm) | B (mm) |
|------------------|--------------|--------------|------|-----|--------|--------|--------|--------|
| 5962-86833012A | FK | LCCC | 20 | 55 | 506.98 | 12.06 | 2030 | NA |
| 5962-8683301DA | W | CFP | 14 | 25 | 506.98 | 26.16 | 6220 | NA |
| JM38510/37001B2A | FK | LCCC | 20 | 55 | 506.98 | 12.06 | 2030 | NA |
| M38510/37001B2A | FK | LCCC | 20 | 55 | 506.98 | 12.06 | 2030 | NA |
| SN74ALS00AN | N | PDIP | 14 | 25 | 506 | 13.97 | 11230 | 4.32 |
| SN74ALS00AN | N | PDIP | 14 | 25 | 506 | 13.97 | 11230 | 4.32 |
| SN74AS00N | N | PDIP | 14 | 25 | 506 | 13.97 | 11230 | 4.32 |
| SN74AS00N | N | PDIP | 14 | 25 | 506 | 13.97 | 11230 | 4.32 |
| SNJ54ALS00AFK | FK | LCCC | 20 | 55 | 506.98 | 12.06 | 2030 | NA |
| SNJ54ALS00AW | W | CFP | 14 | 25 | 506.98 | 26.16 | 6220 | NA |



SMALL OUTLINE INTEGRATED CIRCUIT



- 1. All linear dimensions are in millimeters. Dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm, per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.43 mm, per side.
- 5. Reference JEDEC registration MS-012, variation AB.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



MECHANICAL DATA

NS (R-PDSO-G**)

14-PINS SHOWN

PLASTIC SMALL-OUTLINE PACKAGE



- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.



W (R-GDFP-F14)

CERAMIC DUAL FLATPACK



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- C. This package can be hermetically sealed with a ceramic lid using glass frit.
- D. Index point is provided on cap for terminal identification only.
- E. Falls within MIL STD 1835 GDFP1-F14





SMALL OUTLINE PACKAGE



- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
 4. Reference JEDEC registration MO-150.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- 5. Publication IPC-7351 may have alternate designs.
- 6. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- 7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.



8.89 x 8.89, 1.27 mm pitch

LEADLESS CERAMIC CHIP CARRIER

This image is a representation of the package family, actual package may vary. Refer to the product data sheet for package details.



CERAMIC DUAL IN LINE PACKAGE



Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4040083-5/G





CERAMIC DUAL IN LINE PACKAGE



- 1. All controlling linear dimensions are in inches. Dimensions in brackets are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This package is hermitically sealed with a ceramic lid using glass frit.
- His package is remitted by sealed with a ceramic its using glass mit.
 Index point is provided on cap for terminal identification only and on press ceramic glass frit seal only.
 Falls within MIL-STD-1835 and GDIP1-T14.



CERAMIC DUAL IN LINE PACKAGE



N (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE

16 PINS SHOWN



- A. All linear dimensions are in inches (millimeters).
- B. This drawing is subject to change without notice.
- Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
- The 20 pin end lead shoulder width is a vendor option, either half or full width.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated