





TPS732 SBVS037Q - AUGUST 2003 - REVISED SEPTEMBER 2024

TPS732 Capacitor-Free, NMOS, 250mA, Low-Dropout Regulator With Reverse Current **Protection**

1 Features

- Stable with no output capacitor or any value or type of capacitor
- Input voltage range: 1.7V to 5.5V
- Ultra-low dropout voltage: 40mV typical at 250mA
- Excellent load transient response—with or without optional output capacitor
- NMOS topology provides low reverse leakage
- Low noise: $30\mu V_{RMS}$ typical (10kHz to 100kHz)
- 0.5% initial accuracy
- 1% overall accuracy (line, load, and temperature)
- Less than 1µA maximum I_O in shutdown mode
- Thermal shutdown and specified min and max current limit protection
- Available in multiple output voltage versions:
 - Fixed outputs of 1.2V to 5V
 - Adjustable outputs from 1.2V to 5.5V
 - Custom outputs available

2 Applications

- Portable and battery-powered equipment
- Post-regulation for switching supplies
- Noise-sensitive circuitry such as VCOs
- Point of load regulation for DSPs, FPGAs, ASICs, and microprocessors

3 Description


The TPS732 low-dropout (LDO) voltage regulator uses an NMOS pass transistor in a voltage-follower configuration. This topology is stable using output capacitors with low equivalent series resistance (ESR), and even allows operation without a capacitor. The device also provides high reverse blockage (low reverse current) and ground pin current that is nearly constant over all values of output current.

The TPS732 uses an advanced BiCMOS process to yield high precision while delivering very low dropout voltages and low ground pin current. Current consumption, when not enabled, is less than 1µA and designed for portable applications. The extremely low output noise ($30\mu V_{RMS}$ with $0.1\mu F$ C_{NR}) is designed for powering VCOs. This device is protected by thermal shutdown and foldback current limit.

Package Information

| PART NUMBER | PACKAGE ⁽¹⁾ | PACKAGE SIZE ⁽²⁾ |
|-------------|------------------------|-----------------------------|
| TPS732 | DBV (SOT-23, 5) | 2.9mm × 2.8mm |
| | DCQ (SOT-223, 6) | 6.5mm × 7.06mm |
| | DRB (VSON, 8) | 3mm × 3mm |

- For more information, see the Mechanical, Packaging, and Orderable Information.
- The package size (length × width) is a nominal value and (2) includes pins, where applicable.



Typical Application Circuit for Fixed-Voltage Versions



Table of Contents

| 1 Features1 | 6.4 Device Functional Modes1 | 19 |
|---------------------------------------|--|----|
| 2 Applications1 | 7 Application and Implementation | 20 |
| 3 Description1 | 7.1 Application Information2 | 20 |
| 4 Pin Configuration and Functions3 | 7.2 Typical Application2 | |
| 5 Specifications4 | 7.3 Power Supply Recommendations | 23 |
| 5.1 Absolute Maximum Ratings4 | 7.4 Layout2 | |
| 5.2 ESD Ratings4 | 8 Device and Documentation Support2 | |
| 5.3 Recommended Operating Conditions4 | 8.1 Device Support | |
| 5.4 Thermal Information4 | 8.2 Documentation Support2 | |
| 5.5 Thermal Information5 | 8.3 Receiving Notification of Documentation Updates2 | 27 |
| 5.6 Electrical Characteristics6 | 8.4 Support Resources | 27 |
| 5.7 Switching Characteristics6 | 8.5 Trademarks2 | 27 |
| 5.8 Typical Characteristics7 | 8.6 Electrostatic Discharge Caution | |
| 6 Detailed Description16 | 8.7 Glossary2 | 28 |
| 6.1 Overview | 9 Revision History | 28 |
| 6.2 Functional Block Diagrams | 10 Mechanical, Packaging, and Orderable | |
| 6.3 Feature Description17 | | 28 |
| , | | |



4 Pin Configuration and Functions



Figure 4-1. DBV Package, 5-Pin SOT-23 (Top View)

Figure 4-2. DRB Package, 8-Pin VSON With Exposed Thermal Pad (Top View)




Figure 4-3. DCQ Package, 6-Pin SOT-223 (Top View)

Table 4-1. Pin Functions

| | PIN | | | | | |
|---------|---------------------|------|--------|---|--|--|
| NAME | | NO. | | TYPE | DESCRIPTION | |
| INAIVIE | SOT-23 SOT-223 VSON | | | | | |
| IN | 1 | 1 | 8 | I | Input supply. | |
| GND | 2 | 3, 6 | 4, Pad | _ | — Ground. | |
| EN | 3 | 5 | 5 | I | Driving the enable pin (EN) high turns on the regulator. Driving this pin low puts the regulator into shutdown mode. See the <i>Enable Pin and Shutdown</i> section under <i>Feature Description</i> for more details. Connect EN to IN if not used. | |
| NR | 4 | 4 | 3 | _ | Fixed voltage versions only—connecting an external capacitor to this pin bypasses noise generated by the internal band gap, reducing output noise to very low levels. | |
| FB | 4 | 4 | 3 | Adjustable voltage version only—this pin is the input to the control loop error amplifier, and is used to set the output voltage of the device. | | |
| OUT | 5 | 2 | 1 | 0 | Output of the regulator. There are no output capacitor requirements for stability. | |



5 Specifications

5.1 Absolute Maximum Ratings

over operating junction temperature range (unless otherwise noted)(1)

| | | MIN | MAX | UNIT |
|------------------------------------|------------------------------------|------------|---------------|------|
| | Input, V _{IN} | -0.3 | 6 | |
| Voltage | Enable, V _{EN} | -0.3 | -0.3 6 | |
| Voltage | Output, V _{OUT} | -0.3 | 5.5 | V |
| | V _{NR} , V _{FB} | -0.3 | 6 | |
| Current | Maximum output, I _{OUT} | Internall | y limited | |
| Output short-circuit duration | | Indet | finite | |
| Continuous total power dissipation | P _{DISS} | See Therma | I Information | |
| Townsersture | Operating junction, T _J | -55 | 150 | °C |
| Temperature | Storage, T _{stg} | -65 | 150 | C |

⁽¹⁾ Operation outside the Absolute Maximum Ratings may cause permanent device damage. Absolute Maximum Ratings do not imply functional operation of the device at these or any other conditions beyond those listed under Recommended Operating Conditions. If used outside the Recommended Operating Conditions but within the Absolute Maximum Ratings, the device may not be fully functional, and this may affect device reliability, functionality, performance, and shorten the device lifetime.

5.2 ESD Ratings

| | | | VALUE | UNIT |
|--|-------------------------|--|-------|------|
| V | Electrostatic discharge | Human-body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins ⁽¹⁾ | ±2000 | V |
| V _(ESD) Electrostatic discharge | | Charged-device model (CDM), per JEDEC specification JESD22-C101, all pins ⁽²⁾ | ±500 | v |

- (1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.
- (2) JEDEC document JEP157 states that 250-V CDM allows safe manufacturing with a standard ESD control process.

5.3 Recommended Operating Conditions

over operating junction temperature range (unless otherwise noted)

| | | MIN | NOM | MAX | UNIT |
|------------------|--------------------------------|-----|-----|-----|------|
| V _{IN} | Input supply voltage | 1.7 | | 5.5 | V |
| I _{OUT} | Output current | 0 | | 250 | mA |
| TJ | Operating junction temperature | -40 | | 125 | °C |

5.4 Thermal Information

| | | TPS732 M3 | | |
|-----------------------|--|------------|---------------|------|
| | THERMAL METRIC ⁽¹⁾ | DRB (VSON) | DCQ (SOT-223) | UNIT |
| | | 8 PINS | 6 PINS | |
| R _{θJA} | Junction-to-ambient thermal resistance | 47.7 | 76 | °C/W |
| R _{0JC(top)} | Junction-to-case (top) thermal resistance | 68.9 | 46.6 | °C/W |
| R _{θJB} | Junction-to-board thermal resistance | 20.6 | 18.1 | °C/W |
| ΨЈТ | Junction-to-top characterization parameter | 3.4 | 8.6 | °C/W |
| ΨЈВ | Junction-to-board characterization parameter | 20.6 | 17.6 | °C/W |
| R _{0JC(bot)} | Junction-to-case (bottom) thermal resistance | 3.5 | N/A | °C/W |

(1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application note.

Submit Document Feedback

Copyright © 2024 Texas Instruments Incorporated



5.5 Thermal Information

| | THERMAL METRIC ⁽¹⁾ (2) | | TPS732 Legacy silicon ⁽³⁾ | | | | |
|-----------------------|--|--------|--------------------------------------|--------------|------|--|--|
| | | | DCQ (SOT-223) | DBV (SOT-23) | UNIT | | |
| | | 8 PINS | 6 PINS | 5 PINS | | | |
| R _{0JA} | Junction-to-ambient thermal resistance | 58.3 | 53.1 | 205.9 | °C/W | | |
| R _{0JC(top)} | Junction-to-case (top) thermal resistance | 93.8 | 35.2 | 119 | °C/W | | |
| R _{0JB} | Junction-to-board thermal resistance | 72.8 | 7.8 | 35.4 | °C/W | | |
| Ψлт | Junction-to-top characterization parameter | 2.7 | 2.9 | 12.7 | °C/W | | |
| ΨЈВ | Junction-to-board characterization parameter | 25 | 7.7 | 34.5 | °C/W | | |
| R _{0JC(bot)} | Junction-to-case (bottom) thermal resistance | 5 | N/A | N/A | °C/W | | |

- (1) For more information about traditional and new thermal metrics, see the Semiconductor and IC Package Thermal Metrics application note.
- (2) For thermal estimates of this device based on PCB copper area, see the TI PCB Thermal Calculator.
- (3) Thermal data for the DRB, DCQ, and DBV packages are derived by thermal simulations based on JEDEC-standard methodology as specified in the JESD51 series. The following assumptions are used in the simulations:
 - (a) i. DRB: The exposed pad is connected to the PCB ground layer through a 2x2 thermal via array.
 - ii. DCQ: The exposed pad is connected to the PCB ground layer through a 3x2 thermal via array.
 - iii. DBV: There is no exposed pad with the DBV package.
 - (b) i. DRB: The top and bottom copper layers are assumed to have a 20% thermal conductivity of copper representing a 20% copper coverage.
 - ii. DCQ: Each of top and bottom copper layers has a dedicated pattern for 20% copper coverage.
 - iii. DBV: The top and bottom copper layers are assumed to have a 20% thermal conductivity of copper representing a 20% copper coverage.
 - (c) These data were generated with only a single device at the center of a JEDEC high-K (2s2p) board with $3in \times 3in$ copper area.

To understand the effects of the copper area on thermal performance, see the Power Dissipation section of this data sheet.



5.6 Electrical Characteristics

Over operating temperature range (T_J = -40° C to 125°C), V_{IN} = V_{OUT(nom)} + 0.5V ⁽¹⁾, I_{OUT} = 10mA, V_{EN} = 1.7V , and C_{OUT} = 0.1µF , unless otherwise noted. Typical values are at T_J = 25°C

| PARAMETER | | TEST CONDITIONS | | MIN | TYP | MAX | UNIT |
|-------------------------------|---|---|--|-----------------|---------------------------|--------------------------|-------------------|
| V _{IN} | Input voltage range ⁽¹⁾ | | | 1.7 | | 5.5 | V |
| V _{FB} | Internal reference (TPS73201) | T _J = 25°C | | 1.198 | 1.204 | 1.210 | V |
| | Output voltage range (TPS73201) ⁽²⁾ | | | V _{FB} | | 5.5 - V _{DO} | V |
| V _{OUT} | | Nominal | T _J = 25°C | -0.5 | | 0.5 | |
| | Accuracy ⁽¹⁾ (3) | V _{IN} , I _{OUT} , and T | $V_{OUT} + 0.5V \le V_{IN} \le$ 5.5V; 10mA $\le I_{OUT} \le 250$ mA | -1 | ±0.5 | 1 | % |
| $\Delta V_{OUT(\Delta VIN)}$ | Line regulation (1) | $V_{OUT(NOM)} + 0.5V \le V_{IN} \le 5.5V$ | 1 | | 0.01 | | %/V |
| ۸۷/ | Load regulation | 1mA ≤ I _{OUT} ≤ 250mA | | | 0.002 | | %/mA |
| $\Delta V_{OUT(\Delta IOUT)}$ | Load regulation | 10mA ≤ I _{OUT} ≤ 250mA | | | 0.0005 | | 70/111A |
| V _{DO} | Dropout voltage ⁽⁴⁾ (V _{IN} = V _{OUT(NOM)} - 0.1V) | I _{OUT} = 250mA | | | 40 | 150 | mV |
| Z _{O(do)} | Output impedance in dropout | $1.7V \le V_{IN} \le V_{OUT} + V_{DO}$ | | | 0.25 | | Ω |
| I _{CL} | Output current limit | $V_{OUT} = 0.9 \times V_{OUT(nom)}$ | | 250 | 425 | 600 | mA |
| I _{SC} | Short-circuit current | V _{OUT} = 0V | | | 300 | | mA |
| I _{REV} | Reverse leakage current ⁽⁵⁾ (- | $V_{EN} \le 0.5V$, $0V \le V_{IN} \le V_{OUT}$ | | | 0.1 | 10 | μA |
| | | I _{OUT} = 10mA (I _Q), legacy silicon | | | 400 | 550 | |
| I _{GND} | Ground pin current | I _{OUT} = 10mA (I _Q), new silicon, M3 suffix | | | 400 | 630 | μA |
| I _{GND} | Ground pin current | I _{OUT} = 250mA | | | 650 | 950 | μA |
| I _{SHDN} | Shutdown current (I _{GND}) | $V_{EN} \le 0.5V$, $V_{OUT} \le V_{IN} \le 5.5V$ silicon | /, –40°C ≤ T _J ≤ 100°C, legacy | | 0.02 | 1 | μA |
| ons.v | (3.1.5) | $V_{EN} \le 0.5 \text{V}, V_{OUT} \le V_{IN} \le 5.5 \text{V}$ | , new silicon, M3 suffix | | 0.02 | 1 | • |
| I _{FB} | Feedback pin current (TPS73201) | | | | 0.1 | 0.3 | μΑ |
| 2022 | Power-supply rejection ratio | f = 100Hz, I _{OUT} = 250mA | | | 58 | | |
| PSRR | (ripple rejection) | f = 10kHz, I _{OUT} = 250mA | | | 37 | | dB |
| V | Output noise voltage, BW = | C _{OUT} = 10µF, no C _{NR} | | | 27 x V _{OUT} | | |
| V _N | 10Hz to 100kHz | C _{OUT} = 10µF, C _{NR} =0.01µF | | | 8.5 x V _{OUT} | | μV _{RMS} |
| V _{EN(high)} | EN pin high (enabled) | | | 1.7 | | V _{IN} | V |
| V _{EN(low)} | EN pin low (shutdown) | | | 0 | | 0.5 | V |
| I _{EN(high)} | Enable pin current (enabled) | V _{EN} = 5.5V | | | 0.02 | 0.1 | μΑ |
| т | Thermal shutdown | Shutdown, temperature increasing | | | 160 | | °C |
| T _{SD} | temperature | Reset, temperature decreasing | | 140 | | C | |
| T _J | Operating junction temperature | | | -40 | | 125 | °C |
| | | 1 | | | | | |

- Minimum $V_{IN} = V_{OUT} + V_{DO}$ or 1.7V, whichever is greater.
- TPS73201 is tested at VOUT = 2.5V. (2)
- (3) Tolerance of external resistors not included in this specification.
- V_{DO} is not measured for output versions with $V_{OUT(nom)}$ < 1.8V, because minimum V_{IN} = 1.7V. Fixed-voltage versions only; refer to *Application Information* section for more information. (4)

5.7 Switching Characteristics


over operating free-air temperature range (unless otherwise noted)

| · | PARAMETER | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|------------------|---------------|--|-----|-----|-----|------|
| t _{STR} | Start-up time | V_{OUT} = 3V, R_L = 30 Ω , C_{OUT} = 1 μ F, C_{NR} = 0.01 μ F | | 600 | | μs |


Submit Document Feedback

Copyright © 2024 Texas Instruments Incorporated


5.8 Typical Characteristics







for all voltage versions at T_J = 25°C, V_{IN} = $V_{OUT(nom)}$ + 0.5V, I_{OUT} = 10mA, V_{EN} = 1.7V, and C_{OUT} = 0.1 μ F (unless otherwise noted)






Figure 5-14. Ground Pin Current vs Temperature




Figure 5-15. Ground Pin Current in Shutdown vs Temperature




Figure 5-16. Ground Pin Current in Shutdown vs Temperature




Figure 5-17. Current Limit vs V_{OUT} (Foldback)





Figure 5-18. Current Limit vs V_{OUT} (Foldback)

Copyright © 2024 Texas Instruments Incorporated

Submit Document Feedback



for all voltage versions at T_J = 25°C, V_{IN} = $V_{OUT(nom)}$ + 0.5V, I_{OUT} = 10mA, V_{EN} = 1.7V, and C_{OUT} = 0.1 μ F (unless otherwise noted)



Submit Document Feedback

Copyright © 2024 Texas Instruments Incorporated




Figure 5-25. PSRR (Ripple Rejection) vs (V_{IN} - V_{OUT})




Figure 5-26. PSRR (Ripple Rejection) vs $(V_{IN} - V_{OUT})$




Figure 5-27. Noise Spectral Density C_{NR} = 0μF





Figure 5-28. Noise Spectral Density $C_{NR} = 0\mu F$









Figure 5-30. Noise Spectral Density $C_{NR} = 0.01 \mu F$
















6 Detailed Description

6.1 Overview

The TPS732 low-dropout linear regulator operates down to an input voltage of 1.7V and supports output voltages down to 1.2V while sourcing up to 250mA of load current. This linear regulator uses an NMOS pass transistor with an integrated 4MHz charge pump to provide a dropout voltage of less than 150mV at full load current. This unique architecture also permits stable regulation over a wide range of output capacitors. Furthermore, the TPS732 does not require any output capacitor for stability. The increased insensitivity to the output capacitor value and type makes this linear regulator designed for powering a load where the effective capacitance is unknown.

The TPS732 also features a noise-reduction (NR) pin that allows for additional reduction of the output noise. With a noise reduction capacitor of $0.01\mu F$ connected from the NR pin to GND, the TPS73215 typical output noise is $12.75\mu V_{RMS}$. The low noise output featured by the TPS732 makes the device designed for powering VCOs or any other noise-sensitive load.

6.2 Functional Block Diagrams




Figure 6-1. Fixed-Voltage Version

Submit Document Feedback

Copyright © 2024 Texas Instruments Incorporated




Table 1. Standard 1% Resistor Values for Common Output Voltages

| Vo | R ₁ | R ₂ |
|------|----------------|----------------|
| 1.2V | Short | Open |
| 1.5V | 23.2kΩ | 95.3kΩ |
| 1.8V | 28.0kΩ | 56.2kΩ |
| 2.5V | 39.2kΩ | 36.5kΩ |
| 2.8V | 44.2kΩ | 33.2kΩ |
| 3.0V | 46.4kΩ | 30.9kΩ |
| 3.3V | 52.3kΩ | 30.1kΩ |

NOTE: $V_{OUT} = (R_1 + R_2)/R_2 \times 1.204$; $R_1 || R_2 \cong 19k\Omega$ for best accuracy.

Figure 6-2. Adjustable-Voltage Version

6.3 Feature Description

6.3.1 Output Noise

A precision band-gap reference is used to generate the internal reference voltage, V_{REF} . This reference is the dominant noise source within the TPS732 and generates approximately $32\mu V_{RMS}$ (10Hz to 100kHz) at the reference output (NR). The regulator control loop gains up the reference noise with the same gain as the reference voltage, so that the noise voltage of the regulator is approximately given by:

$$V_{N} = 32\mu V_{RMS} \times \left(\frac{R_{1} + R2}{R_{2}}\right) = 32\mu V_{RMS} \times \frac{V_{OUT}}{V_{REF}}$$

$$\tag{1}$$

Because the value of V_{REF} is 1.2V, this relationship reduces to:

$$V_{N}(\mu V_{RMS}) = 27 \left(\frac{\mu V_{RMS}}{V}\right) \times V_{OUT}(V)$$
(2)

An internal $27k\Omega$ resistor in series with the noise-reduction pin (NR) forms a low-pass filter for the voltage reference when an external noise-reduction capacitor, C_{NR} , is connected from NR to ground. For C_{NR} = 10nF, the total noise in the 10Hz to 100kHz bandwidth is reduced by a factor of approximately 3.2, giving the approximate relationship:

$$V_{N}(\mu V_{RMS}) = 8.5 \left(\frac{\mu V_{RMS}}{V}\right) \times V_{OUT}(V)$$
(3)

for $C_{NR} = 10nF$.



This noise-reduction effect is shown as RMS Noise Voltage vs C_{NR} (Figure 5-33) in the Typical Characteristics section.

The TPS73201 adjustable version does not have the NR pin available. However, connecting a feedback capacitor, C_{FB} , from the output to the feedback pin (FB) reduces output noise and improves load transient performance.

The TPS732 uses an internal charge pump to develop an internal supply voltage sufficient to drive the gate of the NMOS pass transistor above V_{OUT} . The charge pump generates approximately 250 μ V of switching noise at approximately 4MHz; however, charge-pump noise contribution is negligible at the output of the regulator for most values of I_{OUT} and C_{OUT} .

6.3.2 Internal Current Limit

The TPS732 internal current limit helps protect the regulator during fault conditions. Foldback current limit helps to protect the regulator from damage during output short-circuit conditions by reducing current limit when V_{OUT} drops below 0.5V. See Figure 5-17 in the *Typical Characteristics* section for a graph of I_{OUT} vs V_{OUT} .

From Figure 5-17 approximately -0.2V of V_{OUT} results in a current limit of 0mA. Therefore, if OUT is forced below -0.2V before EN goes high, the device potentially does not start up. In applications that work with both a positive and negative voltage supply, enable the TPS732 first.

6.3.3 Enable Pin and Shutdown

The enable pin (EN) is active high and is compatible with standard TTL-CMOS levels. A V_{EN} below 0.5V (maximum) turns the regulator off and drops the GND pin current to approximately 10nA. When EN is used to shut down the regulator, all charge is removed from the pass transistor gate. A V_{EN} above 1.7V (minimum) turns the regulator on and the output ramps back up to a regulated V_{OUT} (see Figure 5-39).

When shutdown capability is not required, connect EN to V_{IN} . However, the pass transistor potentially does not discharge using this configuration, causing the pass transistor to be left on (enhanced) for a significant time after V_{IN} is removed. This scenario results in reverse current flow (if the IN pin is low impedance) and faster ramp times upon power up. In addition, for V_{IN} ramp times slower than a few milliseconds, the output potentially overshoots upon power up.

Current limit foldback prevents device start-up under some conditions. See the *Internal Current Limit* section.

6.3.4 Dropout Voltage

The TPS732 uses an NMOS pass transistor to achieve extremely low dropout. When $(V_{IN} - V_{OUT})$ is less than the dropout voltage (V_{DO}) , the NMOS pass transistor is in the linear region of operation and the input-to-output resistance is the $R_{DS(on)}$ of the NMOS pass transistor.

For large step changes in load current, the TPS732 requires a larger voltage drop from V_{IN} to V_{OUT} to avoid degraded transient response. The boundary of this transient dropout region is approximately twice the DC dropout. Values of $(V_{IN} - V_{OUT})$ above this line provide normal transient response.

Operating in the transient dropout region causes an increase in recovery time. The time required to recover from a load transient is a function of the magnitude of the change in load current rate, the rate of change in load current, and the available headroom (V_{IN} to V_{OUT} voltage drop). Under worst-case conditions [full-scale instantaneous load change with ($V_{IN} - V_{OUT}$) close to DC dropout levels], the TPS732 takes a couple of hundred microseconds to return to the specified regulation accuracy.

Submit Document Feedback



6.3.5 Reverse Current

The NMOS pass transistor of the TPS732 provides inherent protection against current flow from the output of the regulator to the input when the gate of the pass transistor is pulled low. To make sure all charge is removed from the gate of the pass transistor, drive the EN pin low before the input voltage is removed. If this process is not done, the pass transistor is potentially left on because of stored charge on the transistor.

After the EN pin is driven low, no bias voltage is needed on any pin for reverse current blocking. Reverse current is specified as the current flowing out of the IN pin resulting from the voltage applied on the OUT pin. Additional current flows into the OUT pin from the $80k\Omega$ internal resistor divider to ground (see Figure 6-1 and Figure 6-2).

For the TPS73201, reverse current potentially flows when V_{FB} is more than 1V above V_{IN} .

6.4 Device Functional Modes

6.4.1 Normal Operation With 1.7V $\leq V_{IN} \leq$ 5.5V and $V_{EN} \geq$ 1.7V

The TPS732 requires an input voltage of at least 1.7V to function properly and attempt to maintain regulation.

When operating the device near 5.5V, suppress any transient spikes that exceed the 6V absolute maximum voltage rating. Never operate the device at a DC voltage greater than 5.5V.

Copyright © 2024 Texas Instruments Incorporated

Submit Document Feedback



7 Application and Implementation

Note

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes, as well as validating and testing their design implementation to confirm system functionality.

7.1 Application Information

The TPS732 LDO regulator uses an NMOS pass transistor to achieve ultra-low-dropout performance, reverse current blockage, and freedom from output capacitor constraints. These features, combined with low noise and an enable input, make the TPS732 designed for portable applications. This regulator offers a wide selection of fixed-output voltage versions and an adjustable-output version. All versions have thermal and overcurrent protection, including foldback current limit.

7.2 Typical Application

Figure 7-1 shows the basic circuit connections for the fixed-voltage models. Figure 7-2 gives the connections for the adjustable-voltage version (TPS73201).




Figure 7-1. Typical Application Circuit for Fixed-Voltage Versions




Figure 7-2. Typical Application Circuit for Adjustable-Voltage Version

Product Folder Links: TPS732

7.2.1 Design Requirements

 R_1 and R_2 are calculated for any output voltage using the formula in Figure 7-2. Sample resistor values for common output voltages are given in Figure 6-2.

For best accuracy, make the parallel combination of R_1 and R_2 approximately equal to $19k\Omega$. This $19k\Omega$, in addition to the internal $8k\Omega$ resistor, presents the same impedance to the error amplifier as the $27k\Omega$ band-gap reference output. This impedance helps compensate for leakages into the error amplifier terminals.

7.2.2 Detailed Design Procedure

7.2.2.1 Input and Output Capacitor Requirements

Although an input capacitor is not required for stability, good analog design practice is to connect a 0.1µF to 1µF, low ESR capacitor across the input supply near the regulator. This capacitor counteracts reactive input sources and improves transient response, noise rejection, and ripple rejection. A higher-value capacitor is necessary if large, fast rise-time load transients are anticipated or the device is located several inches from the power source.

The TPS732 does not require an output capacitor for stability and has maximum phase margin with no capacitor. The device is designed to be stable for all available types and values of capacitors. In applications where multiple low ESR capacitors are in parallel, ringing potentially occurs when the product of C_{OUT} and total ESR drops below $50nF \times \Omega$. Total ESR includes all parasitic resistances, including capacitor ESR and board, socket, and solder joint resistance. In most applications, the sum of capacitor ESR and trace resistance meets this requirement.

7.2.2.2 Transient Response

The low open-loop output impedance provided by the NMOS pass transistor in a voltage follower configuration allows operation without an output capacitor for many applications. As with any regulator, the addition of a capacitor (nominal value $1\mu F$) from the OUT pin to ground reduces undershoot magnitude but increases the duration. In the adjustable version, the addition of a capacitor, C_{FB} , from the OUT pin to the FB pin also improves transient response.

The TPS732 does not have active pulldown when the output is overvoltage. This feature allows applications that connect higher voltage sources, such as alternate power supplies, to the output. This feature also results in an output overshoot of several percent if the load current quickly drops to zero when a capacitor is connected to the output. The duration of overshoot is reduced by adding a load resistor. The overshoot decays at a rate determined by output capacitor C_{OUT} and the internal or external load resistance. The rate of decay is given by:

(Fixed voltage versions)

$$dV / dt = \frac{V_{OUT}}{C_{OUT} \times 80k\Omega \parallel R_{LOAD}}$$
(4)

(Adjustable voltage version)


$$dV / dt = \frac{V_{OUT}}{C_{OUT} \times 80k\Omega \| (R_1 + R_2) \| R_{LOAD}}$$
(5)

Copyright © 2024 Texas Instruments Incorporated


Submit Document Feedback



7.2.3 Application Curves



7.2.3 Application Curves (continued)



7.3 Power Supply Recommendations

This device is designed to operate from an input voltage supply range between 1.7V and 5.5V. The input voltage range provides adequate headroom for the device to have a regulated output. Make sure this input supply is well regulated. If the input supply is noisy, additional input capacitors with low ESR help improve output noise performance.

7.4 Layout

7.4.1 Layout Guidelines

To improve AC performance such as PSRR, output noise, and transient response, design the PCB with ground plane connections for V_{IN} and V_{OUT} capacitors, and connect the ground plane at the GND pin of the device. In addition, the ground connection for the bypass capacitor should connect directly to the GND pin of the device.

7.4.1.1 Thermal Considerations

Thermal protection disables the output when the junction temperature rises to approximately 160°C, allowing the device to cool. When the junction temperature cools to approximately 140°C, the output circuitry is again enabled. Depending on power dissipation, thermal resistance, and ambient temperature, the thermal protection circuit potentially cycles on and off. This cycling limits the dissipation of the regulator, protecting the regulator from damage caused by overheating.

Any tendency to activate the thermal protection circuit indicates excessive power dissipation or an inadequate heat sink. For reliable operation, limit junction temperature to 125°C maximum. To estimate the margin of safety in a complete design (including heat sink), increase the ambient temperature until the thermal protection is triggered; use worst-case loads and signal conditions. For good reliability, thermal protection triggers at least 35°C above the maximum expected ambient condition of the application. This level produces a worst-case junction temperature of 125°C at the highest expected ambient temperature and worst-case load.

The internal protection circuitry of the TPS732 is designed to protect against overload conditions. This circuitry is not intended to replace proper heat sinking. Continuously running the TPS732 into thermal shutdown degrades device reliability.



7.4.1.1.1 Power Dissipation

The ability to remove heat from the die is different for each package type, presenting different considerations in the PCB layout. The PCB area around the device that is free of other components moves the heat from the device to the ambient air. Performance data for JEDEC low- and high-K boards are shown in the *Thermal Information* table. Using heavier copper increases the effectiveness in removing heat from the device. The addition of plated through-holes to heat-dissipating layers also improves the heat-sink effectiveness.

Power dissipation depends on input voltage and load conditions. Power dissipation (P_D) is equal to the product of the output current times the voltage drop across the output pass transistor (V_{IN} to V_{OUT}):

$$P_{D} = (V_{IN} - V_{OUT}) \times I_{OUT}$$
(6)

Power dissipation is minimized by using the lowest possible input voltage necessary to provide the required output voltage.

7.4.2 Layout Examples




Figure 7-11. Fixed Output Voltage Option Layout (DRB Package)

Submit Document Feedback

Copyright © 2024 Texas Instruments Incorporated




Figure 7-12. Adjustable Output Voltage Option Layout (DRB Package)




Figure 7-13. Layout Example for the DBV Package Fixed Version






Figure 7-14. Layout Example for the DBV Package Adjustable Version




Figure 7-15. Layout Example for the DCQ Package Fixed Version




Figure 7-16. Layout Example for the DCQ Package Adjustable Version

Submit Document Feedback

Copyright © 2024 Texas Instruments Incorporated

8 Device and Documentation Support

8.1 Device Support

8.1.1 Development Support

8.1.1.1 Evaluation Modules

An evaluation module (EVM) is available to assist in the initial circuit performance evaluation using the TPS732. Request the TPS73201DRBEVM-518 evaluation module (and related user guide) at the Texas Instruments website through the product folders or purchased directly from the TI eStore.

8.1.1.2 Spice Models

Computer simulation of circuit performance using SPICE is often useful when analyzing the performance of analog circuits and systems. A SPICE model for the TPS732 is available through the product folders under Simulation Models.

8.1.2 Device Nomenclature

Table 8-1. Device Nomenclature

| PRODUCT ⁽¹⁾ | V _{OUT} |
|---------------------------------|---|
| TPS732 xx<i>yyyz(M3)</i> | xx is the nominal output voltage (for example, 25 = 2.5V; 01 = Adjustable). yyy is the package designator. z is the tape and reel quantity (R = 3000, T = 250). M3 is a suffix designator for devices that only use the latest manufacturing flow (CSO: RFB). Devices without this suffix ship with the <i>legacy silicon</i> (CSO: DLN) or the <i>new silicon</i> (CSO: RFB). The reel packaging label provides CSO information to distinguish which chip is being used. Device performance for new and legacy chips is denoted throughout the document. |

⁽¹⁾ For the most current package and ordering information see the Package Option Addendum at the end of this document, or see the TI website at www.ti.com.

8.2 Documentation Support

8.2.1 Related Documentation

- Texas Instruments, Regulating V_{OUT} Below 1.2 V Using an External Reference application note
- Texas Instruments, TPS73x01DRBEVM-518 User's Guide

8.3 Receiving Notification of Documentation Updates

To receive notification of documentation updates, navigate to the device product folder on ti.com. Click on *Notifications* to register and receive a weekly digest of any product information that has changed. For change details, review the revision history included in any revised document.

8.4 Support Resources

TI E2E[™] support forums are an engineer's go-to source for fast, verified answers and design help — straight from the experts. Search existing answers or ask your own question to get the quick design help you need.

Linked content is provided "AS IS" by the respective contributors. They do not constitute TI specifications and do not necessarily reflect TI's views; see TI's Terms of Use.

8.5 Trademarks

TI E2E™ is a trademark of Texas Instruments.

All trademarks are the property of their respective owners.

8.6 Electrostatic Discharge Caution



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.

ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.



8.7 Glossary

This glossary lists and explains terms, acronyms, and definitions. TI Glossary

9 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

| Changes from Revision P (December 2015) to Revision Q (September 2024) | Page |
|---|--|
| Updated the numbering format for tables, figures, and cross-references through | ghout the document1 |
| Changed SON to VSON throughout document | |
| Changed VFB typical value | |
| Added M3 ground pin current spec | |
| Added M3 shutdown current spec | |
| Added new silicon plots to Typical Characteristics | |
| Changed load current max source from 500mA to 250mA and dropout voltage Overview section | |
| Changed total ESR drops below 50nΩF to total ESR drops below 50nF × Ω in Requirements section | Input and Output Capacitor |
| Added new silicon plots to Application Curves section | |
| Changed Layout Guidelines section | |
| Added DBV and DCQ layout figures to Layout Examples section | 24 |
| Added M3 information to Device Nomenclature | |
| Changes from Revision O (August 2010) to Revision P (December 2015) | Page |
| Changed Features bullet about NMOS topology; deleted "new" | 1 |
| Added ESD Ratings table, Feature Description section, Device Functional Mo Implementation section, Power Supply Recommendations section, Layout sec | des, Application and ction, Device and |
| Documentation Support section, and Mechanical, Packaging, and Orderable I | |
| • Changed first paragraph of <i>Description</i> section; deleted description of NMOS | |
| Changed Pin Configuration and Functions section; updated table format | 3 |

10 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

Product Folder Links: TPS732

Submit Document Feedback



www.ti.com

11-Dec-2024

PACKAGING INFORMATION

| Orderable Device | Status | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead finish/ Ball material | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|----------|--------------|--------------------|------|----------------|--------------|-------------------------------|---------------------|--------------|-------------------------|---------|
| TPS73201DBVR | ACTIVE | SOT-23 | DBV | 5 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | PJEQ | Samples |
| TPS73201DBVT | ACTIVE | SOT-23 | DBV | 5 | 250 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | PJEQ | Samples |
| TPS73201DBVTG4 | ACTIVE | SOT-23 | DBV | 5 | 250 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | PJEQ | Samples |
| TPS73201DCQ | OBSOLETE | SOT-223 | DCQ | 6 | | TBD | Call TI | Call TI | -40 to 125 | PS73201 | |
| TPS73201DCQR | ACTIVE | SOT-223 | DCQ | 6 | 2500 | RoHS & Green | SN | Level-2-260C-1 YEAR | -40 to 125 | PS73201 | Samples |
| TPS73201DRBR | ACTIVE | SON | DRB | 8 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | PJEQ | Samples |
| TPS73201DRBRG4 | ACTIVE | SON | DRB | 8 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | PJEQ | Samples |
| TPS73201DRBRM3 | ACTIVE | SON | DRB | 8 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | PJEQ | Samples |
| TPS73201DRBT | OBSOLETE | SON | DRB | 8 | | TBD | Call TI | Call TI | -40 to 125 | PJEQ | |
| TPS73213DBVR | ACTIVE | SOT-23 | DBV | 5 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | BWD | Samples |
| TPS73215DBVR | ACTIVE | SOT-23 | DBV | 5 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | T38 | Samples |
| TPS73215DCQ | OBSOLETE | SOT-223 | DCQ | 6 | | TBD | Call TI | Call TI | -40 to 125 | PS73215 | |
| TPS73215DCQR | ACTIVE | SOT-223 | DCQ | 6 | 2500 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | PS73215 | Samples |
| TPS73216DBVT | ACTIVE | SOT-23 | DBV | 5 | 250 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | T50 | Samples |
| TPS73216DBVTG4 | ACTIVE | SOT-23 | DBV | 5 | 250 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | T50 | Samples |
| TPS73218DBVR | ACTIVE | SOT-23 | DBV | 5 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | T37 | Samples |
| TPS73218DBVT | OBSOLETE | SOT-23 | DBV | 5 | | TBD | Call TI | Call TI | -40 to 125 | T37 | |
| TPS73218DCQ | OBSOLETE | SOT-223 | DCQ | 6 | | TBD | Call TI | Call TI | -40 to 125 | PS73218 | |
| TPS73218DCQR | ACTIVE | SOT-223 | DCQ | 6 | 2500 | RoHS & Green | SN | Level-2-260C-1 YEAR | -40 to 125 | PS73218 | Samples |
| TPS73219DBVR | ACTIVE | SOT-23 | DBV | 5 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | CGE | Samples |
| TPS73219DBVT | OBSOLETE | SOT-23 | DBV | 5 | | TBD | Call TI | Call TI | -40 to 125 | CGE | |
| TPS73225DBVR | ACTIVE | SOT-23 | DBV | 5 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | T36 | Samples |



www.ti.com 11-Dec-2024

| Orderable Device | Status | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead finish/ Ball material | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|----------|--------------|--------------------|------|----------------|--------------|-------------------------------|---------------------|--------------|-------------------------|---------|
| TPS73225DBVT | ACTIVE | SOT-23 | DBV | 5 | 250 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | T36 | Samples |
| TPS73225DBVTG4 | ACTIVE | SOT-23 | DBV | 5 | 250 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | T36 | Samples |
| TPS73225DCQ | OBSOLETE | SOT-223 | DCQ | 6 | | TBD | Call TI | Call TI | -40 to 125 | PS73225 | |
| TPS73225DCQR | ACTIVE | SOT-223 | DCQ | 6 | 2500 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | PS73225 | Samples |
| TPS73230DBVR | ACTIVE | SOT-23 | DBV | 5 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | T39 | Samples |
| TPS73230DBVT | OBSOLETE | SOT-23 | DBV | 5 | | TBD | Call TI | Call TI | -40 to 125 | T39 | |
| TPS73230DCQR | ACTIVE | SOT-223 | DCQ | 6 | 2500 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | PS73230 | Samples |
| TPS73233DBVR | ACTIVE | SOT-23 | DBV | 5 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | T40 | Samples |
| TPS73233DBVT | ACTIVE | SOT-23 | DBV | 5 | 250 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | T40 | Samples |
| TPS73233DCQ | OBSOLETE | SOT-223 | DCQ | 6 | | TBD | Call TI | Call TI | -40 to 125 | PS73233 | |
| TPS73233DCQR | ACTIVE | SOT-223 | DCQ | 6 | 2500 | RoHS & Green | SN | Level-2-260C-1 YEAR | -40 to 125 | PS73233 | Samples |
| TPS73250DBVR | ACTIVE | SOT-23 | DBV | 5 | 3000 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | T41 | Samples |
| TPS73250DBVT | ACTIVE | SOT-23 | DBV | 5 | 250 | RoHS & Green | NIPDAU | Level-1-260C-UNLIM | -40 to 125 | T41 | Samples |
| TPS73250DCQR | ACTIVE | SOT-223 | DCQ | 6 | 2500 | RoHS & Green | NIPDAU | Level-2-260C-1 YEAR | -40 to 125 | PS73250 | Samples |

⁽¹⁾ The marketing status values are defined as follows: **ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽²⁾ RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

PACKAGE OPTION ADDENDUM

www.ti.com 11-Dec-2024

(3) MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

(4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

(6) Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

OTHER QUALIFIED VERSIONS OF TPS732:

Automotive: TPS732-Q1

NOTE: Qualified Version Definitions:

Automotive - Q100 devices qualified for high-reliability automotive applications targeting zero defects



www.ti.com 18-Nov-2024

TAPE AND REEL INFORMATION





| A0 | Dimension designed to accommodate the component width |
|----|---|
| В0 | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | Package Type | Package Drawing | | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|-----------------|--------------------|---|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| TPS73201DBVR | SOT-23 | DBV | 5 | 3000 | 178.0 | 9.0 | 3.3 | 3.2 | 1.4 | 4.0 | 8.0 | Q3 |
| TPS73201DBVT | SOT-23 | DBV | 5 | 250 | 178.0 | 9.0 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| TPS73201DBVT | SOT-23 | DBV | 5 | 250 | 179.0 | 8.4 | 3.2 | 3.2 | 1.4 | 4.0 | 8.0 | Q3 |
| TPS73201DCQR | SOT-223 | DCQ | 6 | 2500 | 330.0 | 12.4 | 6.85 | 7.3 | 1.88 | 8.0 | 12.0 | Q3 |
| TPS73201DRBR | SON | DRB | 8 | 3000 | 330.0 | 12.4 | 3.3 | 3.3 | 1.1 | 8.0 | 12.0 | Q2 |
| TPS73213DBVR | SOT-23 | DBV | 5 | 3000 | 178.0 | 9.0 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| TPS73215DBVR | SOT-23 | DBV | 5 | 3000 | 178.0 | 9.0 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| TPS73215DCQR | SOT-223 | DCQ | 6 | 2500 | 330.0 | 12.4 | 7.1 | 7.45 | 1.88 | 8.0 | 12.0 | Q3 |
| TPS73216DBVT | SOT-23 | DBV | 5 | 250 | 179.0 | 8.4 | 3.2 | 3.2 | 1.4 | 4.0 | 8.0 | Q3 |
| TPS73218DBVR | SOT-23 | DBV | 5 | 3000 | 178.0 | 9.0 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| TPS73218DCQR | SOT-223 | DCQ | 6 | 2500 | 330.0 | 12.4 | 6.85 | 7.3 | 1.88 | 8.0 | 12.0 | Q3 |
| TPS73219DBVR | SOT-23 | DBV | 5 | 3000 | 178.0 | 9.0 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| TPS73225DBVR | SOT-23 | DBV | 5 | 3000 | 178.0 | 9.0 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| TPS73225DBVT | SOT-23 | DBV | 5 | 250 | 178.0 | 9.0 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| TPS73225DCQR | SOT-223 | DCQ | 6 | 2500 | 330.0 | 12.4 | 7.1 | 7.45 | 1.88 | 8.0 | 12.0 | Q3 |
| TPS73230DBVR | SOT-23 | DBV | 5 | 3000 | 178.0 | 9.0 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |




PACKAGE MATERIALS INFORMATION

www.ti.com 18-Nov-2024

| Device | Package Type | Package Drawing | | SPQ | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|--------------|-----------------|--------------------|---|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| TPS73230DCQR | SOT-223 | DCQ | 6 | 2500 | 330.0 | 12.4 | 7.1 | 7.45 | 1.88 | 8.0 | 12.0 | Q3 |
| TPS73233DBVR | SOT-23 | DBV | 5 | 3000 | 178.0 | 9.0 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| TPS73233DBVT | SOT-23 | DBV | 5 | 250 | 178.0 | 9.0 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| TPS73233DCQR | SOT-223 | DCQ | 6 | 2500 | 330.0 | 12.4 | 6.85 | 7.3 | 1.88 | 8.0 | 12.0 | Q3 |
| TPS73250DBVR | SOT-23 | DBV | 5 | 3000 | 178.0 | 9.0 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| TPS73250DBVT | SOT-23 | DBV | 5 | 250 | 178.0 | 9.0 | 3.23 | 3.17 | 1.37 | 4.0 | 8.0 | Q3 |
| TPS73250DCQR | SOT-223 | DCQ | 6 | 2500 | 330.0 | 12.4 | 7.1 | 7.45 | 1.88 | 8.0 | 12.0 | Q3 |



www.ti.com 18-Nov-2024



*All dimensions are nominal

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TPS73201DBVR | SOT-23 | DBV | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| TPS73201DBVT | SOT-23 | DBV | 5 | 250 | 180.0 | 180.0 | 18.0 |
| TPS73201DBVT | SOT-23 | DBV | 5 | 250 | 200.0 | 183.0 | 25.0 |
| TPS73201DCQR | SOT-223 | DCQ | 6 | 2500 | 356.0 | 356.0 | 36.0 |
| TPS73201DRBR | SON | DRB | 8 | 3000 | 367.0 | 367.0 | 35.0 |
| TPS73213DBVR | SOT-23 | DBV | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| TPS73215DBVR | SOT-23 | DBV | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| TPS73215DCQR | SOT-223 | DCQ | 6 | 2500 | 346.0 | 346.0 | 41.0 |
| TPS73216DBVT | SOT-23 | DBV | 5 | 250 | 213.0 | 191.0 | 35.0 |
| TPS73218DBVR | SOT-23 | DBV | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| TPS73218DCQR | SOT-223 | DCQ | 6 | 2500 | 356.0 | 356.0 | 36.0 |
| TPS73219DBVR | SOT-23 | DBV | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| TPS73225DBVR | SOT-23 | DBV | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| TPS73225DBVT | SOT-23 | DBV | 5 | 250 | 180.0 | 180.0 | 18.0 |
| TPS73225DCQR | SOT-223 | DCQ | 6 | 2500 | 346.0 | 346.0 | 41.0 |
| TPS73230DBVR | SOT-23 | DBV | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| TPS73230DCQR | SOT-223 | DCQ | 6 | 2500 | 346.0 | 346.0 | 41.0 |
| TPS73233DBVR | SOT-23 | DBV | 5 | 3000 | 180.0 | 180.0 | 18.0 |



PACKAGE MATERIALS INFORMATION

www.ti.com 18-Nov-2024

| Device | Package Type | Package Drawing | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) |
|--------------|--------------|-----------------|------|------|-------------|------------|-------------|
| TPS73233DBVT | SOT-23 | DBV | 5 | 250 | 180.0 | 180.0 | 18.0 |
| TPS73233DCQR | SOT-223 | DCQ | 6 | 2500 | 356.0 | 356.0 | 36.0 |
| TPS73250DBVR | SOT-23 | DBV | 5 | 3000 | 180.0 | 180.0 | 18.0 |
| TPS73250DBVT | SOT-23 | DBV | 5 | 250 | 180.0 | 180.0 | 18.0 |
| TPS73250DCQR | SOT-223 | DCQ | 6 | 2500 | 346.0 | 346.0 | 41.0 |



SMALL OUTLINE TRANSISTOR



NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
 2. This drawing is subject to change without notice.
 3. Reference JEDEC MO-178.

- 4. Body dimensions do not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.25 mm per side.
- 5. Support pin may differ or may not be present.



SMALL OUTLINE TRANSISTOR



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE TRANSISTOR




NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.





PLASTIC SMALL OUTLINE



NOTES:


- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

 2. This drawing is subject to change without notice.

 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.



PLASTIC SMALL OUTLINE




NOTES: (continued)

- 4. Publication IPC-7351 may have alternate designs.
- 5. Solder mask tolerances between and around signal pads can vary based on board fabrication site.6. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



PLASTIC SMALL OUTLINE



NOTES: (continued)

- 7. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 8. Board assembly site may have different recommendations for stencil design.






Images above are just a representation of the package family, actual package may vary. Refer to the product data sheet for package details.

4203482/L





PLASTIC SMALL OUTLINE - NO LEAD




NOTES:

- All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. The package thermal pad must be soldered to the printed circuit board for thermal and mechanical performance.



PLASTIC SMALL OUTLINE - NO LEAD




NOTES: (continued)

- 4. This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature number SLUA271 (www.ti.com/lit/slua271).
- Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.



PLASTIC SMALL OUTLINE - NO LEAD



NOTES: (continued)

6. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated