

TEXAS INSTRUMENTS INCORPORATED

# PMP11438 Rev A

---

## Power Design Services Test Report

**Ryan Manack**

**4/8/2016**

PMP11438 REVA is a power evaluation module showcasing three different implementations for a 12V input, 1.2V output power supply at 6-10A. The board contains three non-isolated buck power supplies controlled by TPS54A20, TPS62184 and TPS53515. Each design is optimized for various parameters including size, efficiency, and transient response to name a few. The output filters have been designed to satisfy DC regulation of +-3% and DC+AC regulation of +-5%.

# PMP11438 Rev A Test Results

## Table of Contents


1	PMP11438 Board Photos .....	3
2	PMP11438 REVA 1.2V/10A – TPS54A20 .....	5
2.1	Board Photos.....	5
2.2	Efficiency and Power Loss .....	6
2.3	Load Regulation .....	6
2.4	Thermal .....	7
2.5	Startup .....	8
2.6	Shutdown .....	8
2.7	Output Ripple.....	9
2.8	Transient response.....	10
2.9	Synchronous Rectifier Stress.....	11
2.10	Frequency Characteristics.....	12
2.11	Loop Response .....	13
3	PMP11438 REVA 1.2V/6A – TPS62184 .....	14
3.1	Board Photos.....	14
3.2	Efficiency and Power Loss .....	15
3.3	Load Regulation .....	15
3.4	Thermal .....	16
3.5	Startup .....	17
3.6	Shutdown .....	17
3.7	Output Ripple.....	18
3.8	Transient response.....	20
3.9	Synchronous Rectifier Stress.....	20
3.10	Frequency Characteristics.....	21
3.11	Loop Response .....	22
4	PMP11438 REVA 1.2V/6A – TPS53515 .....	23
4.1	Board Photos.....	23
4.2	Efficiency and Power Loss .....	24
4.3	Load Regulation .....	24
4.4	Thermal .....	25
4.5	Startup .....	26


# PMP11438 Rev A Test Results

4.6	Shutdown .....	26
4.7	Output Ripple .....	27
4.8	Transient response.....	29
4.9	Synchronous Rectifier Stress.....	29
4.10	Frequency Characteristics.....	30
4.11	Loop Response .....	31

## 1 PMP11438 Board Photos

The front and back photos of PMP11438 are shown below. The board measures 3.2" x 1.5" and each circuit lies upon the same amount of PCB copper.





4/08/2016



# PMP11438 Rev A Test Results



## 2 PMP11438 REVA 1.2V/10A - TPS54A20


### 2.1 Board Photos

The top and bottom images of PMP11438 TPS54A20 are shown below.




## 2.2 Efficiency and Power Loss

The efficiency and power loss of the power supply is shown below at 12Vin with natural convection.




## 2.3 Load Regulation

The load regulation of the power supply is shown below at 12Vin.



2.4 Thermal

The thermal image of the power supply is shown at room temperature with 12Vin, 6Aout, and natural convection. The power supply soaked for 10min at 6A before the measurement was taken. The IC, which has integrated MOSFETs, is the hottest component at 59.7°C.




Area analysis	Value	NO.1
IC Max	59.7°C	
Inductors Max	52.5°C	




## 2.5 Startup

The power supply startup at 0A is shown below. The startup time is 500 $\mu$ s.





## 2.6 Shutdown


The shutdown of the power supply with 1.2 $\Omega$  constant-resistance load is shown below.



## 2.7 Output Ripple


The 1.2V output ripple is shown in red below, DC coupled with offset, for 0A, 6A and 10A, respectively.





## 2.8 Transient response

The transient response is shown in the plot below where the red trace is the DC offset output voltage. The current step is 1A-6A-1A at 5A/μs slew rate.




# PMP11438 Rev A Test Results





## 2.9 Synchronous Rectifier Stress

The voltage stresses on the synchronous MOSFETs are shown below. The image is taken at 12Vin and 6A with 200MHz of bandwidth limit.



### 2.10 Frequency Characteristics

The switch nodes are shown below in blue and red and measured on the inductor. The first image illustrates the power supply switching frequency of ~2MHz per phase. The second image shows frequency jitter of 12ns. Both images are taken with 12Vin and 6Aout.




# PMP11438 Rev A Test Results



## 2.11 Loop Response

The loop response of the power supply at 12Vin and 6A load current is shown below. The bandwidth is 400kHz with ~45° of phase margin.



4/08/2016



# PMP11438 Rev A Test Results



## 3 PMP11438 REVA 1.2V/6A - TPS62184


### 3.1 Board Photos

The top and bottom images of PMP11438 TPS62184 are shown below.




### 3.2 Efficiency and Power Loss

The efficiency and power loss of the power supply is shown below at 12Vin with natural convection.



### 3.3 Load Regulation


The load regulation of the power supply is shown below at 12Vin.





### 3.4 Thermal

The thermal image of the power supply is shown at room temperature with 12Vin, 6Aout, and natural convection. The power supply soaked for 10min at 6A before the measurement was taken. The IC, which has integrated MOSFETs, is one of the hottest components at 66.7°C.




Area analysis	Value
IC Max	66.7°C
Ind L3 Max	67.2°C
Ind L4 Max	60.3°C

NO.1

## 3.5 Startup

The power supply startup at 0A is shown below. The startup time is 750 $\mu$ s.





## 3.6 Shutdown

The shutdown of the power supply with 1.2 $\Omega$  constant-resistance load is shown below.




## 3.7 Output Ripple

The 1.2V output ripple is shown in red below, DC coupled with offset, for 0A, 3A and 6A, respectively.




4/08/2016

# PMP11438 Rev A Test Results




## 3.8 Transient response

The transient response is shown in the plot below where the red trace is the DC offset output voltage. The current step is 1A-6A-1A at 5A/us slew rate.



## 3.9 Synchronous Rectifier Stress



The voltage stresses on the synchronous MOSFETs are shown below. The image is taken at 12Vin and 6A with 200MHz of bandwidth limit.



# PMP11438 Rev A Test Results


## 3.10 Frequency Characteristics

The switch nodes are shown below in blue and red and measured on the inductor. The first image illustrates the power supply switching frequency of ~850kHz per phase. The second image shows negligible frequency jitter. Both images are taken with 12Vin and 6Aout.



## 3.11 Loop Response

The loop response of the power supply at 12Vin and 6A load current is shown below. The bandwidth is 17kHz with  $\sim 62^\circ$  of phase margin.



4/08/2016



## PMP11438 Rev A Test Results



### 4 PMP11438 REVA 1.2V/6A - TPS53515

#### 4.1 Board Photos


The top and bottom images of PMP11438 TPS53515 are shown below.






### 4.2 Efficiency and Power Loss

The efficiency and power loss of the power supply is shown below at 12Vin with natural convection.




### 4.3 Load Regulation

The load regulation of the power supply is shown below at 12Vin.



**4.4 Thermal**

The thermal image of the power supply is shown at room temperature with 12Vin, 6Aout, and natural convection. The power supply soaked for 10min at 6A before the measurement was taken. The IC, which has integrated MOSFETs, is one of the hottest components at 48.1°C.




Area analysis	Value
Inductor Max	36.6°C
IC Max	48.1°C

NO.1


## 4.5 Startup

The power supply startup at 0A is shown below. The startup time is 750 $\mu$ s.





## 4.6 Shutdown

The shutdown of the power supply with 1.2 $\Omega$  constant-resistance load is shown below.




## 4.7 Output Ripple

The 1.2V output ripple is shown in red below, DC coupled with offset, for 0A, 6A and 10A, respectively.




4/08/2016

# PMP11438 Rev A Test Results




### 4.8 Transient response

The transient response is shown in the plot below where the red trace is the DC offset output voltage. The current step is 1A-6A-1A at 5A/us slew rate.



### 4.9 Synchronous Rectifier Stress



The voltage stresses on the synchronous MOSFETs are shown below. The image is taken at 12Vin and 6A with 200MHz of bandwidth limit.



# PMP11438 Rev A Test Results


## 4.10 Frequency Characteristics

The switch node is shown below in red and measured on the inductor. The first image illustrates the power supply switching frequency of ~500kHz per phase. The second image shows ~200ns of frequency jitter. Both images are taken with 12Vin and 6Aout.



## 4.11 Loop Response

The loop response of the power supply at 12Vin and 6A load current is shown below. The bandwidth is 140kHz with  $\sim 60^\circ$  of phase margin.





## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2021, Texas Instruments Incorporated