
- Undershoot Protection for Off-Isolation on A and B Ports Up To -2 V
- Bidirectional Data Flow, With Near-Zero Propagation Delay
- Low ON-State Resistance (r<sub>on</sub>)
   Characteristics (r<sub>on</sub> = 3 Ω Typical)
- Low Input/Output Capacitance Minimizes Loading and Signal Distortion (C<sub>io(OFF)</sub> = 5 pF Typical)
- Data and Control Inputs Provide Undershoot Clamp Diodes
- Low Power Consumption (I<sub>CC</sub> = 3 μA Max)
- V<sub>CC</sub> Operating Range From 4 V to 5.5 V
- Data I/Os Support 0 to 5-V Signaling Levels (0.8-V, 1.2-V, 1.5-V, 1.8-V, 2.5-V, 3.3-V, 5-V)

- Control Inputs Can Be Driven by TTL or 5-V/3.3-V CMOS Outputs
- I<sub>off</sub> Supports Partial-Power-Down Mode Operation
- Latch-Up Performance Exceeds 100 mA Per JESD 78, Class II
- ESD Performance Tested Per JESD 22
  - 2000-V Human-Body Model (A114-B, Class II)
  - 1000-V Charged-Device Model (C101)
- Supports Both Digital and Analog Applications: USB Interface, Bus Isolation, Low-Distortion Signal Gating

# OF THE PACKAGE (TOP VIEW)



#### description/ordering information

The SN74CBT3306C is a high-speed TTL-compatible FET bus switch with low ON-state resistance ( $r_{on}$ ), allowing for minimal propagation delay. Active Undershoot-Protection Circuitry on the A and B ports of the SN74CBT3306C provides protection for undershoot up to -2 V by sensing an undershoot event and ensuring that the switch remains in the proper OFF state.

The SN74CBT3306C is organized as two 1-bit bus switches with separate output-enable (1OE, 2OE) inputs. It can be used as two 1-bit bus switches or as one 2-bit bus switch. When  $\overline{OE}$  is low, the associated 1-bit bus switch is ON, and the A port is connected to the B port, allowing bidirectional data flow between ports. When  $\overline{OE}$  is high, the associated 1-bit bus switch is OFF, and the high-impedance state exists between the A and B ports.

#### ORDERING INFORMATION

TA	PACKA	GE <sup>†</sup>	ORDERABLE PART NUMBER	TOP-SIDE MARKING	
	0010 B	Tube	SN74CBT3306CD	0110000	
4000 1- 0500	SOIC – D	Tape and reel	SN74CBT3306CDR	CU306C	
–40°C to 85°C	TSSOP – PW	Tube	SN74CBT3306CPW	CU306C	
	1330P – PW	Tape and reel	SN74CBT3306CPWR	C0306C	

<sup>†</sup> Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at www.ti.com/sc/package.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



### description/ordering information (continued)


This device is fully specified for partial-power-down applications using  $I_{off}$ . The  $I_{off}$  feature ensures that damaging current will not backflow through the device when it is powered down. The device has isolation during power off.

To ensure the high-impedance state during power up or power down,  $\overline{OE}$  should be tied to  $V_{CC}$  through a pullup resistor; the minimum value of the resistor is determined by the current-sinking capability of the driver.


# FUNCTION TABLE (each bus switch)

INPUT OE	INPUT/OUTPUT A	FUNCTION
L	В	A port = B port
Н	Z	Disconnect

## logic diagram (positive logic)



#### simplified schematic, each FET switch (SW)



<sup>†</sup>EN is the internal enable signal applied to the switch.



# SN74CBT3306C DUAL FET BUS SWITCH 5-V BUS SWITCH WITH –2-V UNDERSHOOT PROTECTION

SCDS127A - SEPTEMBER 2003 - REVISED OCTOBER 2003

# absolute maximum ratings over operating free-air temperature range (unless otherwise noted)†

Supply voltage range, V <sub>CC</sub>	–0.5 V to 7 V
Control input voltage range, V <sub>IN</sub> (see Notes 1 and 2)	–0.5 V to 7 V
Switch I/O voltage range, V <sub>I/O</sub> (see Notes 1, 2, and 3)	–0.5 V to 7 V
Control input clamp current, I <sub>IK</sub> (V <sub>IN</sub> < 0)	–50 mA
I/O port clamp current, $I_{I/OK}$ ( $V_{I/O}$ < 0)	–50 mA
ON-state switch current, I <sub>I/O</sub> (see Note 4)	±128 mA
Continuous current through V <sub>CC</sub> or GND terminals	±100 mA
Package thermal impedance, θ <sub>JA</sub> (see Note 5): D package	97°C/W
PW package	149°C/W
Storage temperature range, T <sub>stq</sub>	65°C to 150°C

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES: 1. All voltages are with respect to ground unless otherwise specified.
  - 2. The input and output voltage ratings may be exceeded if the input and output clamp-current ratings are observed.
  - 3.  $V_I$  and  $V_O$  are used to denote specific conditions for  $V_{I/O}$ .
  - 4. I<sub>I</sub> and I<sub>O</sub> are used to denote specific conditions for I<sub>I/O</sub>.
  - 5. The package thermal impedance is calculated in accordance with JESD 51-7.

# recommended operating conditions (see Note 6)

		MIN	MAX	UNIT
VCC	Supply voltage	4	5.5	V
VIH	High-level control input voltage	2	5.5	V
VIL	Low-level control input voltage	0	0.8	V
V <sub>I/O</sub>	Data input/output voltage	0	5.5	V
TA	Operating free-air temperature	-40	85	°C

NOTE 6: All unused control inputs of the device must be held at V<sub>CC</sub> or GND to ensure proper device operation. Refer to the TI application report, *Implications of Slow or Floating CMOS Inputs*, literature number SCBA004.



# electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PAR	RAMETER		TEST CONDITIO	NS	MIN	TYP	MAX	UNIT
VIK	Control inputs	$V_{CC} = 4.5 \text{ V},$	$I_{IN} = -18 \text{ mA}$				-1.8	V
VIKU	Data inputs	V <sub>CC</sub> = 5 V,	$0 \text{ mA} > I_{I} \ge -50 \text{ mA},$ $V_{IN} = V_{CC} \text{ or GND},$	Switch ()EE			-2	٧
I <sub>IN</sub>	Control inputs	$V_{CC} = 5.5 \text{ V},$	$V_{IN} = V_{CC}$ or GND				±1	μΑ
loz‡		V <sub>CC</sub> = 5.5 V,	$V_O = 0 \text{ to } 5.5 \text{ V},$ $V_I = 0,$	Switch OFF, V <sub>IN</sub> = V <sub>CC</sub> or GND			±10	μА
I <sub>off</sub>		$V_{CC} = 0$ ,	$V_0 = 0 \text{ to } 5.5 \text{ V},$	V <sub>I</sub> = 0			10	μΑ
ICC		V <sub>CC</sub> = 5.5 V,	$I_{I/O} = 0,$ $V_{IN} = V_{CC} \text{ or GND},$	Switch ON or OFF			3	μА
∆lCC§	Control inputs	$V_{CC} = 5.5 \text{ V},$	One input at 3.4 V,	Other inputs at V <sub>CC</sub> or GND			2.5	mA
C <sub>in</sub>	Control inputs	$V_{IN} = 3 V \text{ or } 0$				3.5		pF
C <sub>io(OFF)</sub>		$V_{I/O} = 3 \text{ V or } 0,$	Switch OFF,	$V_{IN} = V_{CC}$ or GND		5		pF
C <sub>io(ON)</sub>		$V_{I/O} = 3 \text{ V or } 0,$	Switch ON,	$V_{IN} = V_{CC}$ or GND		12.5		pF
		$V_{CC} = 4 \text{ V},$ TYP at $V_{CC} = 4 \text{ V}$	V <sub>I</sub> = 2.4 V,	I <sub>O</sub> = -15 mA		8	12	
r <sub>on</sub> ¶			V 0	I <sub>O</sub> = 64 mA		3	6	Ω
		V <sub>CC</sub> = 4.5 V	V <sub>I</sub> = 0	I <sub>O</sub> = 30 mA	3		6	]
			V <sub>I</sub> = 2.4 V,	$I_O = -15 \text{ mA}$		5	10	

 $V_{\mbox{\footnotesize{IN}}}$  and  $I_{\mbox{\footnotesize{IN}}}$  refer to control inputs.  $V_{\mbox{\footnotesize{I}}},\,V_{\mbox{\footnotesize{O}}},\,I_{\mbox{\footnotesize{I}}},$  and  $I_{\mbox{\footnotesize{O}}}$  refer to data pins.

# switching characteristics over recommended operating free-air temperature range (unless otherwise noted) (see Figure 3)

PARAMETER	FROM (INPUT)	TO (OUTPUT)	V <sub>CC</sub> = 4 V	У <sub>С</sub> С	V <sub>CC</sub> = 5 V ± 0.5 V		
	(INPOT)	(001701)	MIN MA	X MIN	MAX		
t <sub>pd</sub> #	A or B	B or A	0.2	4	0.15	ns	
t <sub>en</sub>	ŌĒ	A or B	4.	6 1.5	4.2	ns	
t <sub>dis</sub>	ŌĒ	A or B	4.	3 1.5	4.3	ns	

<sup>#</sup> The propagation delay is the calculated RC time constant of the typical ON-state resistance of the switch and the specified load capacitance, when driven by an ideal voltage source (zero output impedance).

<sup>†</sup> All typical values are at  $V_{CC} = 5 \text{ V}$  (unless otherwise noted),  $T_A = 25^{\circ}\text{C}$ .

<sup>‡</sup> For I/O ports, the parameter I<sub>OZ</sub> includes the input leakage current.

<sup>§</sup> This is the increase in supply current for each input that is at the specified voltage level, rather than V<sub>CC</sub> or GND.

<sup>¶</sup> Measured by the voltage drop between the A and B terminals at the indicated current through the switch. ON-state resistance is determined by the lower of the voltages of the two (A or B) terminals.

## undershoot characteristics (see Figures 1 and 2)

PARAMETER		TEST CONDI	MIN	TYP†	MAX	UNIT	
VOUTU	$V_{CC} = 5.5 \text{ V},$	Switch OFF,	$V_{IN} = V_{CC}$ or GND	2	V <sub>OH</sub> -0.3		V

 $<sup>\</sup>dagger$  All typical values are at V<sub>CC</sub> = 5 V (unless otherwise noted), T<sub>A</sub> = 25°C.




Figure 1. Device Test Setup






Figure 2. Transient Input Voltage (V<sub>I</sub>) and Output Voltage (V<sub>OUTU</sub>) Waveforms (Switch OFF)

#### PARAMETER MEASUREMENT INFORMATION



TEST	VCC	S1	RL	VI	CL	$v_{\!\scriptscriptstyle\Delta}$
<sup>t</sup> pd(s)	$\begin{array}{c} \textbf{5 V} \pm \textbf{0.5 V} \\ \textbf{4 V} \end{array}$	Open Open	<b>500</b> Ω <b>500</b> Ω	V <sub>CC</sub> or GND V <sub>CC</sub> or GND	50 pF 50 pF	
tPLZ/tPZL	5 V ± 0.5 V 4 V	7 V 7 V	<b>500</b> Ω <b>500</b> Ω	GND GND	50 pF 50 pF	0.3 V 0.3 V
tPHZ/tPZH	5 V ± 0.5 V 4 V	Open Open	<b>500</b> Ω <b>500</b> Ω	V <sub>CC</sub>	50 pF 50 pF	0.3 V 0.3 V



NOTES: A. C<sub>L</sub> includes probe and jig capacitance.

- B. Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
- C. All input pulses are supplied by generators having the following characteristics: PRR  $\leq$  10 MHz,  $Z_O = 50 \Omega$ ,  $t_f \leq$  2.5 ns,  $t_f \leq$  2.5 ns.
- D. The outputs are measured one at a time with one transition per measurement.
- E. tpLZ and tpHZ are the same as tdis.
- F. tpzL and tpzH are the same as ten.
- G. tplH and tpHL are the same as tpd(s). The tpd propagation delay is the calculated RC time constant of the typical ON-state resistance of the switch and the specified load capacitance, when driven by an ideal voltage source (zero output impedance).
- H. All parameters and waveforms are not applicable to all devices.

Figure 3. Test Circuit and Voltage Waveforms







10-Dec-2020

#### PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead finish/ Ball material	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
							(6)				
SN74CBT3306CD	ACTIVE	SOIC	D	8	75	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	CU306C	Samples
SN74CBT3306CDR	ACTIVE	SOIC	D	8	2500	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	CU306C	Samples
SN74CBT3306CPW	ACTIVE	TSSOP	PW	8	150	RoHS & Green	NIPDAU	Level-1-260C-UNLIM	-40 to 85	CU306C	Samples
SN74CBT3306CPWR	ACTIVE	TSSOP	PW	8	2000	RoHS & Green	NIPDAU   SN	Level-1-260C-UNLIM	-40 to 85	CU306C	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and



## **PACKAGE OPTION ADDENDUM**

10-Dec-2020

continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 2-Oct-2024

#### TAPE AND REEL INFORMATION





A0	Dimension designed to accommodate the component width
В0	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

#### QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



#### \*All dimensions are nominal

	Device		Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
ı	SN74CBT3306CDR	SOIC	D	8	2500	330.0	12.4	6.4	5.2	2.1	8.0	12.0	Q1
ĺ	SN74CBT3306CPWR	TSSOP	PW	8	2000	330.0	12.4	7.0	3.6	1.6	8.0	12.0	Q1

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 2-Oct-2024




#### \*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
SN74CBT3306CDR	SOIC	D	8	2500	353.0	353.0	32.0
SN74CBT3306CPWR	TSSOP	PW	8	2000	367.0	367.0	35.0

# **PACKAGE MATERIALS INFORMATION**

www.ti.com 2-Oct-2024

#### **TUBE**



#### \*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (µm)	B (mm)
SN74CBT3306CD	D	SOIC	8	75	507	8	3940	4.32
SN74CBT3306CPW	PW	TSSOP	8	150	530	10.2	3600	3.5



SMALL OUTLINE INTEGRATED CIRCUIT



#### NOTES:

- 1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
- 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
- 4. This dimension does not include interlead flash.
- 5. Reference JEDEC registration MS-012, variation AA.



SMALL OUTLINE INTEGRATED CIRCUIT



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE INTEGRATED CIRCUIT



#### NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.





SMALL OUTLINE PACKAGE



#### NOTES:

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.

  2. This drawing is subject to change without notice.

  3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not
- exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MO-153, variation AA.



SMALL OUTLINE PACKAGE



NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.

7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.



SMALL OUTLINE PACKAGE



NOTES: (continued)

- 8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 9. Board assembly site may have different recommendations for stencil design.



#### **IMPORTANT NOTICE AND DISCLAIMER**

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated